

AS-interface® modules CESA

FESTO



AS-interface® modules CESA

Key features

Basic principles and features of the bus system

Introduction

The AS-interface system permits the transfer of power and data using a single cable.

The advanced technology used to connect stations to the yellow cable and the low connection costs mean that even stations with a small number of inputs and outputs (max. 8 inputs and 8 outputs per valve terminal with two chips) can be networked.

The AS-interface gateways from Festo act as a master for the AS-interface network and a slave for the higher-level fieldbus system (PROFIBUS or CANopen).

From the point of view of the higher-level fieldbus, the AS-interface gateways behave like modular I/O modules. This makes commissioning and troubleshooting much easier.

The gateways can be connected to the controllers FED-CEC/-CECCAN (CANopen master), CPX-CEC (CANopen master) and CECX (PROFIBUS DP and CANopen master) from Festo as well as any other controllers with a PROFIBUS or CANopen interface.

For the Festo controllers, the controller functionality is programmed as normal using the CoDeSys programming tool. Larger systems can be easily configured with the help of the AS-interface control software. The data of the connected AS-interface slave devices can be easily diagnosed for servicing.

- Extended AS-interface diagnostic functions that far surpass the standard diagnostic functions according to the AS-interface Specification
- Simple configuration error history enables sporadic configuration errors to be located
- Error counters enable the quality of data communication on the AS-interface cable to be monitored

AS-interface Specification version	Inputs	Outputs	Bus cycle (ms)	No. of slaves, digital	No. of slaves, analogue	Σ I/O
2.0	4/4	4	5	31	31	248
2.1	4	3	10	62	31	434
3.0	4/8	4/8	20	62	62	992

Master/slave principle


- Non-proprietary
- No restrictions in terms of cable layout and/or topology
- Data and power via a single two-wire cable
- Immune to interference
- Medium: unscreened cable 2x 1.5 mm²
- With 31 slaves, max. 4 inputs and 4 outputs per slave
- Data and power supply for up to 8 outputs per AS-interface string
- With 62 slaves, max. 4 inputs and 3 outputs per slave (A/B operation as per Specification V2.1)
- Modules for control cabinets (IP20) and harsh industrial environments (IP65, IP67)
- With 31 slaves, 4 analogue inputs or outputs per slave
- Profile 7.3: analogue values (16 bits) per slave (as per Specification V2.1)
- Profile 7.4: parameterisable communication profile, e.g. 16x 16 bits per slave (as per Specification V2.1)
- Profile 7.A.7 permits 4 bits for digital inputs and 4 bits for digital outputs on just one A/B slave. The 4 outputs are transmitted in two A/B bus cycles of 2 bits each. This extends the cycle time (in the worst-case scenario) to 20 ms.
- Insulation displacement technology
- Cable length 100 m, can be extended to up to 200 m through the use of an extension plug and to up to 500 m through the use of repeaters, etc.
- Highly effective error control
- Simple commissioning
- Electronic address selection via the bus connection

Note

Slaves to Specification V3.0 require a master to Specification V3.0.

AS-interface® modules CESA


System overview



AS-interface® modules CESA

System overview

Master




AS-interface gateways are used to connect the AS-interface network to a higher-level fieldbus. They behave like a master within the AS-interface network and a slave within the fieldbus network.

The AS-interface gateways from Festo conform to the AS-interface Specification 3.0 and support the extended addressing range with up to 62 AS-interface slaves.

- Versions
- CANopen
 - PROFIBUS

Slaves

Actuators




Actuators for the process industry
Quarter turn actuators DRD (Copar)
Linear valve actuators DLP (Copac)

- Local controllers for actuators for the process industry in exterior applications in the range -5 ... +50 °C

- Individual valve interface ASI-EVA for Namur valves
- Sensor box with visual position detection DAPZ

Valves




- A universal solution from the individual valve interface up to a compact solution with 8 valves

- Integrated inputs on individual valve interfaces and valve terminals CPV, MPA-S and VTSA/VTSA-F

- More inputs thanks to 4-way and 8-way input modules
- On request: Application-specific valves and integration solutions

Compact I/O modules, valve interfaces




- Highly compact modules
- Sturdy, encapsulated electrics
- Bus and auxiliary power supply 2x M12 looped through

- Inputs 200 mA
- Outputs 1 A

- 8 inputs M8
- 4 inputs and 3 outputs M12

Accessories



- Addressing device with user-friendly operating and diagnostic functions for the entire AS-interface, for example to perform the following tasks in a fully installed network:
 - change addresses
 - set outputs
 - read inputs
 - and many more

- Power supply unit for AS-interface
- Primary switched mode modular power supply
- Compact, modular and energy-saving power supply system for AS-interface – with integrated earth-fault monitoring system. AS-interface load: 4.8 A. Optional auxiliary power supply 24 VDC, load: 5 or 10 A


- Installation accessories for installing the flat cable

AS-interface® modules CESA

Connection technology and addressing

Handling


Operation



The AS-interface gateways can be configured and programmed using the GSPF software.


An alternative option for programming, commissioning or troubleshooting is to use the operating buttons on the gateway and the LED and LCD displays on the gateway.

AS-interface connections



The AS-interface network as well as the power supply for the gateway and AS-interface are connected via a terminal strip.

Mounting



The gateway is mounted using an H-rail. There are appropriate lugs on the rear of the device.


Extended addressing range

The extended addressing range enables a total of 62 slaves to be operated on one AS-interface master. The masters as well as the slaves must be designed for the extended addressing range in order to be able to exploit the full number of slaves. With the extended addressing range, two slaves share one address. Standard slaves do not have this capability. They can be connected to a

master with an extended addressing range, but also occupy a full address. In other words, up to 62 slaves with an extended addressing range but only 31 standard slaves can be connected to a master with an extended addressing range. Slaves with an extended addressing range can be connected like standard slaves to a standard master, but must be configured as an "A" slave.

AS-interface® modules CESA

Type codes



AS-interface® modules CESA

Technical data

CESA-GW-AS-PB

AS-interface module with PROFIBUS DP connection

CESA-GW-AS-CO

AS-interface module with CANopen connection

The AS-interface modules are used to couple decentralised AS-interface networks to higher-level controllers via a fieldbus.

The following fieldbus connections are available:

- PROFIBUS DP
- CANopen



General technical data		CESA-GW-AS-PB	CESA-GW-AS-CO
Operating elements		4 buttons	
Status displays		LCD display	
		Yellow LED: Projection mode	
		Green LED: AS-interface operating normally	
		Green LED: AS-interface voltage OK	
		Green LED: PROFIBUS master detected	
		Green LED: Slave programming	
		Green LED: Voltage ON	
		Red LED: Configuration error	
Operating voltage	[V DC]	30 (AS-interface voltage)	
Current consumption	[mA]	200 (from the AS-interface line)	
Protection class		IP20	
Resistance test		As per EN 61131-2 (resistance to shock, vibration)	
Product weight	[g]	460	520
Dimensions W x L x H	[mm]	75 x 120 x 83	85 x 120 x 83
Materials			
Housing		High-alloy stainless steel	
Note on materials		Contains PWIS (paint-wetting impairment substances)	
		RoHS-compliant	

Technical data – Interfaces		CESA-GW-AS-PB	CESA-GW-AS-CO
Fieldbus interface			
Type		PROFIBUS to DIN 19245 Part 3	CANopen, Device Specification CiA DS-301
Connection technology		Sub-D socket, 9-pin	COMBICON plug, 5-pin
Transmission rate		9.6 kbps ... 12 Mbps	10 kbps ... 1 Mbps
Programming/diagnostic interface			
Type		RS232 serial interface	


Operating and environmental conditions		CESA-GW-AS-PB	CESA-GW-AS-CO
Ambient temperature	[°C]	0 ... +55	
Storage temperature	[°C]	-25 ... +85	
Certification		cULus listed (OL)	
		C-Tick	
CE mark (see declaration of conformity) ¹⁾		To EU EMC Directive	

1) For information about the applicability of the component see the manufacturer's EC declaration of conformity at: www.festo.com → Support → User documentation.
If the component is subject to restrictions on usage in residential, office or commercial environments or small businesses, further measures to reduce the emitted interference may be necessary.


AS-interface® modules CESA

Technical data


Connection and display components



Pin allocation – PROFIBUS


	Pin	Signal	Meaning
Sub-D socket to DIN 50170			
	1	n.c.	Not connected
	2	n.c.	Not connected
	3	RxD/TxD-P	Data transmission line B
	4	n.c.	Not connected
	5	DGND	Data reference potential (0 V)
	6	VP	Supply voltage (+5 V)
	7	n.c.	Not connected
	8	RxD/TxD-N	Data transmission line A
	9	n.c.	Not connected

Pin allocation – CANopen

	Pin	Signal	Meaning
Terminal strip, 5-pin ¹⁾			
	1	V+	24 V DC supply CAN interface
	2	CAN_H	Received/transmitted data high
	3	Screened	Connection to FE (functional earth)
	4	CAN_L	Received/transmitted data low
	5	V-	0 V CAN interface

1) The interface is supplied with voltage via the plug.

Pin allocation – AS-interface

	Signal	Meaning	
Screw terminal			
	1	+AS-i-	Connection to AS-interface line
	2	AS-i +PWR-	Power supply for AS-interface line (max. 8 A)
	3	FE	Functional earth


AS-interface® modules CESA

Technical data


Dimensions

Download CAD Data → www.festo.com/us/cad

CESA-GW-AS-PB












CESA-GW-AS-CO



Type	B1	B2	H1	H2	L1	L2
CESA-GW-AS-PB	76	7	125	120	75	55
CESA-GW-AS-CO	76	7	125	120	85	55

AS-interface® modules CESA

Accessories

Ordering data		Part No.	Type
AS-interface gateway			
	AS-interface master with PROFIBUS DP fieldbus connection	567032	CESA-GW-AS-PB
	AS-interface master with CANopen fieldbus connection	567033	CESA-GW-AS-CO
PROFIBUS bus connection			
	Sub-D plug, angled	533780	FBS-SUB-9-WS-PB-K
AS-interface			
	AS-interface flat cable, yellow	100 m	18940 KASI-1,5-Y-100
	AS-interface flat cable, black	100 m	18941 KASI-1,5-Z-100
	Cable cap for flat cable (pack of 50)	18787	ASI-KK-FK
	Cable sleeve (pack of 20)	165593	ASI-KT-FK
	AS-interface module as bus termination	567035	CACF-BT-AS
	Primary switched mode modular power supply 24 V DC power supply	5 A	547867 SVG-1/230-24VDC-5A
		10 A	547868 SVG-1/230-24VDC-10A
	H-rail to EN 60715	35430	NRH-35-2000
	Software for configuring the system and diagnosing the AS-interface slaves during servicing	567036	GSPF-BS-1-AF-ML

Product Range and Company Overview

A Complete Suite of Automation Services

Our experienced engineers provide complete support at every stage of your development process, including: conceptualization, analysis, engineering, design, assembly, documentation, validation, and production.



Custom Automation Components
Complete custom engineered solutions



Custom Control Cabinets
Comprehensive engineering support and on-site services



Complete Systems
Shipment, stocking and storage services

The Broadest Range of Automation Components

With a comprehensive line of more than 30,000 automation components, Festo is capable of solving the most complex automation requirements.



Electromechanical
Electromechanical actuators, motors, controllers & drives



Pneumatics
Pneumatic linear and rotary actuators, valves, and air supply



PLCs and I/O Devices
PLC's, operator interfaces, sensors and I/O devices

Supporting Advanced Automation... As No One Else Can!

Festo is a leading global manufacturer of pneumatic and electromechanical systems, components and controls for industrial automation, with more than 12,000 employees in 56 national headquarters serving more than 180 countries. For more than 80 years, Festo has continuously elevated the state of manufacturing with innovations and optimized motion control solutions that deliver higher performing, more profitable automated manufacturing and processing equipment. Our dedication to the advancement of automation extends beyond technology to the education and development of current and future automation and robotics designers with simulation tools, teaching programs, and on-site services.

Quality Assurance, ISO 9001 and ISO 14001 Certifications

Festo Corporation is committed to supply all Festo products and services that will meet or exceed our customers' requirements in product quality, delivery, customer service and satisfaction.

To meet this commitment, we strive to ensure a consistent, integrated, and systematic approach to management that will meet or exceed the requirements of the ISO 9001 standard for Quality Management and the ISO 14001 standard for Environmental Management.



© Copyright 2008, Festo Corporation. While every effort is made to ensure that all dimensions and specifications are correct, Festo cannot guarantee that publications are completely free of any error, in particular typing or printing errors. Accordingly, Festo cannot be held responsible for the same. For Liability and Warranty conditions, refer to our "Terms and Conditions of Sale", available from your local Festo office. All rights reserved. No part of this publication may be reproduced, distributed, or transmitted in any form or by any means, electronic, mechanical, photocopying or otherwise, without the prior written permission of Festo. All technical data subject to change according to technical update.



Printed on recycled paper at New Horizon Graphic, Inc., FSC certified as an environmentally friendly printing plant.

Festo North America

Festo Regional Contact Center

5300 Explorer Drive
Mississauga, Ontario L4W 5G4
Canada

USA Customers:

For ordering assistance,

Call: 1.800.99.FESTO (1.800.993.3786)

Fax: 1.800.96.FESTO (1.800.963.3786)

Email: customer.service@us.festo.com

For technical support,

Call: 1.866.GO.FESTO (1.866.463.3786)

Fax: 1.800.96.FESTO (1.800.963.3786)

Email: product.support@us.festo.com

Canadian Customers:

Call: 1.877.GO.FESTO (1.877.463.3786)

Fax: 1.877.FX.FESTO (1.877.393.3786)

Email: festo.canada@ca.festo.com

USA Headquarters

Festo Corporation
395 Moreland Road
P.O. Box 18023
Hauppauge, NY 11788, USA
www.festo.com/us

USA Sales Offices

Appleton

North 922 Tower View Drive, Suite N
Greenville, WI 54942, USA

Boston

120 Presidential Way, Suite 330
Woburn, MA 01801, USA

Chicago

1441 East Business Center Drive
Mt. Prospect, IL 60056, USA

Dallas

1825 Lakeway Drive, Suite 600
Lewisville, TX 75057, USA

Detroit – Automotive Engineering Center

2601 Cambridge Court, Suite 320
Auburn Hills, MI 48326, USA

New York

395 Moreland Road
Hauppauge, NY 11788, USA

Silicon Valley

4935 Southfront Road, Suite F
Livermore, CA 94550, USA

United States



USA Headquarters, East: Festo Corp., 395 Moreland Road, Hauppauge, NY 11788

Phone: 1.631.435.0800; Fax: 1.631.435.8026;

Email: info@festo-usa.com

www.festo.com/us

Canada



Headquarters: Festo Inc., 5300 Explorer Drive, Mississauga, Ontario L4W 5G4

Phone: 1.905.624.9000; Fax: 1.905.624.9001;

Email: festo.canada@ca.festo.com

www.festo.ca

Mexico



Headquarters: Festo Pneumatic, S.A., Av. Ceylán 3, Col. Tequesquahuac,
54020 Tlalneantla, Edo. de México

Phone: 011 52 [55] 53 21 66 00; Fax: 011 52 [55] 53 21 66 65;

Email: festo.mexico@mx.festo.com

www.festo.com/mx

Central USA

Festo Corporation
1441 East Business
Center Drive
Mt. Prospect, IL 60056, USA
Phone: 1.847.759.2600
Fax: 1.847.768.9480



Western USA

Festo Corporation
4935 Southfront Road,
Suite F
Livermore, CA 94550, USA
Phone: 1.925.371.1099
Fax: 1.925.245.1286



Festo Worldwide

Argentina Australia Austria Belarus Belgium Brazil Bulgaria Canada Chile China Colombia Croatia Czech Republic Denmark
Estonia Finland France Germany Great Britain Greece Hong Kong Hungary India Indonesia Iran Ireland Israel Italy Japan Latvia
Lithuania Malaysia Mexico Netherlands New Zealand Norway Peru Philippines Poland Romania Russia Serbia Singapore
Slovakia Slovenia South Africa South Korea Spain Sweden Switzerland Taiwan Thailand Turkey Ukraine United States Venezuela

www.festo.com