

Plug connectors NECV for valves, for self-assembly

Technical data

Plug socket MSSD-E

- For valves with E solenoid coils



General technical data		
Type	MSSD-E	MSSD-E-M12
Electrical connection 1	Angled socket	Angled socket
	3-pin	3-pin
	Square design	Square design
	Type C	Type C
	Industrial design	To EN 175301-803
Electrical connection 2	Screw terminal	Screw terminal
Operating voltage range	[V DC]	0 ... 300
	[V AC]	0 ... 250
Current-carrying capacity	[A]	6
Cable connector	Pg7	M12
Max. tightening torque of locking clip	[Nm]	0.35
Permissible cable diameter	[mm]	6 ... 8
Connection cross section	[mm ²]	0.75
Connection frequency	–	50
Type of mounting	M3 central screw	M3 central screw
Mounting position	Any	Any
Protection class to EN 60529	IP65 (assembled)	IP65 (assembled)

Materials		
Type	MSSD-E	MSSD-E-M12
Housing	PA reinforced	PA reinforced
Housing colour	Black	Black
Seals	NBR	HNBR
Note on materials	–	Conforms to RoHS

Operating and environmental conditions		
Type	MSSD-E	MSSD-E-M12
Ambient temperature	[°C]	–25 ... +90
Degree of contamination		3

Plug connectors NECV for valves, for self-assembly

Technical data

Dimensions Download CAD data → www.festo.com

MSSD-E

1 Insert can be repositioned by 90°

MSSD-E-M12

1 Insert can be repositioned by 90°


Type	B1	D1	D2	D3	H1	L1
MSSD-E	15.5	14	Pg7	M3	24.5	25
MSSD-E-M12	15.5	15	M12x 1.5	M3	26	25.5

Ordering data				
Description	Cable connector	Weight	Part No.	Type
Plug socket for valves with E solenoid coils	Pg7	8 g	14098	MSSD-E
	M12	11 g	539711	MSSD-E-M12


Product Range and Company Overview

A Complete Suite and Company Overview

Our experienced engineers provide complete support at every stage of your development process, including: conceptualization, analysis, engineering, design, assembly, documentation, validation, and production.



Custom Automation Components
Complete custom engineered solutions



Custom Control Cabinets
Comprehensive engineering support and on-site services



Complete Systems
Shipment, stocking and storage services

The Broadest Range of Automation Components

With a comprehensive line of more than 30,000 automation components, Festo is capable of solving the most complex automation requirements.



Electromechanical
Electromechanical actuators, motors, controllers & drivers



Pneumatics
Pneumatic linear and rotary actuators, valves, and air supply



PLCs and I/O Devices
PLC's, operator interfaces, sensors and I/O devices

Supporting Advanced Automation... As No One Else Can!

Festo is a leading global manufacturer of pneumatic and electromechanical systems, components and controls for industrial automation, with more than 16,000 employees in 60 national headquarters serving more than 180 countries. For more than 80 years, Festo has continuously elevated the state of manufacturing with innovations and optimized motion control solutions that deliver higher performing, more profitable automated manufacturing and processing equipment. Our dedication to the advancement of automation extends beyond technology to the education and development of current and future automation and robotics designers with simulation tools, teaching programs, and on-site services.

Quality Assurance, ISO 9001 and ISO 14001 Certifications

Festo Corporation is committed to supply all Festo products and services that will meet or exceed our customers' requirements in product quality, delivery, customer service and satisfaction.

To meet this commitment, we strive to ensure a consistent, integrated, and systematic approach to management that will meet or exceed the requirements of the ISO 9001 standard for Quality Management and the ISO 14001 standard for Environmental Management.




© Copyright 2013, Festo Corporation. While every effort is made to ensure that all dimensions and specifications are correct, Festo cannot guarantee that publications are completely free of any error, in particular typing or printing errors. Accordingly, Festo cannot be held responsible for the same. For Liability and Warranty conditions, refer to our "Terms and Conditions of Sale", available from your local Festo office. All rights reserved. No part of this publication may be reproduced, distributed, or transmitted in any form or by any means, electronic, mechanical, photocopying or otherwise, without the prior written permission of Festo. All technical data subject to change according to technical update.



Printed on recycled paper at New Horizon Graphic, Inc., FSC certified as an environmental friendly printing plant.

Festo North America



**1 Festo Canada
Headquarters
Festo Inc.**
5300 Explorer Drive
Mississauga, ON
L4W 5G4

2 Montréal
5600, Trans-Canada
Pointe-Claire, QC
H9R 1B6

3 Québec City
2930, rue Watt#117
Québec, QC
G1X 4G3



**4 Festo United States
Headquarters
Festo Corporation**
395 Moreland Road
Hauppauge, NY
11788

5 Appleton
North 922 Tower View Drive, Suite N
Greenville, WI
54942

7 Detroit
1441 West Long Lake Road
Troy, MI
48098

6 Chicago
85 W Algonquin - Suite 340
Arlington Heights, IL
60005

8 Silicon Valley
4935 Southfront Road, Suite F
Livermore, CA
94550

Festo Regional Contact Center

Canadian Customers

Commercial Support:
Tel: 1 877 GO FESTO (1 877 463 3786)
Fax: 1 877 FX FESTO (1 877 393 3786)
Email: festo.canada@ca.festo.com

Technical Support:
Tel: 1 866 GO FESTO (1 866 463 3786)
Fax: 1 877 FX FESTO (1 877 393 3786)
Email: technical.support@ca.festo.com

USA Customers

Commercial Support:
Tel: 1 800 99 FESTO (1 800 993 3786)
Fax: 1 800 96 FESTO (1 800 963 3786)
Email: customer.service@us.festo.com

Technical Support:
Tel: 1 866 GO FESTO (1 866 463 3786)
Fax: 1 800 96 FESTO (1 800 963 3786)
Email: product.support@us.festo.com