


Vacuum generators VAD/VAK

FESTO




Vacuum generators

Key features

FESTO

Product overview

Vacuum generator



All Festo vacuum generators have a single-stage design and operate according to the venturi principle. The product families described below

have been designed for a wide range of applications. The different performance classes of the individual

product families make it possible to select vacuum generators tailored to suit specific requirements.

Standard and inline ejectors

VN-...

Technical data → Internet: vn



- Nominal size
0.45 ... 3 mm
- Max. vacuum
93%
- Temperature range
0 ... +60 °C
- A range of extremely effective generators suitable for use directly in the workplace
- Available as straight or T-shaped housing
- Low space requirement
- Low-cost
- No wearing parts
- Extremely fast evacuation time
- Vacuum switch (optional)
- Optional with additional functions:
 - integrated eject pulse
 - electric control for vacuum ON/OFF
 - combination of eject pulse and control

VAD-.../VAK-...

→ 6 / 1.1-6



- Nominal size
0.5 ... 1.5 mm
- Max. vacuum
80%
- Temperature range
-20 ... +80 °C
- Range of vacuum generators with sturdy aluminium casing
- VAK-...: Built-in reservoir
- VAD-...: Connection for additional external reservoir
- Maintenance-free
- VAK-...: Reliable setting down of workpieces

Vacuum generators

Key features

FESTO

Compact ejectors

VADM-...VADMI-...

Technical data → Internet: [vadm](#)



- Nominal size
0.45 ... 3 mm
- Max. vacuum
84%
- Temperature range
0 ... +60 °C
- Compact design
- Minimal installation work required
- Short response times
- Built-in solenoid valve (on/off)
- VADMI-...: Additional built-in solenoid valve for ejector pulse
- Filter with display
- Air-saving circuit (optional)
- Vacuum switch (optional)
- Reliable setting down of workpieces

VAD-M-.../VAD-M-I-...

Technical data → Internet: [vad-m](#)




- Nominal size
0.7 ... 2 mm
- Max. vacuum
85%
- Temperature range
0 ... +40 °C
- Compact design
- Minimal installation work required
- Short response times
- Built-in solenoid valve (on/off)
- VAD-M-I-...: Additional built-in solenoid valve for ejector pulse
- Reliable setting down of workpieces

Vacuum generators VAD/VAK

FESTO

Key features

At a glance



- Vacuum generation via ejector principle
- Mounting holes in metal housing
- Connecting thread for the suction cup

Compressed air flowing from 1 to 3 generates a vacuum at port 2 in accordance with the ejector principle.


The low noise levels which occur during exhaust can be further reduced with a silencer at port 3.

Workpieces can be picked up in any position. When the compressed air is turned off, the suction process ends and the vacuum dissipates. During the suction process, the vacuum generator VAK fills a reservoir of approx. 32 cm³ with compressed

air, which creates an ejector pulse when the input pressure is switched off and reliably releases the workpiece from the suction cup. Max. switching frequency approx. 10 Hz at 6 bar and with approx. 1 m suction line.



Vacuum generator VAD-... without ejector pulse

- Workpieces can be picked up in any position.
- Sturdy and resistant to environmental factors
- Easy to install
- No moving parts, maintenance-free
- Connecting threads and mounting holes available



Vacuum generator VAK-... with ejector pulse

- Quick and reliable setting down of parts via an ejector pulse from a pre-filled reservoir
- Robust vacuum generator for a broad field of applications
- Optional silencer




Vacuum generators VAD/VAK

Peripherals overview and type codes



Peripherals overview



Mounting attachments and accessories		→ Page/Internet
1	Push-in fitting QS	qs
2	Silencer U/UC	u
3	Suction cups VAS/VASB	vas
–	Suction gripper ESG	esg
–	Suction cup holder ESH	esh
–	suction cup ESS	ess

Type codes

		VAD	–	M5
Type				
VAD	Vacuum generator			
VAK	Vacuum generator			
Connection sizes				
M5	Thread M5			
1/8	Thread G1/8			
1/4	Thread G1/4			
3/8	Thread G3/8			



Possible combinations can be found in the ordering data.


Vacuum generators VAD/VAK

FESTO

Technical data

Function

VAD-...





Temperature range

−20 ... +80 °C

Pressure

1.5 ... 10 bar

VAK-...



General technical data						
Type		VAD-...				VAK-...
Size		M5	G1/8	G1/4	G3/8	G1/4
Design		Block-shaped				
Mounting position		Any				
Ejector features		High vacuum				
Type of mounting		Via through-holes				
Pneumatic connection		M5	G1/8	G1/4	G3/8	G1/4
Nominal size of laval nozzle	[mm]	0.5	0.8	1.0	1.5	1.0
Max. vacuum	[%]	80				

Ambient conditions		
Variant		VAD/VAK
Operating pressure	[bar]	1.5 ... 10
Operating medium		Compressed air in accordance with ISO 8573-1:2010 [7:4:4]
Note on operating/pilot medium		Operation with lubricated medium possible (in which case lubricated operation will always be required)
Ambient temperature	[°C]	−20 ... +80
Corrosion resistance	CRC ¹⁾	2
Note on material		Free of copper, PTFE and silicone

1) Corrosion resistance class 2 according to Festo standard 940 070

Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a surrounding industrial atmosphere or media such as cooling or lubricating agents.


Weights [g]					
Type	VAD-...				VAK-...
Size	M5	G1/8	G1/4	G3/8	G1/4
VAD-.../VAK-...	14	40	90	155	265

Vacuum generators VAD/VAK


Technical data

FESTO


Vacuum Δp as a function of operating pressure p




Suction capacity q_n as a function of vacuum p




Suction capacity q_n as a function of operating pressure p



Air consumption q_n as a function of operating pressure p




Noise level L_p as a function of operating pressure p



* = without silencer; ° = with silencer

Technical data

VAD-M5



Technical drawing of a mechanical part, showing front and top views with dimensions.

Front View Dimensions:

- Overall height: 25
- Distance from top edge to center of hole 1: 17
- Distance from center of hole 1 to center of hole 3: 9
- Distance from center of hole 3 to right edge: $G/8$
- Distance from left edge to center of hole 1: 15.3
- Distance from center of hole 1 to center of hole 3: 34
- Distance from center of hole 3 to right edge: 6
- Overall width: 46
- Distance from center of hole 1 to right edge: 4.5
- Distance from center of hole 3 to right edge: 4.5

Top View Dimensions:

- Overall width: 18
- Distance from top edge to center of hole 1: 11
- Distance from center of hole 1 to center of hole 3: 15.3
- Distance from center of hole 3 to right edge: 20.4

Other Features:

- Hole 1: Diameter $\phi 4.5$
- Hole 3: Diameter $\phi 4.5$
- Feature 2: A central rectangular feature with a width of 34 and a height of 9.

- 1 Compressed air connection
- 2 Vacuum port
- 3 Exhaust


Vacuum generators VAD/VAK

Technical data

FESTO

Dimensions

VAK-1/4



- 1 Alternative connection 2
- 2 Connection for additional reservoir
- 1 Compressed air connection
- 2 Vacuum port
- 3 Exhaust

Response time [s] as a function of vacuum [bar] at 6 bar operating pressure and 1 l volume

Type	Vacuum			
	0.2	0.4	0.6	0.8
VAD-M5				
Evacuation	1.3	3.53	8.18	26.6 ¹⁾
Air supply	2.8	3.8	4.65	5.45
VAD-1/8				
Evacuation	0.51	1.38	3.41	11.67
Air supply	0.89	1.3	1.64	1.98
VAD-1/4				
Evacuation	0.29	0.745	1.69	4.04 ¹⁾
Air supply	0.61	0.89	1.12	1.32
VAD-3/8				
Evacuation	0.142	0.35	0.817	2.72
Air supply	0.265	0.372	0.46	0.536 ¹⁾
VAK-1/4				
Evacuation	0.29	0.745	1.69	4.04 ¹⁾
Air supply	0.61	0.89	1.12	1.32

1) At 0.75 bar vacuum.

Ordering data

Pneumatic connection	Part No.	Type
Without ejector pulse		
M5	19 293	VAD-M5
G1/8	14 015	VAD-1/8
G1/4	9 394	VAD-1/4
G3/8	19 294	VAD-3/8
With ejector pulse		
G1/4	6 890	VAK-1/4

Product Range and Company Overview

A Complete Suite of Automation Services

Our experienced engineers provide complete support at every stage of your development process, including: conceptualization, analysis, engineering, design, assembly, documentation, validation, and production.



Custom Automation Components
Complete custom engineered solutions



Custom Control Cabinets
Comprehensive engineering support and on-site services



Complete Systems
Shipment, stocking and storage services

The Broadest Range of Automation Components

With a comprehensive line of more than 30,000 automation components, Festo is capable of solving the most complex automation requirements.



Electromechanical
Electromechanical actuators, motors, controllers & drives



Pneumatics
Pneumatic linear and rotary actuators, valves, and air supply



PLCs and I/O Devices
PLC's, operator interfaces, sensors and I/O devices

Supporting Advanced Automation... As No One Else Can!

Festo is a leading global manufacturer of pneumatic and electromechanical systems, components and controls for industrial automation, with more than 12,000 employees in 56 national headquarters serving more than 180 countries. For more than 80 years, Festo has continuously elevated the state of manufacturing with innovations and optimized motion control solutions that deliver higher performing, more profitable automated manufacturing and processing equipment. Our dedication to the advancement of automation extends beyond technology to the education and development of current and future automation and robotics designers with simulation tools, teaching programs, and on-site services.

Quality Assurance, ISO 9001 and ISO 14001 Certifications

Festo Corporation is committed to supply all Festo products and services that will meet or exceed our customers' requirements in product quality, delivery, customer service and satisfaction.

To meet this commitment, we strive to ensure a consistent, integrated, and systematic approach to management that will meet or exceed the requirements of the ISO 9001 standard for Quality Management and the ISO 14001 standard for Environmental Management.



© Copyright 2008, Festo Corporation. While every effort is made to ensure that all dimensions and specifications are correct, Festo cannot guarantee that publications are completely free of any error, in particular typing or printing errors. Accordingly, Festo cannot be held responsible for the same. For Liability and Warranty conditions, refer to our "Terms and Conditions of Sale", available from your local Festo office. All rights reserved. No part of this publication may be reproduced, distributed, or transmitted in any form or by any means, electronic, mechanical, photocopying or otherwise, without the prior written permission of Festo. All technical data subject to change according to technical update.



Printed on recycled paper at New Horizon Graphic, Inc., FSC certified as an environmentally friendly printing plant.

Festo North America

Festo Regional Contact Center

5300 Explorer Drive
Mississauga, Ontario L4W 5G4
Canada

USA Customers:

For ordering assistance,

Call: 1.800.99.FESTO (1.800.993.3786)

Fax: 1.800.96.FESTO (1.800.963.3786)

Email: customer.service@us.festo.com

For technical support,

Call: 1.866.GO.FESTO (1.866.463.3786)

Fax: 1.800.96.FESTO (1.800.963.3786)

Email: product.support@us.festo.com

Canadian Customers:

Call: 1.877.GO.FESTO (1.877.463.3786)

Fax: 1.877.FX.FESTO (1.877.393.3786)

Email: festo.canada@ca.festo.com

USA Headquarters

Festo Corporation
395 Moreland Road
P.O. Box 18023
Hauppauge, NY 11788, USA
www.festo.com/us

USA Sales Offices

Appleton

North 922 Tower View Drive, Suite N
Greenville, WI 54942, USA

Boston

120 Presidential Way, Suite 330
Woburn, MA 01801, USA

Chicago

1441 East Business Center Drive
Mt. Prospect, IL 60056, USA

Dallas

1825 Lakeway Drive, Suite 600
Lewisville, TX 75057, USA

Detroit – Automotive Engineering Center

2601 Cambridge Court, Suite 320
Auburn Hills, MI 48326, USA

New York

395 Moreland Road
Hauppauge, NY 11788, USA

Silicon Valley

4935 Southfront Road, Suite F
Livermore, CA 94550, USA

United States



USA Headquarters, East: Festo Corp., 395 Moreland Road, Hauppauge, NY 11788

Phone: 1.631.435.0800; Fax: 1.631.435.8026;

Email: info@festo-usa.com

www.festo.com/us

Canada



Headquarters: Festo Inc., 5300 Explorer Drive, Mississauga, Ontario L4W 5G4

Phone: 1.905.624.9000; Fax: 1.905.624.9001;

Email: festo.canada@ca.festo.com

www.festo.ca

Mexico



Headquarters: Festo Pneumatic, S.A., Av. Ceylán 3, Col. Tequesquahuac,
54020 Tlalneapantla, Edo. de México

Phone: 011 52 [55] 53 21 66 00; Fax: 011 52 [55] 53 21 66 65;

Email: festo.mexico@mx.festo.com

www.festo.com/mx

Central USA

Festo Corporation
1441 East Business
Center Drive
Mt. Prospect, IL 60056, USA
Phone: 1.847.759.2600
Fax: 1.847.768.9480



Western USA

Festo Corporation
4935 Southfront Road,
Suite F
Livermore, CA 94550, USA
Phone: 1.925.371.1099
Fax: 1.925.245.1286



Festo Worldwide

Argentina Australia Austria Belarus Belgium Brazil Bulgaria Canada Chile China Colombia Croatia Czech Republic Denmark
Estonia Finland France Germany Great Britain Greece Hong Kong Hungary India Indonesia Iran Ireland Israel Italy Japan Latvia
Lithuania Malaysia Mexico Netherlands New Zealand Norway Peru Philippines Poland Romania Russia Serbia Singapore
Slovakia Slovenia South Africa South Korea Spain Sweden Switzerland Taiwan Thailand Turkey Ukraine United States Venezuela

www.festo.com