

Three-point grippers HGDD, sealed

FESTO



Three-point grippers HGDD, sealed

Key features

FESTO

At a glance

General information

The fully encapsulated gripper kinematics enable the gripper to be used in extremely harsh ambient conditions.

Sturdy and precise kinematics for maximum torque resistance and long service life.

The force generated by the linear motion is translated into the gripper jaw movement via a wedge mechanism


with forced motion sequence. This also guarantees synchronous movement of the gripper jaw. The ground gripper jaws and slideway ensure a virtually backlash-free movement.

Flexible range of applications


- Can be used as a double-acting and single-acting gripper
- Compression spring for supplementary or retaining gripping forces
- Suitable for external and internal gripping

The technology in detail

Gripper closed



Gripper open




- 1 Gripper jaw
- 2 Wedge with forced guidance
- 3 Piston with magnet
- 4 Slot for proximity sensor

- Note
Gripper selection
sizing software
→ www.festo.com

Wide range of supply ports

Direct


From the front




- 1 Supply ports
- 2 O-rings

Via adapter plate

From underneath




Other ports



- 1 Port for lubrication nipple
- 2 Exhaust hole or sealing air port

Use in harsh ambient conditions



When using the gripper in damp environments or with liquid/gaseous media, make sure that the filter is installed in a neutral environment. The same applies to unused supply ports when operating the gripper as a single-acting gripper.

Three-point grippers HGDD, sealed


Key features

FESTO

Mounting options

Direct mounting

From above




1 Mounting screws

2 Centring pins

Via adapter plate


From underneath



Note


These grippers are not suitable or are of limited suitability for the following sample applications:

Not suitable for:




- Welding spatter

Of limited suitability for:



- Aggressive media only possible after consultation with Festo



- Grinding dust

Three-point grippers HGDD, sealed

Type codes

FESTO


		HGDD	—	35	—	A	—	G1
Type								
HGDD	Three-point gripper							
Size								
Position sensing								
A	Via proximity sensor							
Gripping force retention								
G1	Opening							
G2	Closing							

Three-point grippers HGDD, sealed


Peripherals overview

FESTO


Peripherals overview



System product for handling and assembly technology



Proportional pressure regulator VPPM




Accessories			
Type	Description		→ Page/Internet
1 Lubrication nipple	Included in the scope of delivery of the gripper		–
2 Push-in fitting QS	For connecting compressed air tubing with standard O.D.		qs
3 Blanking plug B	For sealing the supply ports when using the lower supply ports		17
4 Sensor bracket DASI	Switch lug for sensing the gripper jaw position. Mounted on the gripper jaw blank		17
5 Sensor bracket DASI	Clamping block for securing the proximity sensors SIEH or SIEN		17
6 Proximity sensor SIEH/SIEN	For sensing the piston position		18
7 Gripper jaw blank BUB-HGDD	Blank specially matched to the gripper jaws for custom fabrication of gripper fingers		16
8 Centring sleeve ZBH	- For centring gripper jaw blanks/gripper fingers on the gripper jaws 6 centring sleeves included in the scope of delivery of the gripper		17
9 Proximity sensor SMT-8G	- For sensing the piston position, 3 slots available - Proximity sensor does not project past the housing at the bottom		17
11 Adapter plate DHAA, HAPG	Connecting plate between drive and gripper		14
12 Proportional pressure regulator VPPM	For infinite adjustment of the gripping force		vppm

Three-point grippers HGDD, sealed

FESTO

Technical data

Function
Double-acting
HGDD-...




-  Size
35 ... 80 mm

-  Stroke
4 ... 12 mm

-  www.festo.com

Function – Variants
Single-acting or
with gripping force retention ...
... opening HGDD-...-G1



... closing HGDD-...-G2



General technical data						
Size		35	40	50	63	80
Design		Wedge-shaped actuator				
		Forced motion sequence				
Mode of operation		Double-acting				
Gripper function		3-point				
Number of gripper jaws		3				
Max. load per external gripper finger ¹⁾	[g]	57	130	276	440	790
Stroke per gripper jaw	[mm]	4	6	8	10	12
Pneumatic connection		M5	M5	G¼	G¼	G¼
Pneumatic connection for sealing air		M3	M3	M5	M5	G¼
Pneumatic connection for lubrication nipple		M3	M3	M5	M5	M5
Repetition accuracy ²⁾	[mm]	≤0.03			≤0.05	
Max. interchangeability	[mm]	≤±0.2				
Max. operating frequency	[Hz]	≤4				
Rotational symmetry	[mm]	< Ø 0.2				
Position sensing		Via proximity sensor				
Type of mounting		Via through-hole and dowel pin				
		Via female thread and dowel pin				
Mounting position		Any				

1) Valid for unthrottled operation

2) End-position drift under constant conditions of use with 100 consecutive strokes, concentric to the central shaft

Operating and environmental conditions		
Min. operating pressure		
HGDD-...-A	[bar]	3
HGDD-...-A-G	[bar]	4
Max. operating pressure	[bar]	8
Operating pressure for sealing air	[bar]	0 ... 0.5
Operating medium	Compressed air in accordance with ISO 8573-1:2010 [7:4:4]	
Note on operating/pilot medium	Operation with lubricated medium possible (in which case lubricated operation will always be required)	
Ambient temperature ¹⁾	[°C]	+5 ... +60
Protection class	IP65	
Corrosion resistance class CRC ²⁾	2	

1) Note operating range of proximity sensors

2) Corrosion resistance class 2 according to Festo standard 940 070

Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

Three-point grippers HGDD, sealed


Technical data

FESTO

Weight [g]					
Size	35	40	50	63	80
HGDD-...-A	309	599	1,117	2,175	3,522
HGDD-...-A-G	370	775	1,495	2,848	4,788


Materials

Sectional view




Size	35	40	50	63	80
1 Cover cap	High-alloy stainless steel				
2 Gripper jaw	Hardened steel				
3 Housing	Anodised aluminium				
4 Piston	Hard anodised aluminium				
– Seals	Nitrile rubber				
– Note on materials	Free of copper and PTFE			–	
	RoHS-compliant				

Gripping force [N] at 6 bar



Size	35	40	50	63	80
Gripping force per gripper jaw					
HGDD-...-A	Opening	122	216	371	582
	Closing	112	200	348	553
Total gripping force					
HGDD-...-A	Opening	366	648	1,113	1,746
	Closing	336	600	1,044	1,659

Characteristic load values at the gripper jaws



The indicated permissible forces and torques apply to a single gripper jaw. They include the lever arm, additional applied loads due to the workpiece or external gripper fingers and acceleration forces occurring during movement.

The zero coordinate line (gripper finger point of rotation) must be taken into consideration for the calculation of torques.


Size	35	40	50	63	80
Max. permissible force F_z	[N]	300	700	1,300	2,300
Max. permissible torque M_x	[Nm]	12	25	45	70
Max. permissible torque M_y	[Nm]	8	18	30	45
Max. permissible torque M_r	[Nm]	8	20	30	50

Three-point grippers HGDD, sealed

Technical data

FESTO


Mass moment of inertia [kgcm²]



Mass moment of inertia of the three-point gripper in relation to the central axis, without external gripper fingers, without load.

Size	35	40	50	63	80
HGDD-...-A	1.01	3.31	9.65	29	70.22
HGDD-...-A-G	1.37	5.01	15.07	45.05	109

Gripper jaw backlash




The plain-bearing guide used in the grippers means that there is backlash between the gripper jaws and the guide element. The values entered in the table for the backlash were calculated in accordance with the traditional accumulative tolerance method.

Size	35	40	50	63	80
Max. gripper jaw backlash S_z [mm]	0.05				
Max. gripper jaw angular backlash α_x, α_y [°]	0.1				

Opening and closing times [ms] at 6 bar

Without external gripper fingers

With external gripper fingers



The indicated opening and closing times [ms] were measured at room temperature at an operating pressure of 6 bar with horizontally mounted grippers without additional gripper

fingers. The grippers must be throttled for greater loads [g]. Opening and closing times must then be adjusted accordingly.

Size		35	40	50	63	80
Without external gripper fingers						
HGDD-...-A	Opening	44	78	93	115	152
	Closing	52	106	128	145	142
HGDD-...-A-G1	Opening	38	70	25	48	72
	Closing	85	211	160	190	246
HGDD-...-A-G2	Opening	81	144	111	135	159
	Closing	42	110	87	68	107
With external gripper fingers per gripper finger (as a function of the load)						
HGDD-...	200 g	52	–	–	–	–
	400 g	74	70	–	–	–
	500 g	83	78	–	–	–
	800 g	105	99	106	–	–
	1,000 g	–	111	118	128	–
	1,500 g	–	–	145	157	209
	1,800 g	–	–	–	172	229
	2,000 g	–	–	–	181	241
	2,200 g	–	–	–	–	253
2,400 g	–	–	–	–	264	


Three-point grippers HGDD, sealed

Technical data

FESTO

Gripping force F_H per gripper jaw as a function of operating pressure and lever arm x

The gripping forces as a function of operating pressure and lever arm can be determined from the following graphs.




— 3 bar
- - - 6 bar
- · - 8 bar


Note
Gripper selection
sizing software
→ www.festo.com

External gripping (closing)


HGDD-35-A




HGDD-40-A




HGDD-50-A



HGDD-63-A



HGDD-80-A




Three-point grippers HGDD, sealed

Technical data

FESTO

Gripping force F_H per gripper jaw as a function of operating pressure and lever arm x

The gripping forces as a function of operating pressure and lever arm can be determined from the following graphs.




— 3 bar
- - - 6 bar
- · - 8 bar


Note
Gripper selection
sizing software
→ www.festo.com

Internal gripping (opening)


HGDD-35-A




HGDD-40-A




HGDD-50-A



HGDD-63-A



HGDD-80-A



Three-point grippers HGDD, sealed


Technical data

FESTO


Spring force F_F as a function of size and gripper jaw stroke l per gripper finger

Gripping force retention for HGDD-...-G...

The spring forces F_F as a function of gripper jaw stroke can be determined from the following graph.




Size 35 ... 50



— HGDD-35-A-G
 - - - HGDD-40-A-G
 - · - HGDD-50-A-G

Size 63 ... 80



— HGDD-63-A-G
 - - - HGDD-80-A-G

Spring force F_F as a function of size, gripper jaw stroke l and lever arm x per gripper finger

The lever arm x must be taken into consideration when determining the actual spring force F_{Ftotal} .

The formulae for calculating the spring force are provided in the table below.

Gripping force retention	Size	F_{Ftotal} per gripper finger
G1	35	$-0.85 \cdot x + 0.45 \cdot F_F$
	40	$-0.55 \cdot x + 0.35 \cdot F_F$
	50	$-2.5 \cdot x + 0.75 \cdot F_F$
	63	$-0.2 \cdot x + 0.4 \cdot F_F$
	80	$-1.5 \cdot x + 0.35 \cdot F_F$
Gripping force retention	Size	F_{Ftotal} per gripper finger
G2	35	$-0.6 \cdot x + 0.45 \cdot F_F$
	40	$-0.55 \cdot x + 0.35 \cdot F_F$
	50	$-2.5 \cdot x + 0.6 \cdot F_F$
	63	$-1.0 \cdot x + 0.4 \cdot F_F$
	80	$-4.0 \cdot x + 0.85 \cdot F_F$

Determination of the actual gripping forces F_{Gr} for HGDD-...-G1 and HGDD-...-G2 as a function of application

The three-point grippers with integrated spring type HGDD-...-G1 (opening gripping force retention) and HGDD-...-G2 (closing gripping force retention) can be used as

- single-acting grippers

- grippers with supplementary gripping force and
- grippers with gripping force retention depending on requirements.

In order to calculate the available gripping forces F_{Gr} (per gripper finger), the gripping force (F_H) and spring force (F_{Ftotal}) must be combined accordingly.

Application forces per gripper finger

Single-acting	Supplementary gripping force	Gripping force retention
- Gripping with spring force: $F_{Gr} = F_{Ftotal}$ - Gripping with pressure force: $F_{Gr} = F_H - F_{Ftotal}$	Gripping with pressure and spring force: $F_{Gr} = F_H + F_{Ftotal}$	Gripping with spring force: $F_{Gr} = F_{Ftotal}$


Three-point grippers HGDD, sealed

Technical data


FESTO

Dimensions

Download CAD data → www.festo.com



View A



- 1 Supply port, opening
- 2 Supply port, closing
- 3 Alternative supply port (supplied sealed)
- 4 Exhaust hole (filter integrated)
- 5 Lubrication nipple (supplied sealed)
- 6 Slot for proximity sensor
- 7 O-ring for three-point gripper
HGDD-35: $\varnothing$ 3x1.5
HGDD-40 ... 80: $\varnothing$ 5x1.5

Three-point grippers HGDD, sealed

Technical data

FESTO

Size	B1	B2	B3	B4	D1 Ø	D2 Ø	D3 Ø	D4 Ø	D5 Ø	D6 Ø	D7	D8	D9
[mm]	±0.5	±0.5			±0.1	H8	±0.1	H8	H13	H13			
35	28	32	11	22	58	3	44	5	5.9	3.3	M4	M3	M3
40	36	42	14	28	74	4	56	7	9.4	5.1	M6	M4	M3
50	44.5	52.5	17.5	35	93	5	70	9	10.2	6.8	M8	M6	M3
63	55	65	22.5	45	114	5	90	9	10.2	6.8	M8	M6	M3
80	68	80	28	56	139	6	112	9	13.5	8.4	M10	M6	M3

Size [mm]	D10 Ø h7	D11 Ø	D12 Ø +0.2	EE	EE1	EE2	EE3	H1		H2	
								±0.05	-G ±0.05		-G
35	5	3.2	6	M5	M3	M3	M3	41	51	29	39
40	7	5.3	8	M5	M5	M3	M3	48.5	66	34.5	52
50	9	6.4	8	G $\frac{1}{8}$	M5	M5	M5	58.5	83.5	40.4	65.4
63	9	6.4	8	G $\frac{1}{8}$	M5	M5	M5	74	104	50	80
80	9	6.4	8	G $\frac{1}{8}$	M5	G $\frac{1}{8}$	M5	83.5	120.5	55.5	92.5

Size [mm]	H3		H5	H6	H7		H8 ¹⁾	H9	H10	L1	L2	L3	L4
	-0.2	-G -0.2	±0.1	±0.1	±0.1	-G ±0.1		-0.02	-0.3	±0.1	±0.1	±0.02	
35	23	33	9	18.5	7	17	7	15.5	1.2	12	15	45	19.05
40	27.5	45	9	25	10	27.5	10	19	1.4	12	18	56	24.25
50	32.5	57.5	12	32	12.5	37.5	12	24.1	1.9	24	18	70	30.31
63	39	69	12	42	16	46	15	31.5	1.9	24	24	90	38.97
80	43	80	12	53	21	58	18	37	1.9	30	30	112	48.5

Size	L5	L6	T1	T2	T3	T4	T5	T6	T7	T8	T9	T10	W1
[mm]	-0.02	±0.1	min.	min.	min.	min.	+0.1	min.	+0.1	min.	+0.2	min.	
35	14	12	5	5	3	3	1.2	4	1.3	5	3.2	8	120°
40	18	12	6	6	3	5	1.2	5	1.6	6	5	10	120°
50	22	12	8	7	6	5	1.2	5	2.1	10	6.1	12	120°
63	28	14	8	7	6	5	1.2	5	2.1	10	6.1	12	120°
80	32	14	10	8	10	5	1.2	5	2.1	10	8	15	120°

1) Tolerance for centring hole ±0.02 mm
Tolerance for thread ±0.1 mm

Ordering data													
Size [mm]	Double-acting without compression spring				Single-acting or with gripping force retention								
	Part No.		Type		Opening				Closing				
					Part No.		Type		Part No.		Type		
35	1163037		HGDD-35-A		1163038		HGDD-35-A-G1		1163039		HGDD-35-A-G2		
40	1163040		HGDD-40-A		1163041		HGDD-40-A-G1		1163042		HGDD-40-A-G2		
50	1163043		HGDD-50-A		1163044		HGDD-50-A-G1		1163045		HGDD-50-A-G2		
63	1163046		HGDD-63-A		1163047		HGDD-63-A-G1		1163048		HGDD-63-A-G2		
80	1163049		HGDD-80-A		1163050		HGDD-80-A-G1		1163051		HGDD-80-A-G2		

Three-point grippers HGDD, sealed

Accessories

FESTO




Adapter kit
DHAA, HAPG

Material:
Wrought aluminium alloy
Free of copper and PTFE
RoHS-compliant



Note

The kit includes the individual mounting interface as well as the necessary mounting material.

Permissible drive/gripper combinations with adapter kit				Download CAD data → www.festo.com	
Combination	Drive	Gripper	Adapter kit		
	Size	Size	CRC ¹⁾	Part No.	Type
DGSL/HGDD	DGSL	HGDD	DHAA		
	16, 20, 25	35	2	2371422	DHAA-G-G3-20-B13-35
	20, 25	40		2373773	DHAA-G-H2-16-B13-40
	25	50		2377625	DHAA-G-H2-20-B13-50
	DGSL	HGDD-G1/G2	DHAA, HAPG		
	16, 20, 25	35	2	542436	HAPG-94
	20, 25	40		542437	HAPG-95
	25	50		2378415	DHAA-G-H2-20-B13G-50
	SLT/HGDD	SLT	HGDD	DHAA	
	16	35	2	2360918	DHAA-G-G3-16-B13-35
	20, 25	35		2371422	DHAA-G-G3-20-B13-35
	20, 25	40		2373773	DHAA-G-H2-16-B13-40
	25	50		2377625	DHAA-G-H2-20-B13-50
	SLT	HGDD-G1/G2	DHAA, HAPG		
	16	35	2	542435	HAPG-99
	20, 25	35		542436	HAPG-94
	20, 25	40		542437	HAPG-95
	25	50		2378415	DHAA-G-H2-20-B13G-50
	HMP/HGDD	HMP	HGDD	DHAA	
	16	35	2	2350468	DHAA-G-H2-16-B13-35
	16, 20, 25	40		2373773	DHAA-G-H2-16-B13-40
	20, 25, 32	50		2377625	DHAA-G-H2-20-B13-50
	25, 32	63		2367926	DHAA-G-H2-25-B13-63
	HMP	HGDD-G1/G2	DHAA, HAPG		
	16	35	2	542434	HAPG-98
	16, 20, 25	40		542437	HAPG-95
	20, 25, 32	50		2378415	DHAA-G-H2-20-B13G-50
	25, 32	63		2367800	DHAA-G-H2-25-B13G-63

1) Corrosion resistance class 2 according to Festo standard 940 070

Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

Three-point grippers HGDD, sealed

Accessories

FESTO





Adapter kit
DHAA, HAPG

Material:
Wrought aluminium alloy
Free of copper and PTFE
RoHS-compliant



Note

The kit includes the individual mounting interface as well as the necessary mounting material.

Permissible drive/gripper combinations with adapter kit				Download CAD data → www.festo.com	
Combination	Drive	Gripper	Adapter kit		
	Size	Size	CRC ¹⁾	Part No.	Type
DRRD/HGDD	DRRD	HGDD	DHAA		
	20	35	2	2075498	DHAA-G-Q11-20-B13-35
	25	35		1718041	DHAA-G-Q11-25-B13-35
	25	40		1718564	DHAA-G-Q11-25-B13-40
	32	40		2077119	DHAA-G-Q11-32-B13-40
	32	50		2078975	DHAA-G-Q11-32-B13-50
	35	50		2079171	DHAA-G-Q11-35-B13-50
	35, 40	63		2079579	DHAA-G-Q11-35/40-B13-63
	DRRD	HGDD-G1/G2		DHAA	
	20	35	2	2837144	DHAA-G-Q11-20-B13G-35
	25	35		2837169	DHAA-G-Q11-25-B13G-35
	25	40		2837182	DHAA-G-Q11-25-B13G-40
	32	40		2837254	DHAA-G-Q11-32-B13G-40
	32	50		2837269	DHAA-G-Q11-32-B13G-50
	35	50		2837283	DHAA-G-Q11-35-B13G-50
	35, 40	63		2837337	DHAA-G-Q11-35/40-B13G-63
EGSL/HGDD	EGSL	HGDD	DHAA		
	45, 55, 75	35	2	2371422	DHAA-G-G3-20-B13-35
	75	40		2373773	DHAA-G-H2-16-B13-40
	75	50		2377625	DHAA-G-H2-20-B13-50
	EGSL	HGDD-G1/G2	DHAA, HAPG		
	45, 55, 75	35	2	542436	HAPG-94
	75	40		542437	HAPG-95
	75	50		2378415	DHAA-G-H2-20-B13G-50
ERMB/HGDD	ERMB	HGDD	DHAA		
	20, 25, 32	35	2	2376297	DHAA-G-Q5-20-B13-35
	25, 32	40		2376728	DHAA-G-Q5-25-B13-40
	32	50		2377625	DHAA-G-H2-20-B13-50
	ERMB	HGDD-G1/G2	DHAA, HAPG		
	20, 25, 32	35	2	542441	HAPG-SD2-34
	25, 32	40		542442	HAPG-SD2-35
	32	50		2378415	DHAA-G-H2-20-B13G-50
EHMB/HGDD	EHMB	HGDD	DHAA		
	20	35	2	2376297	DHAA-G-Q5-20-B13-35
	20	40		2376728	DHAA-G-Q5-25-B13-40
	20	50		2377625	DHAA-G-H2-20-B13-50
	EHMB	HGDD-G1/G2	DHAA, HAPG		
	20	35	2	542441	HAPG-SD2-34
	20	40		542442	HAPG-SD2-35
	20	50		2378415	DHAA-G-H2-20-B13G-50

1) Corrosion resistance class 2 according to Festo standard 940 070

Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

Three-point grippers HGDD, sealed

Accessories

FESTO

Gripper jaw blank BUB-HGDD



(scope of delivery: 3 pieces)

Material:

Wrought aluminium alloy

Free of copper and PTFE

RoHS-compliant



Dimensions and ordering data							
For size	B1	B2	B3	D1 Ø	D2 Ø	D3 Ø	D4
[mm]	±0.05			H13	H13	H8	
35	14	8.5	2	5.9	3.2	5	M3
40	20	14	2	7.4	4.3	7	M3
50	29	23	2	10.4	6.4	9	M3
63	32	26	2	10.4	6.4	9	M3
80	35	26	2	10.4	6.4	9	M3

For size	H1	H2	H3 ¹⁾	H4	L1	L2	L3
[mm]	±0.05	±0.02			±0.05		
35	60.5	9	7	35	37	3	10
40	77	7	10	50	45	5	10
50	96	11	12	60	55	6	12
63	121	13.5	15	75	64	6	12
80	153.5	15.5	18	100	79.4	10	15

For size	T1	T2	T3	W1	Weight per blank [g]	Part No.	Type
[mm]		+0.1					
35	3 ^{+0.2}	1.3	5	30°	57	1180955	BUB-HGDD-35
40	4 ^{+0.2}	1.6	5	30°	131	1180956	BUB-HGDD-40
50	6.1 ^{+0.1}	2.1	5	30°	276	1180957	BUB-HGDD-50
63	6.1 ^{+0.1}	2.1	5	30°	440	1180958	BUB-HGDD-63
80	6.1 ^{+0.1}	2.1	5	30°	793	1180959	BUB-HGDD-80

1) ±0.02 and ±0.01 applies to the centring D3
±0.1 applies to the through-holes D1 and D2

Three-point grippers HGDD, sealed

Accessories

FESTO



Sensor bracket DASI

(scope of delivery: 1 piece)

Material:

Wrought aluminium alloy

RoHS-compliant



Dimensions and ordering data							
For size	B1	H1		H2	L1	Weight	Part No. Type
[mm]			-G			[g]	
35	13	3	13	8	21	20	1435236 DASI-B13-35-S3
40	16	6	23.5	10	20	27	1435232 DASI-B13-40-S8
50	16	8.5	33.5	10	20	30	1435233 DASI-B13-50-S8
63	16	10	36	10	22	35	1435234 DASI-B13-63-S8
80	22	10	47	15	22	45	1435235 DASI-B13-80-S8

Ordering data						
	For size [mm]	Comment	Weight [g]	Part No.	Type	PU ¹⁾
Centring sleeve ZBH				Technical data → Internet: zbh		
	35	For centring gripper jaw blanks/gripper fingers on the gripper jaws	1	189652	ZBH-5	10
	40		1	186717	ZBH-7	
	50, 63, 80		1	150927	ZBH-9	
Blanking plug B				Technical data → Internet: blanking plug		
	35, 40	For sealing the supply ports	1	174308	B-M5-B	10
	50, 63, 80		5	3568	B-1/8	

1) Packaging unit

Ordering data – Proximity sensors for T-slot, magneto-resistive							Technical data → Internet: smt
	Type of mounting	Electrical connection, connection direction	Switching output	Cable length [m]	Part No.	Type	
N/O contact							
	Insertable in the slot lengthwise	Cable, 3-wire, lateral	PNP	2.5	547859	SMT-8G-PS-24V-E-2,5Q-OE	
		Plug M8x1, 3-pin, lateral		0.3	547860	SMT-8G-PS-24V-E-0,3Q-M8D	

Ordering data – Connecting cables							Technical data → Internet: nebu
	Electrical connection, left	Electrical connection, right	Cable length [m]	Part No.	Type		
	Straight socket, M8x1, 3-pin	Cable, open end, 3-wire	2.5	541333	NEBU-M8G3-K-2.5-LE3		
			5	541334	NEBU-M8G3-K-5-LE3		
	Angled socket, M8x1, 3-pin	Cable, open end, 3-wire	2.5	541338	NEBU-M8W3-K-2.5-LE3		
			5	541341	NEBU-M8W3-K-5-LE3		

Three-point grippers HGDD, sealed

Accessories

FESTO

Proximity sensor for size 35

Ordering data – Proximity sensors 3 mm (round design), inductive					Technical data → Internet: sieh	
	Electrical connection	LED	Switching output	Cable length [m]	Part No.	Type
N/O contact						
	Cable, 3-wire	■	PNP	2.5	538264	SIEH-3B-PS-K-L
	Plug M8x1, 3-pin	■		–	538263	SIEH-3B-PS-S-L

Proximity sensor for size 40 ... 80

Ordering data – Proximity sensors M8 (round design), inductive					Technical data → Internet: sien	
	Electrical connection	LED	Switching output	Cable length [m]	Part No.	Type
N/O contact						
	Cable, 3-wire	■	PNP	2.5	150386	SIEN-M8B-PS-K-L
	Plug M8x1, 3-pin	■		–	150387	SIEN-M8B-PS-S-L

Ordering data – Connecting cables				Technical data → Internet: nebu	
	Electrical connection, left	Electrical connection, right	Cable length [m]	Part No.	Type
	Straight socket, M8x1, 3-pin	Cable, open end, 3-wire	2.5	541333	NEBU-M8G3-K-2.5-LE3
			5	541334	NEBU-M8G3-K-5-LE3
	Angled socket, M8x1, 3-pin	Cable, open end, 3-wire	2.5	541338	NEBU-M8W3-K-2.5-LE3
			5	541341	NEBU-M8W3-K-5-LE3