

Filter regulators MS-LFR, MS series


FESTO



Filter regulators MS-LFR, MS series

Product range overview – MS series service units

FESTO

Type	Size	Pneumatic connection in housing	Connecting plate	Pressure regulation range [bar]						Grade of filtration [μm]				
				0.05	0.05	0.1	0.3	0.1	0.5	0.01	1	5	40	
Code	AG...			D2	D4	D5	D6	D7	D8	A	B	C	E	
Service units														
MSB-FRC		4	G1/8, G1/4	G1/8, G1/4, G3/8	–	–	–	■	■	–	–	–	■	■
		6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	–	–	–	■	■	–	–	–	■	■
		9	–	–	–	–	–	–	–	–	–	–	–	–
		12	–	–	–	–	–	–	–	–	–	–	–	–
Service unit combinations (further variants can be ordered using the configurator → Internet: msb4, msb6 or msb9)														
MSB		4	G1/4	G1/8, G1/4, G3/8	–	–	–	■	■	–	–	–	■	■
		6	G1/2	G1/4, G3/8, G1/2, G3/4	–	–	–	■	■	–	–	–	■	■
		9	–	–	–	–	–	–	–	–	–	–	–	–
		12	–	–	–	–	–	–	–	–	–	–	–	–
Individual devices														
Filter regulators MS-LFR		4	G1/8, G1/4	G1/8, G1/4, G3/8	–	–	■	■	■	–	–	–	■	■
		6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	–	–	■	■	■	■	–	–	■	■
		9	G3/4, G1	G1/2, G3/4, G1, G11/4, G11/2	–	–	■	■	■	■	–	–	■	■
		12	–	G1, G11/4, G11/2, G2	–	–	–	■	■	■	–	–	■	■
Filters MS-LF		4	G1/8, G1/4	G1/8, G1/4, G3/8	–	–	–	–	–	–	–	–	■	■
		6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	–	–	–	–	–	–	–	–	■	■
		9	G3/4, G1	G1/2, G3/4, G1, G11/4, G11/2	–	–	–	–	–	–	–	–	■	■
		12	–	G1, G11/4, G11/2, G2	–	–	–	–	–	–	–	–	■	■
Fine and micro filters MS-LFM		4	G1/8, G1/4	G1/8, G1/4, G3/8	–	–	–	–	–	–	■	■	–	–
		6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	–	–	–	–	–	–	■	■	–	–
		9	G3/4, G1	G1/2, G3/4, G1, G11/4, G11/2	–	–	–	–	–	–	■	■	–	–
		12	–	G1, G11/4, G11/2, G2	–	–	–	–	–	–	■	■	–	–
Activated carbon filters MS-LFX		4	G1/8, G1/4	G1/8, G1/4, G3/8	–	–	–	–	–	–	–	–	–	–
		6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	–	–	–	–	–	–	–	–	–	–
		9	G3/4, G1	G1/2, G3/4, G1, G11/4, G11/2	–	–	–	–	–	–	–	–	–	–
		12	–	G1, G11/4, G11/2, G2	–	–	–	–	–	–	–	–	–	–
Water separators MS-LWS		4	–	–	–	–	–	–	–	–	–	–	–	–
		6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	–	–	–	–	–	–	–	–	–	–
		9	G3/4, G1	G1/2, G3/4, G1, G11/4, G11/2	–	–	–	–	–	–	–	–	–	–
		12	–	G1, G11/4, G11/2, G2	–	–	–	–	–	–	–	–	–	–

Filter regulators MS-LFR, MS series

FESTO

Product range overview – MS series service units

Type	Size	Bowl guard		Condensate drains				Pressure indicator				Security		Options		➔ Page/ Internet		
		Plastic bowl with plastic bowl guard	Metal bowl	Manual rotary	Semi-automatic	Fully automatic	External, fully automatic, electrical	Cover plate (without pressure gauge)	Integrated MS pressure gauge	Adapter plate for EN pressure gauge G ¹ / ₈	Adapter plate for EN pressure gauge G ¹ / ₄	Pressure sensor	Rotary knob with detent, lockable via accessories	Rotary knob with integrated lock	Silencer	Flow direction from right to left		
Code		R	U	M	H	V	E...	VS	AG	A8	A4	AD...	AS	E11	S	Z		
Service units																		
MSB-FRC	4	■	–	■	–	■	–	–	■	–	–	–	■	–	–	■	msb4	
	6	■	■	■	–	■	–	–	■	–	–	–	■	–	–	■	msb6	
	9	–															–	
	12	–															–	
Service unit combinations																		
MSB	4	■	■	■	–	■	–	–	■	–	–	–	■	–	–	■	msb4	
	6	■	■	■	–	■	–	–	■	–	–	–	■	–	–	■	msb6	
	9	–															–	
	12	–															–	
Individual devices																		
Filter regulators MS-LFR	4	■	■	■	■	■	■	–	■	■	■	■	■	■	■	–	■	8
	6	■	■	■	■	■	■	■	■	–	■	■	■	■	■	–	■	8
	9	–	■	■	■	■	■	■	■	–	■	■	■	■	■	–	■	24
	12	–	■	■	■	–	■	■	■	■	–	■	–	■	■	–	■	36
Filters MS-LF	4	■	■	■	■	■	■	–	–	–	–	–	–	–	–	–	■	ms4-lf
	6	■	■	■	■	■	■	■	■	–	–	–	–	–	–	–	■	ms6-lf
	9	–	■	■	■	■	■	■	■	–	–	–	–	–	–	–	■	ms9-lf
	12	–	■	■	■	–	■	■	–	–	–	–	–	–	–	–	■	ms12-lf
Fine and micro filters MS-LFM	4	■	■	■	■	■	■	–	–	–	–	–	–	–	–	–	■	ms4-lfm
	6	■	■	■	■	■	■	■	■	–	–	–	–	–	–	–	■	ms6-lfm
	9	–	■	■	■	■	■	■	■	–	–	–	–	–	–	–	■	ms9-lfm
	12	–	■	■	■	–	■	■	–	–	–	–	–	–	–	–	■	ms12-lfm
Activated carbon filters MS-LFX	4	■	■	–	–	–	–	–	–	–	–	–	–	–	–	–	■	ms4-lfx
	6	■	■	–	–	–	–	–	–	–	–	–	–	–	–	–	■	ms6-lfx
	9	–	■	–	–	–	–	–	–	–	–	–	–	–	–	–	■	ms9-lfx
	12	–	■	–	–	–	–	–	–	–	–	–	–	–	–	–	■	ms12-lfx
Water separators MS-LWS	4	–															–	
	6	–	■	–	–	■	■	–	–	–	–	–	–	–	–	–	■	ms6-lws
	9	–	■	–	–	■	■	–	–	–	–	–	–	–	–	–	■	ms9-lws
	12	–	■	–	–	–	■	■	–	–	–	–	–	–	–	–	■	ms12-lws

Filter regulators MS-LFR, MS series

Product range overview – MS series service units

FESTO

Type	Size	Pneumatic connection in housing	Connecting plate	Pressure regulation range [bar]						Supply voltage			
				0.05 ...	0.05 2.5	0.1 4	0.3 7	0.1 12	0.5 16	24 VDC, connection pattern to EN 175301.	24 VDC, connection M12 to IEC 61076-2-101	110 VAC, connection pattern to EN 175301.	230 VAC, connection pattern to EN 175301.
Code	AG...	D2	D4	D5	D6	D7	D8	V24	V24P	V110	V230		
Individual devices													
Pressure regulators MS-LR		4	G1/8, G1/4	G1/8, G1/4, G3/8	–	–	■	■	■	–	–	–	–
		6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	–	–	■	■	■	■	–	–	–
		9	G3/4, G1	G1/2, G3/4, G1, G11/4, G11/2	–	–	■	■	■	■	–	–	–
		12	–	G1, G11/4, G11/2, G2	–	–	–	■	■	■	–	–	–
Pressure regulators MS-LRB		4	G1/4	G1/8, G1/4, G3/8	–	–	■	■	■	–	–	–	–
		6	G1/2	G1/4, G3/8, G1/2, G3/4	–	–	■	■	■	■	–	–	–
		9	–										
		12	–										
Precision pressure regulators MS-LRP		4	–										
		6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	■	■	■	–	■	–	–	–	–
		9	–										
		12	–										
Precision pressure regulators MS-LRPB		4	–										
		6	G1/2	G1/4, G3/8, G1/2, G3/4	■	■	■	–	■	–	–	–	–
		9	–										
		12	–										
Electrical pressure regulators MS-LRE		4	–										
		6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	–	–	■	■	■	■	–	–	–
		9	–										
		12	–										
Lubricators MS-LOE		4	G1/8, G1/4	G1/8, G1/4, G3/8	–	–	–	–	–	–	–	–	–
		6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	–	–	–	–	–	–	–	–	–
		9	G3/4, G1	G1/2, G3/4, G1, G11/4, G11/2	–	–	–	–	–	–	–	–	–
		12	–	G1, G11/4, G11/2, G2	–	–	–	–	–	–	–	–	–
On-off valves, manually actuated MS-EM(1)		4	G1/8, G1/4	G1/8, G1/4, G3/8	–	–	–	–	–	–	–	–	–
		6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	–	–	–	–	–	–	–	–	–
		9	G3/4, G1	G1/2, G3/4, G1, G11/4, G11/2	–	–	–	–	–	–	–	–	–
		12	–	G1, G11/4, G11/2, G2	–	–	–	–	–	–	–	–	–
On-off valves, electrically actuated MS-EE		4	G1/8, G1/4	G1/8, G1/4, G3/8	–	–	–	–	–	–	■	–	■
		6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	–	–	–	–	–	–	■	–	■
		9	G3/4, G1	G1/2, G3/4, G1, G11/4, G11/2	–	–	–	–	–	–	■	■	■
		12	–	G1, G11/4, G11/2, G2	–	–	–	–	–	–	■	■	■
Soft-start valves, pneumatically actuated MS-DL		4	G1/8, G1/4	G1/8, G1/4, G3/8	–	–	–	–	–	–	–	–	–
		6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	–	–	–	–	–	–	–	–	–
		9	–										
		12	–	G1, G11/4, G11/2, G2	–	–	–	–	–	–	–	–	–
Soft-start valves, electrically actuated MS-DE		4	G1/8, G1/4	G1/8, G1/4, G3/8	–	–	–	–	–	–	■	–	■
		6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	–	–	–	–	–	–	■	–	■
		9	–										
		12	–	G1, G11/4, G11/2, G2	–	–	–	–	–	–	■	■	■

Filter regulators MS-LFR, MS series

FESTO

Product range overview – MS series service units

Type	Size	Bowl guard		Pressure indicator					Security		Options		➔ Page/ Internet
		Plastic bowl with plastic bowl guard	Metal bowl	Cover plate (without pressure gauge)	Integrated MS pressure gauge	Adapter plate for EN pressure gauge G ¹ / ₈	Adapter plate for EN pressure gauge G ¹ / ₄	Pressure sensor	Rotary knob with detent, lockable via accessories	Rotary knob with integrated lock	Silencer	Flow direction from right to left	
Code		R	U	VS	AG	A8	A4	AD...	AS	E11	S	Z	
Individual devices													
Pressure regulators MS-LR	4	–	–	■	■	■	■	■	■	■	–	■	ms4-lr
	6	–	–	■	■	–	■	■	■	■	–	■	ms6-lr
	9	–	–	■	■	–	■	■	■	■	–	■	ms9-lr
	12	–	–	■	■	–	■	–	■	■	–	■	ms12-lr
Pressure regulators MS-LRB	4	–	–	■	■	■	■	■	■	■	–	■	ms4-lrb
	6	–	–	■	■	–	■	■	■	■	–	■	ms6-lrb
	9	–	–	–	–	–	–	–	–	–	–	–	–
	12	–	–	–	–	–	–	–	–	–	–	–	–
Precision pressure regulators MS-LRP	4	–	–	–	–	–	–	–	–	–	–	–	–
	6	–	–	■	–	■	■	■	■	■	–	■	ms6-lrp
	9	–	–	–	–	–	–	–	–	–	–	–	–
	12	–	–	–	–	–	–	–	–	–	–	–	–
Precision pressure regulators MS-LRPB	4	–	–	–	–	–	–	–	–	–	–	–	–
	6	–	–	■	–	■	■	■	■	■	–	■	ms6-lrbp
	9	–	–	–	–	–	–	–	–	–	–	–	–
	12	–	–	–	–	–	–	–	–	–	–	–	–
Electrical pressure regulators MS-LRE	4	–	–	–	–	–	–	–	–	–	–	–	–
	6	–	–	■	■	–	■	–	–	–	–	■	ms6-lre
	9	–	–	–	–	–	–	–	–	–	–	–	–
	12	–	–	–	–	–	–	–	–	–	–	–	–
Lubricators MS-LOE	4	■	■	–	–	–	–	–	–	–	–	■	ms4-loe
	6	■	■	–	–	–	–	–	–	–	–	■	ms6-loe
	9	–	■	–	–	–	–	–	–	–	–	■	ms9-loe
	12	–	■	–	–	–	–	–	–	–	–	■	ms12-loe
On-off valves, manually actuated MS-EM(1)	4	–	–	■	■	■	■	■	■	–	–	■	ms4-em1
	6	–	–	■	■	–	■	■	■	–	–	■	ms6-em1
	9	–	–	■	■	–	■	–	–	–	–	■	ms9-em
	12	–	–	■	■	–	■	–	–	–	–	■	ms12-em
On-off valves, electrically actuated MS-EE	4	–	–	■	■	■	■	■	■	–	–	■	ms4-ee
	6	–	–	■	■	–	■	■	■	–	–	■	ms6-ee
	9	–	–	■	■	–	■	–	–	–	–	■	ms9-ee
	12	–	–	■	■	–	■	–	–	–	–	■	ms12-ee
Soft-start valves, pneumatically actuated MS-DL	4	–	–	■	■	■	■	■	■	–	–	■	ms4-dl
	6	–	–	■	■	–	■	■	■	–	–	■	ms6-dl
	9	–	–	–	–	–	–	–	–	–	–	–	–
	12	–	–	■	■	–	■	–	–	–	–	■	ms12-dl
Soft-start valves, electrically actuated MS-DE	4	–	–	■	■	■	■	■	■	–	–	■	ms4-de
	6	–	–	■	■	–	■	■	■	–	–	■	ms6-de
	9	–	–	–	–	–	–	–	–	–	–	–	–
	12	–	–	■	■	–	■	–	–	–	–	■	ms12-de

Filter regulators MS-LFR, MS series

Product range overview – MS series service units

FESTO

Type	Size	Pneumatic connection in housing	Connecting plate	Performance Level			Supply voltage			
				Category 1, 1-channel	Category 3, 2-channel	Category 4, 2-channel with self-monitoring	24 V DC, connection pattern to EN 175301	24 V DC, connection M12 to IEC 61076-2-101 / to EN 60947-5-2	110 V AC, connection pattern to EN 175301	230 V AC, connection pattern to EN 175301
Code		AG...		C	D	E	V24	V24P	V110	V230
Individual devices										
Soft start and exhaust valves MS-SV-C		4	–							
		6	G1/2	G1/4, G3/8, G1/2, G3/4	■	–	–	■	■	■
		9	G3/4, G1	G1/2, G3/4, G1, G11/4, G11/2	■	–	–	■	■	■
		12	–							
Soft start and exhaust valves MS-SV-D		4	–							
		6	G1/2	G1/4, G3/8, G1/2, G3/4	–	■	–	■	■	–
		9	–							
		12	–							
Soft start and exhaust valves MS-SV-E		4	–							
		6	G1/2	G1/4, G3/8, G1/2, G3/4	–	–	■	■	–	–
		9	–							
		12	–							
Membrane air dryers MS-LDM1		4	G1/8, G1/4	G1/8, G1/4, G3/8	–	–	–	–	–	–
		6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	–	–	–	–	–	–
		9	–							
		12	–							
Branching modules MS-FRM		4	G1/8, G1/4	G1/8, G1/4, G3/8	–	–	–	–	–	–
		6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	–	–	–	–	–	–
		9	G3/4, G1	G1/2, G3/4, G1, G11/4, G11/2	–	–	–	–	–	–
		12	–	G1, G11/4, G11/2, G2	–	–	–	–	–	–
Distributor blocks MS-FRM-FRZ		4	G1/4	–	–	–	–	–	–	–
		6	G1/2	–	–	–	–	–	–	–
		9	–							
		12	–							
Flow sensors SFAM		4	–							
		6	G1/2	G1/2	–	–	–	–	–	–
		9	–	G1, G11/2	–	–	–	–	–	–
		12	–							

Filter regulators MS-LFR, MS series

FESTO

Product range overview – MS series service units

Type	Size	Bowl guard		Pressure indicator					Switch output		Options		➔ Page/ Internet
		Plastic bowl with plastic bowl guard	Metal bowl	Cover plate (without pressure gauge)	Integrated MS pressure gauge	Adapter plate for EN pressure gauge G1/8	Adapter plate for EN pressure gauge G1/4	Pressure sensor	2x PNP or NPN, 1 analogue output 4 ... 20 mA	2x PNP or NPN, 1 analogue output 0 ... 10 V	Silencer	Flow direction from right to left	
Code		R	U	VS	AG	A8	A4	AD...	2SA	2SV	S	Z/R	
Individual devices													
MS-SV-C	4	–											–
	6	–	–	■	■	–	■	■	–	–	■	■	ms6-sv
	9	–	–	■	■	–	■	■	–	–	■	■	ms9-sv
	12	–											–
MS-SV-D	4	–											–
	6	–	–	■	■	–	■	■	–	–	■	■	ms6-sv
	9	–											–
	12	–											–
MS-SV-E	4	–											–
	6	–	–	■	■	–	■	■	–	–	■	■	ms6-sv
	9	–											–
	12	–											–
MS-LDM1	4	–	■	–	–	–	–	–	–	–	–	■	ms4-ldm1
	6	–	■	–	–	–	–	–	–	–	–	■	ms6-ldm1
	9	–											–
	12	–											–
MS-FRM	4	–	–	■	■	■	■	■	–	–	–	■	ms4-frm
	6	–	–	■	■	–	■	■	–	–	–	■	ms6-frm
	9	–	–	■	■	–	■	■	–	–	–	■	ms9-frm
	12	–	–	■	–	–	–	–	–	–	–	–	ms12-frm
MS-FRM-FRZ	4	–	–	–	–	–	–	–	–	–	–	■	ms4-frm
	6	–	–	–	–	–	–	–	–	–	–	■	ms6-frm
	9	–											–
	12	–											–
SFAM	4	–											–
	6	–	–	–	–	–	–	–	■	■	–	■	sfam-62
	9	–	–	–	–	–	–	–	■	■	–	■	sfam-90
	12	–											–


 New
Variant EX4, UL1

Filter regulators MS4/MS6-LFR, MS series

Peripherals overview

FESTO

Filter regulator MS4/MS6-LFR



 Note

Additional accessories:

- Module connector for combination with size MS4/MS6 or size MS9 → Internet: amv, rmv, armv
- Adapter plate for mounting on profiles → Internet: ipm-80, ipm-40-80, ipm-80-80

Filter regulators MS4/MS6-LFR, MS series

Peripherals overview

Mounting attachments and accessories	Individual device		Combination		➔ Page/ Internet
	Without connecting plate	With connecting plate	Without connecting plate	With connecting plate	
[1] Cover cap MS4/6-END	■	-	■	-	ms4-end, ms6-end
[2] Connecting plate-SET MS4/6-AG...	-	■	-	■	ms4-ag, ms6-ag
[3] Module connector MS4/6-MV	-	■	■	■	ms4-mv, ms6-mv
[4] Mounting bracket MS4/6-WB	■	■	-	-	ms4-wb, ms6-wb
[5] Mounting bracket MS4-WBM	■	■	-	-	ms4-wbm
[6] Mounting bracket MS4/6-WR	■	■	-	-	ms4-wr, ms6-wr
[7] Hex nut MS4/6-WRS	■	■	■	■	ms4-wrs, ms6-wrs
[8] Cover plate VS	■	■	■	■	22
[9] Adapter plate for EN pressure gauge 1/8/1/4 A8/A4	■	■	■	■	22
[10] Pressure gauge MA	■	■	■	■	47
[11] Pressure sensor without display AD7 ... AD10	■	■	■	■	22
[12] Connecting cable NEBU-M8...-LE3	■	■	■	■	47
[13] Pressure sensor with display AD1 ... AD4	■	■	■	■	22
[14] Connecting cable NEBU-M8...-LE3/NEBU-M12...-LE4	■	■	■	■	47
[15] Fully automatic condensate drain, electrically actuated E2/E3/E4	■	■	■	■	22
[16] Padlock LRS-D	■	■	■	■	47
- Mounting bracket MS4/6-WP/WPB/WPE/WPM	-	■	■	■	ms4-wp, ms6-wp

 **New**
Variant EX4, UL1

Filter regulators MS4/MS6-LFR, MS series

Type codes

FESTO

MS	6	-	LFR	-	1/2	-	D7	-	E	R	M	-	AS
Series													
MS	Standard service unit												
Size													
4	Grid dimension 40 mm												
6	Grid dimension 62 mm												
Service function													
LFR	Filter regulator												
Pneumatic connection													
MS4													
1/8	Thread G1/8												
1/4	Thread G1/4												
MS6													
1/4	Thread G1/4												
3/8	Thread G3/8												
1/2	Thread G1/2												
Pressure regulation range													
D6	Pressure regulation range 0.3 ... 7 bar												
D7	Pressure regulation range 0.5 ... 12 bar												
Grade of filtration													
C	5 µm												
E	40 µm												
Bowl guard													
R	Plastic bowl guard												
U	Integrated as metal bowl												
Condensate drain													
M	Manual rotary												
V	Fully automatic												
Security													
AS	Standard rotary knob with detent, lockable via accessories												


Additional variants can be ordered using the modular system ➔ 22

- Connecting plates
- Pressure regulation range
- Condensate drain
- Pressure gauge alternatives
- Alternative pressure gauge scale
- Secondary venting
- Rotary knob
- Security
- Type of mounting
- EU certification
- UL certification
- Alternative flow direction


Filter regulators MS4/MS6-LFR, MS series

Technical data

Manual rotary condensate drain,
with pressure gauge



Semi or fully automatic condensate
drain, with pressure gauge



With this device, the filter and pressure regulator are combined into a single unit. The sintered filter with water separator removes contamination, pipe sinter, rust and condensate from the compressed air.

-  - Flow rate
850 ... 7,200 l/min
-  - Temperature range
-10 ... +60 °C
-  - Operating pressure
0.8 ... 20 bar
-  - www.festo.com

Wearing parts kits
→ 21



- Good regulation characteristics with low hysteresis and primary pressure compensation
- Good particle and condensate separation
- Available with or without secondary venting
- High flow rate
- Directly-actuated diaphragm regulator
- Four pressure regulation ranges:
0.3 ... 4 bar, 0.3 ... 7 bar,
0.5 ... 12 bar and 0.5 ... 16 bar
- Regulator lock for protecting the values against adjustment
- Two pressure gauge connections for different fitting options
- Return flow option for exhausting from output 2 to output 1 already integrated
- Optional pressure sensor
- Optional device variant EX4 for use in potentially explosive areas in zones 1, 2, 21 and 22
- Choice of filter cartridges:
5 µm or 40 µm
- New filter cartridges → 46

General technical data

Size	MS4		MS6		
Pneumatic connection 1, 2	G1/8	G1/4	G1/4	G3/8	G1/2
Constructional design	Filter regulator with/without pressure display				
Regulating function	Output pressure constant, with return flow action, with/without secondary venting				
Type of mounting	Via accessories				
	In-line installation				
	Front panel mounting				
Mounting position	Vertical ±5°				
Grade of filtration [µm]	5				
	40				
Air purity class at the output	Compressed air in accordance with ISO 8573-1:2010 [6:4:4] (Grade of filtration 5 µm) Compressed air in accordance with ISO 8573-1:2010 [7:4:4] (Grade of filtration 40 µm)				
Bowl guard	Plastic bowl guard				
	Integrated as metal bowl				
Condensate drain	Manual rotary				
	Semi-automatic				
	Fully automatic				
	–	Fully automatic, electrically actuated			
Regulator lock	Rotary knob with detent				
	Rotary knob with detent, lockable via accessories				
	Rotary knob with integrated lock				
Pressure regulation range	D5 [bar]	0.3 ... 4			
	D6 [bar]	0.3 ... 7			
	D7 [bar]	0.5 ... 12 (0.5 ... 10 with pressure sensor variant AD... or with UL certification)			
	D8 [bar]	–	0.5 ... 16 (0.5 ... 10 with UL certification)		
Max. hysteresis [bar]	0.25				
Pressure display	Via pressure sensor for displaying output pressure via LCD display and electrical output Via pressure sensor for displaying output pressure via operational status indicator and electrical output Via pressure gauge for displaying output pressure				
Max. condensate volume [cm³]	19 (with plastic bowl guard) 25 (with metal bowl)		38		

• Note: This product conforms to ISO 1179-1 and to ISO 228-1

 **New**
Variant EX4, UL1

Filter regulators MS4/MS6-LFR, MS series

Technical data

FESTO

Standard nominal flow rate q_{nN}^1 [l/min]						
Size	MS4		MS6			
Pneumatic connection	G1/8	G1/4	G1/4	G3/8	G1/2	
D5 – Pressure regulation range 0.3 ... 4 bar						
Grade of filtration	5 µm	900 ²⁾	1,800 ²⁾	2,000 ²⁾	5,500 ²⁾	6,900 ²⁾
	40 µm	1,100 ²⁾	1,900 ²⁾	2,200 ²⁾	6,000 ²⁾	7,200 ²⁾
D6 – Pressure regulation range 0.3 ... 7 bar						
Grade of filtration	5 µm	900	1,500	2,700	5,000	5,600
	40 µm	1,000	1,700	2,800	5,700	6,200
D7 – Pressure regulation range 0.5 ... 12 bar						
Grade of filtration	5 µm	850	1,200	2,200	3,500	4,000
	40 µm	900	1,500	2,500	4,000	4,500
D8 – Pressure regulation range 0.5 ... 16 bar						
Grade of filtration	5 µm	-	-	2,000	3,300	3,800
	40 µm	-	-	2,300	3,500	4,000

1) Measured at $p_1 = 10$ bar and $p_2 = 6$ bar, $\Delta p = 1$ bar

2) Measured at $p_1 = 10$ bar and $p_2 = 3$ bar, $\Delta p = 1$ bar

Operating and environmental conditions								
Condensate drain	Manual rotary M		Semi-automatic H		Fully automatic V			
Size	MS4	MS6	MS4	MS6	MS4	MS6		
Operating pressure [bar]	0.8 ... 14 (0.8 ... 10) ¹⁾	0.8 ... 20 (0.8 ... 10) ¹⁾	1.5 ... 12 (1.5 ... 10) ¹⁾	1.5 ... 12 (1.5 ... 10) ¹⁾	2 ... 12 (2 ... 10) ¹⁾	2 ... 12 (2 ... 10) ¹⁾		
Operating medium	Compressed air in accordance with ISO 8573-1:2010 [-:4:-]			Compressed air in accordance with ISO 8573-1:2010 [-:4:-]		Compressed air in accordance with ISO 8573-1:2010 [7:4:-]		
Ambient temperature [°C]	-10 ... +60 (0 ... +50) ²⁾			+5 ... +60 (+5 ... +50) ²⁾		+1 ... +60 (+1 ... +50) ²⁾		
Temperature of medium [°C]	-10 ... +60 (0 ... +50) ²⁾			+5 ... +60 (+5 ... +50) ²⁾		+1 ... +60 (+1 ... +50) ²⁾		
Storage temperature [°C]	-10 ... +60			-10 ... +60		+1 ... +60		
Corrosion resistance class CRC ³⁾	2							
UL certification	cULus recognized (OL)							

1) Value in brackets applies to MS4/MS6-LFR with UL certification.

2) Value in brackets applies to MS4/MS6-LFR with pressure sensor AD....

3) Corrosion resistance class CRC 2 to Festo standard FN 940070

Moderate corrosion stress. Indoor applications in which condensation may occur. External visible parts with primarily decorative requirements for the surface and which are in direct contact with the ambient atmosphere typical for industrial applications.

ATEX	
EU certification	EX4
ATEX category gas	II 2G
Ex-ignition protection type gas	c T6 X
ATEX category dust	II 2D
Ex-ignition protection type dust	c 60 °C X
ATEX ambient temperature	-10 °C ≤ Ta ≤ +60 °C (manual rotary condensate drain M) +5 °C ≤ Ta ≤ +60 °C (semi-automatic/fully automatic condensate drain H/V)
CE mark (see declaration of conformity)	To EU Explosion Protection Directive (ATEX)


Filter regulators MS4/MS6-LFR, MS series

Technical data

Weight [g]		MS4	MS6
Size			
Rotary knob	Without integrated lock E11	With integrated lock E11	Without integrated lock E11
Filter regulator with plastic bowl guard R	275	400	875
Filter regulator with metal bowl U	475	600	1,087
Filter regulator with metal bowl U and fully automatic condensate drain, electrically actuated E2/E3/E4	–	–	1,627
		1,800	2,070

Materials

Sectional view



Filter regulator	
[1] Housing	Die-cast aluminium
[2] Rotary knob	PA/POM
Rotary knob with integrated lock E11	Aluminium
[3] Plastic bowl guard	PC
[4] Metal bowl	Wrought aluminium alloy, die-cast aluminium
Inspection window	PA
[5] Filter element	PE
[6] Spin disc	POM
[7] Filter holder	POM
[8] Separating plate	POM
[9] Stabilising disc	POM
[10] Diaphragm	NBR
[11] Spring	Steel
– Seals	NBR
Note on materials	RoHS-compliant (not with variant E2, E3 or E4) Free of copper and PTFE only with cover plate VS

**-○- New
Variant EX4, UL1**

Filter regulators MS4/MS6-LFR, MS series

Technical data

FESTO


Standard flow rate q_n as a function of output pressure p_2

Pressure regulation range D6 or D7


Grade of filtration 5 μm

MS4-LFR-1/8

Input pressure $p_1 = 10$ bar





Grade of filtration 40 μm



MS4-LFR-1/4

Input pressure $p_1 = 10$ bar



Filter regulators MS4/MS6-LFR, MS series


Technical data

Standard flow rate q_n as a function of output pressure p_2

Pressure regulation range D6 or D7


MS6-LFR-1/4

Input pressure $p_1 = 10$ bar





Grade of filtration 5 μm

Grade of filtration 40 μm





MS6-LFR-3/8

Input pressure $p_1 = 10$ bar



MS6-LFR-1/2

Input pressure $p_1 = 10$ bar



**- New
Variant EX4, UL1**

Filter regulators MS4/MS6-LFR, MS series


Technical data

FESTO

Dimensions – Standard

Integrated pressure gauge, display unit [bar], standard rotary knob with detent, manual rotary condensate drain

Download CAD data → www.festo.com



[1] Installation dimensions

→ Flow direction

Type	B1	B2	B3		D1	D2	L1		L2	L3	L4	L5	L6		L7
			Pressure gauge	Standard scale			Bowl guard	Plastic					Bowl guard	Plastic	
MS4-LFR-1/8	40	21	57	58.5	G1/8	37.2	140.6	158.2	27	51.1	58.5	25	17.7	17.7	2
MS4-LFR-1/4					G1/4										
MS6-LFR-1/4	62	31	77	78.5	G1/4	51	189	194.4	39	86	84	68	15.8	19	5
MS6-LFR-3/8					G3/8										
MS6-LFR-1/2					G1/2										


• Note: This product conforms to ISO 1179-1 and to ISO 228-1

Filter regulators MS4/MS6-LFR, MS series

Technical data


Dimensions – Pressure gauge alternatives

Cover plate VS



Download CAD data → www.festo.com

Adapter plate A8/A4 for EN pressure gauge 1/8/1/4, without pressure gauge



Type	B2	B3	D1	D4
MS4-LFR-1/8...-VS	21	54	G1/8	–
MS4-LFR-1/4...-VS			G1/4	
MS4-LFR-1/8...-A8	21	58.5	G1/8	G1/8
MS4-LFR-1/4...-A8			G1/4	
MS4-LFR-1/8...-A4	21	58.5	G1/8	G1/4
MS4-LFR-1/4...-A4			G1/4	
MS6-LFR-1/4...-VS	31	76	G1/4	–
MS6-LFR-3/8...-VS			G3/8	
MS6-LFR-1/2...-VS			G1/2	
MS6-LFR-1/4...-A4	31	78.5	G1/4	G1/4
MS6-LFR-3/8...-A4			G3/8	
MS6-LFR-1/2...-A4			G1/2	

Note: This product conforms to ISO 1179-1 and to ISO 228-1

**New
Variant EX4, UL1**


Filter regulators MS4/MS6-LFR, MS series

Technical data

FESTO

Dimensions – Pressure gauge alternatives

Pressure sensor with LCD display AD1 ... AD4



Variant AD1:
SDE1-D10-G2-MS-L-P1-M8 with
3-pin plug M8x1, 1 switching
output PNP

Variant AD2:
SDE1-D10-G2-MS-L-N1-M8 with
3-pin plug M8x1, 1 switching
output NPN


Download CAD data → www.festo.com
Technical data → Internet: sde1

Variant AD3:
SDE1-D10-G2-MS-L-PI-M12 with
4-pin plug M12x1, 1 switching
output PNP and 4 ... 20 mA
analogue

Variant AD4:
SDE1-D10-G2-MS-L-NI-M12 with
4-pin plug M12x1, 1 switching
output NPN and 4 ... 20 mA
analogue

Pressure sensor without LCD display (operational status indicator only) AD7 ... AD10

Technical data → Internet: sde5



Variant AD7:
SDE5-D10-O-...-P-M8 with 3-pin
plug M8x1, threshold value
comparator, 1 switching output PNP,
N/O contact

Variant AD8:
SDE5-D10-C-...-P-M8 with 3-pin
plug M8x1, threshold value
comparator, 1 switching output PNP,
N/C contact

Variant AD9:
SDE5-D10-O3-...-P-M8 with 3-pin
plug M8x1, window comparator,
1 switching output PNP, N/O contact

Variant AD10:
SDE5-D10-C3-...-P-M8 with 3-pin
plug M8x1, window comparator,
1 switching output PNP, N/C contact

Type	B2	B3	D1	D6	L5	L6
MS4-LFR-1/8-...-AD1/AD2	21	82.6	G $\frac{1}{8}$	M8x1	35.1	46.7
MS4-LFR-1/4-...-AD1/AD2			G $\frac{1}{4}$			
MS4-LFR-1/8-...-AD3/AD4	21	82.6	G $\frac{1}{8}$	M12x1	35.1	55.8
MS4-LFR-1/4-...-AD3/AD4			G $\frac{1}{4}$			
MS4-LFR-1/8-...-AD7/AD8/AD9/AD10	21	59.1	G $\frac{1}{8}$	M8x1	-	-
MS4-LFR-1/4-...-AD7/AD8/AD9/AD10			G $\frac{1}{4}$			
MS6-LFR-1/4-...-AD1/AD2	31	103	G $\frac{1}{4}$	M8x1	35.1	46.7
MS6-LFR-3/8-...-AD1/AD2			G $\frac{3}{8}$			
MS6-LFR-1/2-...-AD1/AD2			G $\frac{1}{2}$			
MS6-LFR-1/4-...-AD3/AD4	31	103	G $\frac{1}{4}$	M12x1	35.1	55.8
MS6-LFR-3/8-...-AD3/AD4			G $\frac{3}{8}$			
MS6-LFR-1/2-...-AD3/AD4			G $\frac{1}{2}$			
MS6-LFR-1/4-...-AD7/AD8/AD9/AD10	31	79	G $\frac{1}{4}$	M8x1	-	-
MS6-LFR-3/8-...-AD7/AD8/AD9/AD10			G $\frac{3}{8}$			
MS6-LFR-1/2-...-AD7/AD8/AD9/AD10			G $\frac{1}{2}$			

Note: This product conforms to ISO 1179-1 and to ISO 228-1

Filter regulators MS4/MS6-LFR, MS series

Technical data

Dimensions – Rotary knob

For installation into control panel or attaching with hex nut MS4/6-WRS (not included in the scope of delivery)




Download CAD data → www.festo.com

Standard rotary knob with detent

Standard rotary knob with detent,
lockable via accessories AS

Rotary knob with integrated lock



E11



[2] Installation dimensions

Long rotary knob with detent LD

Long rotary knob with detent,
lockable via accessories LD-AS



[3] For pressure adjustment: pull out telescopic rotary knob fully

Type	B4	B5	D2	D3 +1	L3	L8	L9	L10	L11	=C1
MS4-LFR...	–	–	37.2	30	51.1	13	6	–	6	36
MS4-LFR...-AS	48.3	29.7			60.2					
MS4-LFR...-E11	–	–			76					
MS4-LFR...-LD	–	–			51.1				76.8	
MS4-LFR...-LD-AS	48.3	29.7	37.2	–	60.2	–	–	76.8	–	–
MS6-LFR...	–	–			86					
MS6-LFR...-AS	64.4	39			95.5					
MS6-LFR...-E11	–	–			112.1				60	
MS6-LFR...-LD	–	–	51	–	86	–	–	139	–	–
MS6-LFR...-LD-AS	64.4	39			95.5				148.5	

**- New
Variant EX4, UL1**


Filter regulators MS4/MS6-LFR, MS series

Technical data


FESTO

Dimensions – Condensate drain

Manual rotary M




Semi-automatic H



Download CAD data → www.festo.com

Fully automatic V




Type	L6
Plastic bowl guard	
MS4-LFR-...-M	17.7
MS6-LFR-...-M	15.8
Metal bowl	
MS4-LFR-...-M	17.7
MS6-LFR-...-M	19

Type	L6
Plastic bowl guard	
MS4-LFR-...-H	22.1
MS6-LFR-...-H	20.2
Metal bowl	
MS4-LFR-...-H	22.1
MS6-LFR-...-H	22.8

Type	L6
Plastic bowl guard	
MS4-LFR-...-V	20.4
MS6-LFR-...-V	18.5
Metal bowl	
MS4-LFR-...-V	20.4
MS6-LFR-...-V	22

Fully automatic, electrically actuated E2/E3/E4



Technical data → Internet: pwea

Condensate drain PWEA:

- [2] Electrical connection: Screw terminal PG9
- [3] Connection 360° rotatable for plastic tubing PUN-H-12x2

Filter regulators MS4/MS6-LFR, MS series

Technical data

Ordering data

Pressure regulation range 0.3 ... 7 bar, integrated pressure gauge, display unit [bar], standard rotary knob with detent, lockable via accessories

Size	Condensate drain	Connection	Grade of filtration 5 µm		Grade of filtration 40 µm	Part No.	Type
			Part No.	Type			
Plastic bowl guard							
MS4	Manual rotary	G1/8	529160	MS4-LFR-1/8-D6-CRM-AS	529164	MS4-LFR-1/8-D6-ERM-AS	
		G1/4	529144	MS4-LFR-1/4-D6-CRM-AS	529148	MS4-LFR-1/4-D6-ERM-AS	
	Fully automatic	G1/8	529162	MS4-LFR-1/8-D6-CRV-AS	529166	MS4-LFR-1/8-D6-ERV-AS	
		G1/4	529146	MS4-LFR-1/4-D6-CRV-AS	529150	MS4-LFR-1/4-D6-ERV-AS	
MS6	Manual rotary	G1/4	529196	MS6-LFR-1/4-D6-CRM-AS	529200	MS6-LFR-1/4-D6-ERM-AS	
		G3/8	529216	MS6-LFR-3/8-D6-CRM-AS	529220	MS6-LFR-3/8-D6-ERM-AS	
		G1/2	529176	MS6-LFR-1/2-D6-CRM-AS	529180	MS6-LFR-1/2-D6-ERM-AS	
	Fully automatic	G1/4	-	-	529202	MS6-LFR-1/4-D6-ERV-AS	
		G3/8	529218	MS6-LFR-3/8-D6-CRV-AS	529222	MS6-LFR-3/8-D6-ERV-AS	
		G1/2	529178	MS6-LFR-1/2-D6-CRV-AS	529182	MS6-LFR-1/2-D6-ERV-AS	

Ordering data

Pressure regulation range 0.5 ... 12 bar, integrated pressure gauge, display unit [bar], standard rotary knob with detent, lockable via accessories

Size	Condensate drain	Connection	Grade of filtration 5 µm		Grade of filtration 40 µm	Part No.	Type
			Part No.	Type			
Plastic bowl guard							
MS4	Manual rotary	G1/8	529168	MS4-LFR-1/8-D7-CRM-AS	529172	MS4-LFR-1/8-D7-ERM-AS	
		G1/4	529152	MS4-LFR-1/4-D7-CRM-AS	529156	MS4-LFR-1/4-D7-ERM-AS	
	Fully automatic	G1/8	529170	MS4-LFR-1/8-D7-CRV-AS	529174	MS4-LFR-1/8-D7-ERV-AS	
		G1/4	529154	MS4-LFR-1/4-D7-CRV-AS	529158	MS4-LFR-1/4-D7-ERV-AS	
MS6	Manual rotary	G1/4	529204	MS6-LFR-1/4-D7-CRM-AS	529208	MS6-LFR-1/4-D7-ERM-AS	
		G3/8	529224	MS6-LFR-3/8-D7-CRM-AS	529228	MS6-LFR-3/8-D7-ERM-AS	
		G1/2	529184	MS6-LFR-1/2-D7-CRM-AS	529188	MS6-LFR-1/2-D7-ERM-AS	
	Fully automatic	G1/4	529206	MS6-LFR-1/4-D7-CRV-AS	529210	MS6-LFR-1/4-D7-ERV-AS	
		G3/8	529226	MS6-LFR-3/8-D7-CRV-AS	529230	MS6-LFR-3/8-D7-ERV-AS	
		G1/2	529186	MS6-LFR-1/2-D7-CRV-AS	529190	MS6-LFR-1/2-D7-ERV-AS	
Integrated as metal bowl							
MS4	Manual rotary	G1/4	-	-	535724	MS4-LFR-1/4-D7-EUM-AS	
	Fully automatic	G1/4	535720	MS4-LFR-1/4-D7-CUV-AS	535722	MS4-LFR-1/4-D7-EUV-AS	
MS6	Manual rotary	G3/8	-	-	529232	MS6-LFR-3/8-D7-EUM-AS	
		G1/2	530338	MS6-LFR-1/2-D7-CUM-AS	529192	MS6-LFR-1/2-D7-EUM-AS	
	Fully automatic	G3/8	530348	MS6-LFR-3/8-D7-CUV-AS	529234	MS6-LFR-3/8-D7-EUV-AS	
		G1/2	530340	MS6-LFR-1/2-D7-CUV-AS	529194	MS6-LFR-1/2-D7-EUV-AS	

Ordering data – Wearing parts kits

Size	Part No.	Type
MS4	673647	MS4-LFR
MS6	673648	MS6-LFR

 **New**
Variant EX4, UL1

Filter regulators MS4/MS6-LFR, MS series

Ordering data – Modular products

FESTO

M Mandatory data →								
Module No.	Series	Size	Function	Connection size	Pressure regulation range	Grade of filtration	Bowl	Condensate drain
526489	MS	4,	LFR	1/8, 1/4, 3/8, 1/2, AGA, AGB, AGC, AGD, AGE	D5, D6, D7, D8	E, C	R, U	M, H, V, E2, E3, E4
526490		6						
Order example	526489	MS	4	- LFR	- AGA	- D6	- C	- R
								- M

Ordering table								
Grid dimension	[mm]	40	62	Conditions	Code		Enter code	
M Module No.	526489		526490					
Series	Standard				MS		MS	
Size	4	6			...			
Function	Filter regulator				-LFR		-LFR	
Connection size	Thread G1/8 Thread G1/4 – – Connecting plate G1/8 Connecting plate G1/4 Connecting plate G3/8 – –	– Thread G1/4 Thread G3/8 Thread G1/2 – Connecting plate G1/4 Connecting plate G3/8 Connecting plate G1/2 Connecting plate G3/4			[1] [1] [1] [1] -AGA -AGB -AGC -AGD -AGE	-1/8 -1/4 -3/8 -1/2 -AGA -AGB -AGC -AGD -AGE		
Pressure regulation range	0.3 ... 4 bar 0.3 ... 7 bar 0.5 ... 12 bar –	0.3 ... 4 bar 0.3 ... 7 bar 0.5 ... 12 bar 0.5 ... 16 bar			[1]	-D5 -D6 -D7 -D8		
Grade of filtration	40 µm 5 µm					-E -C		
Bowl	Plastic bowl with plastic bowl guard Metal bowl					-R -U		
Condensate drain	Manual Semi-automatic (P1 max. 12 bar) Fully automatic (P1 max. 12 bar)					-M -H -V		
External, fully automatic, electrical	– – –	110 V AC, terminals 230 V AC, terminals 24 V DC, terminals			[1] [3] [1] [3] [1] [3]	-E2 -E3 -E4		

[1] 1/8, 1/4, 3/8, 1/2, D8, E2, E3, E4, AD1 ... AD4, AD7 ... AD10, E11, WPM
Not with EU certification EX4

[2] H, V Not with pressure regulation range D8

[3] E2, E3, E4 Only with metal bowl U

Transfer order code

MS **LFR** **-** **-** **-** **-**

Filter regulators MS4/MS6-LFR, MS series

Ordering data – Modular products

→ Options

Pressure gauge alternatives	Alternative pressure gauge scale	Secondary venting	Rotary knob	Security	Type of mounting	EU certification	UL certification	Flow direction
VS, A8, A4, RG, AD1 ... AD4, AD7 ... AD10	PSI, MPA	OS	LD	AS, E11	WR, WP, WPM, WB, WBM	EX4	UL1	Z
- A8 -	-	- LD -	- AS -	- WPM -	-	-	-	-

Ordering table

Grid dimension [mm]	40	62	Conditions	Code	Enter code
<input type="checkbox"/> Pressure gauge alternatives	Cover plate			-VS	
	Adapter plate for EN pressure gauge 1/8, without pressure gauge	-		-A8	
	Adapter plate for EN pressure gauge 1/4, without pressure gauge			-A4	
	Integrated pressure gauge, red-green scale	[4]		-RG	
	Pressure sensor with display, plug M8, 1 switching output PNP, 3-pin	[1][5]		-AD1	
	Pressure sensor with display, plug M8, 1 switching output NPN, 3-pin	[1][5]		-AD2	
	Pressure sensor with display, plug M12, 1 switching output PNP, 4-pin, analogue output 4 ... 20 mA	[1][5]		-AD3	
	Pressure sensor with display, plug M12, 1 switching output NPN, 4-pin, analogue output 4 ... 20 mA	[1][5]		-AD4	
	Pressure sensor without display, plug M8, threshold value comparator, PNP, N/O contact	[1][5]		-AD7	
	Pressure sensor without display, plug M8, threshold value comparator, PNP, N/C contact	[1][5]		-AD8	
	Pressure sensor without display, plug M8, window comparator, PNP, N/O contact	[1][5]		-AD9	
	Pressure sensor without display, plug M8, window comparator, PNP, N/C contact	[1][5]		-AD10	
<input type="checkbox"/> Alternative pressure gauge scale	psi	[6]		-PSI	
	MPa	[6]		-MPA	
<input type="checkbox"/> Secondary venting	Without secondary venting			-OS	
<input type="checkbox"/> Rotary knob	Long rotary knob	[7]		-LD	
<input type="checkbox"/> Security	Lockable via accessories			-AS	
	With integrated lock	[1]		-E11	
<input type="checkbox"/> Type of mounting	Mounting bracket with knurled nut for regulator head	[8]		-WR	
	Mounting bracket	[9]		-WP	
	Mounting bracket	[1][9]		-WPM	
	Mounting bracket			-WB	
	Mounting bracket	-		-WBM	
<input type="checkbox"/> EU certification	II 2GD to EU Directive 94/9/EG			-EX4	
<input type="checkbox"/> UL certification	cULus, ordinary location for Canada and USA			-UL1	
<input type="checkbox"/> Flow direction	Flow direction from right to left			-Z	

[4] RG Alternative pressure gauge scale PSI serves only as an auxiliary scale

[5] AD1 ... AD4, AD7 ... AD10

Measuring range max. 10 bar

Not with pressure regulation range D8

[6] PSI, MPA Not with pressure gauge alternatives VS, A8, A4, RG, AD1 ... AD4, AD7 ... AD10

[7] LD Not with security E11

[8] WR Not with long rotary knob LD

[9] WP, WPM Only with connecting plate AGA, AGB, AGC, AGD or AGE

Transfer order code


- - - - - - - - -

**New
Variant EX4, UL1**

Filter regulators MS9-LFR, MS series

Peripherals overview

FESTO



Note

Additional accessories:

- Module connector for combinations with size MS6, MS9 or MS12
- ➔ Internet: rmv, armv

Mounting attachments and accessories

	Individual unit			Combination	➔ Page/ Internet	
	With female thread ¾ or 1	With connecting plate AG...		Module without connect- ing thread, without connecting plate G		
		Without EU certification EX4	With EU certification EX4			
[1] Connecting plate-SET MS9-AG...	-	■	■	■	ms9-ag	
[2] Module connector MS9-MV	-	-	-	■	ms9-mv	
[3] Mounting bracket MS9-WP	■	■	■	■	ms9-wp	
[4] Mounting bracket MS9-WPB	■	■	■	■	ms9-wp	
[5] Mounting bracket MS9-WPM	■	■	-	■	ms9-wp	
[6] MS pressure gauge AG	■	■	■	■	34	
[7] Cover plate VS	■	■	■	■	34	
[8] Pressure sensor without display AD7 ... AD10	■	■	-	■	34	
[9] Connecting cable NEBU-M8...-LE3	■	■	-	■	47	
[10] Adapter plate for EN pressure gauge ¼ A4	■	■	■	■	34	
[11] Pressure gauge MA	■	■	■	■	47	
[12] Padlock LRVS-D	■	■	■	■	47	
[13] Condensate drain, fully automatic, electrically actuated E2/E3/E4	■	■	-	■	34	

Filter regulators MS9-LFR, MS series

Type codes

MS	9	-	LFR	-	G	-	D6	-	E	U	M	-	DI	-	AG	-	BAR	-	AS
Series																			
MS	Standard service unit																		
9	Grid dimension 90 mm																		
Service function																			
LFR	Filter regulator																		
Connection size																			
G	Module without connecting thread, without connecting plate																		
Pressure regulation range/operation mode																			
D6	0.5 ... 7 bar, manually operated																		
D7	0.5 ... 12 bar, manually operated																		
Grade of filtration																			
C	5 µm																		
E	40 µm																		
Bowl guard																			
U	Integrated as metal bowl																		
Condensate drain																			
M	Manual rotary																		
V	Fully automatic																		
Regulator type																			
	Piloted																		
DI	Directly actuated (only with pressure regulation range D6)																		
Pressure gauge																			
AG	MS pressure gauge																		
Pressure gauge scale																			
BAR	Bar																		
Security																			
AS	Rotary knob with detent, can be locked using accessories																		

Additional variants can be ordered using the modular system → 34

- Connecting plates
- Pressure regulation range
- Condensate drain
- Pressure gauge alternatives
- Alternative pressure gauge scale
- Secondary venting
- Security lock
- Type of mounting
- EU certification
- UL certification
- Alternative flow direction


**New
Variant EX4, UL1**

FESTO

Filter regulators MS9-LFR, MS series


Technical data

Manual rotary condensate drain, with pressure gauge



- - Flow rate
6,000 ... 23,000 l/min
- - Temperature range
-10 ... +60 °C
- - Supply pressure
1 ... 20 bar

Semi or fully automatic condensate drain, with pressure gauge



With this component, the filter and pressure regulator are combined into a single unit. The sintered filter with water separator removes contamination, pipe sinter, rust and condensate from the compressed air.



- Good regulation characteristics with low hysteresis and primary pressure compensation
- Good particle and condensate separation
- Piloted or directly actuated filter-diaphragm regulator
- High flow rates
- Available with or without secondary venting
- Four pressure regulation ranges:
0.5 ... 4 bar, 0.5 ... 7 bar,
0.5 ... 12 bar and 0.5 ... 16 bar
- Pressure gauge connection for different fitting options
- Available with manual, semi-automatic, fully automatic or fully automatic, electrically actuated condensate drain
- Actuator lock to protect set values against adjustment
- Optional pressure sensor
- Choice of filter cartridges: 5 µm or 40 µm
- New filter cartridges → 46
- Optional device variant EX4 for use in potentially explosive areas in zones 1, 2, 21 and 22

General technical data

Pneumatic connection 1, 2	G3/4	G1	G1/2 ... G1½ (with connecting plate AG...)	– (without connecting thread G)			
Design	Piloted filter-diaphragm regulator						
	Directly actuated filter-diaphragm regulator						
Regulator type	Piloted	Output pressure constant, with return flow action, with primary pressure compensation, with secondary venting					
	Directly actuated	Output pressure constant, with return flow action, with/without secondary venting					
Type of mounting	Via accessories						
	In-line installation						
Mounting position	Vertical ±5°						
Grade of filtration [µm]	5 (air purity class at the output: compressed air in accordance with ISO 8573-1:2010 [6:4:4]) 40 (air purity class at the output: compressed air in accordance with ISO 8573-1:2010 [7:4:4])						
Bowl guard	Integrated as metal bowl						
Condensate drain	Manual rotary Semi-automatic Fully automatic Fully automatic, electrically actuated						
Security	Rotary knob with detent Rotary knob with detent, can be locked using accessories Rotary knob with integrated lock						
Pressure regulation range/operation mode D5 [bar]	0.5 ... 4, manually operated						
D6 [bar]	0.5 ... 7, manually operated						
D7 [bar]	0.5 ... 12, manually operated (0.5 ... 10 with pressure sensor variant AD...)						
D8 [bar]	0.5 ... 16, manually operated (0.5 ... 10 with pressure sensor variant AD...)						
Max. pressure hysteresis [bar]	0.4						
Pressure display	Via pressure sensor for displaying output pressure via operational status indicator and electrical output Via pressure gauge for displaying output pressure Via pressure gauge with red/green scale for displaying output pressure G1/4 prepared						
Max. condensate volume [ml]	220						

Note: This product conforms to ISO 1179-1 and to ISO 228-1

Filter regulators MS9-LFR, MS series

Technical data

Standard nominal flow rate $q_{nN}^{1,2)} [l/min]$				
Design	Piloted filter-diaphragm regulator		Directly actuated filter-diaphragm regulator DI	
Pneumatic connection	G3/4	G1	G3/4	G1
D5 – Pressure regulation range 0.5 ... 4 bar				
Grade of filtration	5 µm	17,000 ³⁾	20,000 ³⁾	16,000 ³⁾
	40 µm	18,000 ³⁾	23,000 ³⁾	16,000 ³⁾
D6 – Pressure regulation range 0.5 ... 7 bar				
Grade of filtration	5 µm	15,000	18,000	12,000
	40 µm	16,000	20,000	12,000
D7 – Pressure regulation range 0.5 ... 12 bar				
Grade of filtration	5 µm	15,000	18,000	–
	40 µm	16,000	20,000	–
D8 – Pressure regulation range 0.5 ... 16 bar				
Grade of filtration	5 µm	15,000	18,000	–
	40 µm	16,000	20,000	–

1) All values ±15%

2) Measured at p1 = 10 bar and p2 = 6 bar, Δp = 1 bar

3) Measured at p1 = 10 bar and p2 = 4 bar, Δp = 1 bar

Operating and environmental conditions				
Condensate drain	Manual rotary M	Semi-automatic H	Fully automatic V	Fully automatic, electrically actuated E2/E3/E4
Operating pressure [bar]	1 ... 20	1.5 ... 12	2 ... 12	1 ... 16
Operating medium	Compressed air in accordance with ISO 8573-1:2010 [-:4:-]	Compressed air in accordance with ISO 8573-1:2010 [-:4:-]	Compressed air in accordance with ISO 8573-1:2010 [7:4:-]	Compressed air in accordance with ISO 8573-1:2010 [-:4:-]
Ambient temperature [°C]	-10 ... +60	+5 ... +60	+5 ... +60	+1 ... +60
Ambient temperature with pressure sensor AD [°C]	0 ... +50	+5 ... +50	+5 ... +50	+1 ... +50
Temperature of medium [°C]	-10 ... +60	+5 ... +60	+5 ... +60	+1 ... +60
Temperature of medium with pressure sensor AD [°C]	0 ... +50	+5 ... +50	+5 ... +50	+1 ... +50
Storage temperature [°C]	-10 ... +60	+5 ... +60	+5 ... +60	+1 ... +60
Corrosion resistance class CRC ¹⁾	2			
Certification (variant UL1)	cULus recognized (OL)			

1) Corrosion resistance class CRC 2 to Festo standard FN 940070

Moderate corrosion stress. Indoor applications in which condensation may occur. External visible parts with primarily decorative requirements for the surface and which are in direct contact with the ambient atmosphere typical for industrial applications.

ATEX	
EU certification	EX4
ATEX category gas	II 2G
Ex-ignition protection type gas	c T6 X
ATEX category dust	II 2D
Ex-ignition protection type dust	c T60 °C X
ATEX ambient temperature	-10 °C ≤ Ta ≤ +60 °C (manual rotary condensate drain M) +5 °C ≤ Ta ≤ +60 °C (semi-automatic/fully automatic condensate drain H/V)
CE mark (see declaration of conformity)	To EU Explosion Protection Directive (ATEX)

Weight [g]		
Rotary knob	Without integrated lock E11	With integrated lock E11
Filter regulator with metal bowl U	2,400	2,700
Filter regulator with metal bowl U and fully automatic condensate drain, electrically actuated E2/E3/E4	2,800	3,100

**- New
Variant EX4, UL1**


Filter regulators MS9-LFR, MS series

Technical data

FESTO

Materials

Sectional view




Filter regulator	
[1] Housing	Die-cast aluminium
[2] Rotary knob	PA
Rotary knob with integrated lock E11	Aluminium
[3] Bowl	Wrought aluminium alloy
Inspection window	PA
[4] Filter element	PE
[5] Spin disc	POM
[6] Filter holder	POM
[7] Separating plate	POM
[8] Diaphragm	NBR
[9] Valve stem	Wrought aluminium alloy, NBR, POM
– Cover	PA reinforced
– Connecting plate, module connector, mounting bracket	Die-cast aluminium
– Seals	NBR
Note on materials	RoHS-compliant (not with variant E2, E3 or E4)


Standard flow rate q_n as a function of output pressure p_2 at operating pressure $p_1 = 10$ bar

Piloted filter-diaphragm regulator

Grade of filtration 5 µm, pneumatic connection G $\frac{3}{4}$



Grade of filtration 40 µm, pneumatic connection G $\frac{3}{4}$




Filter regulators MS9-LFR, MS series

Technical data


Standard flow rate q_n as a function of output pressure p_2 at operating pressure $p_1 = 10$ bar

Piloted filter-diaphragm regulator

Grade of filtration 5 µm, pneumatic connection G1




Grade of filtration 40 µm, pneumatic connection G1




Standard flow rate q_n as a function of output pressure p_2 at operating pressure $p_1 = 10$ bar

Directly actuated filter-diaphragm regulator DI


Grade of filtration 5 µm, pneumatic connection G $\frac{3}{4}$




Grade of filtration 40 µm, pneumatic connection G $\frac{3}{4}$



Grade of filtration 5 µm, pneumatic connection G1



Grade of filtration 40 µm, pneumatic connection G1



D5: 0.5 ... 4 bar

D6: 0.5 ... 7 bar

**- New
Variant EX4, UL1**

Filter regulators MS9-LFR, MS series


Technical data

FESTO

Dimensions – Basic version

Without connecting thread G, cover plate VS, rotary knob with detent

Download CAD data ➔ www.festo.com




Type	B1	B2	B3	L1		L2		L3	L4		L5	L6
				pilot actuated	directly actuated DI	pilot actuated	directly actuated DI		pilot actuated	directly actuated DI		
MS9-LFR-G	90	45	109	320	313	69	62	86	127	120	150	34.5

Filter regulators MS9-LFR, MS series

Technical data


Dimensions – Connecting thread/connecting plate

With connecting thread 3/4 or 1



[2] Mounting screw M6xmin.90 to DIN 912 (not included in the scope of delivery) for wall mounting without mounting bracket

With connecting plate AG...



[3] Earthing screw M4x8 (only with MS9...-EX4)

Download CAD data → www.festo.com

→ Flow direction

Type	B4	B5	B6	B7		B8	D1	D4	D5	L7	L8	T1	EX4	=G
					EX4									
MS9-LFR-3/4	90	104	91.5	-	-	-	G3/4	11	6.5	66	-	6	-	-
MS9-LFR-1							G1							
MS9-LFR-AGD						132	G1/2							30
MS9-LFR-AGE						132	G3/4							36
MS9-LFR-AGF					112	122	142	G1	-	-	35	-		41
MS9-LFR-AGG							162	G1 1/4						50
MS9-LFR-AGH							176	G1 1/2						55


Note: This product conforms to ISO 1179-1 and to ISO 228-1

Dimensions – Pressure gauge alternatives

Integrated MS pressure gauge with standard scale AG or red/green scale RG, display unit [bar]

Download CAD data → www.festo.com

Adapter plate A4 for EN pressure gauge 1/4, without pressure gauge



→ Flow direction

Type	B2	B3	B9	D2
MS9-LFR...-AG/RG	45	109	-	-
MS9-LFR...-A4		-	110	G1/4

Note: This product conforms to ISO 1179-1 and to ISO 228-1

**New
Variant EX4, UL1**


Filter regulators MS9-LFR, MS series

Technical data

FESTO

Dimensions – Pressure gauge alternatives

Pressure sensor without LCD display (operational status indicator only) AD7 ... AD10



Download CAD data → www.festo.com

Technical data → Internet: sde5

Variant AD7:
SDE5-D10-O...-P-M8 with
3-pin plug M8x1, threshold
value comparator, 1 switching
output PNP, N/O contact

Variant AD9:
SDE5-D10-O3...-P-M8 with
3-pin plug M8x1, window
comparator, 1 switching
output PNP, N/O contact

Variant AD8:
SDE5-D10-C...-P-M8 with
3-pin plug M8x1, threshold
value comparator, 1 switching
output PNP, N/C contact

Variant AD10:
SDE5-D10-C3...-P-M8 with
3-pin plug M8x1, window
comparator, 1 switching
output PNP, N/C contact


Type	B2	B11	D3
MS9-LFR-...-AD7/AD8/AD9/AD10	45	112	M8

Dimensions – Rotary knob

Rotary knob with detent

Rotary knob with detent, can be
locked using accessories AS

Rotary knob with integrated lock
E11



Download CAD data → www.festo.com


Type	B1	D1	L1	L2	L3
MS9-LFR	–	52	–	86	–
MS9-LFR-...-AS	65	52	–	96	–
MS9-LFR-...-E11	–	52	174	114	25

Filter regulators MS9-LFR, MS series

Technical data


Dimensions – Condensate drain

Manual rotary M/fully automatic V



Barbed connector for plastic tubing PCN-4


Semi-automatic H



Download CAD data → www.festo.com

Fully automatic, electrically actuated E2/E3/E4

Technical data → Internet: pwea



Condensate drain PWEA:

- [2] Electrical connection: Screw terminal PG9
- [3] Connection 360° rotatable for plastic tubing PUN-H-12x2

Type	B1	D1	H1	L1	L2	L3
MS9-LFR-...-M/V		5				
MS9-LFR-...-H		6	34.5			
MS9-LFR-...-E2/E3/E4	72	–	178	140	108	15

Ordering data

Pressure regulation range 0.5 ... 7 bar, integrated pressure gauge, display unit [bar], rotary knob with detent, can be locked using accessories

Size	Condensate drain	Connection	Grade of filtration 5 µm		Grade of filtration 40 µm	
			Part No.	Type	Part No.	Type
Piloted filter-diaphragm regulator						
MS9	Manual rotary	–	564114	MS9-LFR-G-D6-CUM-AG-BAR-AS	564110	MS9-LFR-G-D6-EUM-AG-BAR-AS
	Fully automatic	–	564115	MS9-LFR-G-D6-CUV-AG-BAR-AS	564111	MS9-LFR-G-D6-EUV-AG-BAR-AS
Directly actuated filter-diaphragm regulator						
MS9	Manual rotary	–	564116	MS9-LFR-G-D6-CUM-DI-AG-BAR-AS	564112	MS9-LFR-G-D6-EUM-DI-AG-BAR-AS
	Fully automatic	–	564117	MS9-LFR-G-D6-CUV-DI-AG-BAR-AS	564113	MS9-LFR-G-D6-EUV-DI-AG-BAR-AS

Ordering data

Pressure regulation range 0.5 ... 12 bar, integrated pressure gauge, display unit [bar], rotary knob with detent, can be locked using accessories

Size	Condensate drain	Connection	Grade of filtration 5 µm		Grade of filtration 40 µm	
			Part No.	Type	Part No.	Type
Piloted filter-diaphragm regulator						
MS9	Manual rotary	–	564120	MS9-LFR-G-D7-CUM-AG-BAR-AS	564118	MS9-LFR-G-D7-EUM-AG-BAR-AS
	Fully automatic	–	564121	MS9-LFR-G-D7-CUV-AG-BAR-AS	564119	MS9-LFR-G-D7-EUV-AG-BAR-AS

 **New**
Variant EX4, UL1

FESTO

Filter regulators MS9-LFR, MS series

Ordering data – Modular products

M Mandatory data								
Module No.	Series	Size	Function	Connection size	Pressure range/operation mode	Grade of filtration	Bowl	Condensate drain
562531	MS	9	LFR	3/4, 1, AGD, AGE, AGF, AGG, AGH, G	D5, D6, D7, D8	E, C	U	M, H, V, E2, E3, E4
Ordering example	562531	MS	9	- LFR	- G	- D5	- E	- U
								- M

Ordering table		
Grid dimension	[mm]	90
M Module No.	562531	
Series	Standard	MS
Size	9	9
Function	Filter regulator	-LFR
Connection size	Thread G3/4 Thread G1 Connecting plate G1/2 Connecting plate G3/4 Connecting plate G1 Connecting plate G1 1/4 Connecting plate G1 1/2 Module without connecting thread, without connecting plate	[1] -3/4 [1] -1 -AGD -AGE -AGF -AGG -AGH [1] -G
Pressure range/operation mode	0.5 ... 4 bar, manually operated 0.5 ... 7 bar, manually operated 0.5 ... 12 bar, manually operated 0.5 ... 16 bar, manually operated	-D5 -D6 -D7 [1] -D8
Grade of filtration	40 µm 5 µm	-E -C
Bowl	Metal bowl	-U
Condensate drain	Manual Semi-automatic (P1 max. 12 bar) Fully automatic (P1 max. 12 bar)	-M -H -V
External, fully automatic, electric	110 V AC, terminals (P1 max. 16 bar) 230 V AC, terminals (P1 max. 16 bar) 24 V DC, terminals (P1 max. 16 bar)	[1] -E2 [1] -E3 [1] -E4

[1] 3/4, 1, G, D8, E2, E3, E4, AD7, AD8, AD9, AD10, E11, WPM

Not with EU certification EX4

Transfer order code

562531 **MS** **9** **- LFR** **- []** **- []** **- []** **- []** **- U** **- []**

Filter regulators MS9-LFR, MS series

Ordering data – Modular products

→ [O]	[M]	[O] Options	Regulator type	Pressure gauge/pressure gauge alternatives	Alternative pressure gauge scale	Secondary venting	Security	Type of mounting	EU certification	UL certification	Alternative flow direction
DI	AG, VS, A4, RG, AD7 ... AD10	PSI, MPA, BAR	OS	AS, E11	WP, WPM, WPB	EX4	UL1	Z			
- DI - AG - BAR - OS - AS -	-	-	-	-	-	-	-	-	-	-	

Ordering table		Grid dimension [mm]	90	Conditions	Code	Enter code
[O]	Regulator type	Directly actuated		[2]	-DI	
[M]	Pressure gauge/pressure gauge alternatives	MS pressure gauge			-AG	
	Cover plate				-VS	
	Adapter plate for EN pressure gauge 1/4, without pressure gauge				-A4	
	Integrated pressure gauge, red/green scale			[3]	-RG	
	Pressure sensor without display, plug M8, threshold value comparator, PNP, N/O contact			[1][4]	-AD7	
	Pressure sensor without display, plug M8, threshold value comparator, PNP, N/C contact			[1][4]	-AD8	
	Pressure sensor without display, plug M8, window comparator, PNP, N/O contact			[1][4]	-AD9	
	Pressure sensor without display, plug M8, window comparator, PNP, N/C contact			[1][4]	-AD10	
[O]	Alternative pressure gauge scale	Psi		[5]	-PSI	
		MPa		[5]	-MPA	
		Bar		[5]	-BAR	
	Secondary venting	Without secondary venting		[6]	-OS	
	Security	Can be locked using accessories			-AS	
		With integrated lock		[1]	-E11	
	Type of mounting	Mounting bracket		[7]	-WP	
		Mounting bracket		[1][7]	-WPM	
		Mounting bracket for large wall gap		[7]	-WPB	
	EU certification	II 2GD to EU Directive 94/9/EG			-EX4	
	UL certification	cULus, ordinary location for Canada and USA			-UL1	
	Alternative flow direction	Flow direction from right to left			-Z	

[1] ¾, 1, G, D8, E2, E3, E4, AD7, AD8, AD9, AD10, E11, WPM

Not with EU certification EX4

[2] DI

Not with pressure range D7, D8

[3] RG

Not with alternative pressure gauge scale PSI

PSI scale serves only as an auxiliary scale

[4] AD7 ... AD10

Measuring range max. 10 bar

[5] PSI, MPA, BAR

Not with pressure gauge alternatives VS, A4, AD7, AD8, AD9, AD10

[6] OS Only with regulator type DI

[7] WP, WPM, WPB Not with module G

Transfer order code


- [] - [] - [] - [] - [] - [] - [] - [] - []

Filter regulators MS12-LFR, MS series

Peripherals overview

FESTO

Filter regulators MS12-LFR



- - Note

Additional accessories:

- Module connector for combination with size MS9 → Internet: armv

Mounting attachments and accessories

→ Page/Internet

[1]	Connecting plate-SET MS12-AG...	ms12-ag
[2]	Mounting bracket MS12-WP	ms12-wp
[3]	Module connector MS12-MV	ms12-mv
[4]	Padlock LRVS-D	47
[5]	Cover plate VS	44
[6]	Adapter for EN pressure gauge 1/4 A4	44
[7]	Pressure gauge MA	47

Filter regulators MS12-LFR, MS series

FESTO

Type codes

MS	12	-	LFR	-	G	-	D7	-	C	U	V	-	LD	-	AS
Series															
MS	Standard service unit														
Size															
12	Grid dimension 124 mm														
Service function															
LFR	Filter regulator														
Connection size															
G	Module without connecting thread, without connecting plate Connecting plates → Accessories														
Pressure regulation range															
D7	Pressure regulation range 0.5 ... 12 bar														
Grade of filtration															
C	5 µm														
E	40 µm														
Bowl guard															
U	Integrated as metal bowl														
Condensate drain															
V	Fully automatic														
Rotary knob															
LD	Long rotary knob														
Security															
AS	Rotary knob with detent, lockable via accessories														

Further variants can be ordered using the modular system → 44

- Connecting plates
- Pressure regulation range
- Condensate drain
- Pressure gauge alternatives
- Alternative pressure gauge scale
- Security
- Type of mounting
- Alternative flow direction


Filter regulators MS12-LFR, MS series

Technical data

FESTO


Function

Condensate drain
manual rotary
with pressure gauge



- - Flow rate
11,000 ... 17,000 l/min
- - Temperature range
-10 ... +60 °C
- - Operating pressure
0.8 ... 20 bar
- - www.festo.com

Condensate drain
fully automatic
with pressure gauge



Wearing parts kits
→ 43

With this device, the filter and pressure regulator are combined into a single unit. The sintered filter with water separator removes contamination, pipe sinter, rust and condensate from the compressed air.



- Good control characteristics with low hysteresis and primary pressure compensation
- Good particle and condensate separation
- High flow rates
- Pilot actuated diaphragm regulator without intrinsic air consumption
- Three pressure regulation ranges:
0.3 ... 7 bar, 0.5 ... 12 bar and
0.5 ... 16 bar
- Pressure gauge connection for different fitting options
- Available with manual, fully automatic or fully automatic, electrically actuated condensate drain
- Regulator lock for protecting the values against adjustment
- Choice of filter cartridges: 5 µm or 40 µm
- New filter cartridges → 46

General technical data

Pneumatic connection 1, 2 ¹⁾		G1	G1½	G1½	G2
Design		Filter regulator with/without pressure gauge			
		Sintered filter with centrifugal separation			
		Pilot actuated diaphragm regulator			
Regulating function	Output pressure constant, with primary pressure compensation, with secondary venting				
Type of mounting	Via accessories				
	In-line installation				
Assembly position	Vertical ±5°				
Grade of filtration [µm]	5				
	40				
Air purity class at the output	Compressed air in accordance with ISO 8573-1:2010 [6:4:4] (Grade of filtration 5 µm) Compressed air in accordance with ISO 8573-1:2010 [7:4:4] (Grade of filtration 40 µm)				
Bowl guard	Integrated as metal bowl				
Condensate drain	Manual rotary				
	Fully automatic				
	Fully automatic, electrical actuated				
Regulator lock	Rotary knob with detent				
	Rotary knob with detent, lockable via accessories				
	Rotary knob with integrated lock				
Pressure regulation range	D6 [bar]	0.3 ... 7			
	D7 [bar]	0.5 ... 12			
	D8 [bar]	0.5 ... 16			
Max. hysteresis	[bar]	0.4			
Pressure indicator	With pressure gauge				
Max. condensate volume	[cm ³]	400			

1) Dependent on connecting plate selected, must be ordered separately as an accessory → Internet: ms12-ag

Note: This product conforms to ISO 1179-1 and to ISO 228-1

Filter regulators MS12-LFR, MS series

FESTO

Technical data

Standard nominal flow rate q_{nN}^1 [l/min]

Pneumatic connection	G1	G1½	G1½	G2
Grade of filtration	5 µm	11,000	11,500	12,000
	40 µm	12,000	12,500	13,000
				17,000

- 1) Dependent on connecting plate selected, must be ordered separately as an accessory → Internet: ms12-ag
measured at $p_1 = 10$ bar and $p_2 = 6$ bar, $\Delta p = 0.5$ bar

Operating and environmental conditions

Condensate drain	Manual rotary M	Fully automatic V	Fully automatic, electrically actuated E2/E3/E4
Operating pressure [bar]	0.8 ... 20	2 ... 12	0.8 ... 16
Operating medium	Compressed air in accordance with ISO 8573-1:2010 [-:4:-] Inert gases	Compressed air in accordance with ISO 8573-1:2010 [7:4:-]	Compressed air in accordance with ISO 8573-1:2010 [-:4:-]
Ambient temperature [°C]	-10 ... +60	+5 ... +60	+1 ... +60
Temperature of medium [°C]	-10 ... +60	+5 ... +60	+1 ... +60
Storage temperature [°C]	-10 ... +60	-10 ... +60	+1 ... +60
Corrosion resistance class CRC ¹⁾	2		


- 1) Corrosion resistance class CRC 2 to Festo standard FN 940070
Moderate corrosion stress. Indoor applications in which condensation may occur. External visible parts with primarily decorative requirements for the surface and which are in direct contact with the ambient atmosphere typical for industrial applications.

Weights [g]

Rotary knob	Without integrated lock E11	With integrated lock E11
Filter regulator with metal bowl U	7,000	7,300
Filter regulator with metal bowl U and fully automatic, electrically actuated condensate drain E2/E3/E4	7,700	8,000

Materials

Sectional view



Filter regulator

[1] Body	Die-cast aluminium
[2] Rotary knob	PA
Rotary knob with integrated lock E11	Aluminium
[4] Metal bowl	Wrought aluminium alloy
[6] Filter element	Sintered bronze
[7] Spin disc	POM
[8] Filter holder	POM
[9] Separating plate	POM
[10] Stabilising disc	POM
[11] Diaphragm	NBR
[12] Spring	Steel
- Seals	NBR

Filter regulators MS12-LFR, MS series

Technical data

FESTO


Standard flow rate q_n as a function of output pressure p_2

Grade of filtration 40 µm

With connecting plate MS12-AGF


Pneumatic connection G1

Input pressure $p_1 = 10$ bar



With connecting plate MS12-AGG


Pneumatic connection G1½



Input pressure $p_1 = 10$ bar


With connecting plate MS12-AGH

Pneumatic connection G1½



With connecting plate MS12-AGI

Pneumatic connection G2



Filter regulators MS12-LFR, MS series


FESTO

Technical data

Dimensions

Integrated pressure gauge, display unit [bar], long rotary knob with detent

Download CAD data ➔ www.festo.com



Type	B1	B2	B3	B4	B5	D5 ∅	L1	L2	L3	L4	L5	L6
MS12-LFR-...-LD	124	122	61	148	52	40	460	88	86	168	250	16

Filter regulators MS12-LFR, MS series

Technical data


FESTO

Dimensions – Pressure gauge alternatives

Cover plate VS

Download CAD data → www.festo.com

Adapter A4 for EN pressure gauge 1/4, without pressure gauge



Type	B3	B4	D4
MS12-LFR...-VS	61	148	–
MS12-LFR...-A4	61	148	G1/4

• Note: This product conforms to ISO 1179-1 and to ISO 228-1


Dimensions – Rotary knob

Long rotary knob with detent LD

Long rotary knob with detent,
lockable via accessories LD-AS

Rotary knob with integrated lock
E11

Download CAD data → www.festo.com



Type	B1	D1	L1	L2	L3
MS12-LFR...-LD	–	52	–	86	–
MS12-LFR...-LD-AS	65	52	–	96	–
MS12-LFR...-E11	–	52	174	114	25


Filter regulators MS12-LFR, MS series

FESTO

Technical data


Dimensions – Condensate drain

Manual rotary M



Barbed fitting for plastic tubing
PCN-4

Fully automatic V




Download CAD data → www.festo.com

Type	L6
MS12-LFR-...-M	11

Type	L6
MS12-LFR-...-V	13

Fully automatic, electrically actuated E2/E3/E4



Technical data → Internet: pwea

Condensate drain PWEA:

- [2] Electrical connection: Screw terminal PG9
- [3] Connection 360° rotatable for plastic tubing PUN-H-12x2

Ordering data

Pressure regulation range 0.5 ... 12 bar, metal bowl, integrated pressure gauge, display unit [bar], long rotary knob with detent, lockable via accessories

Size	Condensate drain	Connection	Grade of filtration 5 µm		Grade of filtration 40 µm	
			Part No.	Type	Part No.	Type
MS12	fully automatic	G1 ... G2 ¹⁾	537150	MS12-LFR-G-D7-CUV-LD-AS	537149	MS12-LFR-G-D7-EUV-LD-AS

1) Connecting plate must be ordered separately as an accessory → Internet: ms12-ag

- Note: This product conforms to ISO 1179-1 and to ISO 228-1

Ordering data – Wearing parts kits

Size	Part No.	Type
MS12	673586	MS12-LR/LFR

Filter regulators MS12-LFR, MS series

Ordering data – Modular products

FESTO

M Mandatory data →							
Module No.	Series	Size	Function	Connection sizes	Pressure regulation range	Grade of filtration	Bowl
535022	MS	12	LFR	AGF, AGG, AGH, AGI, G	D6, D7, D8	E, C	U
Order example	535022	MS	12	- LFR - AGF	- D6	- C	- U

Ordering table		Grid dimension [mm]	124	Conditions	Code	Enter code
M	Module No.	535022				
Series	Standard				MS	MS
Size	12				12	12
Function	Filter regulator				-LFR	-LFR
Connection sizes	Connecting plate G1 Connecting plate G1½ Connecting plate G1½ Connecting plate G2 Module without connecting thread, without connecting plate				-AGF -AGG -AGH -AGI -G	
Pressure regulation range	0.3 ... 7 bar 0.5 ... 12 bar 0.5 ... 16 bar				-D6 -D7 -D8	
Grade of filtration	40 µm 5 µm				-E -C	
↓ Bowl	Metal bowl				-U	-U

Transfer order code

535022 MS 12 - LFR - - - - U

Filter regulators MS12-LFR, MS series

FESTO

Ordering data – Modular products

<input checked="" type="checkbox"/> M	<input type="checkbox"/> Options	Condensate drain	Pressure gauge alternatives	Alternative pressure gauge scale	Rotary knob	Security	Type of mounting	Alternative flow direction
M, V, E2, E3, E4,		VS, A4	PSI, MPA	LD	AS, E11	WP	Z	
- E2 -	-			- LD -	- AS -	- WP -	- Z -	

Ordering table		Grid dimension [mm]	124	Conditions	Code	Enter code
<input checked="" type="checkbox"/> Condensate drain	Manual				-M	
	Fully automatic (P1 max. 12 bar)		[1]		-V	
	External fully automatic condensate drain, electrical, 110 V AC, terminal strip				-E2	
	External fully automatic condensate drain, electrical, 230 V AC, terminal strip				-E3	
	External fully automatic condensate drain, electrical, 24 V DC, terminal strip				-E4	
<input type="checkbox"/> Pressure gauge alternatives	Cover plate				-VS	
	Adapter plate for EN pressure gauge 1/4, without pressure gauge				-A4	
<input type="checkbox"/> Alternative pressure gauge scale	psi		[2]		-PSI	
	MPa		[2]		-MPA	
<input type="checkbox"/> Rotary knob	Long rotary knob		[3] [4]		-LD	
	Lockable via accessories				-AS	
<input type="checkbox"/> Security	With integrated lock		[3]		-E11	
	Mounting bracket		[5]		-WP	
<input type="checkbox"/> Type of mounting	Flow direction from right to left				-Z	

- [1] **V** Not with pressure regulation range D8
- [2] **PSI, MPA** Not with pressure gauge alternatives VS, A4
- [3] **LD, E11** Either rotary knob LD or security E11 must be selected
- [4] **LD** Not with security E11
- [5] **WP** Only with connecting plate AGF, AGG, AGH or AGI

Transfer order code

- - - - - - -

Filter regulators MS-LFR, MS series

Accessories

FESTO

Filter cartridges



Ordering data


Size	Grade of filtration [µm]	Part No.	Type
MS4	5 (colour: blue)	534501	MS4-LFP-C
	40 (colour: white)	534502	MS4-LFP-E
MS6	5 (colour: blue)	534499	MS6-LFP-C
	40 (colour: white)	534500	MS6-LFP-E
MS9	5	570309	MS9-LFP-C
	40	570310	MS9-LFP-E
MS12	5	537143	MS12-LFP-C
	40	537144	MS12-LFP-E

Filter regulators MS-LFR, MS series


FESTO

Accessories

Ordering data – Connecting cable NEBU-M8					Technical data → Internet: nebu	
	Electrical connection	Number of wires	Cable length [m]	Part No.	Type	
	M8x1, straight socket	3	2.5	541333	NEBU-M8G3-K-2.5-LE3	
			5	541334	NEBU-M8G3-K-5-LE3	
	M8x1, angled socket	3	2.5	541338	NEBU-M8W3-K-2.5-LE3	
			5	541341	NEBU-M8W3-K-5-LE3	

Ordering data – Connecting cable NEBU-M12					Technical data → Internet: nebu	
	Electrical connection	Number of wires	Cable length [m]	Part No.	Type	
	M12x1, straight socket	4	2.5	550326	NEBU-M12G5-K-2.5-LE4	
			5	541328	NEBU-M12G5-K-5-LE4	
	M12x1, angled socket	4	2.5	550325	NEBU-M12W5-K-2.5-LE4	
			5	541329	NEBU-M12W5-K-5-LE4	

Ordering data – Pressure gauge MA					Technical data → Internet: ma	
Nominal size	Pneumatic connection	Indicating range		Part No.	Type	
Pressure gauge MA, DIN EN 837-1					Technical data → Internet: ma	
40	R1/4	0 ... 16	0 ... 232	187080	MA-40-16-R1/4-EN	
	G1/4	0 ... 16	0 ... 232	183901	MA-40-16-G1/4-EN	
Pressure gauge MA, DIN EN 837-1, with red-green range					Technical data → Internet: ma	
40	R1/8	0 ... 16	-	525726	MA-40-16-R1/8-E-RG	
50	R1/4	0 ... 16	-	525729	MA-50-16-R1/4-E-RG	

Ordering data – Padlock LRV5-D					Technical data → Internet: ma	
Weight [g]				Part No.	Type	
	120			193786	LRV5-D	