Vacuum efficiency valves ISV

FESTO



Vacuum efficiency valves ISV

Features

FESTO


Areas of application

- For parallel arrangement of several suction cups
- To prevent dissipation of the vacuum if one or several suction cups do not make full contact
- Gripping of randomly placed products
- · Saves compressed air and energy
 - Retention is only successful if 100% contact is achieved
- Maintains vacuum

Function diagram

These valves are suitable for applications requiring several vacuum suction cups and for the maintenance of vacuum in the event that one suction cup should fail to make contact.

- 1 Vacuum generator
- 2 Distributor
- 3 Vacuum efficiency valve
- 4 Suction cup



Vacuum efficiency valve function

The ISV valve is fitted between the vacuum generator and the suction cup.


If, during vacuum generation, a suction cup is uncovered, or only partly covered, the ISV automatically stops the influx of air.

When the suction cup fits tightly against the surface, a vacuum is regenerated.

Removal of the object from the suction cup causes the ISV valve to close immediately.

- When the suction cup is open to atmosphere, the float is drawn back against the housing. In this position, flow is only possible through the small hole in the end of the float.
- When an object is in contact with the suction cup, flow is reduced and the spring forces the float forward.

The seal is thus broken and full vacuum is generated within the suction cup.



- 1 Spring
- 2 Float
- 3 Filter
- 4 Retaining screw
- 5 Suction cup


Vacuum efficiency valves ISV Technical data













| General technical data | | | | | | | | | | |
|---------------------------|----------|-------------|------|------|-----------|-----------------------------|-----|---|--|--|
| Pneumatic connection 1, 2 | | For suction | cups | | For vacuu | For vacuum suction grippers | | | | |
| | M5 | G½8 | G1/4 | G3/8 | M4 | M6 | M10 | | | |
| Mounting position | Any | Any | | | | | | | | |
| Type of mounting | Screw-in | Screw-in | | | | | | | | |
| Ejector pulse possibility | [bar] | ≤8 | | | | | | | | |
| Required suction rate | [l/min] | 1 | 2 | 1.6 | 1.5 | 1 | 2 | 2 | | |
| at -0.5 bar | | | | | | | | | | |

| Operating and environmental conditions | | | | | | | |
|--|-------------------|--|--|--|--|--|--|
| Operating pressure | [bar] | -0.95 0 | | | | | |
| Operating medium | | Atmospheric air based on ISO 8573-1:2010 [7:-:-] | | | | | |
| Ambient temperature | [°C] | -10 +60 | | | | | |
| Corrosion resistance class | CRC ¹⁾ | 2 | | | | | |

1) Corrosion resistance class CRC 2 to Festo standard FN 940070
Moderate corrosion stress. Indoor applications in which condensation may occur. External visible parts with primarily decorative requirements for the surface and which are in direct contact with the ambient atmosphere typical for industrial applications.

| Weights [g] | | | | | | | |
|---------------------------|------------|-----------------------------|------|------|-----|----|-----|
| Pneumatic connection 1, 2 | For vacuui | For vacuum suction grippers | | | | | |
| | M5 | G1/8 | G1/4 | G3/8 | M4 | M6 | M10 |
| Vacuum efficiency valve | 4 | 9 | 16 | 33 | 1.5 | 14 | 18 |


| Materials | | | | | | | | | |
|---------------------------|----------------|-------------------|---|------------|-----------------------------|-----------------|----------------|--|--|
| Pneumatic connection 1, 2 | For suction cu | ıps | | For vacuui | For vacuum suction grippers | | | | |
| | M5 | G ¹ /8 | G ¹ / ₄ | G3/8 | M4 | M6 | M10 | | |
| Housing | Wrought alun | ninium alloy | | Wrought a | Wrought aluminium alloy | | | | |
| Filter | Sintered | Wrought alumi | Wrought aluminium alloy, stainless steel mesh | | Sintered b | Sintered bronze | | | |
| | bronze | | | | | | | | |
| Spring | - | High-alloy stair | nless steel | | - | High-alloy s | tainless steel | | |
| Hollow bolt | - | Wrought alumi | Wrought aluminium alloy | | | - | | | |
| Float | - | POM | POM | | | - POM | | | |

Vacuum efficiency valves ISV Technical data


FESTO

Evacuation time t as a function of the volume to be evacuated V with various ejectors


ISV-M5



ISV-1/8/ISV-1/4



ISV-3/8



- 1 VAD-...-3/8 with suction cup VAS-125
- 2 VAD-ME-...-3/8 with suction cup VAS-125
- 3 VAD-...-3/8 with suction cup VASB-125
- 4 VAD-ME-...-3/8 with suction cup VASB-125



Evacuation time is the time required to attain 90% maximum possible vacuum.

Vacuum efficiency valves ISV Technical data




Conditions for operation of the vacuum efficiency valve ISV

- The number of vacuum suction cups that can be attached depends upon the suction capacity of the ejector.
- A minimum switching flow rate is required to ensure the function of each ISV vacuum efficiency valve connected in parallel to an ejector.
- The number of cups which can be reliably operated can be estimated on the basis of the ratio of ejector

suction power and the minimum switching flow rate of the ISV vacuum efficiency valve.

| Max. no. of sealed suction cup | s as a function | of the vacu | ıum genera | itor used a | nd the atta | inable vac | uum level | | | | | | | |
|--------------------------------|-----------------|---|------------|-------------|-------------|------------|-----------|------|------|---------|------|------|--|--|
| Vacuum generator | Max. nu | Max. number of suction cups at P _u [bar] | | | | | | | | | | | | |
| | ISV-M5 | ISV-M5 | | ISV-1/8 | ISV-1/8 | | ISV-1/4 | | | ISV-3/8 | | | | |
| | -0.5 | -0.6 | -0.7 | -0.5 | -0.6 | -0.7 | -0.5 | -0.6 | -0.7 | -0.5 | -0.6 | -0.7 | | |
| VAD-M5 | 2 | 1 | - | 1 | 1 | - | 1 | - | - | - | - | - | | |
| VAD-1/8 | 4 | 2 | 1 | 2 | 1 | - | 2 | 1 | - | - | - | - | | |
| VAD-1/4 | 8 | 6 | 3 | 4 | 3 | 1 | 4 | 3 | 1 | - | - | - | | |
| VAD-3/8 | 8 | 8 | 7 | 7 | 6 | 3 | 7 | 6 | 3 | - | 2 | 1 | | |
| VADM/VADMI-45 | 2 | 1 | - | 1 | 1 | - | 1 | - | - | _ | - | - | | |
| VADM/VADMI-70 | 4 | 2 | 1 | 2 | 1 | - | 2 | 1 | - | - | - | - | | |
| VADM/VADMI-95 | 8 | 6 | 3 | 4 | 3 | 1 | 4 | 2 | 1 | - | - | - | | |
| VADM/VADMI-140 | 8 | 8 | 7 | 7 | 6 | 3 | 7 | 6 | 3 | 3 | 2 | 1 | | |
| VADM/VADMI-200 | 16 | 16 | 14 | 14 | 12 | 6 | 14 | 12 | 6 | 6 | 4 | 2 | | |
| VADM/VADMI-300 | 32 | 32 | 28 | 28 | 24 | 12 | 28 | 14 | 12 | 12 | 8 | 4 | | |



| Туре | D1 | D2 Ø | D3 Ø | D5 Ø | L1 | L2 | T1 | =©1 |
|---------|------|---------|---------|---------|------|-----|-----|-----|
| | | Ø | Ø | Ø | | | | |
| ISV-M5 | M5 | - | 2 | - | 15 | 4.3 | 5.5 | 8 |
| ISV-1/8 | G1/8 | - | 4 | - | 36 | 6.5 | 11 | 13 |
| ISV-1/4 | G1/4 | - | 4 | - | 37.5 | 8 | 11 | 17 |
| ISV-3/8 | G3/8 | - | 4 | _ | 42 | 9 | 13 | 22 |
| ISV-M4 | M4 | 7.8 | - | 7 | 10.7 | 3.8 | 5 | 7 |
| ISV-M6 | M6 | 8.4 | - | 14 | 28.3 | 5 | 5 | 14 |
| ISV-M10 | M10 | 14 | ı | 17 | 32 | 6.5 | 10 | 17 |

| Ordering data | | | |
|---------------------------|------------------|---------------------------|-----------------------------|
| Pneumatic connection 1, 2 | For suction cups | Pneumatic connection 1, 2 | For vacuum suction grippers |
| | Part No. Type | | Part No. Type |
| M5 | 151217 ISV-M5 | M4 | 545996 ISV-M4 |
| G1/8 | 33969 ISV-1/8 | M6 | 545997 ISV-M6 |
| G1/4 | 33970 ISV-1/4 | M10 | 545998 ISV-M10 |
| G3/8 | 33971 ISV-3/8 | | |