





Distributor, universal



Distributor, universal

Product range overview

FESTO

Function	Version	Version	Type	Connection technology	Protection class	→ Page/ Internet
T-distributor 	Round plug M8					
	4-pin	NEDU-M8D3-M8T4		2x socket M8, 3-pin	IP65, IP67	3
	Round plug M12					
	3-pin	NEDU-L2R1-V8-M12G5-M12G5		1x socket M12, 5-pin 1x plug M12, 2-pin	IP65, IP67	5
	4-pin	NEDU-M8D3-M12T4		2x socket M8, 3-pin	IP65, IP67	7
		NEDU-M12D5-M12T4		2x socket M12, 4-pin	IP65, IP67	7
		NEDU-M12D4-M12T4-IS		2x socket M12, 4-pin	IP65, IP67	7
	5-pin	FB-TA-M12		2x socket M12, 5-pin	IP67	10
5-pin	NEDU-L2R1-V10-M12G5-M12G5		2x socket M12, 5-pin	IP65, IP67	10	
Y-connecting cable 	Open cable end					
	2-wire	FB-TA-1		Socket M12, 3-pin Plug M12, 3 pin	IP67	12
	Round plug M8					
	4-pin	NEDU-L2R1-M8G3-K-1L1-1L2-M8G4		2x socket M8, 3-pin	IP67	14
	Round plug M12					
	4-pin	KM12-DUO-M8		2x socket M8, 3-pin	IP67	16
	5-pin	FB-TA		2x socket M12, 5-pin	IP67	12
	Socket M12					
	5-pin	FB-TA		1x plug M12, 5-pin 1x socket M12, 5-pin	IP67	12
		FB-TA-1		1x plug M12, 5-pin 1x open cable end	IP67	12
	8-pin	NEBV-M12G8-KD-3-M12G4		2x plug M12, 4-pin	IP67	18
8-pin	NEDU-L1R2-V9-M12G8-...		2x open cable end	IP65, IP67	18	
Multiple distributor/ multi-pin plug distributor 	Open cable end					
	11-wire	MPV-E/A08-M12		8x socket M12, 5-pin	IP67	21
	Round plug M12					
	8-pin	NEDU-L4R1-M8G3L-M12G8		4x socket M8, 3-pin	IP68	24
		NEDU-L6R1-M8G3L-M12G8		6x socket M8, 3-pin	IP68	24
	Plug Sub-D					
15-pin	MPV-E/A08-M8		8x socket M8, 3-pin	IP65	27	
	MPV-E/A12-M8		12x socket M8, 3-pin	IP65	27	

T-distributor, plug M8, 4-pin

Technical data

FESTO

Push-in T-connector NEDU-M8

• T-adapter



General technical data		
Type of mounting		Screw-in
Mounting position		Any
Connection frequency		100
Nominal operating voltage	[V AC]	32
	[V DC]	32
Operating voltage range	[V AC]	32
	[V DC]	32
Acceptable current load	[A]	2
Protection class to EN 60529		IP65, IP67
Electrical connection		To EN 60947-5-2
Max. tightening torque	[Nm]	0.3
Product weight	[g]	9.5



Materials	
Housing	PA
Housing colour	Black
Pin contacts	Gold-plated brass
Union nut	Chrome-plated and nickel-plated brass
Note on materials	Free of copper and PTFE

Operating and environmental conditions		
Ambient temperature	[°C]	-25 ... +85
Storage temperature	[°C]	-25 ... +85
Corrosion resistance class CRC ¹⁾		2

1) Corrosion resistance class 2 according to Festo standard 940 070
Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

T-distributor, plug M8, 4-pin

Technical data



Type	B1	D1 ∅	D2	H1	H2	L1	L2
NEDU-M8D3-M8T4	10	9.7	M8	23	12.5	33.6	10.4

Ordering data		Part No.	Type
Electrical connection			
Plug M8, 4-pin	2x socket M8, 3-pin	544391	NEDU-M8D3-M8T4

T-distributor, plug M12, 4-pin

Technical data

FESTO

Push-in T-connector NEDU-L2R1-V8

- T-adapter
- For IO-Link



General technical data	
Electrical connection 3	Straight plug, M12, 3-pin, A-coded
Electrical connection 1	Straight socket, M12, 5-pin, A-coded
Electrical connection 2	Straight plug, M12, 2-pin, A-coded
Type of mounting	Screw-in
Max. tightening torque [Nm]	0.6
Operating voltage range [V DC]	0 ... 30
Surge strength [kV]	1.5
Acceptable current load [A]	4
Protection class to EN 60529	IP65, IP67, in assembled state
Product weight [g]	28



Materials	
Housing	TPE-U(PUR)
Housing colour	Black
Union nut	Die-cast zinc, nickel plated
Seals	FPM
Pin contacts	Gold-plated copper alloy
Note on materials	RoHS-compliant

Operating and environmental conditions	
Ambient temperature [°C]	-25 ... +85
Corrosion resistance class CRC ¹⁾	2
Degree of contamination	3

1) Corrosion resistance class 2 according to Festo standard 940 070
Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

T-distributor, plug M12, 4-pin

Technical data



Type	B1	B2	D1	D2	D3	D4	D5	H1	H2	H3	L1	L2	≈C 1
NEDU-L2R1-V8	15	8.3	15	M12	15	M12	4.2	33.3	21	36	48.5	13.2	13

Ordering data			
Electrical connection	Product weight [g]	Part No.	Type
Plug M12 A-coded, 3-pin	28	2839846	NEDU-L2R1-V8-M12G5-M12G5
1x socket M12 A-coded, 5-pin 1x plug M12 A-coded, 2-pin			

T-distributor, plug M12, 4-pin

Technical data

FESTO

Push-in T-connector NEDU-M

• T-adapter



General technical data			
Type	NEDU-M8D3-M12T4	NEDU-M12D4-M12T4-IS	NEDU-M12D5-M12T4
Type of mounting	Screw-in	Screw-in	Screw-in
Mounting position	Any	–	Any
Connection frequency	500	100	500
Nominal operating voltage	[V AC]	60	–
	[V DC]	60	–
Operating voltage range	[V AC]	60	–
	[V DC]	60	0 ... 30
Acceptable current load	[A]	4	–
Protection class to EN 60529	IP65, IP67	IP65, IP67	IP65, IP67
Based on standard	EN 60947-5-2	EN 61076-2-101	EN 60947-5-2
Max. tightening torque	[Nm]	0.3 with M8	0.5
	[Nm]	0.5 with M12	
Product weight	[g]	16.9	25.5










Materials			
Type	NEDU-M8D3-M12T4	NEDU-M12D4-M12T4-IS	NEDU-M12D5-M12T4
Housing	Reinforced TPE-U(PU)	Reinforced TPE-U(PU) Die-cast zinc	Reinforced TPE-U(PU)
Housing colour	Black	–	Black
Pin contacts	Gold-plated brass	Gold-plated copper alloy	Gold-plated brass
Union nut	Chrome-plated and nickel-plated brass	PA reinforced	Chrome-plated and nickel-plated brass
Seals	–	FPM	–
Note on materials	Free of copper and PTFE	RoHS-compliant	Free of copper and PTFE

Operating and environmental conditions			
Type	NEDU-M8D3-M12T4	NEDU-M12D4-M12T4-IS	NEDU-M12D5-M12T4
Ambient temperature	[°C]	–25 ... +85	–25 ... +85
Storage temperature	[°C]	–25 ... +85	–25 ... +85
Corrosion resistance class CRC	2 ¹⁾	3 ²⁾	2 ¹⁾

- 1) Corrosion resistance class 2 according to Festo standard 940 070
Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.
- 2) Corrosion resistance class 3 according to Festo standard 940 070
Components subject to high corrosion stress. Externally visible parts with primarily functional surface requirements which are in direct contact with a normal industrial environment or media such as solvents and cleaning agents.

T-distributor, plug M12, 4-pin

Technical data

Circuitry (socket/plug view)		
NEDU-M8D3-M12T4		
Socket	Circuitry	Socket
		
<hr/>		
NEDU-M12D4-M12T4-IS		
Socket	Circuitry	Socket
		
<hr/>		
NEDU-M12D5-M12T4		
Socket	Circuitry	Socket
		

T-distributor, plug M12, 4-pin


Technical data

FESTO


Dimensions

Download CAD data → www.festo.com


NEDU-M8D3-M12T4



NEDU-M12D4-M12T4-IS



NEDU-M12D5-M12T4



Type	B1	D1 Ø	D2	D3 Ø	D4	H1	H2	L1	L2
NEDU-M8D3-M12T4	13.5	9.7	M8	14.5	M12	33	20	35.6	10
NEDU-M12D4-M12T4-IS	13.5	14	M12	14.4	-	33	20	40.3	10
NEDU-M12D5-M12T4	13.5	14.5	M12	-	-	33	20	40.3	10

Ordering data

Electrical connection	Part No.	Type
Plug M12, A-coded, 4-pin	541597	NEDU-M8D3-M12T4
	562248	NEDU-M12D4-M12T4-IS
	541596	NEDU-M12D5-M12T4

T-distributor, plug M12, 5-pin

Technical data

FESTO

T-adapter
FB-TA
NEDU-L2R1-V10

- T-adapter
- Branch line for connecting and disconnecting fieldbus components
- Connected fieldbus components can be disconnected without interrupting signal transmission (to other components)



General technical data		
Type	FB-TA	NEDU-L2R1-V10
Electrical connection 3	Plug, M12, 5-pin	Straight plug, M12, 5-pin, A-coded
Electrical connection 1	Socket, M12, 5-pin	Straight socket, M12, 5-pin, A-coded
Electrical connection 2	Socket, M12, 5-pin	Straight socket, M12, 5-pin, A-coded
Type of mounting	Via through-hole	Screw-in
Max. tightening torque [Nm]	–	0.6
Operating voltage range [V DC]	10 ... 30	0 ... 30
Surge strength [kV]	–	1.5
Acceptable current load [A]	4	4
Protection class to EN 60529	IP67, in assembled state	IP65, IP67, in assembled state

Materials		
Type	FB-TA	NEDU-L2R1-V10
Housing	–	TPE-U(PUR)
Housing colour	–	Black
Union nut	–	Die-cast zinc, nickel plated
Seals	–	FPM
Pin contacts	–	Gold-plated copper alloy
Note on materials	–	RoHS-compliant

Operating and environmental conditions		
Type	FB-TA	NEDU-L2R1-V10
Ambient temperature [°C]	–25 ... +90	–25 ... +85
Corrosion resistance class CRC ¹⁾	–	2
Degree of contamination	–	3

1) Corrosion resistance class 2 according to Festo standard 940 070
 Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

T-distributor, plug M12, 5-pin

Technical data

FESTO

Circuitry (socket/plug view)		
	Circuitry	
FB-TA		
NEDU-L2R1-V10		

Dimensions		Download CAD data → www.festo.com
FB-TA		NEDU-L2R1-V10
1 Socket M12, 5-pin	2 Plug M12, 5-pin	

Type	B1	B2	D1	D2	D3	D4	D5	H1	H2	H3	L1	L2	L3	⌀C1
FB-TA	17	12	8	4.5	-	-	-	45.2	16	6.5	57	23.5	10.4	-
NEDU-L2R1-V10	15	8.3	15	M12	15	M12	4.2	33.3	21	36	45	13.2	-	13

Ordering data			
Electrical connection		Product weight [g]	Part No. Type
Plug M12, 5 pin	2x socket, M12, 5-pin	-	171175 FB-TA-M12-5POL
		25	2839867 NEDU-L2R1-V10-M12G5-M12G5

Y-connecting cable, socket M12, 5-pin

Technical data

T-adapter FB-TA

- Branch line for connecting and disconnecting fieldbus components
- Connected fieldbus components can be disconnected without interrupting signal transmission (to other components)










General technical data		
Type of mounting		Via union nut
Mounting position		Any
Operating voltage range	[V AC]	Max. 10
	[V DC]	Max. 30
Acceptable current load	[A]	4
Cable composition	[mm ²]	2x 0.25
Cable diameter	[mm]	5
Protection class to EN 60529		IP67



Materials	
Housing	PA
Cable sheath	PVC
Pin contacts	Nickel-plated/tin-plated brass

Operating and environmental conditions		
Ambient temperature	[°C]	-25 ... +90

Y-connecting cable, socket M12, 5-pin

Technical data

Circuitry (socket/plug view)		
FB-TA		
Socket	Circuitry	Plug
		
		
FB-TA-1		
Socket	Circuitry	Plug
		
	<ul style="list-style-type: none"> 1 White 2 Black 3 Screening 	

Dimensions		Download CAD data → www.festo.com
FB-TA		FB-TA-1
		

Type	D1	D2	L1
FB-TA	M12	M12	150
FB-TA-1	M12	-	140


Ordering data				
Electrical connection		Weight [g]	Part No.	Type
Plug M12, 5 pin	2x socket M12, 5-pin	37	18498	FB-TA
Open cable end, 2-wire	Plug/socket M12, 5-pin	23	18499	FB-TA-1

Y-connecting cable, plug M8, 4-pin

Technical data

DUO cable NEDU-L2

- Y-connecting cable
- For connecting 2 sensors to an input socket with double allocation




General technical data		
Operating voltage range	[V AC]	0 ... 60
Acceptable current load	[A]	2
Surge resistance	[kV]	1.5
Cable diameter	[mm]	3.1
Cable length	[m]	1
Protection class to EN 60529		IP67

Materials	
Housing	PUR
Socket	PUR
Pin contacts	Gold-plated brass
Note on materials	RoHS-compliant
Corrosion resistance class CRC ¹⁾	1


1) Corrosion resistance class 1 according to Festo standard 940 070
 Components subject to low corrosion stress. Transport and storage protection. Parts that do not have primarily decorative surface requirements, e.g. in internal areas that are not visible or behind covers.

Operating and environmental conditions		
Ambient temperature	[°C]	-25 ... +85



Y-connecting cable, plug M8, 4-pin

Technical data



Type	D1	D2	D3	D4	L1	L2	L3	L4	∠C1
NEDU-L2R1-M8G3-K-1L1-1L2-M8G4	∅ 13	∅ 9.7	∅ M8	∅ 3.1	1000	33.8	39.9	4.7	9

Ordering data

Electrical connection		Part No.	Type
Plug M8, 4 pin	2x socket M8, 3-pin	574591	NEDU-L2R1-M8G3-K-1L1-1L2-M8G4

Y-connecting cable, plug M12, 4-pin

Technical data

DUO cable KM12-DUO


- Y-connecting cable
- For connecting 2 sensors to an input socket with double allocation



General technical data		
Type of mounting	Via through-hole, via threaded connector, via union nut	
Mounting position	Any	
Operating voltage range	[V AC]	Max. 60
	[V DC]	Max. 75
Acceptable current load	[A]	2.8
Cable composition	[mm ²]	2x 3x 0.25
Cable diameter	[mm]	4.5
Cable length	[m]	0.6
Protection class to EN 60529	IP67	

Materials	
Housing	PUR
Cable sheath	PUR
Cable sheath colour	Grey
Pin contacts	Gold-plated brass
Union nut	Nickel-plated brass

Operating and environmental conditions		
Ambient temperature	[°C]	-30 ... +70
Ambient temperature with flexible cable installation	[°C]	-5 ... +70




Y-connecting cable, plug M12, 4-pin

Technical data

Dimensions

Download CAD data → www.festo.com



Type	B1	D1	D2	D3	H1	L1	L2	L3
KM12-DUO-M8	17	4.5 ∅	14 ∅	M12 ∅	17.5	600	500	51.5

Ordering data


Electrical connection		Outlet direction socket M8	Weight [g]	Part No.	Type
Plug M12, 4-pin	2x socket M8, 3-pin	Straight - straight	61	18685	KM12-DUO-M8-GDGD
		Straight - angled	61	18688	KM12-DUO-M8-GDWD
		Angled - angled	61	18687	KM12-DUO-M8-WDWD

Y-connecting cable, socket M12, 8-pin

Technical data

Connecting cable NEBV-M12G8
DUO cable NEDU-L1R2-V9

- Y-connecting cable



General technical data		
Type	NEBV-M12G8	NEDU-L1R2-V9
Conforms to	EN 61076-2-101	–
Cable composition	[mm ²]	8x 0.25, screened
	[mm ²]	–
Cable diameter	[mm]	6.3
	[mm]	–
Cable length	[m]	3
		–
Assembly position	Any	Any
Operating voltage range	[V AC]	0 ... 30
	[V DC]	0 ... 30
Surge strength	[kV]	0.8
Acceptable current load	[A]	1.5
at 40 °C	[A]	2
Cable characteristics	Standard	–
Min. cable bending radius	[mm]	66
Protection class to EN 60529	IP67 in mounted status	IP65, IP67 in mounted status



Materials		
Type	NEBV-M12G8	NEDU-L1R2-V9
Housing	TPE-U	TPE-U(PU), reinforced
Housing colour	–	Black
Cable sheath	TPE-U(PUR)	TPE-U(PUR)
Cable sheath colour	Grey	Black
Union nut	Nickel-plated brass	Nickel-plated brass
Seals	–	FPM
Plug contacts	Nickel-plated and gold-plated bronze	–
Note on materials	RoHS-compliant	RoHS-compliant

Operating and environmental conditions		
Type	NEBV-M12G8	NEDU-L1R2-V9
Ambient temperature	[°C]	–25 ... +85
Ambient temperature with flexible cable installation	[°C]	0 ... +80
Corrosion resistance class CRC ¹⁾	–	2
Degree of contamination	3	3

1) Corrosion resistance class 2 according to Festo standard 940 070
Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

Y-connecting cable, socket M12, 8-pin

Technical data



1) To IEC 757

Y-connecting cable, socket M12, 8-pin


Technical data

FESTO


Dimensions

Download CAD data → www.festo.com

NEBV-M12G8



NEDU-L1R2-V9



Type	B1	B2	B3	D1	D2	D6	D7	D8	H1	H2	H2	L1	L2	L3	L4	L5	L6	L7	L8	L9	L10
NEBV-M12G8	38.8	20.5	13.8	6.3	3.2	-	-	-	18.8	16.3	9.4	2500	500	44.9	41.7	17.5	15	15	13.3	7.1	3.6
NEDU-L1R2-V9	-	-	-	14.5	M12	20	4.5	5.3	-	-	-	5000	51.6	-	-	-	-	-	-	-	-

Ordering data

Electrical connection	Product weight [g]	Part No.	Type
Socket M12, 8-pin	247	547888	NEBV-M12G8-KD-3-M12G4
Socket M12, 8-pin, A-coded	377	2903567	NEDU-L1R2-V9-M12G8-E-LE5-5R1-LE3-5R2

Multi-pin plug distributor, open cable end 11-wire, socket M12, 5-pin

FESTO

Technical data

Multi-pin plug distributor MPV

- Multi-pin plug distributor



General technical data	
Electrical connection technology for I/O	M12, 5-pin
Type of mounting	Via through-hole
Operating voltage range [V DC]	10 ... 30
Acceptable current load [A]	12
Acceptable current load per slot [A]	4
Protection class to EN 60529	IP67 in mounted status

Materials	
Housing	TPE-U (PU)
Cable sheath	TPE-U (PU)
Socket	Galvanized brass


Operating and environmental conditions	
Ambient temperature [°C]	-20 ... +80

Multi-pin plug distributor, open cable end 11-wire, socket M12, 5-pin

Technical data

FESTO

Connection and display components



- 1 Sensor connection, location 1
- 2 Sensor connection, location 2
- 3 Sensor connection, location 3
- 4 Sensor connection, location 4
- 5 Sensor connection, location 5
- 6 Sensor connection, location 6
- 7 Sensor connection, location 7
- 8 Sensor connection, location 8
- 9 Green LED for status display (one LED per input)
- 10 Multi-pin plug connection/ multi-pin cable
- 11 Mounting holes
- 12 Ready status display

Circuitry (socket/plug view)

Individual connection		Allocation		Multi-pin plug connection		Allocation		Individual connection	
Location	Pin		Wire colour ¹⁾				Pin	Location	
	1	1	24 DC V	BN	BN	24 DC V	1	2	
		2	n.c.	-	-	n.c.	2		
		3	0 V	BU	BU	0 V	3		
		4	Input 1	WH	GN	Input 2	4		
		5	PU	GN YE	GN YE	PU	5		
	3	1	24 DC V	BN	BN	24 DC V	1	4	
		2	n.c.	-	-	n.c.	2		
		3	0 V	BU	BU	0 V	3		
		4	Input 3	YE	GY	Input 4	4		
		5	PU	GN YE	GN YE	PU	5		
	5	1	24 DC V	BN	BN	24 DC V	1	6	
		2	n.c.	-	-	n.c.	2		
		3	0 V	BU	BU	0 V	3		
		4	Input 5	PK	RD	Input 6	4		
		5	PU	GN YE	GN YE	PU	5		
	7	1	24 DC V	BN	BN	24 DC V	1	8	
		2	n.c.	-	-	n.c.	2		
		3	0 V	BU	BU	0 V	3		
		4	Input 7	BK	VT	Input 8	4		
		5	PU	GN YE	GN YE	PU	5		

1) To IEC 757

Multi-pin plug distributor, open cable end 11-wire, socket M12, 5-pin

Technical data

Dimensions Download CAD data → www.festo.com


1 Connecting cable, length of 5 m
 2 Socket M12, 5-pin
 3 Switching status indication
 4 Ready status display

Type	B1	B2	B3	D1	D3 ∅	D4 ∅	H2	H3	L1	L2	L4	L7	L8	L9
MPV-E/A08-M12	54	33	27	M12	4.5	9	25	18	127	73	27	4.5	5000	30.5

Ordering data

Electrical connection	Weight [g]	Part No.	Type
Open cable end, 11-pin		177671	MPV-E/A08-M12

Ordering data – Accessories

Designation	Part No.	Type
Cover cap	165592	ISK-M12
 Cover cap for sealing unused sockets (10 pieces)	For M12 connections	


Multi-pin plug distributor, plug M12, 8-pin, socket M8, 3-pin

Technical data

FESTO

Multi-pin plug distributor NEDU-L

- Multi-pin plug distributor
- Particularly compact



General technical data	
Electrical connection	Straight plug, M12, 8-pin Straight socket, M8, 3-pin
Mounting position	Any
Operating voltage range [V DC]	10 ... 30
Acceptable current load [A]	3
Acceptable current load per slot [A]	2
Ready status display	Green LED
Status display	Yellow LED
Protection class to EN 60529	IP68

Materials	
Housing	PBT, reinforced
Housing colour	Grey
Seals	FPM
Pin contacts	Nickel-plated and gold-plated
Socket	Nickel-plated brass
Corrosion resistance class CRC ¹⁾	3

1) Corrosion resistance class 3 according to Festo standard 940 070
Components subject to high corrosion stress. Externally visible parts with primarily functional surface requirements which are in direct contact with a normal industrial environment or media such as solvents and cleaning agents.

Operating and environmental conditions	
Ambient temperature [°C]	-20 ... +80


Multi-pin plug distributor, plug M12, 8-pin, socket M8, 3-pin

Technical data


Connection and display components

NEDU-L4R1-M8G3L-M12G8

NEDU-L6R1-M8G3L-M12G8



- 1 Sensor connection, location 1
- 2 Sensor connection, location 2
- 3 Sensor connection, location 3
- 4 Sensor connection, location 4
- 5 Mounting holes
- 6 Multi-pin plug connection
- 7 Holder for inscription label (ASLR-L-55)
- 8 LED for status display



- 1 Sensor connection, location 1
- 2 Sensor connection, location 2
- 3 Sensor connection, location 3
- 4 Sensor connection, location 4
- 5 Sensor connection, location 5
- 6 Sensor connection, location 6
- 7 Mounting holes
- 8 Multi-pin plug connection
- 9 Holder for inscription label (ASLR-L-55)
- 10 LED for status display

Circuitry (socket/plug view)

Individual connection		Allocation		Multi-pin plug connection	
	Location	Pin		Pin	
	1	1	+UB	5	
		3	-UB	7	
		4	Input 1	1	
	2	1	+UB	5	
		3	-UB	7	
		4	Input 2	2	
	3	1	+UB	5	
		3	-UB	7	
		4	Input 3	3	
	4	1	+UB	5	
		3	-UB	7	
		4	Input 4	4	
	5	1	+UB	5	
		3	-UB	7	
		4	Input 5	6	
	6	1	+UB	5	
		3	-UB	7	
		4	Input 6	8	

Multi-pin plug distributor, plug M12, 8-pin, socket M8, 3-pin

Technical data

Dimensions Download CAD data → www.festo.com

1 Plug M12, 8-pin
2 Socket M8, 3-pin

Type	B1	B2	B3	B4	D1 Ø	D2 Ø	H1	H2	H3	L1	L2	L3	L4	L5	L6
NEDU-L4R1-M8G3L-M12G8	24	17	12	8.4	4.2	4.2	23	18.2	9	87	80	14.5	21	13	3.5
NEDU-L6R1-M8G3L-M12G8	24	17	12	8.4	4.2	4.2	23	18.2	9	113	106	14.5	21	13	3.5

Ordering data

Electrical connection	Weight [g]	Part No.	Type
Plug M12, 8 pin	4x socket, M8, 3-pin	574586	NEDU-L4R1-M8G3L-M12G8
	6x socket, M8, 3-pin	574587	NEDU-L6R1-M8G3L-M12G8

Ordering data – Accessories

Designation	Part No.	Type	
Connecting cable			
	Socket M12, 8-pin, angled	Open cable end, 8-wire	
		Length: 2 m	542256 NEBU-M12W8-2-N-LE8
		Length: 5 m	542257 NEBU-M12W8-5-N-LE8
	Length: 10 m	570007 NEBU-M12W8-10-N-LE8	
	Socket M12, 8-pin, straight	Open cable end, 8-wire	
		Length: 2 m	525616 SIM-M12-8GD-2-PU
		Length: 5 m	525618 SIM-M12-8GD-5-PU
Length: 10 m		570008 SIM-M12-8GD-10-PU	
Plug M12, 8-pin, straight	Length: 2 m	525617 KM12-8GD8GS-2-PU	
Cover cap			
	Cover cap for sealing unused sockets (10 pieces)	For M12 connections	
		165592 ISK-M12	
Inscription label			
	Inscription labels in frames, pack of 1000	5x5 mm	
		574590 ASLR-L-55	

Multi-pin plug distributor, plug Sub-D, 15-pin, socket M8, 3-pin

FESTO

Technical data

Multi-pin plug distributor MPV

- Multi-pin plug distributor



General technical data	
Electrical connection technology for I/O	M8, 3-pin
Type of mounting	Either via H-rail or through-hole
Operating voltage range [V DC]	10 ... 30
Acceptable current load [A]	4
Acceptable current load per slot [A]	1
Protection class to EN 60529	IP65 in mounted status

Materials	
Housing	Reinforced PA6
Socket	Brass

Operating and environmental conditions	
Ambient temperature [°C]	-20 ... +80

Multi-pin plug distributor, plug Sub-D, 15-pin, socket M8, 3-pin



Technical data

FESTO

Connection and display components

MPV-E/A08-M8

MPV-E/A12-M8



- 1 Sensor connection, location 1
- 2 Sensor connection, location 2
- 3 Sensor connection, location 3
- 4 Sensor connection, location 4
- 5 Sensor connection, location 5
- 6 Sensor connection, location 6
- 7 Sensor connection, location 7
- 8 Sensor connection, location 8
- 9 Mounting holes
- 10 Holder for inscription label (IBS-6x10)
- 11 LED for status display
- 12 Multi-pin plug connection

- 1 Sensor connection, location 1
- 2 Sensor connection, location 2
- 3 Sensor connection, location 3
- 4 Sensor connection, location 4
- 5 Sensor connection, location 5
- 6 Sensor connection, location 6
- 7 Sensor connection, location 7
- 8 Sensor connection, location 8
- 9 Sensor connection, location 9
- 10 Sensor connection, location 10
- 11 Sensor connection, location 11
- 12 Sensor connection, location 12
- 13 Mounting holes
- 14 Holder for inscription label (IBS-6x10)
- 15 LED for status display
- 16 Multi-pin plug connection

Circuitry (socket/plug view)



Individual connection	Allocation		Multi-pin plug connection		Allocation		Individual connection		
	Location	Pin	Pin	Pin	Pin	Pin	Location		
	1	1	24 DC V	13	13	24 DC V	2		
		3	0 V	14/15	14/15	0 V		3	
		4	Input 1	1	2	Input 2		4	
	3	1	1	24 DC V	13	13	24 DC V	4	
			3	0 V	14/15	14/15	0 V		3
			4	Input 3	3	4	Input 4		4
	5	1	1	24 DC V	13	13	24 DC V	6	
			3	0 V	14/15	14/15	0 V		3
			4	Input 5	5	6	Input 6		4
	7	1	1	24 DC V	13	13	24 DC V	8	
			3	0 V	14/15	14/15	0 V		3
			4	Input 7	7	8	Input 8		4
9	1	1	24 DC V	13	13	24 DC V	10		
		3	0 V	14/15	14/15	0 V		3	
		4	Input 9	9	10	Input 10		4	
11	1	1	24 DC V	13	13	24 DC V	12		
		3	0 V	14/15	14/15	0 V		3	
		4	Input 11	11	12	Input 12		4	

Multi-pin plug distributor, plug Sub-D, 15-pin, socket M8, 3-pin

Technical data

Dimensions

Download CAD data → www.festo.com



- 1 Connecting cable
- 2 Socket M8, 3-pin
- 3 Switching status indication
- 4 Inscription label





Type	B1	B2	B3	D1	D2	D3 ∅	H1	H2	H3	L1	L2	L3	L4	L5	L6	L7
MPV-E/A08-M8	45	39	29	M8	M3	4.2	126	19.5	15	98	90	18	14	12	9	4
MPV-E/A12-M8	45	39	29	M8	M3	4.2	126	19.5	15	126	118	18	14	12	9	4

Multi-pin plug distributor, plug Sub-D, 15-pin, socket M8, 3-pin

FESTO

Accessories

Ordering data				
Electrical connection		Weight [g]	Part No.	Type
Plug Sub-D, 15-pin	Socket M8x8	100	177669	MPV-E/A08-M8
	Socket M8x12	120	177670	MPV-E/A12-M8

Ordering data – Accessories				
Designation			Part No.	Type
Multi-pin plug connection				
	Plug socket with cable <ul style="list-style-type: none"> • Socket Sub-D, 15-pin • Open cable end, 15-wire 	5 m	177673	KMPV-SUB-D-15-5
		10 m	177674	KMPV-SUB-D-15-10
	Socket Sub-D, 15-pin		177675	SD-SUB-D-BU15
Cover cap				
	Cover cap for sealing unused sockets (10 pieces)	For M8 connections	177672	ISK-M8
Inscription label				
	Inscription labels in frames, pack of 64	6x10 mm	18576	IBS-6x10

Product Range and Company Overview

A Complete Suite and Company Overview

Our experienced engineers provide complete support at every stage of your development process, including: conceptualization, analysis, engineering, design, assembly, documentation, validation, and production.



Custom Automation Components
Complete custom engineered solutions



Custom Control Cabinets
Comprehensive engineering support and on-site services



Complete Systems
Shipment, stocking and storage services

The Broadest Range of Automation Components

With a comprehensive line of more than 30,000 automation components, Festo is capable of solving the most complex automation requirements.



Electromechanical
Electromechanical actuators, motors, controllers & drivers



Pneumatics
Pneumatic linear and rotary actuators, valves, and air supply



PLCs and I/O Devices
PLC's, operator interfaces, sensors and I/O devices

Supporting Advanced Automation... As No One Else Can!

Festo is a leading global manufacturer of pneumatic and electromechanical systems, components and controls for industrial automation, with more than 16,000 employees in 60 national headquarters serving more than 180 countries. For more than 80 years, Festo has continuously elevated the state of manufacturing with innovations and optimized motion control solutions that deliver higher performing, more profitable automated manufacturing and processing equipment. Our dedication to the advancement of automation extends beyond technology to the education and development of current and future automation and robotics designers with simulation tools, teaching programs, and on-site services.

Quality Assurance, ISO 9001 and ISO 14001 Certifications

Festo Corporation is committed to supply all Festo products and services that will meet or exceed our customers' requirements in product quality, delivery, customer service and satisfaction.

To meet this commitment, we strive to ensure a consistent, integrated, and systematic approach to management that will meet or exceed the requirements of the ISO 9001 standard for Quality Management and the ISO 14001 standard for Environmental Management.




© Copyright 2013, Festo Corporation. While every effort is made to ensure that all dimensions and specifications are correct, Festo cannot guarantee that publications are completely free of any error, in particular typing or printing errors. Accordingly, Festo cannot be held responsible for the same. For Liability and Warranty conditions, refer to our "Terms and Conditions of Sale", available from your local Festo office. All rights reserved. No part of this publication may be reproduced, distributed, or transmitted in any form or by any means, electronic, mechanical, photocopying or otherwise, without the prior written permission of Festo. All technical data subject to change according to technical update.



Printed on recycled paper at New Horizon Graphic, Inc., FSC certified as an environmental friendly printing plant.

Festo North America



**1 Festo Canada
Headquarters
Festo Inc.**
5300 Explorer Drive
Mississauga, ON
L4W 5G4

2 Montréal
5600, Trans-Canada
Pointe-Claire, QC
H9R 1B6

3 Québec City
2930, rue Watt#117
Québec, QC
G1X 4G3



**4 Festo United States
Headquarters
Festo Corporation**
395 Moreland Road
Hauppauge, NY
11788

5 Appleton
North 922 Tower View Drive, Suite N
Greenville, WI
54942

7 Detroit
1441 West Long Lake Road
Troy, MI
48098

6 Chicago
85 W Algonquin - Suite 340
Arlington Heights, IL
60005

8 Silicon Valley
4935 Southfront Road, Suite F
Livermore, CA
94550

Festo Regional Contact Center

Canadian Customers

Commercial Support:
Tel: 1 877 GO FESTO (1 877 463 3786)
Fax: 1 877 FX FESTO (1 877 393 3786)
Email: festo.canada@ca.festo.com

Technical Support:

Tel: 1 866 GO FESTO (1 866 463 3786)
Fax: 1 877 FX FESTO (1 877 393 3786)
Email: technical.support@ca.festo.com

USA Customers

Commercial Support:
Tel: 1 800 99 FESTO (1 800 993 3786)
Fax: 1 800 96 FESTO (1 800 963 3786)
Email: customer.service@us.festo.com

Technical Support:

Tel: 1 866 GO FESTO (1 866 463 3786)
Fax: 1 800 96 FESTO (1 800 963 3786)
Email: product.support@us.festo.com