

Pressure sensors SPAE

FESTO



Pressure sensors SPAE

Key features

Function

The SPAE is an electronic pressure sensor with piezoresistive pressure measuring cell, integrated signal processing, numerical percentage pressure indicator, control keys and a switching output, PNP/NPN switchable. Two switching signals and the pressure measurement value can be transmitted via IO-Link.


Key features

- The sensor can be set using the keys and display or alternatively using IO-Link or teach-in
- Switching functions: threshold value or window comparator
- Switching logic: normally open (NO) or normally closed (NC)
- Threshold values and hysteresis are adjustable
- Display of minimum and maximum readings
- Display can be rotated and switched off
- Protection against tampering using security code
- All parameters that have been input can be transferred to other SPAE (replicator function)

Method of measurement	Pressure measuring range [bar]	Measured variable	Pneumatic connection	Output	Electrical connection
Piezoresistive pressure sensor	0 ... -1	Relative pressure	Push-in sleeve 4 mm	PNP/NPN switchable, IO-Link	Cable, 3-wire open end
			Push-in sleeve 6 mm		
			Plug connector 3 mm		
			Plug connector 4 mm		
			Flange		
	0 ... 10	Relative pressure	Push-in sleeve 4 mm		
			Push-in sleeve 6 mm		
			Plug connector 3 mm		
			Plug connector 4 mm		
			Flange		

Pressure sensors SPAE

Peripherals overview



Accessories		→ Page/Internet
1	Pressure sensor SPAE-...-S...	5
2	Pressure sensor SPAE-...-F...	5
3	Pressure sensor SPAE-...-Q...	5
4	Blanking plug (included in the scope of delivery of SPAE-...-Q...)	qs
5	Plug connector NECU-S-M...G3-HX	9
6	Mounting clip SAMH-PE-MC-1	9
7	Mounting clip SAMH-PE-MC-8	9

Pressure sensors SPAE

Type codes

SPAE


SPAE		–		–	R	–		–	PNLK	–	2,5 K
Pressure sensors											
SPAE											
Pressure measuring range¹⁾											
P10	0 ... 10 bar										
V1	0 ... -1 bar										
Supply port											
R	Relative pressure										
Pneumatic connection											
S4	Push-in sleeve 4 mm										
S6	Push-in sleeve 6 mm										
Q3	Plug connector 3 mm										
Q4	Plug connector 4 mm										
F	Flange										
Electrical output											
PNLK	Switching output PNP/NPN/IO-Link										
Electrical connection											
2,5 K	Connecting cable 2.5 m, open end										

1) Additional pressure ranges on request

Pressure sensors SPAE

Technical data

Function



- - Voltage
18 ... 30 V DC
- - Pressure measuring range
-1 ... +10 bar
- - Temperature range
0 ... +50 °C



General technical data	
Certification	RCM mark c UL us - Recognized (OL)
Degree of protection	IP40
Note on materials	RoHS-compliant
Corrosion resistance class CRC ¹⁾	2
CE marking (see declaration of conformity)	In accordance with EU EMC Directive ²⁾

- 1) Corrosion resistance class CRC 2 to Festo standard FN 940070
Moderate corrosion stress. Indoor applications in which condensation may occur. External visible parts with primarily decorative requirements for the surface and which are in direct contact with the ambient atmosphere typical for industrial applications.
- 2) For information about the applicability of the component see the manufacturer's EC declaration of conformity at: www.festo.com/sp → User documentation.
If the component is subject to restrictions on usage in residential, office or commercial environments or small businesses, further measures to reduce the emitted interference may be necessary.

Input signal for measuring element	V1R	P10R
Measured variable	Relative pressure	
Method of measurement	Piezoresistive pressure sensor with display	
Pressure measuring range starting value [bar]	0	
Pressure measuring range final value [bar]	-1	10
Max. overload pressure [bar]	5	15
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]	
Note on operating/pilot medium	Lubricated operation possible	
Temperature of medium [°C]	0 ... 50	
Ambient temperature [°C]	0 ... 50	

Signal processing	
Resolution ADC	10 bits

Output, general		
Accuracy [% FS]	1.5 at room temperature	
Repetition accuracy [% FS]	0.3	
Temperature coefficient [% FS/K]	Typically 0.05	

Switching output		
Switching output	PNP/NPN, switchable	
Switching function	Freely programmable	
Switching element function	N/C or N/O contact, switchable	
Switch-on time [ms]	1	
Switch-off time [ms]	1	
Max. output current [mA]	100	
Protection against short circuit	Yes	

Pressure sensors SPAE

Technical data

FESTO

Measured value display		
Indicating range starting value	[% FS]	0
Indicating range final value	[% FS]	99

Communication interface	
Protocol	IO-Link
IO-Link, protocol version	Device V 1.1
IO-Link, profile	Smart Sensor profile
IO-Link, function classes	Binary data
	Diagnostics
	Identification
	Process Data Variable (PDV)
	Teach channel
IO-Link, communication mode	COM2 (38.4 kbd)
IO-Link, port class	A
IO-Link, process data width OUT	0 byte
IO-Link, process data width IN	2 bytes
IO-Link, process data content IN	2 bit BDC (pressure monitoring)
	14 bit PDV (pressure reading)
IO-Link, minimum cycle time	[ms] 3
IO-Link, SIO mode support	Yes
IO-Link, data memory required	0.5 KB

Electronics		
Operating voltage range DC	[V]	18 ... 30
Reverse polarity protection		For all electrical connections

Electromechanical components	
Electrical connection	Cable, 3-wire open end
Cable length	[m] 2.5

Mechanical system	S4	S6	Q3	Q4	F
Type of mounting	Push-in		Via accessories		Via through-hole and screw
Mounting position	Any				
Pneumatic connection	Push-in sleeve QS-4	Push-in sleeve QS-6	QS3	QS4	Flange

Mechanical system, general	
Product weight	[g] 40
Information on housing materials	Reinforced PA

Display/operation	
Display type	LED display, 2-digit
Displayable units	% FS
Switching status display	Yellow LED
Setting options	Via display and keys, teach-in, IO-Link
Threshold value setting range	[%] 1 ... 98
Protection against tampering	PIN code

Pressure sensors SPAE


Technical data

FESTO

Dimensions

Download CAD data → www.festo.com

SPAE-...-S-...-




- 1 Pressure supply port, push-in sleeve
for SPAE-S4
for SPAE-S6

Type	B1	D1 ∅	D2 ∅	H1	H2	H3	L2	L3	L4	L5
SPAE-V1R-S4-...	9.8	4	2.9	18	30.8	29.3	20.5	2500	17.5	6.9
SPAE-V1R-S6-...		6		21						
SPAE-P10R-S4-...		4		18						
SPAE-P10R-S6-...		6		21						

Dimensions

Download CAD data → www.festo.com

SPAE-...-Q-...-



- 1 Pressure supply port on both sides
for SPAE-Q3 / QSIK-M-3-X
for SPAE-Q4 / QSIK-M-4-X
- 2 Blanking plug
for SPAE-Q3 / QSMC-3H
for SPAE-Q4 / QSC-4H
included

Type	B1	B2	D1 ∅	D2 ∅	H1	H2	H3	L2	L3	L4	L5
SPAE-V1R-Q3-...	9.8	0.7	3	2.9	~42	17.5	8.5	20.5	2500	17.5	13.6
SPAE-V1R-Q4-...			4								16.6
SPAE-P10R-Q3-...			3								13.6
SPAE-P10R-Q4-...			4								16.6

Pressure sensors SPAE


Technical data

FESTO

Dimensions

Download CAD data → www.festo.com

SPAE-...-F-...



1 Pressure supply port with O-ring for flat mounting in the case of SPAE-F

Type	B1	B2	B3	D2 Ø	D3 Ø	D4	H1	L1	L2	L3	L4	L5	L6	L7
SPAE-V1R-F-...	9.8	~5.4	2.1	2.9	2.1	M2x6	~32	30	20.5	2500	17.5	25	13.9	2.3
SPAE-P10R-F-...														

Ordering data

	Pressure measuring range ¹⁾	Pneumatic connection	Electrical connection	Part No.	Type
	0 ... -1	Push-in sleeve 4 mm	Cable, 3-wire open end	8001440	SPAE-V1R-S4-PNLK-2.5K
		Push-in sleeve 6 mm		8001441	SPAE-V1R-S6-PNLK-2.5K
	0 ... -1	Plug connector 3 mm	Cable, 3-wire open end	8001442	SPAE-V1R-Q3-PNLK-2.5K
		Plug connector 4 mm		8001443	SPAE-V1R-Q4-PNLK-2.5K
	0 ... -1	Flange	Cable, 3-wire open end	8001444	SPAE-V1R-F-PNLK-2.5K
	0 ... 10	Push-in sleeve 4 mm	Cable, 3-wire open end	8001445	SPAE-P10R-S4-PNLK-2.5K
		Push-in sleeve 6 mm		8001446	SPAE-P10R-S6-PNLK-2.5K
	0 ... 10	Plug connector 3 mm	Cable, 3-wire open end	8001447	SPAE-P10R-Q3-PNLK-2.5K
		Plug connector 4 mm		8001448	SPAE-P10R-Q4-PNLK-2.5K
	0 ... 10	Flange	Cable, 3-wire open end	8001449	SPAE-P10R-F-PNLK-2.5K

1) Additional pressure ranges on request


Pressure sensors SPAE

Accessories

Mounting clip SAMH-PE-MC-1

Materials:
POM

Note on materials:
RoHS-compliant





Dimensions and ordering data									
B1	D1	H1	L1	L2	L3	Part No.	Type		
10	3.2	5	17.5	5.3	4	571489	SAMH-PE-MC-1		

Mounting clip SAMH-PE-MC-8



Materials:
POM

Note on materials:
RoHS-compliant



-  - Note
The mounting clip SAMH-PE-MC-8 can be shortened by the user to the required number of slots.


Dimensions and ordering data										
B1	B2	B3	D1	H1	L1	L2	L3	L4	Part No.	Type
17.5	4	5.3	3.2	5	80	70	10	5	571490	SAMH-PE-MC-8

Ordering data – Plug connectors		Part No.	Type
	Electrical connection Plug connector M8x1, 3-pin, straight, insulation displacement connector	562024	NECU-S-M8G3-HX
	Electrical connection Plug connector M12x1, A-coded, 3-pin, straight, insulation displacement connector	562027	NECU-S-M12G3-HX

Product Range and Company Overview

A Complete Suite and Company Overview


Our experienced engineers provide complete support at every stage of your development process, including: conceptualization, analysis, engineering, design, assembly, documentation, validation, and production.



Custom Automation Components
Complete custom engineered solutions



Custom Control Cabinets
Comprehensive engineering support and on-site services



Complete Systems
Shipment, stocking and storage services

The Broadest Range of Automation Components

With a comprehensive line of more than 30,000 automation components, Festo is capable of solving the most complex automation requirements.



Electromechanical
Electromechanical actuators, motors, controllers & drivers



Pneumatics
Pneumatic linear and rotary actuators, valves, and air supply



PLCs and I/O Devices
PLC's, operator interfaces, sensors and I/O devices

Supporting Advanced Automation... As No One Else Can!

Festo is a leading global manufacturer of pneumatic and electromechanical systems, components and controls for industrial automation, with more than 16,000 employees in 60 national headquarters serving more than 180 countries. For more than 80 years, Festo has continuously elevated the state of manufacturing with innovations and optimized motion control solutions that deliver higher performing, more profitable automated manufacturing and processing equipment. Our dedication to the advancement of automation extends beyond technology to the education and development of current and future automation and robotics designers with simulation tools, teaching programs, and on-site services.

Quality Assurance, ISO 9001 and ISO 14001 Certifications

Festo Corporation is committed to supply all Festo products and services that will meet or exceed our customers' requirements in product quality, delivery, customer service and satisfaction.

To meet this commitment, we strive to ensure a consistent, integrated, and systematic approach to management that will meet or exceed the requirements of the ISO 9001 standard for Quality Management and the ISO 14001 standard for Environmental Management.




© Copyright 2013, Festo Corporation. While every effort is made to ensure that all dimensions and specifications are correct, Festo cannot guarantee that publications are completely free of any error, in particular typing or printing errors. Accordingly, Festo cannot be held responsible for the same. For Liability and Warranty conditions, refer to our "Terms and Conditions of Sale", available from your local Festo office. All rights reserved. No part of this publication may be reproduced, distributed, or transmitted in any form or by any means, electronic, mechanical, photocopying or otherwise, without the prior written permission of Festo. All technical data subject to change according to technical update.



Printed on recycled paper at New Horizon Graphic, Inc., FSC certified as an environmental friendly printing plant.

Festo North America



**1 Festo Canada
Headquarters
Festo Inc.**
5300 Explorer Drive
Mississauga, ON
L4W 5G4

2 Montréal
5600, Trans-Canada
Pointe-Claire, QC
H9R 1B6

3 Québec City
2930, rue Watt#117
Québec, QC
G1X 4G3



**4 Festo United States
Headquarters
Festo Corporation**
395 Moreland Road
Hauppauge, NY
11788

5 Appleton
North 922 Tower View Drive, Suite N
Greenville, WI
54942

7 Detroit
1441 West Long Lake Road
Troy, MI
48098

6 Chicago
85 W Algonquin - Suite 340
Arlington Heights, IL
60005

8 Silicon Valley
4935 Southfront Road, Suite F
Livermore, CA
94550

Festo Regional Contact Center

Canadian Customers

Commercial Support:
Tel: 1 877 GO FESTO (1 877 463 3786)
Fax: 1 877 FX FESTO (1 877 393 3786)
Email: festo.canada@ca.festo.com

Technical Support:
Tel: 1 866 GO FESTO (1 866 463 3786)
Fax: 1 877 FX FESTO (1 877 393 3786)
Email: technical.support@ca.festo.com

USA Customers

Commercial Support:
Tel: 1 800 99 FESTO (1 800 993 3786)
Fax: 1 800 96 FESTO (1 800 963 3786)
Email: customer.service@us.festo.com

Technical Support:
Tel: 1 866 GO FESTO (1 866 463 3786)
Fax: 1 800 96 FESTO (1 800 963 3786)
Email: product.support@us.festo.com