

Parallel grippers HGPC

FESTO



Parallel grippers HGPC

Key features

At a glance

General

The compact and low-cost parallel gripper consists of a two-part symmetrical housing. The piston moves traverse to the half-shell casing in an optimum housing design that

guarantees reliable operation, long service life and convenient sensing. The gripper jaws move along the half shells in backlash-free, preloaded ball bearing guides.


- Double-acting gripper
- Compression spring for supplementary or retaining gripping forces
- Internal fixed flow control, does away with the need for external flow control in 80% of applications
- High force with minimal volume

- Suitable for external and internal gripping
- Wide range of options for attaching drive units
- Repetition accuracy of 0.05 mm
- Slot for proximity sensor SME/SMT-10




Note
Sizing software
Gripper selection
→www.festo.com

Details




- 1 Gripper jaw with ball bearing guide
- 2 Housing based on half-shell principle
- 3 Slot for proximity sensor, for sensing the piston position
- 4 Mounting option
- 5 Supply port


Mounting option
from underneath



from above




Note
Parallel grippers are not designed for the following applications:




- Machining

- Aggressive media



- Grinding dust




- Welding spatter

Parallel grippers HGPC


Peripherals overview and type codes

FESTO

Peripherals overview



System product for handling and assembly technology



Accessories

Type	Description	➔ Page/Internet
[1] One-way flow control valve GRLA	For regulating speed	grla
[2] Push-in fitting QS	For connecting compressed air tubing with standard O.D.	qs
[3] Proximity sensor SME/SMT-10	For sensing the piston position	13
[4] Centring sleeve ZBH	For centring when attaching to a drive (2 included in the scope of delivery)	13
[5] Adapter kit HMSV, HAPG	Drive/gripper connections	12

Type codes

HGPC – 12 – A – G2

Type

HGPC Parallel gripper

Size

Position sensing

A Via proximity sensor

Gripping force backup

G2 Closing

- L - Type discontinued
Available up until 2018

FESTO


Parallel grippers HGPC

Technical data

Function

Double-acting

HGPC-...-A



- Ø -

Size
12, 16, 20 mm

- | -

Stroke
6 ... 14 mm

Single-acting or
with gripping force retention
closing HGPC-...-G2



General technical data

Size	12	16	20
Constructional design	Wedge-shaped drive		
	Guided motion sequence		
Mode of operation	Double-acting		
Gripper function	Parallel		
Number of gripper jaws	2		
Max. load per external gripper finger ¹⁾ [g]	20	50	80
Stroke per gripper jaw [mm]	3	5	7
Pneumatic connection	M5		
Repetition accuracy ²⁾ [mm]	≤ 0.05		
Max. interchangeability [mm]	≤ 0.2		
Max. gripper jaw backlash ³⁾ [mm]	0		
Max. gripper jaw angular backlash ⁴⁾ [°]	0		
Max. operating frequency [Hz]	4		
Rotational symmetry [mm]	< Ø 0.2		
Position sensing	For proximity sensing		
Type of mounting	With female thread and centring sleeve		
Mounting position	Any		

1) Valid for unthrottled operation

2) End-position drift under constant conditions of use with 100 consecutive strokes in the direction of movement of the gripper jaws

3) Perpendicular to the direction of motion of the gripper jaws

4) Pretensioned, backlash-free ball bearing guide

Operating and environmental conditions

Min. operating pressure	HGPC-...-A	[bar]	2
	HGPC-...-G2	[bar]	4
Max. operating pressure		[bar]	8
Operating medium	Compressed air in accordance with ISO 8573-1:2010 [7:4:4]		
Note on operating/pilot medium	Operation with lubricated medium possible (in which case lubricated operation will always be required)		
Ambient temperature ¹⁾	[°C]	+5 ... +60	
Corrosion resistance class CRC ²⁾		2	

1) Note operating range of proximity sensors

2) Corrosion resistance class 2 according to Festo standard 940 070

Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents

Weights [g]


Size	12	16	20
HGPC-...-A	152	241	473
HGPC-...-G2	154	244	477

Parallel grippers HGPC

Technical data

Materials


Sectional view



Parallel gripper


[1]	Gripper jaw	High-alloy steel
[2]	Housing	Die-cast zinc
[3]	Piston	Polyamide
-	Seals	Polyurethane, nitrile rubber
-	Note on materials	Copper and PTFE-free Conforms to RoHS

Gripping force [N] at 6 bar



Size	12	16	20
Gripping force per gripper jaw			
Opening	22	41.5	63
Closing	22	41.5	63
Total gripping force			
Opening	44	83	126
Closing	44	83	126

Static characteristic load values at the gripper jaws



Indicated permissible forces and torques apply to a single gripper jaw. The indicated values include the lever arm, additional applied loads caused by the workpiece or external gripper fingers, as well as forces which occur

during movement. The zero coordinate line (gripper finger guide) must be taken into consideration for the calculation of torques.

Size	12	16	20
Max. permissible force F_z [N]	40	80	120
Max. permissible torque M_x [Nm]	1	2,5	5
Max. permissible torque M_y [Nm]	1	2,5	5
Max. permissible torque M_z [Nm]	1	2,5	5


- L - Type discontinued
Available up until 2018

FESTO

Parallel grippers HGPC

Technical data

Mass moment of inertia [kgm²×10⁻⁴]




Mass moment of inertia [kgm²×10⁻⁴]
of the parallel gripper in relation to
the central axis with no load.


Size	12	16	20
HGPC-...-A	0.272	0.679	2.095
HGPC-...-G2	0.274	0.683	2.105

Opening and closing times [ms] at 6 bar

without external gripper fingers



with external gripper fingers



The indicated opening and closing times [ms] have been measured at room temperature and at 6 bar operating pressure with horizontally mounted gripper without additional

gripper fingers. The grippers must be throttled for greater loads [g].
Opening and closing times must then be adjusted correspondingly.


Size	12	16	20	
without external gripper fingers				
HGPC-...-A	Opening	30	60	90
	Closing	30	60	90
HGPC-...-G2	Opening	30	70	105
	Closing	30	50	75
with external gripper fingers (as a function of the load per gripper finger)				
HGPC-...	40 g	40	–	–
	50 g	60	–	–
	60 g	80	–	–
	70 g	–	80	–
	100 g	–	100	–
	120 g	–	–	100

Parallel grippers HGPC


Technical data

Gripping force F_{Grip} per gripper jaw as a function of operating pressure and lever arm x


Gripping forces as a function of the operating pressure and the lever arm can be determined for the size using the following graph.




HGPC-12-A



HGPC-16-A



HGPC-20-A



— 3 bar
- - - 6 bar
- - - - 8 bar



Parallel grippers HGPC

Technical data

Spring force F_S as a function of the gripper size and the overall stroke l

Gripping force retention for HGPC-...-G2

Spring forces F_S as a function of the gripper size and the overall stroke l for various gripper types (HGPC-...-G2) can be determined using the following graphs.



The lever arm x must be taken into consideration when determining the actual spring force F_{Total} . The formulae for calculating the spring force are provided in the table opposite.

Size	$F_{\text{Total}} =$
12	$-0.02 * x + 0.5 * F_S$
16	$-0.05 * x + 0.5 * F_S$
20	$-0.05 * x + 0.5 * F_S$

Determination of the actual gripping forces F_{Gr} for HGPC-...-G2 depending on the application

Parallel grippers with integrated spring type HGPC-...-G2 (closing gripping force retention) can be used as:

- single-acting grippers

- grippers with supplementary gripping force
- grippers with gripping force retention

In order to calculate available gripping forces F_{Gr} (per gripper jaw), the gripping force (F_{Grip}) and spring

force (F_{Total}) must be combined accordingly.


Application

Single-acting	Supplementary gripping force	Gripping force retention
• Gripping with spring force: $F_{\text{Gr}} = F_{\text{Total}}$	• Gripping with pressure and spring force: $F_{\text{Gr}} = F_{\text{Grip}} + F_{\text{Total}}$	• Gripping with spring force: $F_{\text{Gr}} = F_{\text{Total}}$
• Gripping with pressure force: $F_{\text{Gr}} = F_{\text{Grip}} - F_{\text{Total}}$		

Parallel grippers HGPC

Technical data

Gripping force F_{Grip} per gripper jaw at 6 bar as a function of lever arm x and eccentricity y



Gripping forces at 6 bar dependent upon eccentric application of force and the maximum permissible off-centre point of force application can be determined for the size using the following graph.

Calculation example

Given:

Lever arm $x = 20$ mm


Eccentricity $y = 22$ mm

To be found:


Gripping force at 6 bar

Procedure:


- Determine the intersection xy between lever arm x and eccentricity y in the graph for HGPC-12-A...
 - Draw an arc (with centre at origin) through intersection xy.
 - Determine the intersection between the arc and the X axis.
 - Read the gripping force.
- Result:
Gripping force $F = \text{approx. } 20.5$ N




HGPC-12-A



HGPC-16-A



HGPC-20-A



- Type discontinued
Available up until 2018


FESTO

Parallel grippers HGPC

Technical data

Dimensions

Download CAD data → www.festo.com



Size [mm]	B1	B2	B3	B4	D1	D2	D3	D4 ∅ F10/h7	D5 ∅	D6
12	38	33	22.4	6	12	$2.5^{+0.04/+0.01}$	3.3	7	5.3	M4
16	46	39	28	7	12	$3^{+0.05/-0.1}$	4.3	7	5.3	M5
20	57	50	35	8	12	$4^{+0.05/-0.1}$	5.3	9	6.4	M6

Size [mm]	EE	H1	H2	H3	H4	H5	H6	H7	H8	H9	H10
		± 0.5							-0.2		
12	M5	48.2	33.6	21.7	20.2	6.9	$5^{+0.05/-0.1}$	$9^{+0.05/-0.1}$	25	1.2	9.2
16	M5	55.2	38.2	25.2	23.7	8.2	$6^{+0.05/-0.1}$	$10.5^{+0.05/-0.1}$	28.5	1.5	10.7
20	M5	68.7	48.2	32.5	30.5	10.2	$7.5^{+0.05/-0.1}$	$13^{+0.05/-0.1}$	34.5	1.5	13.7

Size [mm]	L1	L2	L3	L4 ¹⁾	L5	L6	T1	T2	T3	T4 +0.4 -0.1	T5 +0.1 -0.3
	± 0.5	± 0.5					min.		± 0.1		
12	45	39	$10_{-0.02/-0.06}$	33	42	10	4.5	2.2	1.7	3.1	1.3
16	62	52	$12_{-0.05}$	40	51	12	4.5	2.7	1.8	3.8	1.2
20	77	63	$14_{-0.05}$	50	65	16	4.5	3.2	2.3	5.2	1.7


1) Tolerance for centring hole ± 0.03
Tolerance for thread ± 0.1

 Type discontinued
Available up until 2018

Parallel grippers HGPC

FESTO

Technical data



Minimum distance l between gripper and ferritic object			
Distance	[mm]	12	16
		10	20

Ordering data

	Size [mm]	Double-acting Without compression spring			Single-acting or with gripping force retention	
		Part No.	Type	Closing	Part No.	Type
	12	539 267	HGPC-12-A		539 268	HGPC-12-A-G2
	16	539 269	HGPC-16-A		539 270	HGPC-16-A-G2
	20	539 271	HGPC-20-A		539 272	HGPC-20-A-G2

Parallel grippers HGPC

Accessories

Adapter kit

HAPG

Material:

Wrought aluminium alloy
Free of copper and PTFE
RoHS-compliant



Note

The kit includes the individual mounting interface as well as the necessary mounting material.

Permissible drive/gripper combinations with adapter kit							Download CAD data → www.festo.com	
Combination	Drive	Gripper	Adapter kit			CRC ¹⁾	Part No.	Type
	Size	Size	Mounting option					
DGSL/HGPC	DGSL	HGPC				HAPG		
	12, 16	12	■	■		2	529018	HAPG-58
	20, 25	16	■	■			191267	HAPG-49
	20, 25	20	■	■			191269	HAPG-51
SLT/HGPC	SLT	HGPC				HAPG		
	10	12	■	—		2	542670	HAPG-100
	16	12	■	—			529018	HAPG-58
	16	16	■	—			542666	HAPG-101
	20	16	■	—			191267	HAPG-49
	20	20	■	—			542667	HAPG-102
	25	20	■	—			191269	HAPG-51
HSP/HGPC	HSP	HGPC				HAPG		
	16	16	■	—		2	191901	HAPG-55
	25	20	■	—			540882	HAPG-71-B
							191901	HAPG-55
							540883	HAPG-72-B
HSW/HGPC	HSW	HGPC				HAPG		
	12, 16	16	■	—		2	191901	HAPG-55
							540882	HAPG-71-B
ERMB/HGPC	ERMB	HGPC				HAPG		
	20	16	■	■		2	542668	HAPG-SD2-42
	20	20	■	■			542669	HAPG-SD2-43
	25	20	■	■			542758	HAPG-SD2-44

1) Corrosion resistance class 2 according to Festo standard 940 070

Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

Parallel grippers HGPC

Accessories

Ordering data – Centring sleeves			Technical data → Internet: zbh		
	For size [mm]	Weight [g]	Part No.	Type	PU ¹⁾
	12, 16	1	186717	ZBH-7	10
	20	1	150927	ZBH-9	10

1) Packaging unit

Ordering data – Proximity sensors for C-slot			Technical data → Internet: smt		
	Type of mounting	Electrical connection, connection direction	Switching output	Cable length [m]	Part No. Type
	N/O contact, magneto-resistive		PNP	2.5 0.3	551373 SMT-10M-PS-24V-E-2,5-L-OE
	Insertable in the slot from above	Cable, 3-wire, in-line Plug M8x1, 3-pin, in-line			551375 SMT-10M-PS-24V-E-0,3-L-M8D
N/O contact, magnetic reed			Technical data → Internet: sme		
	Insertable in the slot lengthwise	Cable, 3-wire, in-line Plug M8x1, 3-pin, in-line	Contacting	2.5 0.3	173210 SME-10-KL-LED-24 173212 SME-10-SL-LED-24

Ordering data – Proximity sensors for C-slot			Technical data → Internet: smt		
	Type of mounting	Electrical connection, connection direction	Switching output	Cable length [m]	Part No. Type
	N/O contact, magneto-resistive		PNP	2.5 0.3	551374 SMT-10M-PS-24V-E-2,5-Q-OE
	Insertable in the slot from above	Cable, 3-wire, lateral Plug M8x1, 3-pin, lateral			551376 SMT-10M-PS-24V-E-0,3-Q-M8D
N/O contact, magnetic reed			Technical data → Internet: sme		
	Insertable in the slot lengthwise	Cable, 3-wire, lateral Plug M8x1, 3-pin, lateral	Contacting	2.5 0.3	173211 SME-10-KQ-LED-24 173213 SME-10-SQ-LED-24

Ordering data – Connecting cables			Technical data → Internet: nebu		
	Electrical connection, left	Electrical connection, right	Cable length [m]	Part No.	Type
	Straight socket, M8x1, 3-pin	Cable, open end, 3-wire	2.5	541333	NEBU-M8G3-K-2.5-LE3
			5	541334	NEBU-M8G3-K-5-LE3
	Angled socket, M8x1, 3-pin	Cable, open end, 3-wire	2.5	541338	NEBU-M8W3-K-2.5-LE3
			5	541341	NEBU-M8W3-K-5-LE3

Festo - Your Partner in Automation



1 Festo Inc.

5300 Explorer Drive
Mississauga, ON L4W 5G4
Canada

Festo Customer Interaction Center

Tel: 1 877 463 3786
Fax: 1 877 393 3786
Email: customer.service.ca@festo.com

2 Festo Pneumatic

Av. Ceylán 3,
Col. Tequesquínáhuac
54020 Tlalnepantla,
Estado de México

Multinational Contact Center

01 800 337 8669
ventas.mexico@festo.com

3 Festo Corporation

1377 Motor Parkway
Suite 310
Islandia, NY 11749

Festo Customer Interaction Center

1 800 993 3786
1 800 963 3786
customer.service.us@festo.com

4 Regional Service Center

7777 Columbia Road
Mason, OH 45040

Connect with us



www.festo.com/socialmedia



www.festo.com