

Three-dimensional Gantry

Three-dimensional gantries

3-dimensional gantries are ideal for universal use, for handling light to heavy workpieces that need to be moved across three axes and long strokes.

Three-dimensional gantries

Stacking






A three dimensional gantry for dynamic, precision stacking.

The task:

The application in question is a stacking system with a requirement for high positioning accuracy (± 0.2 mm).

The solution

The selected DGEA is ideal for this task not only because of its positioning accuracy, but also its highly dynamic response. This dynamic response is facilitated by the consistent lightweight design with stationary drive head. As a result, the DGEA delivers acceleration of 15 m/s^2 with a speed of 2 m/s .



Three-dimensional gantries – System matrix

Three-dimensional systems

The system matrix provides you with condensed information regarding the most important parameters for quick selection of your system. Reference to the corresponding page, guides you to standard solutions and individual components.

A standard solution means:

- Complete bill of materials with exploded view
- Quick project planning
- Reliable data, accuracy, travel time

Workpiece load























With a standard front end (semi-rotary drive and gripper or gripper only), the workpiece load can serve as a basis for the approximate selection of a handling/positioning system.

Working load

The working load is a decisive factor in the precise selection of a standard handling system.

The working load of a handling/positioning system is the sum of the loads of the following parts:

























- Function units (semi-rotary drives and grippers)
- Adapter plates
- Gripper fingers
- Workpiece

Three-dimensional gantries								
								
Drive system	P ¹⁾	PS	SP	ZR	P ¹⁾	PS	SP	ZR
Moving loads								
Max. working load	0 ... 6 kg				0 ... 4 kg			
Workpiece load	0 ... 2 kg				0 ... 3 kg			
Stroke range [mm]								
X-direction (horizontal)								
	0 ... 3000	100 ... 1600	100 ... 1000 ²⁾	100 ... 2000 ³⁾	0 ... 3000	100 ... 1600	100 ... 1000 ³⁾	100 ... 2000 ³⁾
Y-direction (horizontal)								
	0 ... 3000	100 ... 1600	100 ... 1000 ³⁾	100 ... 2000 ³⁾	0 ... 3000	100 ... 1600	100 ... 1000 ³⁾	100 ... 2000 ³⁾
Z-direction (vertical)								
	0 ... 200		0 ... 150		0 ... 200			
Intermediate positions								
X	–	any			– ¹⁾	any		
Y	–	any			– ¹⁾	any		
Z	–		any	–	1	–		
Repetition accuracy [mm]								
X	0.02	0.4	±0.02	±0.1	0.02	0.4	±0.02	±0.1
Y	0.02	0.4	±0.02	±0.1	0.02	0.4	±0.02	±0.1
Z	0.02	–			0.02	–		
Standard examples								
Type	DGPL/DGPL/SLT(E)	DGE/DGE/SLT(E)	DGPL/DGPL/HMPL	DGE/DGE/HMPL				
Page								

¹⁾ Also available with end position controller SPC11 (Soft Stop)

²⁾ Stroke of up to 4500 mm

³⁾ Stroke of up to 2000 mm with reduced dynamics

Three-dimensional gantries								
								
Drive system	P ¹⁾	PS	SP	ZR	P ¹⁾	PS	SP	ZR
Moving loads								
Max. working load	0 ... 10 kg				0 ... 10 kg			
Workpiece load	0 ... 5 kg				0 ... 5 kg			
Stroke range [mm]								
X-direction (horizontal)								
	0 ... 3000	100 ... 1600	100 ... 1000 ³⁾	100 ... 2000 ²⁾	0 ... 3000	100 ... 1600	100 ... 1000 ³⁾	100 ... 2000 ²⁾
Y-direction (horizontal)								
	0 ... 3000	100 ... 1600	100 ... 1000 ³⁾	100 ... 2000 ²⁾	0 ... 3000	100 ... 1600	100 ... 1000 ³⁾	100 ... 2000 ²⁾
Z-direction (vertical)								
	0 ... 400				0 ... 3000	100 ... 1600	100 ... 1000 ³⁾	100 ... 2000 ²⁾
Intermediate positions								
X	–	any			– ¹⁾	any		
Y	–	any			– ¹⁾	any		
Z	1	–			– ¹⁾	any		
Repetition accuracy [mm]								
X	0.02	0.4	±0.02	±0.1	0.02	0.4	±0.02	±0.1
Y	0.02	0.4	±0.02	±0.1				
Z	0.01	–						
Standard examples								
Type	DGPL/DGPL/HMP	DGE/DGE/HMP	DGPL/DGPL/DGPL	DGE/DGE/DGE				
Page								

H Note

- P Pneumatic
- PS Servo-pneumatic
- SP Spindle axis, electrical
- ZR Toothed belt axis, electrical

Three-dimensional gantries

Three-dimensional gantry DG.../DG.../SLT(E)


For horizontal strokes up to 3000 mm and vertical Z strokes up to 200 mm with working loads of 6 kg: the combination of two parallel drives DG... and one linear gantry DG.../SLT or DG.../SLTE.

Sample application

Handling of very heavy workpieces using very long strokes, for example assembly, equipping and palletising

Other attributes of the system

- Reliability and precision through high mechanical rigidity
- DUO system structure for particularly high loads
- Operational and process reliability through routing of tubing and cables in conduits and protective trunking
- Flexibility through the variety of solutions offered by the modular handling system
- User friendliness through easy assembly and installation, even during servicing





Attributes of the handling system

- Choice of pneumatic or electrical drive for all axes
- Any number of intermediate positions along X- and Y-axes with servo-pneumatic or electrical axes
- Pneumatic or electrical drive along Z-axis
- Very high dynamic response thanks to twin piston slide SLT along Z-axis


System type	Mono		Duo		
Working load	2 kg	4 kg	4 kg	6 kg	
X-axis					
DGE	Size	25	25	40	
	Max. stroke	3000			
	Drive system	electrical with toothed belt drive			
	Options	roller guide or ball-bearing guide			
Y-axis					
DGPL/DGC/DGE	Size	25	40	25	
	Max. stroke	3000			
	Drive system	pneumatic, electrical			
	Options	electrical: spindle drive or toothed belt drive			
Z-axis					
SLT, SLTE	Size	16	20	20	25
	Max. stroke	150	200		
	Drive system	pneumat.,electr.	pneumatic		
	Options	shock absorber, adjustable cushioning, fixed cushioning, freely positionable (SLTE)			
Basic and installation components					

- 1 Toothed belt axis DGE-ZR
- 2 Servo motor MTR-AC
- 3 Rodless drive DGPL
- 4 Mini slide SLT
- 5 Parallel gripper HGP



The example provides information regarding cycle times for a standard combination. The workpiece is moved diagonally from one corner to the opposite corner.

2 x DGE-40-1000-ZR-KF (X-axis) Cycle:
 DGE-40-800-ZR-KF (X-axis)
 SLT-20-100 (Z-axis)
 DRQD-16-180 (Semi-rotary drive)
 2 x HGP-16 (Gripper)



Cycle time: 4,5 s
 Mean load: 2 x 0.1 kg

Three-dimensional gantries

Three-dimensional gantry DG.../DG.../HMPL

For horizontal X and Y strokes up to 3000 mm and vertical Z strokes up to 200 mm as well as working loads up to 4 kg and additional functions such as intermediate position with through travel capability: the combination of two parallel drives DG... and one linear gantry DG.../HMPL.

Attributes of the handling system


- Choice of pneumatic or electrical drive for horizontal X- and Y-axes
- Any number of intermediate positions along X- and Y-axes with servo-pneumatic or electrical axes
- Additional functions of intermediate position (with through travel capability) and clamping cartridge possible along the Z-axis

Sample application

Handling of workpieces using very long X and Y strokes, for example assembly and equipping


Other attributes of the system

- Reliability and precision through high mechanical rigidity
- DUO system structure for particularly high loads
- Operational and process reliability through routing of tubing and cables in conduits and protective trunking
- Flexibility through the variety of solutions offered by the modular handling system
- User friendliness through easy assembly and installation, even during servicing




System type		Mono		Duo
Working load		2 kg	4 kg	4 kg
X-axis				
DGE	Size	25		25
	Max. stroke	3000		
	Drive system	electrical with toothed belt drive		
	Options	roller guide or ball-bearing guide		
Y-axis				
DGPL/DGC/DGE	Size	25	40	25
	Max. stroke	3000		
	Drive system	pneumatic, electrical		
	Options	electrical: spindle drive or toothed belt drive		
Z-axis				
HMPL	Size	16	20	20
	Max. stroke	160	200	200
	Drive system	pneumatic		
	Options	intermediate position, clamping cartridge		
Basic and installation components				

- 1 Toothed belt axis DGE-ZR
- 2 Servo motor MTR-AC
- 3 Rodless drive DGPL
- 4 Linear module HMPL
- 5 Semi-rotary drive DRQD
- 6 Three-point gripper HGD



The example provides information regarding cycle times for a standard combination. The workpiece is moved diagonally from one corner to the opposite corner.

- 2 x DGE-25-1000-ZR-KF (X-axis)
- DGE-25-500-ZR-KF (X-axis)
- HMPL-20-160 (Z-axis)
- DRQD-16-180 (Semi-rotary drive)
- HGPP-12 (Gripper)



Cycle time: 4,5 s
Mean load: 0,05 kg

Three-dimensional gantries

Three-dimensional gantry DG.../DG.../HMP

For horizontal X and Y strokes up to 3000 mm and vertical Z strokes up to 400 mm as well as working loads up to 10 kg and additional functions: the combination of two parallel drives DG... and one linear gantry DG.../HMP.

Attributes of the handling system

- Choice of pneumatic or electrical drive for horizontal X- and Y-axes
- Any number of intermediate positions along X- and Y-axes with servopneumatic or electrical axes
- Additional functions of intermediate position or clamping cartridge possible along the Z-axis

Sample application

Handling of heavy workpieces using long strokes, for example assembly, equipping


Other attributes of the system

- Reliability and precision through high mechanical rigidity
- DUO system structure for particularly high loads
- Operational and process reliability through routing of tubing and cables in conduits and protective trunking
- Flexibility through the variety of solutions offered by the modular handling system
- User friendliness through straightforward assembly and installation, even during servicing




System type		Mono		Duo	
Working load		4 kg	4 kg	6 kg	10 kg
X-axis					
DGE	Size	25	25	40	
	Max. stroke	3000			
	Drive system	electrical with toothed belt drive			
	Options	roller guide or ball-bearing guide			
Y-axis					
DGPL/DGC/DGE	Size	40	25	40	
	Max. stroke	3000			
	Drive system	pneumatic, electrical			
	Options	electrical: spindle drive or toothed belt drive			
Z-axis					
HMP	Size	16	16	20	25
	Max. stroke	320		400	
	Drive system	pneumatic			
	Options	intermediate position, clamping cartridge			
Basic and installation components					

- 1 Toothed belt axis DGE-ZR see page 96
- 2 Servo motor MTR-AC see page 106
- 3 Linear module HMP see page 72
- 4 Parallel gripper HGPP see page 122



The example provides information regarding cycle times for a standard combination. The workpiece is moved diagonally from one corner to the opposite corner.

2 x DGE-40-1000-ZR-KF (X-axis)
 DGE-25-500-ZR-KF (X-axis)
 HMP-25-160 (Z-axis)
 DRQD-20-180 (Semi-rotary drive)
 HGPP-16 (Gripper)



Cycle time: 6.5 s
 Workpiece load: 1 kg

Three-dimensional gantries

Three-dimensional gantry DG.../DG.../DG...

A three dimensional gantry for working areas exceeding 1 m²: for strokes up to 3000 mm and working loads up to 10 kg.

Attributes of the handling system

- Choice of pneumatic or electrical drive for all axes
- Any number of intermediate positions along X- and Y-axes with servo-pneumatic or electrical axes
- Choice of alternative guiding qualities and drive concepts

Sample application

Handling of very heavy workpieces using very long strokes, for example assembly, equipping and palletising



Other attributes of the system

- Reliability and precision through high mechanical rigidity
- DUO system structure for particularly high loads
- Operational and process reliability through routing of tubing and cables in conduits and protective trunking
- Flexibility through the variety of solutions offered by the modular handling system
- User friendliness through straightforward assembly and installation, even during servicing




System type		Mono		Duo	
Working load		2 kg	4 kg	4 kg	10 kg
X-axis					
DGE	Size	25		40	
	Max. stroke	3000			
	Drive system	electrical with toothed belt drive			
	Options	roller guide or ball-bearing guide			
Y-axis					
DGPL/DGC/DGE	Size	25	40	25	40
	Max. stroke	3000			
	Drive system	pneumatic, pneumatic with Soft Stop SPC11, electrical			
	Options	electrical: spindle drive or toothed belt drive			
Z-axis					
DGEA	Size	18		25	
	Max. stroke	800		900	
	Drive system	electrical			
	Options	spindle drive or toothed belt drive			
Basic and installation components					

- 1 Toothed belt axis DGE-ZR
- 2 Servo motor MTR-AC
- 3 Rodless drive DGC
- 4 Electrical axis DGEA
- 5 Semi-rotary drive DRQD
- 6 Precision parallel gripper HGPP



The example provides information regarding cycle times for a standard combination. The workpiece is moved diagonally from one corner to the opposite corner.


- 2 × DGE-40-1000-ZR-KF (X-axis)
- DGE-25-1000-ZR-KF (X-axis)
- DGE-25-600-SP-KF (Z-axis)
- DRQD-20-180 (Semi-rotary drive)
- HGPP-16 (Gripper)



Cycle time: 8 s
Workpiece load: 1 kg

Product Range and Company Overview

Custom Automation Components



Custom Control Cabinets



Complete Systems



Complete Automation Solutions

Our experienced engineers provide complete support at every stage of your development process, including: conceptualization, analysis, engineering, design, assembly, documentation, validation, and production.

Electromechanical



Pneumatics



PLCs and I/O Devices



Comprehensive Line of Automation Components

With a comprehensive line of more than 30,000 automation components, Festo can support the most complex automation requirements.

Supporting Advanced Automation... As No One Else Can

Festo is a leading global manufacturer of pneumatic and electromechanical systems, components and controls for industrial automation, with more than 11,500 employees in 56 national headquarters serving more than 180 countries. For more than 80 years, Festo has continuously elevated the state of manufacturing with innovations and optimized motion control solutions that deliver higher performing, more profitable automated manufacturing and processing equipment. Our dedication to the advancement of automation extends beyond technology to the education and development of current and future automation and robotics designers with simulation tools, teaching programs, and on-site services.

Festo North America

United States

Customer Resource Center

502 Earth City Expressway, Suite 125
Earth City, MO 63045

For ordering assistance,
or to find your nearest Festo Distributor,
Call: 1.800.99.FESTO
Fax: 1.800.96.FESTO
Email: customer.service@us.festo.com

For technical support,
Call: 1.866.GO.FESTO
Fax: 1.800.96.FESTO
Email: product.support@us.festo.com

Headquarters

Festo Corporation
395 Moreland Road
P.O. Box 18023
Hauppauge, NY 11788
www.festo.com/usa

Sales Offices

Appleton

North 922 Tower View Drive, Suite N
Greenville, WI 54942

Boston

120 Presidential Way, Suite 330
Woburn, MA 01801

Chicago

1441 East Business Center Drive
Mt. Prospect, IL 60056

Dallas

1825 Lakeway Drive, Suite 600
Lewisville, TX 75057

Detroit – Automotive Engineering Center

2601 Cambridge Court, Suite 320
Auburn Hills, MI 48326

New York

395 Moreland Road
Hauppauge, NY 11788

Silicon Valley

4935 Southfront Road, Suite F
Livermore, CA 94550

Design and Manufacturing Operations



East: 395 Moreland Road, Hauppauge, NY 11788



Central: 1441 East Business Center Drive, Mt. Prospect, IL 60056



West: 4935 Southfront Road, Suite F, Livermore, CA 94550

Mexico

Headquarters

Festo Pneumatic, S.A.
Av. Ceylán 3
Col. Tequesquahuac
54020 Tlalnepantla
Edo. de México
Call: 011 52 [55] 53 21 66 00
Fax: 011 52 [55] 53 21 66 65
Email: festo.mexico@mx.festo.com
www.festo.com/mx



Canada

Headquarters

Festo Inc.
5300 Explorer Drive
Mississauga, Ontario L4W 5G4
Call: 1.905.624.9000
Fax: 1.905.624.9001
Email: info_ca@ca.festo.com
www.festo.com/ca



Festo Worldwide

Argentina Australia Austria Belarus Belgium Brazil Bulgaria Canada Chile China
Colombia Croatia Czech Republic Denmark Estonia Finland France Germany Great Britain
Greece Hong Kong Hungary India Indonesia Iran Ireland Israel Italy Japan Latvia
Lithuania Malaysia Mexico Netherlands New Zealand Norway Peru Philippines Poland
Romania Russia Serbia Singapore Slovakia Slovenia South Africa South Korea Spain
Sweden Switzerland Taiwan Thailand Turkey Ukraine United States Venezuela

www.festo.com