Illuminating seals, square design Product range overview



Function	Design	Туре	For plug socket	For plug socket with cable	For solenoid coil (valves with solenoid coil)	→ Page/Internet
Illuminating		MF-LD	MSSD-F	KMF	For solenoid coil type: F Tiger 2000 Solenoid valves to ISO 5599-1 (VSVA) Solenoid valves to ISO 5599-1 Solenoid coils MSF Tiger Classic	3
		MC-LD	MSSD-C	KMC	For solenoid coil type: D, N1 MS-START-UP exhaust valves (on-off valves MS) Solenoid valves to ISO 5599-1 (VSVA) Solenoid valves to ISO 5599-1 Solenoid coils MSN1 Solenoid valves MN1H-MS, brass design	3
		MV-LD-12-24DC	MSSD-V	KMV	For solenoid coil type: V Tiger 2000	3
		ME-LD-12-24DC	MSSD-E	KME	For solenoid coil type: E Solenoid valves MEH/MEBH, midi pneumatic	3
		MEB-LD	MSSD-EB	KMEB	For solenoid coil type: EB, N2 MS-START-UP exhaust valves (on-off valves MS)	3

Illuminating seals, square design Technical data

FESTO

Illuminating seal Illuminating seals are mounted MF-LD between the plug socket and solenoid MC-LD coil. The sealing lip points to the coil MV-LD side, the label to the device socket. ME-LD The seal is illuminated yellow after the MEB-LD power is switched on.



General technical data						
Operating voltage		12 24 V DC	230 V AC			
Operating voltage range [V DC]			12 24	-		
Nominal operating voltage AC [V AC			=	230±10%		
Protective circuit, max. switch-off voltage [V DC]			yes, 50 –			
Degree of contamination			-	3		
Switching position display			LED (yellow)	LED (yellow)		
Rated output of illuminating seal		[mW]	50	330		
Impulse withstand voltage	MF-LD	[kV]	-	4		
	MC-LD	[kV]	-	4		
	MEB-LD	[kV]	-	2.5		
Electrical connection			To EN 175301-803			
Protective earth conductor connection			Yes			
Type of mounting	MF-LD		On solenoid valve via M3 central screw			
	MC-LD		On solenoid valve via M3 central screw			
	MV-LD		On solenoid valve via M3 central screw			
	ME-LD		On solenoid valve via M3 central screw			
	MEB-LD		On solenoid valve via M2.5 central screw			
Housing material			TPE-U (PU)			
Protection class to EN 60529		IP65 (in assembled state)				

Operating and environmental conditions					
Operating voltage		12 24 V DC	230 V AC		
Ambient temperature	[°C]	−25 +85	−25 +85		
CE marking		-	In accordance with EU Low Voltage		
(see declaration of conformity)			Directive		


Circuit diagram 12 ... 24 V DC 230 V AC ZD1 LED1 LED2

Illuminating seals, square design Technical data





Installation of the illuminating seal





The original seal must be removed before the illuminating seal is installed.

The sealing surface of the illuminating seal must point towards the plug socket, and the sealing rim towards the solenoid coil.

The illuminating seal is intended to be installed once. Reusing illuminating seals can impair their function.

Ordering data	Ordering data							
Illuminating seal for		Electrical connection to EN 175301-803	Design, square	Product weight [g]	Max. tighten- ing torque [Nm]	Operating voltage [V]	Part No.	Туре
	F solenoid coils	-	MSF	1.6	0.6	12 24 DC 230 AC	19143 19144	MF-LD-12-24DC MF-LD-230AC
	D and N1 solenoid coils	•	Type A, MSC	1.6	0.6	12 24 DC 230 AC	19145 19146	MC-LD-12-24DC MC-LD-230AC
	V solenoid coils	•	Type B, MSV	1.6	0.35	12 24 DC	35558	MV-LD-12-24DC
	E solenoid coils	-	MSE	0.6	0.35	12 24 DC	19141	ME-LD-12-24DC
	EB solenoid coils		Type C, MSEB	0.6	0.5	12 24 DC 230 AC	151717 151718	MEB-LD-12-24DC MEB-LD-230AC