

Filters MS-LFM/LFX, MS series, NPT


FESTO



Fine and micro filters MS9-LFM, MS series, NPT

Peripherals overview

FESTO



-  - Note

Other accessories:

- Module connector for combination with size MS6, MS9 or MS12
- ➔ Internet: rmv, armv

Mounting attachments and accessories					
		Individual device			➔ Page/ Internet
		With female thread 3/4/1/N3/4/N1	With connecting plate AG.../AQ... Without EU certification EX4	With EU certification EX4	
1	Connecting plate-SET MS9-AG...	-	■	■	ms9-ag
	Connecting plate-SET MS9-AQ...	-	■	-	ms9-aq
2	Module connector MS9-MV	-	-	-	ms9-mv
3	Mounting bracket MS9-WP	■	■	■	ms9-wp
4	Mounting bracket MS9-WPB	■	■	■	ms9-wp
5	Mounting bracket MS9-WPM	■	■	-	ms9-wp
6	Condensate drain, fully automatic, electrically actuated E2/E3/E4	■	■	-	14

Fine and micro filters MS9-LFM, MS series, NPT

FESTO

Type codes

		MS	9	-	LFM	-	N1	-	A	U	M	-	HF	-	DA
Series															
MS	Standard service unit														
Size															
9	Grid dimension 90 mm														
Service function															
LFM	Fine and micro filter														
Pneumatic connection															
N $\frac{3}{4}$	Thread NPT $\frac{3}{4}$														
N1	Thread NPT1														
G	Module without connecting thread, without connecting plate														
Grade of filtration															
A	0.01 µm														
B	1 µm														
Bowl guard															
U	Integrated as metal bowl														
Condensate drain															
M	Manual rotary														
V	Fully automatic														
Flow rate															
	Standard														
HF	High flow rate														
Filter contamination sensor															
	Without differential pressure indicator														
DA	Differential pressure indicator														

Further variants can be ordered using the modular system → 14


- Pneumatic connection
- Condensate drain
- Type of mounting
- EU certification
- UL certification
- Flow direction

Fine and micro filters MS9-LFM, MS series, NPT

FESTO


Technical data

Condensate drain
Manual rotary
Without differential pressure indicator




- Flow rate
325 ... 10,000 l/min
- Temperature range
-10 ... +60 °C
- Operating pressure
0 ... 20 bar


With differential pressure indicator



Condensate drain
Semi or fully automatic
Without differential pressure indicator



With differential pressure indicator



- High-performance filter for exceptionally clean compressed air
- Air quality to ISO 8573-1:2010
- Available with manual, semi-automatic, fully automatic or fully automatic, electrically actuated condensate drain
- Available with differential pressure indicator for indication of contamination
- Choice of filter cartridges: 0.01 µm or 1 µm
- New filter cartridges → 22
- Optional device variant EX4 for use in potentially explosive areas in zones 1, 2, 21 and 22

General technical data	
Size	MS9
Pneumatic connection 1, 2	
Female thread	G3/4, G1, NPT3/4 or NPT1
Connecting plate AG...	G1/2, G3/4, G1, G11/4 or G11/2
Connecting plate AQ...	NPT1/2, NPT3/4, NPT1, NPT11/4 or NPT11/2
Module without connecting thread/plate G	–
Constructional design	Fibre filter
Type of mounting	Via accessories In-line installation
Installation position	Vertical ±5°
Grade of filtration [µm]	0.01 (micro filter MS9-LFM-A) 1 (fine filter MS9-LFM-B)
Air purity class at the output	Compressed air in accordance with ISO 8573-1:2010 [1:7:2] (micro filter MS9-LFM-A) Compressed air in accordance with ISO 8573-1:2010 [5:7:3] (fine filter MS9-LFM-B)
Filter efficiency [%]	99.9999 (Grade of filtration 0.01 µm, micro filter MS9-LFM-A) 99.99 (Grade of filtration 1 µm, fine filter MS9-LFM-B)
Bowl guard	Integrated as metal bowl
Condensate drain	Manual rotary Semi-automatic Fully automatic Fully automatic, electrically actuated
Differential pressure indicator	Visual indicator
Residual oil content [mg/m³]	≤0.01 (micro filter MS9-LFM-A) ≤0.5 (fine filter MS9-LFM-B)
Max. condensate volume [cm³]	225

- Note: This product conforms to ISO 1179-1 and to ISO 228-1

Fine and micro filters MS9-LFM, MS series, NPT

FESTO

Technical data

Standard flow rate $q_n^{1)}$ [l/min]		
Version	Standard	High flow rate HF
Micro filter MS9-LFM-A		
Max. standard flow rate for air purity class $q_n \text{ max}$	6,500	7,800
Min. standard flow rate for air purity class $q_n \text{ min}$	325	390
Fine filter MS9-LFM-B		
Max. standard flow rate for air purity class $q_n \text{ max}$	7,000	10,000
Min. standard flow rate for air purity class $q_n \text{ min}$	350	500

1) Measured at $p_1 = 6 \text{ bar}$

· $\downarrow$ 125 l/min must be available for the fully automatic condensate drain to close correctly.

Operating and environmental conditions				
Condensate drain	Manual rotary	Semi-automatic	Fully automatic	Fully automatic, electrically actuated
	M	H	V	E2/E3/E4
Operating pressure [bar]	0 ... 20	1.5 ... 12	2 ... 12	0.8 ... 16
Operating medium	Compressed air in accordance with ISO 8573-1:2010 [6:8:4] ¹⁾			
Ambient temperature [°C]	-10 ... +60	+5 ... +60	+5 ... +60	+1 ... +60
Temperature of medium [°C]	-10 ... +60	+5 ... +60	+5 ... +60	+1 ... +60
Storage temperature [°C]	-10 ... +60	+5 ... +60	-10 ... +60	+1 ... +60
Corrosion resistance class CRC ²⁾	2			
Certification (variant UL1)	cULus recognized (OL)			

1) It is recommended to prefilter the compressed air for the micro filter MS-LFM-A using a fine filter MS-LFM-B (grade of filtration 1 µm).

2) Corrosion resistance class CRC 2 to Festo standard FN 940070

Moderate corrosion stress. Indoor applications in which condensation may occur. External visible parts with primarily decorative requirements for the surface and which are in direct contact with the ambient atmosphere typical for industrial applications.

ATEX	
EU certification	EX4
ATEX category gas	II 2G
Ex-ignition protection type gas	c T6 X
ATEX category dust	II 2D
Ex-ignition protection type dust	c T60 °C X
ATEX ambient temperature	-10 °C ≤ Ta ≤ +60 °C (manual rotary condensate drain M)
	+5 °C ≤ Ta ≤ +60 °C (semi-automatic/fully automatic condensate drain H/V)
CE mark (see declaration of conformity)	To EU Explosion Protection Directive (ATEX)

Fine and micro filters MS9-LFM, MS series, NPT


FESTO

Technical data

Weights [g]		
Version	Standard	High flow rate HF
Fine and micro filter	2,000	2,500
Fine and micro filter with condensate drain fully automatic, electrically actuated E2/E3/E4	2,900	2,900

Materials

Sectional view



Fine and micro filters		
1	Housing	Die-cast aluminium
2	Bowl	Wrought aluminium alloy
	Inspection window	PA
3	Filter	Borosilicate fibre
–	Cover	PA reinforced
–	Connecting plate, module connector, mounting bracket	Die-cast aluminium
–	Seals	NBR
Note on materials		Free of copper and PTFE


Fine and micro filters MS9-LFM, MS series, NPT

Technical data


FESTO

Standard flow rate q_n as a function of the differential pressure p_{1-2}


Grade of filtration 0.01 μm , pneumatic connection G $\frac{1}{2}$ /NPT $\frac{1}{2}$




Grade of filtration 0.01 μm , pneumatic connection G $\frac{3}{4}$ /NPT $\frac{3}{4}$




Grade of filtration 0.01 μm , pneumatic connection G1/NPT1



Grade of filtration 0.01 μm , pneumatic connection G1 $\frac{1}{4}$ /NPT1 $\frac{1}{4}$



Grade of filtration 0.01 μm , pneumatic connection G1 $\frac{1}{2}$ /NPT1 $\frac{1}{2}$



- 2 bar
- - - 4 bar ($q_{n \text{ min}}$: 268 l/min)
- · - 6 bar ($q_{n \text{ min}}$: 325 l/min)
- · · 8 bar
- - - 10 bar ($q_{n \text{ min}}$: 420 l/min)
- - - 12 bar
- - - 14 bar ($q_{n \text{ min}}$: 498 l/min)
- · · $q_{n \text{ max}}$
(with MS9-LFM-AGD/AQR: $q_{n \text{ max}}$ -values lie above the measured q_n -values)


Fine and micro filters MS9-LFM, MS series, NPT

FESTO


Technical data

Standard flow rate q_n as a function of the differential pressure p_{1-2}


Grade of filtration 1 μm , pneumatic connection $G\frac{1}{2}/NPT\frac{1}{2}$




Grade of filtration 1 μm , pneumatic connection $G\frac{3}{4}/NPT\frac{3}{4}$




Grade of filtration 1 μm , pneumatic connection $G1/NPT1$



Grade of filtration 1 μm , pneumatic connection $G1\frac{1}{4}/NPT1\frac{1}{4}$



Grade of filtration 1 μm , pneumatic connection $G1\frac{1}{2}/NPT1\frac{1}{2}$



- 2 bar
- - - 4 bar ($q_{n \text{ min}}$: 289 l/min)
- · - 6 bar ($q_{n \text{ min}}$: 350 l/min)
- · · 8 bar
- - - 10 bar ($q_{n \text{ min}}$: 450 l/min)
- - - 12 bar
- - - 14 bar ($q_{n \text{ min}}$: 540 l/min)
- · · $q_{n \text{ max}}$
(with MS9-LFM-AGD/AQR: $q_{n \text{ max}}$ -values lie above the measured q_n -values)

Fine and micro filters MS9-LFM, MS series, NPT


FESTO

Technical data

Standard flow rate q_n as a function of the differential pressure p_{1-2}

Grade of filtration 0.01 μm , pneumatic connection G $\frac{3}{4}$ /NPT $\frac{3}{4}$


High flow rate HF



- 2 bar
- - - 4 bar
- · - 6 bar ($q_{n \text{ min}}$: 390 l/min)
- · · 8 bar
- - - 10 bar
- - - 12 bar
- - - 14 bar
- - - $q_{n \text{ max}}$


Grade of filtration 0.01 μm , pneumatic connection G1/NPT1

High flow rate HF



Grade of filtration 1 μm , pneumatic connection G $\frac{3}{4}$ /NPT $\frac{3}{4}$


High flow rate HF



- 2 bar
- - - 4 bar
- · - 6 bar ($q_{n \text{ min}}$: 500 l/min)
- · · 8 bar
- - - 10 bar
- - - 12 bar
- - - 14 bar
- - - $q_{n \text{ max}}$

Grade of filtration 1 μm , pneumatic connection G1/NPT1

High flow rate HF



Fine and micro filters MS9-LFM, MS series, NPT

Technical data


FESTO

Dimensions – Basic version

Download CAD data → www.festo.com

Module without connecting thread, without connecting plate G

Module without connecting thread, without connecting plate G, with differential pressure indicator DA



Type	B1	B2	B3	L1		L2	L3	L5	L6
				Standard	High flow rate HF				
MS9-LFM-G	90	45	109	380.5	480.5	62	120	50	34.5
MS9-LFM-G-...-DA				405.5	505.5	88			

Fine and micro filters MS9-LFM, MS series, NPT

Technical data


FESTO

Dimensions – Connecting thread/connecting plate

Download CAD data → www.festo.com

With female thread 3/4/1/N3/4/N1

With connecting plate AG.../AQ...



Type	B4	B5	B6	B7		B8	D1	L4	L7	≡
					EX4				EX4	
MS9-LFM-3/4	90	104	91.5	-	-	-	G3/4	66	-	-
MS9-LFM-1							G1			
MS9-LFM-AGD	-	-	-	112	122	132	G1 1/2	-	35	30
MS9-LFM-AGE						132	G3/4			36
MS9-LFM-AGF						142	G1			41
MS9-LFM-AGG						162	G1 1/4			50
MS9-LFM-AGH						176	G1 1/2			55
MS9-LFM-N3/4	90	104	91.5	-	-	-	NPT3/4-14	66	-	-
MS9-LFM-N1							NPT1-11 1/2			
MS9-LFM-AQR	-	-	-	112	122	132	NPT1/2-14	-	35	30
MS9-LFM-AQS						132	NPT3/4-14			36
MS9-LFM-AQT						142	NPT1-11 1/2			41
MS9-LFM-AQU						162	NPT1 1/4-11 1/2			50
MS9-LFM-AQV						176	NPT1 1/2-11 1/2			55

- - Note: This product conforms to ISO 1179-1 and to ISO 228-1

Fine and micro filters MS9-LFM, MS series, NPT


FESTO

Technical data

Dimensions – Condensate drain


Download CAD data → www.festo.com

Manual rotary M/fully automatic V



Barbed connector for plastic tubing PUN(-H)-8x1,25


Semi-automatic H



Push-in connector for plastic tubing PUN-6/PAN-6

Fully automatic, electrically actuated E2/E3/E4

Technical data → Internet: pwea



Condensate drain PWEA:

- 2 Electrical connection: Screw terminal PG9
- 3 Connection 360° rotatable for plastic tubing PUN-H-12x2

Type	B1	D1	H1	L1	L2	L3
MS9-LFM-...-M/V	–	5.6	34.5	–	–	–
MS9-LFM-...-H		6.2				
MS9-LFM-...-E2/E3/E4	72	–	178	140	108	15

Fine and micro filters MS9-LFM, MS series, NPT

FESTO

Technical data

Ordering data						
Without differential pressure indicator						
Size	Condensate drain	Connection	Micro filter		Fine filter	
			Grade of filtration 0.01 μm		Grade of filtration 1 μm	
			Part No.	Type	Part No.	Type
Standard						
MS9	Manual rotary	NPT¾	553086	MS9-LFM-N¾-AUM	553090	MS9-LFM-N¾-BUM
		NPT1	553016	MS9-LFM-N1-AUM	553020	MS9-LFM-N1-BUM
		–	564047	MS9-LFM-G-AUM	564039	MS9-LFM-G-BUM
	Fully automatic	NPT¾	553088	MS9-LFM-N¾-AUV	553092	MS9-LFM-N¾-BUV
		NPT1	553018	MS9-LFM-N1-AUV	553022	MS9-LFM-N1-BUV
		–	564049	MS9-LFM-G-AUV	564041	MS9-LFM-G-BUV
High flow rate						
MS9	Manual rotary	NPT¾	552980	MS9-LFM-N¾-AUM-HF	552984	MS9-LFM-N¾-BUM-HF
		NPT1	553054	MS9-LFM-N1-AUM-HF	553058	MS9-LFM-N1-BUM-HF
		–	564051	MS9-LFM-G-AUM-HF	564043	MS9-LFM-G-BUM-HF
	Fully automatic	NPT¾	552982	MS9-LFM-N¾-AUV-HF	552986	MS9-LFM-N¾-BUV-HF
		NPT1	553056	MS9-LFM-N1-AUV-HF	553060	MS9-LFM-N1-BUV-HF
		–	564053	MS9-LFM-G-AUV-HF	564045	MS9-LFM-G-BUV-HF

Ordering data						
With differential pressure indicator						
Size	Condensate drain	Connection	Micro filter		Fine filter	
			Grade of filtration 0.01 μm		Grade of filtration 1 μm	
			Part No.	Type	Part No.	Type
Standard						
MS9	Manual rotary	NPT¾	553094	MS9-LFM-N¾-AUM-DA	553098	MS9-LFM-N¾-BUM-DA
		NPT1	553024	MS9-LFM-N1-AUM-DA	553028	MS9-LFM-N1-BUM-DA
		–	564048	MS9-LFM-G-AUM-DA	564040	MS9-LFM-G-BUM-DA
	Fully automatic	NPT¾	553096	MS9-LFM-N¾-AUV-DA	553100	MS9-LFM-N¾-BUV-DA
		NPT1	553026	MS9-LFM-N1-AUV-DA	553030	MS9-LFM-N1-BUV-DA
		–	564050	MS9-LFM-G-AUV-DA	564042	MS9-LFM-G-BUV-DA
High flow rate						
MS9	Manual rotary	NPT¾	552988	MS9-LFM-N¾-AUM-HF-DA	552992	MS9-LFM-N¾-BUM-HF-DA
		NPT1	553062	MS9-LFM-N1-AUM-HF-DA	553066	MS9-LFM-N1-BUM-HF-DA
		–	564052	MS9-LFM-G-AUM-HF-DA	564044	MS9-LFM-G-BUM-HF-DA
	Fully automatic	NPT¾	552990	MS9-LFM-N¾-AUV-HF-DA	552994	MS9-LFM-N¾-BUV-HF-DA
		NPT1	553064	MS9-LFM-N1-AUV-HF-DA	553068	MS9-LFM-N1-BUV-HF-DA
		–	564054	MS9-LFM-G-AUV-HF-DA	564046	MS9-LFM-G-BUV-HF-DA

Fine and micro filters MS9-LFM, MS series, NPT

FESTO

Ordering data – Modular products

Ordering table				
Grid dimension	[mm]	90	Condi- tions	Code
M Module No.	552940			
Series	Standard service unit			MS
Size	9			9
Function	Fine and micro filter			-LFM
Pneumatic connection	Female thread G $\frac{3}{4}$	1		-$\frac{3}{4}$
	Female thread G1	1		-1
	Connecting plate G $\frac{1}{2}$			-AGD
	Connecting plate G $\frac{3}{4}$			-AGE
	Connecting plate G1			-AGF
	Connecting plate G1 $\frac{1}{4}$			-AGG
	Connecting plate G1 $\frac{1}{2}$			-AGH
	Female thread NPT $\frac{3}{4}$	1		-N$\frac{3}{4}$
	Female thread NPT1	1		-N1
	Connecting plate NPT $\frac{1}{2}$	1		-AQR
	Connecting plate NPT $\frac{3}{4}$	1		-AQS
	Connecting plate NPT1	1		-AQT
	Connecting plate NPT1 $\frac{1}{4}$	1		-AQU
	Connecting plate NPT1 $\frac{1}{2}$	1		-AQV
	Module without connecting thread, without connecting plate	1		-G
Grade of filtration	1 μ m			-B
	0.01 μ m			-A
Bowl	Metal bowl			-U
Condensate drain	Manual			-M
	Semi-automatic (P1 max. 12 bar)			-H
	Fully automatic (P1 max. 12 bar)			-V
	External, fully automatic, electric	110 V AC, terminal strip (P1 max. 16 bar)	1	-E2
		230 V AC, terminal strip (P1 max. 16 bar)	1	-E3
		24 V DC, terminal strip (P1 max. 16 bar)	1	-E4
O Flow rate	High flow rate			-HF
Filter contamination sensor	Differential pressure indicator, visual			-DA
Type of mounting	Mounting bracket standard design	2		-WP
	Mounting bracket for attaching the service units	1 2		-WPM
	Wall mounting bracket for large wall gap	2		-WPB
EU certification	II 2GD to EU Explosion Protection Directive (ATEX)			-EX4
UL certification	cULus, ordinary location for Canada and USA			-UL1
Flow direction	Flow direction from right to left			-Z

1 $\frac{3}{4}$, 1, N $\frac{3}{4}$, N1, AQR, AQS, AQT, AQU, AQV, G, E2, E3, E4, WPM

Not with EU certification EX4

2 WP, WPM, WPB Not with pneumatic connection G

M Mandatory data

O Options


Transfer order code

552940 MS 9 - LFM - - - U - - - - - - - - - -

Activated carbon filters MS9-LFX, MS series, NPT

Peripherals overview

FESTO



-  - Note

Other accessories:

- Module connector for combination with size MS6, MS9 or MS12

➔ Internet: rmv, armv

Mounting attachments and accessories						
		Individual device			Combination Module without connecting thread, without connecting plate G	➔ Page/ Internet
		With female thread 3/4/1/N3/4/N1	With connecting plate AG.../AQ... Without EU certification EX4	With EU certification EX4		
1	Connecting plate-SET MS9-AG...	-	■	■	■	ms9-ag
	Connecting plate-SET MS9-AQ...	-	■	-	■	ms9-aq
2	Module connector MS9-MV	-	-	-	■	ms9-mv
3	Mounting bracket MS9-WP	■	■	■	■	ms9-wp
4	Mounting bracket MS9-WPB	■	■	■	■	ms9-wp
5	Mounting bracket MS9-WPM	■	■	-	■	ms9-wp

Activated carbon filters MS9-LFX, MS series, NPT

FESTO

Type codes

		MS	9	-	LFX	-	N $\frac{3}{4}$	-	U
Series									
MS	Standard service unit								
Size									
9	Grid dimension 90 mm								
Service function									
LFX	Activated carbon filter								
Pneumatic connection									
N $\frac{3}{4}$	Thread NPT $\frac{3}{4}$								
N1	Thread NPT1								
G	Module without connecting thread, without connecting plate								
Bowl guard									
U	Integrated as metal bowl								


Further variants can be ordered using the modular system → 21

- Pneumatic connection
- Type of mounting
- EU certification
- UL certification
- Flow direction

Activated carbon filters MS9-LFX, MS series, NPT

FESTO

Technical data



-  Flow rate
max. 6,500 l/min
-  Temperature range
-10 ... +60 °C
-  Operating pressure
0 ... 20 bar



- Removal of liquid and gaseous oil particles from compressed air using activated carbon
- Eliminates odours and vapours
- Prefiltration with micro filter MS9-LFM-A, grade of filtration 0.01 µm, recommended
- Optional device variant EX4 for use in potentially explosive areas in zones 1, 2, 21 and 22
- New filter cartridges → 22

General technical data	
Size	MS9
Pneumatic connection 1, 2	
Female thread	G3/4, G1, NPT3/4 or NPT1
Connecting plate AG...	G1/2, G3/4, G1, G1 1/4 or G1 1/2
Connecting plate AQ...	NPT1/2, NPT3/4, NPT1, NPT1 1/4 or NPT1 1/2
Module without connecting thread/plate G	–
Constructional design	Activated carbon filter
Type of mounting	Via accessories
	In-line installation
Installation position	Vertical ±5°
Air purity class at the output ¹⁾	Compressed air in accordance with ISO 8573-1:2010 [1:4:1]
Bowl guard	Integrated as metal bowl
Residual oil content [mg/m³]	≤0.003

- 1) It is recommended to replace filter cartridges after 1,000 operating hours (applies to an ambient temperature of 21 °C). The service life of a filter cartridge is reduced at higher temperatures.
 -  Note: This product conforms to ISO 1179-1 and to ISO 228-1

Standard flow rate $q_n^{1)}$ [l/min]	
Max. standard flow rate for air purity class $q_{n \max}$	6,500

- 1) Measured at $p_1 = 6 \text{ bar}$

Operating and environmental conditions	
Operating pressure [bar]	0 ... 20
Operating medium	Compressed air in accordance with ISO 8573-1:2010 [1:4:2]
Ambient temperature [°C]	-10 ... +60
Temperature of medium [°C]	+5 ... +30
Storage temperature [°C]	-10 ... +60
Corrosion resistance class CRC ¹⁾	2
Certification (variant UL1)	cULus recognized (OL)

- 1) Corrosion resistance class CRC 2 to Festo standard FN 940070
 Moderate corrosion stress. Indoor applications in which condensation may occur. External visible parts with primarily decorative requirements for the surface and which are in direct contact with the ambient atmosphere typical for industrial applications.

Activated carbon filters MS9-LFX, MS series, NPT


FESTO

Technical data

ATEX	
EU certification	EX4
ATEX category gas	II 2G
Ex-ignition protection type gas	c T6 X
ATEX category dust	II 2D
EX-ignition protection type dust	c T60 °C X
ATEX ambient temperature	-10 °C ≤ Ta ≤ +60 °C
CE mark (see declaration of conformity)	To EU Explosion Protection Directive (ATEX)


Weights [g]	
Activated carbon filter	2,000

Materials	
Sectional view	




Activated carbon filter		
1	Housing	Die-cast aluminium
2	Bowl	Wrought aluminium alloy
	Inspection window	PA
3	Filter	Activated carbon
-	Cover	PA reinforced
-	Connecting plate, module connector, mounting bracket	Die-cast aluminium
-	Seals	NBR
Note on materials		Free of copper and PTFE

Standard flow rate qn as a function of the differential pressure p1-2	
Pneumatic connection G1/2/NPT1/2	Pneumatic connection G3/4/NPT3/4



- 2 bar
- - - 4 bar
- · · 6 bar
- · - 8 bar
- - - 10 bar
- - - 12 bar
- · - 14 bar




Activated carbon filters MS9-LFX, MS series, NPT

FESTO

Technical data


Standard flow rate q_n as a function of the differential pressure p_1-p_2

Pneumatic connection G1/NPT1



— 2 bar
 - - - 4 bar
 - · - 6 bar
 · · · 8 bar
 - - - - 10 bar
 - - - - 12 bar
 - · · · 14 bar


Pneumatic connection G1½/NPT1½



Dimensions – Basic version

Download CAD data → www.festo.com

Module without connecting thread, without connecting plate G



Type	B1	B2	B3	L1	L2	L3	L5	L6
MS9-LFX-G	90	45	109	380.5	62	120	50	34.5

Activated carbon filters MS9-LFX, MS series, NPT

FESTO


Technical data

Dimensions – Connecting thread/connecting plate

Download CAD data → www.festo.com

With female thread 3/4"/1/N3/4"/N1

With connecting plate AG.../AQ...



Type	B4	B5	B6	B7		B8	D1	L4	L7	≙
					EX4				EX4	
MS9-LFX-3/4	90	104	91.5	-	-	-	G3/4	66	-	-
MS9-LFX-1							G1			
MS9-LFX-AGD	-	-	-	112	122	132	G1/2	-	35	30
MS9-LFX-AGE						132	G3/4			36
MS9-LFX-AGF						142	G1			41
MS9-LFX-AGG						162	G1 1/4			50
MS9-LFX-AGH						176	G1 1/2			55
MS9-LFX-N3/4	90	104	91.5	-	-	-	NPT3/4-14	66	-	-
MS9-LFX-N1							NPT1-11 1/2			
MS9-LFX-AQR	-	-	-	112	122	132	NPT1/2-14	-	35	30
MS9-LFX-AQS						132	NPT3/4-14			36
MS9-LFX-AQT						142	NPT1-11 1/2			41
MS9-LFX-AQU						162	NPT1 1/4-11 1/2			50
MS9-LFX-AQV						176	NPT1 1/2-11 1/2			55

• Note: This product conforms to ISO 1179-1 and to ISO 228-1

Ordering data

Size	Connection	Part No.	Type
MS9	NPT3/4	552998	MS9-LFX-N3/4-U
	NPT1	553034	MS9-LFX-N1-U
	-	564038	MS9-LFX-G-U

Activated carbon filters MS9-LFX, MS series, NPT

FESTO

Ordering data – Modular products

Ordering table					
Grid dimension	[mm]	90	Condi- tions	Code	Enter code
M Module No.	552942				
Series	Standard service unit			MS	MS
Size	9			9	9
Function	Activated carbon filter			-LFX	-LFX
Pneumatic connection	Female thread G $\frac{3}{4}$		1	-$\frac{3}{4}$	
	Female thread G1		1	-1	
	Connecting plate G $\frac{1}{2}$			-AGD	
	Connecting plate G $\frac{3}{4}$			-AGE	
	Connecting plate G1			-AGF	
	Connecting plate G1 $\frac{1}{4}$			-AGG	
	Connecting plate G1 $\frac{1}{2}$			-AGH	
	Female thread NPT $\frac{3}{4}$		1	-N$\frac{3}{4}$	
	Female thread NPT1		1	-N1	
	Connecting plate NPT $\frac{1}{2}$		1	-AQR	
	Connecting plate NPT $\frac{3}{4}$		1	-AQS	
	Connecting plate NPT1		1	-AQT	
	Connecting plate NPT1 $\frac{1}{4}$		1	-AQU	
	Connecting plate NPT1 $\frac{1}{2}$		1	-AQV	
	Module without connecting thread, without connecting plate		1	-G	
Bowl	Metal bowl			-U	-U
O Type of mounting	Mounting bracket standard design		2	-WP	
	Mounting bracket for attaching the service units		1 2	-WPM	
	Wall mounting bracket for large wall gap		2	-WPB	
EU certification	II 2GD to EU Explosion Protection Directive (ATEX)			-EX4	
UL certification	cULus, ordinary location for Canada and USA			-UL1	
Flow direction	Flow direction from right to left			-Z	

1 $\frac{3}{4}$, 1, N $\frac{3}{4}$, N1, AQR, AQS, AQT, AQU, AQV, G, WPM

Not with EU certification EX4

2 WP, WPM, WPB

Not with pneumatic connection G

M Mandatory data

O Options

Transfer order code

552942 MS 9 - LFX - - U - - - -

Filters MS-LFM/LFX, MS series, NPT

Accessories

FESTO

Filter cartridges, MS9 series



Ordering data				
Size	Filter cartridge	Grade of filtration [μm]	Part No.	Type
MS9	Micro-filter cartridge	0.01	553036	MS9-LFM-A
	Fine-filter cartridge	1	553037	MS9-LFM-B
	Activated carbon filter cartridge	–	552946	MS9-LFX
High flow rate HF				
MS9	Micro-filter cartridge	0.01	552944	MS9-LFM-A-HF
	Fine-filter cartridge	1	552945	MS9-LFM-B-HF