

# Electrical connection technology, for fieldbus connection

Technical data – NECU

- Power supply socket for fieldbus connection
- 4 and 5-pin
- Can be assembled with any cable length
- With screw terminals
- Wire cross section of up to 2 mm<sup>2</sup>



General technical data			
Type		NECU-G78G4-C2	NECU-G78G5-C2
Operating voltage range	[V DC]	≤ 250	
	[V AC]	≤ 250	
Surge capacity	[kV]	2.5	
Permissible cable diameter	[mm]	5 ... 12	
Connection cross section	[mm <sup>2</sup> ]	0.25 ... 2	
Plug coding		ODVA AutoSIG	NFPA/T3.5.29 R1-2003
Based on standard		EN 61984	
Housing colour		Black	
Housing material		Polyamide	
Seal material		Nitrile rubber	
Contact material		Copper alloy, gold plated	
Union nut material		Brass, nickel-plated	
Note on materials		Free of copper and PTFE	
		RoHS-compliant	

Operating and environmental conditions		
Ambient temperature	[°C]	-40 ... +80
Corrosion resistance class CRC <sup>1)</sup>		1
Degree of contamination		3
CE mark (see declaration of conformity)		To EU Low Voltage Directive
Certification		CSA C/US (OL)

1) Corrosion resistance class 1 as per Festo standard 940 070  
 Components subject to low corrosion stress. Transport and storage protection. Parts that do not have primarily decorative surface requirements, e.g. in internal areas that are not visible or behind covers.

Ordering data						
	Electrical connection	Acceptable current load [A]	Protection class to EN 60529	Product weight [g]	Type	Part No.
	Straight plug socket, screw terminal, 7/8" round plug connector, 4-pin, suitable for self-assembly	10	IP65/67/68	49	NECU-G78G4-C2	543 108
	Straight plug socket, screw terminal, 7/8" round plug connector, 5-pin, suitable for self-assembly	8	IP65/67/68	51	NECU-G78G5-C2	543 107

# Electrical connection technology, for fieldbus connection


FESTO

Technical data – NECU

## Dimensions

Download CAD data → [www.festo.com](http://www.festo.com)

NECU-G78G4-C2, NECU-G78G5-C2



X Cable diameter 5 ... 12 mm