

Plastic tubing, standard O.D.



★	Festo Core Range Solves the majority of your automation tasks	With the Festo Core Range, we have selected the most important products and functions from our broad product catalogue, and added the quickest delivery. The Core Range offers you the best value for your automation tasks.
Worldwide:	Quickest delivery – wherever, whenever	
Simply good:	Expected high Festo quality	
Fast:	Easy and fast to select	



Key features

Application



The requirements for pressure, temperature, flexibility and environmental influences differ from one industry sector to the next. Users frequently underestimate the risks: around 90% of all cases of damage can be traced back to

the wrong choice of tubing or tubing materials. This can not only result in energy losses, but also machine down-times.

It is therefore really important to find a reliable and cost-effective product that

prevents tubing damage during operation.

Overview of tubing/fitting combinations

Applications	Tubing	Fitting	Description
Standard	PEN	QS	Suitable for a wide range of tasks and attractively priced. Flexible with highly resistant materials, easy to install with optimised bending radii. High level of abrasion resistance in dynamic applications.
	PUN	QS	Maximum flexibility in standard applications thanks to an extremely wide range of options for combining the different types.
	PAN	QS	Meets all requirements, even for standard applications with increased pressure and temperature ranges.
High pressures	PAN-MF	NPQM	Meets DIN standard 73378: ideal for use in mobile pneumatics. Suitable for increased temperature ranges combined with high pressure ranges.
	PAN-R	NPQH	Powerful in pressure ranges up to 20 bar, for example in applications with the pressure booster DPA.
Resistant to chemicals and hydrolysis, food-safe	PLN	NPQP	Resistant to cleaning agents, FDA-compliant and economical. Can be used instead of the combination with stainless steel fittings.
	PUN-H	NPKA	Hydrolysis-resistant and suitable for water applications. Combination suitable for use in clean rooms, FDA-compliant and corrosion resistant as made from 100% polymer. Very easy to install with the "one click principle".
	PFAN/PTFEN	NPQH	For high temperatures up to 150°C. Food-safe, FDA-compliant and resistant to cleaning agents.
	PFAN/PTFEN	NPCK	Easy to clean with the union nut's edge-free design. Maximum corrosion resistance (CRC 4) and FDA-compliant. Suitable for a wide range of media.
	PFAN/PTFEN	CRQS	Maximum corrosion resistance (CRC 4) and to aggressive acids and alkalis.
Resistant to chemicals and hydrolysis	PFAN/PTFEN	NPQR	Optimised design, fewer edges where dirt can collect – all at an attractive price. For high temperatures up to 150°C. Pressure range up to 16 bar. Highest level of corrosion resistance (CRC 4).
Antistatic	PUN-CM	NPQM	Antistatic tubing plus solid metal fitting: maximum protection for electrical and electronic components.
Flame-retardant	PUN-VO	NPQM	Very safe in areas where there is a risk of fire with its flame-retardant properties. The tubing has been tested to DIN 5510-2.
Resistant to welding spatter	PUN-VO-C	NPQH	Ideal for applications involving welding spatter. Reliable with tubing wall thickness of 2 mm for all diameters.
	PAN-VO	QS-VO	Safe even in the close vicinity of welding spatter with the double-walled tubing with special fitting.

Note

Ambient conditions and the medium to be transported can have a considerable effect on the service life of plastic tubing. Based on experience, Festo recommends the following time specifications for using plastic tubing in general and safety-related applications:

- For general applications, a minimum service life of 10 years can be expected.
- For safety-related applications, we recommend regular inspection at least every 12 months.
- For applications that have an effect on the material, inspections must be carried out at suitable intervals. We recommend that the interval between inspections should be no more than 6 months, at most half of the period in which failures can occur.

Technical data

Note

Tubing diameters that are too big or too small as well as bending radii that are too small result in flow rate losses. One of the most important rules when selecting tubing is therefore that it should be as long as necessary and as short as possible.

Make sure therefore that in practice tubing is laid loosely and is not stretched.

Tools for bundling tubing or for avoiding bending/pinching the tubing are available as accessories:


- Tubing strap PB
- Spiral tubing binder PKB
- Tubing support NPAW
- Tubing support PKS
- Multi-tube holder KK

Other accessories include connecting tools for tubing:


- Pipe and tubing cutter ZRS
- Tubing cutter PAN-VOS for flame-retardant plastic tubing PAN-VO
- Connecting pliers ZMS/disconnecting pliers ZDS for connecting/disconnecting the plastic tubing and barbed connector fitting

Measurement method

Flow-relevant bending radius R_d



The tube is bent in the direction of its own curve until the tubing outside diameter is flattened by 5%. R_d is then calculated mathematically. The flow rate is not reduced until R_d is reached.




Cross section flattened by bending the tube.

d = non-deformed tubing O.D.

d_1 = deformed tubing O.D.

Minimum bending radius R_{min}



The tube fixed to the base plate is bent until the deformation results in a kink. The measured value is the minimum bending radius R_{min} . This R_{min} results in significant reductions in flow rate.

Product range overview

Type	Material	O.D. [mm]	Colour														
			silver	blue	translucent blue	black	translucent black	yellow	translucent yellow	green	translucent green	red	translucent red	brown	white	natural	blue/black
PAN	Polyamide	4, 6, 8, 10, 12, 14, 16	■	■	–	■	–	■	–	■	–	■	–	(■) ¹	(■) ¹	■	–
PAN-R	Polyamide	4, 6, 8, 10, 12, (14) ¹ , 16	■	(■) ¹	–	(■) ¹	–	(■) ¹	–	(■) ¹	–	(■) ¹	–	(■) ¹	(■) ¹	(■) ¹	–
		22, 28	–	–	–	■	–	–	–	–	–	–	–	–	–	–	–
PAN-MF	Polyamide	4, 6, 8, 10, 12, 14, 16	(■) ¹	(■) ¹	–	■	–	(■) ¹	–	(■) ¹	–	(■) ¹	–	(■) ¹	(■) ¹	(■) ¹	–
PAN-VO	Polyamide	4, 6, 8, 10, 12	–	■	–	■	–	■	–	■	–	■	–	–	■	–	–
PFAN	Perfluoroalkoxyalkane	3, 4, 6, 8, 10, 12	–	–	–	–	–	–	–	–	–	–	–	–	–	■	–
PTFEN	Polytetrafluoroethylene	4, 6, 8, 10, 12, 14, 16	–	–	–	–	–	–	–	–	–	–	–	–	–	■	–
PTFEN, NPT	Polytetrafluoroethylene	5/32, 1/4, 5/16, 3/8, 1/2	–	–	–	–	–	–	–	–	–	–	–	–	–	■	–
PEN	Polyethylene	4, 6, 8, 10, 12, 14, 16	■	■	–	■	–	■	–	■	–	■	–	(■) ¹	(■) ¹	■	–
PLN	Polyethylene	4, 6, 8, 10, 12, 14, 16	■	■	–	■	–	(■) ¹	–	(■) ¹	–	■	–	(■) ¹	(■) ¹	■	–
PUN	Polyethylene	3, 4, 6, 8, 10, 12, 14, 16	■	■	–	■	–	■	–	■	–	■	–	(■) ¹	(■) ¹	–	–
PUN-DUO	Polyethylene	4, 6, 8, 10	■	–	–	–	–	–	–	–	–	–	–	–	–	–	■
PUN-CM	Polyethylene	4, 6, 8, 10, 12, (14) ¹	–	–	–	■	–	–	–	–	–	–	–	–	–	–	–
PUN-H	Polyethylene	2	–	–	–	■	–	–	–	–	–	■	–	–	–	■	–
		3, 4, 6, 8, 10, 12, 14, 16	■	■	■	■	■	■	■	■	■	■	■	(■) ¹	(■) ¹	■	–
PUN-H-DUO	Polyethylene	4, 6, 8, 10	–	–	–	–	–	–	–	–	–	–	–	–	–	–	■
PUN-VO	Polyethylene	6, 8, 10, 16	–	■	–	■	–	■	–	■	–	■	–	■	■	–	–
PUN-VO-C	Polyethylene	4, 6, 8, 10, 12, 14, 16	–	■	–	■	–	■	–	■	–	■	–	■	■	–	–

 Note

Product options in brackets can only be ordered using the modular product system.
Please note the minimum ordering quantity of 3000 m for tubing with O.D. < 8 mm and 1500 m with O.D. > 8 mm.

There is a modular product system for plastic tubing:

- PAN → 19
- PEN → 33
- PLN → 37
- PUN → 61

Product range overview

Type	Operating medium			Suitability for use in the food industry	Material fire test	Antistatic	Halogen-free	Contact with electric cables	Suitable for energy chains	Approved by TÜV	Maritime classification	Resistance				Flexibility	Shore hardness ⁸⁾	Tolerance on the package length	→ Page/ Internet
	Compressed air, vacuum	Water	Mineral oil									Chemicals	Microbes	UV radiation	Hydrolysis				
PAN	■	-	-	-	-	-	■	■	++	■	■ ³⁾	+	++	+	++	++	D 55 ±3	±1%	7
PAN-R	■	-	-	-	-	-	■	■	++	■	-	+	++	+	++	+	D 62 ±3		11
	■	-	-	-	-	-	■	■	++	-	-	+	++	+	++	+	D 62 ±3		12
PAN-MF	■	-	■ ²⁾	-	-	-	■	■	+++	-	-	+	++	+	++	+	D 65 ±3		14
PAN-V0	■	■	■	-	UL94 V0	-	-	■	++	-	-	+	++	++	++	++	A 72 ±4 ⁵⁾ D 57 ±3 ⁶⁾		17
PFAN	■	■	-	■	UL94 V0	-	-	■	-	■	-	+++	++	++	+++	+	D 60 +5		21
PTFEN	■	-	-	■	UL94 V0	-	-	■	-	-	-	+++	++	++	+++	+	D 55 ±5		24
PTFEN, NPT	■	-	-	■	UL94 V0	-	-	■	-	-	-	+++	++	++	+++	+	D 55 ±5		27
PEN	■	■	-	-	-	-	■	■	+++	■	-	++	++	+++ ⁴⁾	+++	++	D 52 ±3		30
PLN	■	■	-	■	-	-	■	■	-	■	-	++	++	+++ ⁴⁾	+++	+	D 59 ±3		35
PUN	■	-	-	-	UL94 HB	-	■	■ ⁷⁾	++	■	-	-	-	+++ ⁴⁾	+	+++	D 52 ±3		39
PUN-DUO	■	-	-	-	UL94 HB	-	■	■ ⁷⁾	++	■	-	-	-	+	+	++	D 52 ±3		42
PUN-CM	■	-	-	-	-	■	■	■	+++	-	-	+	++	++	++	++	D 52 ±3		45
PUN-H	■	-	-	-	-	-	■	■	++	-	-	+	++	+++ ⁴⁾	++	+++	D 52 ±3		48
	■	■	-	■	UL94 HB	-	■	■	++	■	-	+	++	+++ ⁴⁾	++	+++	D 52 ±3		49
PUN-H-DUO	■	■	-	■	UL94 HB	-	■	■	++	■	-	+	++	+	++	++	D 52 ±3		54
PUN-V0	■	■	-	-	UL94 V0...V2	-	■	■	++	■	-	+	++	+++ ⁴⁾	++	++	D 54 ±3		57
PUN-V0-C	■	■	-	-	UL94 V0...V2	-	■	■	++	■	-	+	++	+++ ⁴⁾	++	++	D 54 ±3		59

2) As a precaution, please consult Festo with reference to the operating medium.

3) Applies to the colour: silver and natural

4) Applies to the colour: black

5) Outside tubing

6) Inside tubing

7) Cables containing organophosphates may damage PUN tubing under unfavourable conditions.

8) Values are determined using test boards. Derived values using tubing may vary.

■ Criterion met

- Not suitable

+++ Highly suitable

++ Suitable

+ Limited suitability (on request)

Type codes

001	Function
PAN	Polyamide tubing, standard O.D.

002	Pipe/tubing O.D. x wall thickness
4x0,75	4x0.75 mm
6x1	6x1 mm
8x1,25	8x1.25 mm
10x1,5	10x1.5 mm
12x1,75	12x1.75 mm
14x2	14x2 mm
16x2	16x2 mm

003	Colour
NT	Natural
SW	Black
BL	Blue
SI	Silver
RT	Red
GN	Green
GE	Yellow

004	Packaging unit [m]
	Standard
100	100 m
200	200 m
300	300 m
400	400 m
500	500 m

Datasheet

Plastic tubing PAN


High thermal and mechanical load capacities.



Operating and environmental conditions					
Type	PAN-4/8	PAN-6	PAN-10/12	PAN-14	PAN-16
Temperature-dependent operating pressure [bar]	-0.95 ... +15 → graph	-0.95 ... +19 → graph	-0.95 ... +17 → graph		-0.95 ... +14 → graph
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-]				
PWIS conformity	VDMA24364-B2-L				
Ambient temperature [°C]	-30 ... +80				
Certification	German Technical Control Board (TÜV)				
Maritime classification	See certificate (colours: silver and natural) ¹⁾			-	See certificate (colours: silver and natural) ¹⁾
Tubing characteristics	Suitability for energy chains in applications with high cycle rates				
Tubing test conditions	Suitability for energy chains: > 5 million cycles to Festo standard 942021				

1) Additional information www.festo.com/catalogue/... → Support/Downloads.

Operating pressure p as a function of temperature t



Accessories

Type	→ Internet
	Recommended fitting
	• Push-in fitting QS ¹⁾ qs
	Well suited
	• Push-in fitting CRQS ¹⁾ crqs
	• Push-in fitting NPQH ²⁾ npqh
	• Push-in fitting NPQP ³⁾ npqp
	• Push-in fitting NPQM ²⁾ npqm
	• Push-in fitting NPQR ³⁾ npqr
	• Click fitting NPKA ⁴⁾ npka
	• Fitting NPCK ⁵⁾ npck
	• Quick connector CK ⁶⁾ ck
	• Barbed fitting CN ⁶⁾ cn
	Limited suitability
	• Push-in fitting QS-V0 ³⁾ qs-v0


- 1) Not for O.D. 14 mm
2) Not for O.D. 16 mm
3) Not for O.D. 14/16 mm

- 4) For O.D. 6 mm only
5) For O.D. 4/6/8/10 mm only
6) For O.D. 4/6/8 mm only

Materials	
Shore hardness	D 55 ±3
Tubing	TPE-A
Note on materials	RoHS-compliant
	Free of copper and PTFE

Datasheet

Dimensions – Reel



Type	D1 Ø	D2 Ø	D3 Ø	D4 Ø	D5 Ø	D6 Ø	D7 Ø	D8 Ø	H1	H2	L1	L2	W1
For PAN-4x0.75-...-500	545	246	21	20	216	75	20	20	152.5	80.5	128	8	45°
For PAN-6x1-...-500	545	246	21	20	216	75	20	20	152.5	80.5	128	8	45°
For PAN-8x1.25-...-400	545	310	21	20	280	75	20	20	152.5	80.5	254	8	45°
For PAN-10x1.5-...-300	600	310	21	20	280	75	20	20	152.5	80.5	254	8	45°
For PAN-12x1.75-...-200	600	310	21	20	280	75	20	20	152.5	80.5	254	8	45°
For PAN-16x2-...-100	545	310	21	20	280	75	20	20	152.5	80.5	254	8	45°

Dimensions and ordering data

O.D. [mm]	I.D. [mm]	Min. bending radius [mm]	Flow-relevant bending radius [mm]	Weight [kg/m]	Colour	Part no.	Type	PJ ¹⁾ [m]
4	2.9	12	18	0.006	silver	152697	PAN-4x0.75-SI	50
					silver	553888	PAN-4x0.75-SI-500	500
					blue	553906	PAN-4x0.75-BL	50
					blue	553894	PAN-4x0.75-BL-500	500
					black	553912	PAN-4x0.75-SW	50
					black	553900	PAN-4x0.75-SW-500	500
					natural	546284	PAN-4x0.75-NT	50
					green	553918	PAN-4x0.75-GN	50
					red	553924	PAN-4x0.75-RT	50
					yellow	553930	PAN-4x0.75-GE	50
6	4	14	32	0.016	silver	152699	PAN-6x1-SI	50
					silver	553889	PAN-6x1-SI-500	500
					blue	553907	PAN-6x1-BL	50
					blue	553895	PAN-6x1-BL-500	500
					black	553913	PAN-6x1-SW	50
					black	553901	PAN-6x1-SW-500	500
					natural	546285	PAN-6x1-NT	50
					green	553919	PAN-6x1-GN	50
					red	553925	PAN-6x1-RT	50
					yellow	553931	PAN-6x1-GE	50

1) Packaging unit

Datasheet

Dimensions and ordering data								
O.D.	I.D.	Min. bending radius	Flow-relevant bending radius	Weight	Colour	Part no.	Type	pU ¹⁾
[mm]	[mm]	[mm]	[mm]	[kg/m]				[m]
8	5.9	22	43	0.024	silver	152700	PAN-8x1.25-SI	1 ... 50
					silver	553890	PAN-8x1.25-SI-400	400
					blue	553908	PAN-8x1.25-BL	1 ... 50
					blue	553896	PAN-8x1.25-BL-400	400
					black	553914	PAN-8x1.25-SW	1 ... 50
					black	553902	PAN-8x1.25-SW-400	400
					natural	546286	PAN-8x1.25-NT	1 ... 50
					green	553920	PAN-8x1.25-GN	1 ... 50
					red	553926	PAN-8x1.25-RT	1 ... 50
					yellow	553932	PAN-8x1.25-GE	1 ... 50
10	7	27	58	0.042	silver	152701	PAN-10x1.5-SI	1 ... 50
					silver	553891	PAN-10x1.5-SI-300	300
					blue	553909	PAN-10x1.5-BL	1 ... 50
					blue	553897	PAN-10x1.5-BL-300	300
					black	553915	PAN-10x1.5-SW	1 ... 50
					black	553903	PAN-10x1.5-SW-300	300
					natural	546287	PAN-10x1.5-NT	1 ... 50
					green	553921	PAN-10x1.5-GN	1 ... 50
					red	553927	PAN-10x1.5-RT	1 ... 50
					yellow	553933	PAN-10x1.5-GE	1 ... 50
12	8.4	29	64	0.060	silver	152702	PAN-12x1.75-SI	1 ... 50
					silver	553892	PAN-12x1.75-SI-200	200
					blue	553910	PAN-12x1.75-BL	1 ... 50
					blue	553898	PAN-12x1.75-BL-200	200
					black	553916	PAN-12x1.75-SW	1 ... 50
					black	553904	PAN-12x1.75-SW-200	200
					natural	546288	PAN-12x1.75-NT	1 ... 50
					green	553922	PAN-12x1.75-GN	1 ... 50
					red	553928	PAN-12x1.75-RT	1 ... 50
					yellow	553934	PAN-12x1.75-GE	1 ... 50
14	10	50	80	0.077	silver	570392	PAN-14x2-SI	1 ... 50
16	12	67	94	0.092	silver	152703	PAN-16x2-SI	1 ... 50
					silver	553893	PAN-16x2-SI-100	100
					blue	553911	PAN-16x2-BL	1 ... 50
					blue	553899	PAN-16x2-BL-100	100
					black	553917	PAN-16x2-SW	1 ... 50
					black	553905	PAN-16x2-SW-100	100
					natural	546289	PAN-16x2-NT	1 ... 50
					green	553923	PAN-16x2-GN	1 ... 50
					red	553929	PAN-16x2-RT	1 ... 50
					yellow	553935	PAN-16x2-GE	1 ... 50

1) Packaging unit
Can only be ordered by the metre.

Type codes

001	Series
PAN	Standard O.D. tubing
002	Alternative material characteristic
R	Sturdy

003	Pipe/tubing O.D. x wall thickness
4x0,75	4x0.75 mm
6x1,1	6x1.1 mm
8x1,5	8x1.5 mm
10x1,9	10x1.9 mm
12x2,2	12x2.2 mm
16x3	16x3 mm
22x2	22x2 mm
28x2,5	28x2.5 mm

004	Colour
SW	Black
SI	Silver

Datasheet

Plastic tubing PAN-R


With O.D. 4 ... 16 mm

For applications with a high pressure range.



Operating and environmental conditions		
Temperature-dependent operating pressure	[bar]	-0.95 ... +35 → graph
Operating medium		Compressed air to ISO 8573-1:2010 [7:-:-]
Ambient temperature	[°C]	-30 ... +80
Certification		German Technical Control Board (TÜV)
Tubing characteristics		Suitability for energy chains in applications with high cycle rates
Tubing test conditions		Suitability for energy chains: > 5 million cycles to Festo standard 942021

Operating pressure p as a function of temperature t



Accessories

Type	→ Internet
	Recommended fitting
	• Push-in fitting NPQH ¹⁾ npqh
	Well suited
	• Push-in fitting QS qs
	• Push-in fitting CRQS crqs
	• Push-in fitting NPQP ¹⁾ npqp
	• Push-in fitting NPQM ¹⁾ npqm
	• Push-in fitting NPQR ¹⁾ npqr
	• Click fitting NPKA ²⁾ npka
	Limited suitability
	• Push-in fitting QS-V0 ¹⁾ qs-v0

1) Not for O.D. 16 mm

2) For O.D. 6 mm only

Materials	
Shore hardness	D 62 ±3
Tubing	TPE-A
Note on materials	RoHS-compliant
	Free of copper and PTFE

Dimensions and ordering data								
O.D.	I.D.	Min. bending radius	Flow-relevant bending radius	Weight	Colour	Part no.	Type	PU ¹⁾
[mm]	[mm]	[mm]	[mm]	[kg/m]				[m]
4	2.5	10	16	0.0079	silver	541674	PAN-R-4x0.75-SI	50
6	3.8	16	21	0.0174		541675	PAN-R-6x1.1-SI	50
8	5	20	29	0.0316		541676	PAN-R-8x1.5-SI	1 ... 50
10	6.2	25	44	0.0498		541677	PAN-R-10x1.9-SI	1 ... 50
12	7.6	30	46	0.0698		541678	PAN-R-12x2.2-SI	1 ... 50
16	10	42	73	0.1262		541679	PAN-R-16x3-SI	1 ... 50

1) Packaging unit
Can only be ordered by the metre.

Datasheet

Plastic tubing PAN-R

With O.D. 22 and 28 mm


High thermal and mechanical load capacities.



Operating and environmental conditions

Temperature-dependent operating pressure	[bar]	-0.95 ... +14 → graph
Operating medium		Compressed air to ISO 8573-1:2010 [7:-:-]
Ambient temperature	[°C]	-30 ... +80

Operating pressure p as a function of temperature t



Accessories

Type	→ Internet	
	Recommended fitting	
	• Push-in fitting QS G3/4-22	qs
	• Push-in fitting CQ-...-22/28	cq
	Pipe cutter ZR	tools

Note

When using the pipe cutter ZR to cut to length, we recommend rotating the tube through approx. 90° at the start of the cutting process.

Rotating the tube gives a drawing cut so that the tube can be cut with a significantly lower force. This also minimises deformation of the tube.

Materials

Shore hardness	D 62 ±3
Tubing	TPE-A
Note on materials	RoHS-compliant
	Free of copper and PTFE

Dimensions and ordering data

O.D.	I.D.	Flow-relevant bending radius	Weight	Colour	Part no.	Type	PU ¹⁾
[mm]	[mm]	[mm]	[kg/m]				[m]
22	18	350	1.31	black	8036207	PAN-R-22x2-SW	50
28	23	350	2.07		8036208	PAN-R-28x2.5-SW	50

1) Packaging unit

Type codes

001	Series
PAN	Standard O.D. tubing

002	Alternative material characteristic
MF	Automotive approval certificate (DIN 73378)

003	Pipe/tubing O.D. x wall thickness
4x0,75	4x0.75 mm
6x1	6x1 mm
8x1	8x1 mm
10x1,25	10x1.25 mm
12x1,5	12x1.5 mm
14x2	14x2 mm
16x2	16x2 mm

004	Colour
SW	Black

005	Packaging unit [m]
	Standard
500	500 m

Datasheet


Plastic tubing PAN-MF

High thermal and mechanical load capacities.
 Meets the requirements according to DIN 73378 "Polyamide tubing for use in motor vehicles".



Operating and environmental conditions						
Type		PAN-MF-4	PAN-MF-6	PAN-MF-8/1 0/12	PAN-MF-14	PAN-MF-16
Temperature-dependent operating pressure [bar]		−0.95 ... +31 → graph	−0.95 ... +27 → graph	−0.95 ... +19 → graph	−0.95 ... +22 → graph	−0.95 ... +19 → graph
Conforms to standard		DIN 73378-PA12-PHL				
Operating medium		Compressed air to ISO 8573-1:2010 [7:--:-]				
		Mineral oil				
Ambient temperature	[°C]	−60 ... +100				
Tubing characteristics		Suitability for energy chains in applications with high cycle rates				
Tubing test conditions		Suitability for energy chains: > 5 million cycles to Festo standard 942021				

Operating pressure p as a function of temperature t



Accessories


Type	→ Internet
	Well suited
	• Push-in fitting QS ¹⁾ qs
	• Push-in fitting CRQS ¹⁾ crqs
	• Push-in fitting NPQH ²⁾ npqh
	• Push-in fitting NPQP ³⁾ npqp
	• Push-in fitting NPQM ²⁾ npqm
	• Push-in fitting NPQR ³⁾ npqr
	Limited suitability
	• Push-in fitting QS-V0 ³⁾ qs-v0

1) Not for O.D. 14 mm
 2) Not for O.D. 16 mm
 3) Not for O.D. 14/16 mm

Materials	
Shore hardness	D 65 ±3
Tubing	PA12-P
Note on materials	RoHS-compliant
	Free of copper and PTFE

Datasheet

Dimensions – Reel



Type	D1 ø	D2 ø	D3 ø	D4 ø	D5 ø	D6 ø	D7 ø	D8 ø	H1	H2	L1	L2	W1
For PAN-MF-4x0.75-...-500	545	246	21	20	216	75	20	20	152.5	80.5	128	8	45°
For PAN-MF-6x1-...-500	600	310	21	20	280	75	20	20	152.5	80.5	114	8	45°

Dimensions and ordering data								
O.D. [mm]	I.D. [mm]	Min. bending radius [mm]	Flow-relevant bending radius [mm]	Weight [kg/m]	Colour	Part no.	Type	PU ¹⁾ [m]
4	2.5	10	15	0.008	black	570357	PAN-MF-4x0.75-SW	50
						572091	PAN-MF-4x0.75-SW-500	500
6	4	15	35	0.016		570358	PAN-MF-6x1-SW	50
						572093	PAN-MF-6x1-SW-500	500
8	6	35	50	0.022		570359	PAN-MF-8x1-SW	50
10	7.5	45	65	0.035		570360	PAN-MF-10x1.25-SW	50
12	9	50	70	0.051		570361	PAN-MF-12x1.5-SW	50
14	10	50	75	0.077		570362	PAN-MF-14x2-SW	50
16	12	75	130	0.09		570363	PAN-MF-16x2-SW	50

1) Packaging unit

Type codes

001	Series	
PAN	Standard O.D. tubing	
002	Alternative material characteristic	
V0	Flame-retardant	

003	Colour	
SW	Black	
BL	Blue	
RT	Red	
GN	Green	
GE	Yellow	
WS	White	

Datasheet

Plastic tubing PAN-V0

PVC casing, flame-retardant. The tubing casing must be cut to length X (table → 15) before being inserted in the push-in fitting QS-V0.

The tubing cutter PAN-V0S is the perfect tool for this task. The tubing cutter PAN-V0S will always cut the casing to the right length.




Operating and environmental conditions

Temperature-dependent operating pressure	[bar]	-0.95 ... +12 → graph
Operating medium		Compressed air to ISO 8573-1:2010 [7:-:-]
		Mineral oil
		Water as per manufacturer's declaration ¹⁾
Ambient temperature	[°C]	-30 ... +90
Material fire test		UL94 V-0 (casing)

1) Additional information www.festo.com/catalogue/... → Support/Downloads.

Operating pressure p as a function of temperature t



Accessories

Type	→ Internet	
	Recommended fitting	
	• Push-in fitting QS-V0	qs-v0
	Limited suitability	
	• Push-in fitting QS	qs
	• Push-in fitting CRQS	crqs
	• Push-in fitting NPQP	npqp
	• Push-in fitting NPQR	npqr
	Tubing cutter PAN-V0S	tools

Materials

Shore hardness	Outside tubing	A 72 ±4
	Inside tubing	D 57 ±3
Tubing	Outside tubing	PVC-P
	Inside tubing	PA12-P
Note on materials		RoHS-compliant

Datasheet

Pneumatic connection	
O.D. [mm]	Pneumatic connection
6	For push-in connector O.D. 4 mm
8	For push-in connector O.D. 6 mm
10	For push-in connector O.D. 8 mm
12	For push-in connector O.D. 10 mm
14	For push-in connector O.D. 12 mm

Dimensions and ordering data									
O.D. [mm]	I.D. [mm]	Min. bending radius [mm]	Flow-relevant bending radius [mm]	Max. cut length X [mm]	Weight [kg/m]	Colour	Part no.	Type	PU ¹⁾ [m]
6	2.5	10	20	15	0.0335	blue	132899	PAN-V0-4x0.75-BL	1 ... 50
8	4	13	30	17	0.049	black	160550	PAN-V0-6x1-SW	1 ... 50
						blue	132905	PAN-V0-6x1-BL	1 ... 50
						green	525470	PAN-V0-6x1-GN	1 ... 50
						red	525474	PAN-V0-6x1-RT	1 ... 50
						white	525478	PAN-V0-6x1-WS	1 ... 50
						yellow	525482	PAN-V0-6x1-GE	1 ... 50
10	6	24	45	18	0.065	black	160551	PAN-V0-8x1-SW	1 ... 50
						blue	132906	PAN-V0-8x1-BL	1 ... 50
						green	525471	PAN-V0-8x1-GN	1 ... 50
						red	525475	PAN-V0-8x1-RT	1 ... 50
						white	525479	PAN-V0-8x1-WS	1 ... 50
						yellow	525483	PAN-V0-8x1-GE	1 ... 50
12	7.5	34	56	20	0.088	black	160552	PAN-V0-10x1.25-SW	1 ... 50
						blue	132907	PAN-V0-10x1.25-BL	1 ... 50
						green	525472	PAN-V0-10x1.25-GN	1 ... 50
						red	525476	PAN-V0-10x1.25-RT	1 ... 50
						white	525480	PAN-V0-10x1.25-WS	1 ... 50
						yellow	525484	PAN-V0-10x1.25-GE	1 ... 50
14	9	43	65	23	0.133	black	160553	PAN-V0-12x1.5-SW	1 ... 50
						blue	525469	PAN-V0-12x1.5-BL	1 ... 50
						green	525473	PAN-V0-12x1.5-GN	1 ... 50
						red	525477	PAN-V0-12x1.5-RT	1 ... 50
						white	525481	PAN-V0-12x1.5-WS	1 ... 50
						yellow	525485	PAN-V0-12x1.5-GE	1 ... 50

1) Packaging unit
Can only be ordered by the metre.

Ordering data – Modular product system

Ordering table (minimum order quantity 3000 m, rounded value 25 m)												
Size	4	6	8	10	14	12	14	16	Conditions	Code	Enter code	
Module no.	553610											
Function	Polyamide tubing, standard O.D.									PAN	PAN	
Alternative material characteristic	Standard											
	Automotive certification (DIN 73378)									-MF		
	Sturdy									-R		
Tubing O.D. [mm]	4	–	–	–	–	–	–	–		-4		
	–	6	–	–	–	–	–	–		-6		
	–	–	8	–	–	–	–	–		-8		
	–	–	–	10	–	–	–	–		-10		
	–	–	–	–	12	–	–	–		-12		
	–	–	–	–	–	14	–	–		-14		
	–	–	–	–	–	–	16	–		-16		
Colour	silver									-SI		
	blue									-BL		
	black									-SW		
	yellow									-GE		
	green									-GN		
	red									-RT		
	brown									-BR		
	white									-WS		
	natural									-NT		
Labelling text (on request)	Standard											
	Customer-specific tubing inscription								[1]	-TXT		
Packaging unit [m]	25									-25		
	50									-50		
	100									-100		
	200						–	–		-200		
	300					–	–	–		-300		
	400			–	–	–	–	–		-400		
	500		–	–	–	–	–	–		-500		
Packaging	Cardboard box								[2] [4]	-CB		
	PE bag								[2] [5]	-BA		
	Reel								[3]	-HA		

[1] **TXT** Only on request[2] **CB, BA** Only with packaging unit 25, 50[3] **HA** Only with packaging unit 25, 50[4] **CB** Not with alternative material characteristic MF[5] **BA** Only with alternative material characteristic MF

Plastic tubing, standard O.D.

Type codes

001	Series	
PFAN	Plastic tubing	

002	Pipe/tubing O.D. x wall thickness	
3x0,5	3x0.5 mm	
4x0,75	4x0.75 mm	
6x1	6x1 mm	
8x1,25	8x1.25 mm	
10x1,5	10x1.5 mm	
12x1,75	12x1.75 mm	

003	Colour	
NT	Natural	

Datasheet

Plastic tubing PFAN

Pneumatic tubing with resistance to high temperatures and chemicals.




Operating and environmental conditions

Type	PFAN-3/4/8	PFAN-6/10/12
Temperature-dependent operating pressure [bar]	-0.95 ... +15 → graph	-0.95 ... +16 → graph
Note on operating pressure	Water: 0 - 0.6 MPa,... Steam: 0 - 0.15 MPa,...	
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-] Water (liquid, ice-free) ¹⁾ Steam ¹⁾	
Note on temperature of medium	Water: 0 - 85°C Steam: max. 120°C	
Ambient temperature [°C]	-20 ... +150	
Suitability for use in the food industry	See supplementary material information ¹⁾ See declaration of conformity ¹⁾	
Material fire test	UL94 V-0	
Certification	German Technical Control Board (TÜV)	

1) Additional information www.festo.com/catalogue/... → Support/Downloads.

Operating pressure p as a function of temperature t



1) PFAN-6/10/12

2) PFAN-4/8

Accessories

Type	→ Internet	
	Recommended fitting	
	• Push-in fitting CRQS ¹⁾	crqs
	• Push-in fitting NPQH ¹⁾	npqh
	• Push-in fitting NPQP ¹⁾	npqp
	• Push-in fitting NPQR ¹⁾	npqr
	• Fitting NPCK ²⁾	npck
	Well suited	
	• Push-in fitting QS	qs
	• Push-in fitting NPQM ¹⁾	npqm
	• Click fitting NPKA ³⁾	npka
	• Quick connector CK ⁴⁾	ck
	• Barbed fitting CN ⁵⁾	cn
	Limited suitability	
	• Push-in fitting QS-V0 ¹⁾	qs-v0

1) Not for O.D. 3 mm

2) For O.D. 4/6/8/10 mm only

3) For O.D. 6 mm only

4) For O.D. 4/6/8 mm only

5) For O.D. 3/4/6/8 mm only



Note

Greater force is required when assembling the fittings CK/CN.

Expanding the tube ends using a tapered mandrel makes pushing them on easier.

Materials

Shore hardness	D 60 +5
Tubing	PFA
Note on materials	RoHS-compliant

Datasheet

Dimensions and ordering data								
O.D.	I.D.	Min. bending radius	Flow-relevant bending radius	Weight	Colour	Part no.	Type	pU ¹⁾
[mm]	[mm]	[mm]	[mm]	[kg/m]				[m]
3	2.3	10	30	0.0075	natural	8061167	PFAN-3x0.5-NT	1 ... 50
4	2.9	11	37	0.012		197061	PFAN-4x0.75-NT	1 ... 50
6	4	12	50	0.034		197062	PFAN-6x1-NT	1 ... 50
8	5.9	25	110	0.049		197063	PFAN-8x1.25-NT	1 ... 50
10	7	22	140	0.087		197064	PFAN-10x1.5-NT	1 ... 50
12	8.4	29	165	0.125		197065	PFAN-12x1.75-NT	1 ... 50

- 1) Packaging unit
Can only be ordered by the metre.

Type codes

001	Series
PTFEN	Plastic tubing, polytetrafluorethylene, standard O.D.

002	Pipe/tubing O.D. x wall thickness
4x0,5	4x0.5 mm
6x1	6x1 mm
8x1	8x1 mm
10x1,5	10x1.5 mm
12x2	12x2 mm
14x2	14x2 mm
16x2,5	16x2.5 mm

003	Colour
NT	Natural

004	Packaging unit [m]
	Standard
25	1 m ... 25 m
100	100 m
300	300 m
400	400 m
500	500 m

Datasheet

Plastic tubing PTFEN


Pneumatic tubing with resistance to high temperatures and chemicals.



Operating and environmental conditions		
Type	PTFEN-4/8/10/12/14/16	PTFEN-6
Temperature-dependent operating pressure [bar]	−0.95 ... +12 → graph	−0.95 ... +15 → graph
Operating medium	Compressed air to ISO 8573-1:2010 [7:--:-]	
Ambient temperature [°C]	−20 ... +150	
Suitability for use in the food industry ¹⁾	See supplementary material information	
Material fire test	UL94 V-0	

1) Additional information www.festo.com/catalogue/... → Support/Downloads.

Operating pressure p as a function of temperature t



Accessories

Type	→ Internet
	Recommended fitting
	• Push-in fitting CRQS ¹⁾ crqs
	• Push-in fitting NPQH ²⁾ npqh
	• Push-in fitting NPQP ³⁾ npqp
	• Push-in fitting NPQR ³⁾ npqr
	• Fitting NPCK ⁴⁾ npck
	Well suited
	• Push-in fitting QS ¹⁾ qs
	• Push-in fitting NPQM ²⁾ npqm
	• Click fitting NPKA ⁵⁾ npka
	• Quick connector CK ⁶⁾ ck
	• Barbed fitting CN ⁶⁾ cn
	Limited suitability
	• Push-in fitting QS-V0 ³⁾ qs-v0

1) Not for O.D. 14 mm
 2) Not for O.D. 16 mm
 3) Not for O.D. 14/16 mm

4) For O.D. 4/6/8/10 mm only
 5) For O.D. 6 mm only
 6) For O.D. 4/6/8 mm only

Note

Greater force is required when assembling the fittings CK/NPCK. Expanding the tube ends using a tapered mandrel makes pushing them on easier.

Materials	
Shore hardness	D 55 ±5
Tubing	PTFE
Note on materials	RoHS-compliant

Datasheet

Pneumatic connection			
For push-in connector		For barbed connector	
Push-in fitting	Fitting NPCK	Barbed fitting CN	Quick connector CK
O.D. 4 mm	O.D. 4 mm with union nut	I.D. 3 mm	I.D. 3 mm with union nut
O.D. 6 mm	O.D. 6 mm with union nut	I.D. 4 mm	I.D. 4 mm with union nut
O.D. 8 mm	O.D. 8 mm with union nut	I.D. 6 mm	I.D. 6 mm with union nut
O.D. 10 mm	O.D. 10 mm with union nut	–	–
O.D. 12 mm	–	–	–
O.D. 14 mm	–	–	–
O.D. 16 mm	–	–	–

Ordering data								
O.D.	I.D.	Min. bending radius	Flow-relevant bending radius	Weight	Colour	Part no.	Type	PU ¹⁾
[mm]	[mm]	[mm]	[mm]	[kg/m]				[m]
4	2.9	32	32	0.013	natural	8061171	PTFEN-4x0.5-NT-100	100
6	4	38	40	0.034		8061172	PTFEN-6X1-NT-100	100
						8061178	PTFEN-6X1-NT-500	500
8	5.9	64	90	0.047		8061173	PTFEN-8X1-NT	1 ... 50
						8061179	PTFEN-8X1-NT-400	400
10	7	70	100	0.086		8061174	PTFEN-10X1.5-NT	1 ... 50
						8061180	PTFEN-10X1.5-NT-300	300
12	8.4	84	120	0.124		8061175	PTFEN-12X2-NT	1 ... 50
14	10	106	120	0.162		8061176	PTFEN-14X2-NT	1 ... 50
16	11	109	160	0.228		8061177	PTFEN-16X2.5-NT-25	1 ... 25

- 1) Packaging unit
Can only be ordered by the metre.



Note

Do not bend tubing!

It is crucial that during assembly and operation the tubing is not bent or excessively constricted when using cable binders.

This could damage the tubing and cause it to split at the bend after a short while under normal operating conditions.

Type codes

001	Series	
PTFEN	Plastic tubing, polytetrafluorethylene, standard O.D.	

002	Tubing outside diameter	
5/32	5/32"	
1/4	1/4"	
5/16	5/16"	
3/8	3/8"	
1/2	1/2"	

003	Colour	
NT	Natural	

004	Packaging unit [m]	
150	150 m	
300	300 m	

Datasheet

Plastic tubing PTFEN, NPT


Pneumatic tubing with resistance to high temperatures and chemicals.



Operating and environmental conditions		
Temperature-dependent operating pressure	[bar]	-0.95 ... +12 → graph
Operating medium		Compressed air to ISO 8573-1:2010 [7:-:-]
Ambient temperature	[°C]	-20 ... +150
Suitability for use in the food industry ¹⁾		See supplementary material information
Material fire test		UL94 V-0

1) Additional information www.festo.com/catalogue/... → Support/Downloads.

Operating pressure p as a function of temperature t



Accessories

Type	→ Internet	
	Recommended fitting	
	• Push-in fitting CRQS-U	crqs
	Well suited	
	• Push-in fitting QS-U,	qs
	• Push-in fitting QB-U	qb

Materials	
Shore hardness	D 55 ±5
Tubing	PTFE
Note on materials	RoHS-compliant

Datasheet

Ordering data									
Pneumatic connection For push-in connector	O.D. [mm]	I.D. [mm]	Min. bending radius [mm]	Flow-relevant bending radius [mm]	Weight [kg/m]	Colour	Part no.	Type	PU ¹⁾ [ft]
O.D 5/32"	3.97	2.9	32	32	0.013	natural	8063350	PTFEN-5/32-NT-300	300
O.D 1/4"	6.35	4.1	37	40	0.04		8061181	PTFEN-1/4-NT-300	300
O.D 5/16"	7.94	5.9	64	90	0.049		8063351	PTFEN-5/16-NT-150	150
O.D 3/8"	9.53	6.5	63	100	0.084		8061182	PTFEN-3/8-NT-150	150
O.D 1/2"	12.7	8.5	81	120	0.153		8061183	PTFEN-1/2-NT-150	150

1) Packaging unit

**Note****Do not bend tubing!**

It is crucial that during assembly and operation the tubing is not bent or excessively constricted when using cable binders.

This could damage the tubing and cause it to split at the bend after a short while under normal operating conditions.

Type codes

001	Series	
PEN	Plastic tubing	

002	Pipe/tubing O.D. x wall thickness	
4x0,75	4x0.75 mm	
6x1	6x1 mm	
8x1,25	8x1.25 mm	
10x1,5	10x1.5 mm	
12x1,75	12x1.75 mm	
14x2	14x2 mm	
16x2,5	16x2.5 mm	

003	Colour	
NT	Natural	
SW	Black	
BL	Blue	
SI	Silver	
RT	Red	
GN	Green	
GE	Yellow	

004	Packaging unit [m]	
	Standard	
100	100 m	
200	200 m	
300	300 m	
400	400 m	
500	500 m	

Datasheet

Plastic tubing PEN


Polyethylene tubing is characterised by good resistance to chemicals and hydrolysis. It is resistant to most cleaning agents and lubricants.



Operating and environmental conditions		
Temperature-dependent operating pressure	[bar]	−0.95 ... +10 → graph
Operating medium		Compressed air to ISO 8573-1:2010 [7:--:] Water as per manufacturer's declaration ¹⁾
Ambient temperature	[°C]	−30 ... +60
Certification		German Technical Control Board (TÜV)
Tubing characteristics		Suitability for energy chains in applications with high cycle rates
Tubing test conditions		Suitability for energy chains: > 5 million cycles to Festo standard 942021

1) Additional information www.festo.com/catalogue/... → Support/Downloads.

Operating pressure p as a function of temperature t



Accessories

Type	→ Internet	
	Recommended fitting	
	• Push-in fitting QS ¹⁾	qs
	• Push-in fitting NPQM ²⁾	npqm
	Well suited	
	• Push-in fitting CRQS ¹⁾	crqs
	• Push-in fitting NPQH ²⁾	npqh
	• Push-in fitting NPQP ³⁾	npqp
	• Push-in fitting NPQR ³⁾	npqr
	• Click fitting NPKA ⁴⁾	npka
	• Fitting NPCK ⁵⁾	npck
	• Quick connector CK ⁶⁾	ck
	• Barbed fitting CN ⁶⁾	cn
	Limited suitability	
	• Push-in fitting QS-V0 ³⁾	qs-v0

1) Not for O.D. 14 mm
2) Not for O.D. 16 mm
3) Not for O.D. 14/16 mm


4) For O.D. 6 mm only
5) For O.D. 4/6/8/10 mm only
6) For O.D. 4/6/8 mm only


Note
 Greater force is required when assembling the fittings CK/CN.

Materials	
Shore hardness	D 52 ±3
Tubing	PU
Note on materials	RoHS-compliant Free of copper and PTFE

Datasheet

Dimensions – Reel



Type	D1 ø	D2 ø	D3 ø	D4 ø	D5 ø	D6 ø	D7 ø	D8 ø	H1	H2	L1	L2	W1
For PEN-4x0.75-...-500	545	246	21	20	216	75	20	20	152.5	80.5	128	8	45°
For PEN-6x1-...-500	545	246	21	20	216	75	20	20	152.5	80.5	128	8	45°
For PEN-8x1.25-...-400	545	310	21	20	280	75	20	20	152.5	80.5	254	8	45°
For PEN-10x1.5-...-300	600	310	21	20	280	75	20	20	152.5	80.5	254	8	45°
For PEN-12x1.75-...-200	600	310	21	20	280	75	20	20	152.5	80.5	254	8	45°
For PEN-16x2.5-...-100	545	310	21	20	280	75	20	20	152.5	80.5	254	8	45°

Dimensions and ordering data

O.D. [mm]	I.D. [mm]	Min. bending radius [mm]	Flow-relevant bending radius [mm]	Weight [kg/m]	Colour	Part no.	Type	PJ ¹⁾ [m]
4	2.7	10	20	0.0064	black	543240	PEN-4x0.75-SW	50
					black	551438	PEN-4x0.75-SW-500	500
					blue	551456	PEN-4x0.75-BL	50
					blue	551444	PEN-4x0.75-BL-500	500
					silver	551462	PEN-4x0.75-SI	50
					silver	551450	PEN-4x0.75-SI-500	500
					natural	543246	PEN-4x0.75-NT	50
					green	551468	PEN-4x0.75-GN	50
					red	551474	PEN-4x0.75-RT	50
					yellow	551480	PEN-4x0.75-GE	50
6	4	13.5	26	0.0148	black	543241	PEN-6x1-SW	50
					black	551439	PEN-6x1-SW-500	500
					blue	551457	PEN-6x1-BL	50
					blue	551445	PEN-6x1-BL-500	500
					silver	551463	PEN-6x1-SI	50
					silver	551451	PEN-6x1-SI-500	500
					natural	543247	PEN-6x1-NT	50
					green	551469	PEN-6x1-GN	50
					red	551475	PEN-6x1-RT	50
					yellow	551481	PEN-6x1-GE	50

1) Packaging unit

Datasheet

Dimensions and ordering data								
O.D.	I.D.	Min. bending radius	Flow-relevant bending radius	Weight	Colour	Part no.	Type	PJ ¹⁾
[mm]	[mm]	[mm]	[mm]	[kg/m]				[m]
8	5.7	22.5	35	0.0233	black	543242	PEN-8x1.25-SW	50
					black	551440	PEN-8x1.25-SW-400	400
					blue	551458	PEN-8x1.25-BL	50
					blue	551446	PEN-8x1.25-BL-400	400
					silver	551464	PEN-8x1.25-SI	50
					silver	551452	PEN-8x1.25-SI-400	400
					natural	543248	PEN-8x1.25-NT	50
					green	551470	PEN-8x1.25-GN	50
					red	551476	PEN-8x1.25-RT	50
					yellow	551482	PEN-8x1.25-GE	50
10	7	23.5	40	0.0377	black	543243	PEN-10x1.5-SW	50
					black	551441	PEN-10x1.5-SW-300	300
					blue	551459	PEN-10x1.5-BL	50
					blue	551447	PEN-10x1.5-BL-300	300
					silver	551465	PEN-10x1.5-SI	50
					silver	551453	PEN-10x1.5-SI-300	300
					natural	543249	PEN-10x1.5-NT	50
					green	551471	PEN-10x1.5-GN	50
					red	551477	PEN-10x1.5-RT	50
					yellow	551483	PEN-10x1.5-GE	50
12	8.4	33	58	0.0542	black	543244	PEN-12x1.75-SW	50
					black	551442	PEN-12x1.75-SW-200	200
					blue	551460	PEN-12x1.75-BL	50
					blue	551448	PEN-12x1.75-BL-200	200
					silver	551466	PEN-12x1.75-SI	50
					silver	551454	PEN-12x1.75-SI-200	200
					natural	543250	PEN-12x1.75-NT	50
					green	551472	PEN-12x1.75-GN	50
					red	551478	PEN-12x1.75-RT	50
					yellow	551484	PEN-12x1.75-GE	50
14	9.5	45	80	0.0773	black	570516	PEN-14x2-SW	50
					natural	570517	PEN-14x2-NT	50
16	10.8	57.5	122	0.1029	black	543245	PEN-16x2.5-SW	50
					black	551443	PEN-16x2.5-SW-100	100
					blue	551461	PEN-16x2.5-BL	50
					blue	551449	PEN-16x2.5-BL-100	100
					silver	551467	PEN-16x2.5-SI	50
					silver	551455	PEN-16x2.5-SI-100	100
					natural	543251	PEN-16x2.5-NT	50
					green	551473	PEN-16x2.5-GN	50
					red	551479	PEN-16x2.5-RT	50
					yellow	551485	PEN-16x2.5-GE	50

1) Packaging unit

Ordering data – Modular product system

Ordering table (minimum order quantity 3000 m, rounded value 25 m)										
Size	4	6	8	10	12	14	16	Condi- tions	Code	Enter code
Module no.	553769									
Function	Polyethylene tubing, standard O.D., economical								PEN	PEN
Tubing O.D. [mm]	4	–	–	–	–	–	–		-4	
	–	6	–	–	–	–	–		-6	
	–	–	8	–	–	–	–		-8	
	–	–	–	10	–	–	–		-10	
	–	–	–	–	12	–	–		-12	
	–	–	–	–	–	14	–		-14	
	–	–	–	–	–	–	16		-16	
Colour	silver								-SI	
	blue								-BL	
	black								-SW	
	yellow								-GE	
	green								-GN	
	red								-RT	
	brown								-BR	
	white								-WS	
	natural								-NT	
Labelling text (on request)	Standard									
	Customer-specific tubing inscription							[1]	-TXT	
Packaging unit [m]	25								-25	
	50								-50	
	100								-100	
	200						–		-200	
	300					–	–		-300	
	400			–	–	–	–		-400	
	500		–	–	–	–	–		-500	
Packaging	Cardboard box							[2]	-CB	
	Reel							[3]	-HA	

[1] **TXT** Only on request[2] **CB** Only with packaging unit 25, 50[3] **HA** Only with packaging unit 25, 50

Type codes

001	Series	
PLN	Plastic tubing, polyethylene, standard O.D.	
002	Pipe/tubing O.D. x wall thickness	
4x0,75	4x0.75 mm	
6x1	6x1 mm	
8x1,25	8x1.25 mm	
10x1,5	10x1.5 mm	
12x1,75	12x1.75 mm	
14x2	14x2 mm	
16x2	16x2 mm	

003	Colour	
NT	Natural	
SW	Black	
BL	Blue	
SI	Silver	
RT	Red	

Datasheet

Plastic tubing PLN


Polyethylene tubing is characterised by good resistance to chemicals and hydrolysis. It is resistant to most cleaning agents and lubricants.



Operating and environmental conditions		
Temperature-dependent operating pressure	[bar]	-0.95 ... +14 → graph
Operating medium		Compressed air to ISO 8573-1:2010 [7:-:-] Water as per manufacturer's declaration ¹⁾
Ambient temperature	[°C]	-30 ... +80
Suitability for use in the food industry ¹⁾		See supplementary material information
Certification		German Technical Control Board (TÜV)

1) Additional information www.festo.com/catalogue/... → Support/Downloads.

Operating pressure p as a function of temperature t



Accessories

Type	→ Internet	
	Recommended fitting	
	• Push-in fitting NPQP ¹⁾	npqp
	• Push-in fitting NPQR ¹⁾	npqr
	Well suited	
	• Push-in fitting QS ²⁾	qs
	• Push-in fitting CRQS ²⁾	crqs
	• Push-in fitting NPQH ³⁾	npqh
	• Push-in fitting NPQM ³⁾	npqm
	• Click fitting NPKA ⁴⁾	npka
	• Fitting NPCK ⁵⁾	npck
	• Quick connector CK ⁶⁾	ck
	Limited suitability	
	• Push-in fitting QS-V0 ¹⁾	qs-v0
	• Barbed fitting CN ⁶⁾	cn

1) Not for O.D. 14/16 mm

2) Not for O.D. 14 mm

3) Not for O.D. 16 mm

4) For O.D. 6 mm only

5) For O.D. 4/6/8/10 mm only

6) For O.D. 4/6/8 mm only



Note

Greater force is required when assembling the fittings CK/CN. Expanding the tube ends using a tapered mandrel makes pushing them on easier.

Materials	
Shore hardness	D 59 ±3
Tubing	PU
Note on materials	RoHS-compliant Free of copper and PTFE

Datasheet

Dimensions and ordering data								
O.D.	I.D.	Min. bending radius	Flow-relevant bending radius	Weight	Colour	Part no.	Type	PJ ¹⁾
[mm]	[mm]	[mm]	[mm]	[kg/m]				[m]
4	2.9	12	25	0.0056	natural	193403	PLN-4x0.75-NT	50
					black	195280	PLN-4x0.75-SW	50
					blue	558205	PLN-4x0.75-BL	50
					silver	558211	PLN-4x0.75-SI	50
					red	558217	PLN-4x0.75-RT	50
6	4	11	32	0.0147	natural	193404	PLN-6x1-NT	50
					black	195281	PLN-6x1-SW	50
					blue	558206	PLN-6x1-BL	50
					silver	558212	PLN-6x1-SI	50
					red	558218	PLN-6x1-RT	50
8	5.9	23	50	0.0214	natural	193405	PLN-8x1.25-NT	1 ... 50
					black	195282	PLN-8x1.25-SW	1 ... 50
					blue	558207	PLN-8x1.25-BL	1 ... 50
					silver	558213	PLN-8x1.25-SI	1 ... 50
					red	558219	PLN-8x1.25-RT	1 ... 50
10	7	22	57	0.0375	natural	193406	PLN-10x1.5-NT	1 ... 50
					black	195283	PLN-10x1.5-SW	1 ... 50
					blue	558208	PLN-10x1.5-BL	1 ... 50
					silver	558214	PLN-10x1.5-SI	1 ... 50
					red	558220	PLN-10x1.5-RT	1 ... 50
12	8.4	23	65	0.054	natural	193407	PLN-12x1.75-NT	1 ... 50
					black	195284	PLN-12x1.75-SW	1 ... 50
					blue	558209	PLN-12x1.75-BL	1 ... 50
					silver	558215	PLN-12x1.75-SI	1 ... 50
					red	558221	PLN-12x1.75-RT	1 ... 50
14	10	40	80	0.07	natural	570424	PLN-14x2-NT	1 ... 50
					black	570423	PLN-14x2-SW	1 ... 50
16	12	55	95	0.082	natural	539064	PLN-16x2-NT	1 ... 50
					black	539065	PLN-16x2-SW	1 ... 50
					blue	558210	PLN-16x2-BL	1 ... 50
					silver	558216	PLN-16x2-SI	1 ... 50
					red	558222	PLN-16x2-RT	1 ... 50

1) Packaging unit
Can only be ordered by the metre.

Ordering data – Modular product system

Ordering table (minimum order quantity 3000 m, rounded value 25 m)										
Size	4	6	8	10	12	14	16	Conditions	Code	Enter code
Module no.	553850									
Function	Polyethylene tubing, standard O.D., resistant to cleaning agents								PLN	PLN
Tubing O.D. [mm]	4	–	–	–	–	–	–		-4	
	–	6	–	–	–	–	–		-6	
	–	–	8	–	–	–	–		-8	
	–	–	–	10	–	–	–		-10	
	–	–	–	–	12	–	–		-12	
	–	–	–	–	–	14	–		-14	
	–	–	–	–	–	–	16		-16	
Colour	silver								-SI	
	blue								-BL	
	black								-SW	
	yellow								-GE	
	green								-GN	
	red								-RT	
	brown								-BR	
	white								-WS	
	natural								-NT	
Labelling text (on request)	Standard									
	Customer-specific tubing inscription							[1]	-TXT	
Packaging unit [m]	25								-25	
	50								-50	
	100								-100	
	200					–	–		-200	
	300				–	–	–		-300	
	400			–	–	–	–		-400	
	500		–	–	–	–	–		-500	
Packaging	Cardboard box							[2]	-CB	
	Reel							[3]	-HA	

[1] **TXT** Only on request[2] **CB** Only with packaging unit 25, 50[3] **HA** Only with packaging unit 25, 50

Type codes

001	Series
PUN	Plastic tubing, polyurethane

002	Pipe/tubing O.D. x wall thickness
3x0,5	3x0.5 mm
4x0,75	4x0.75 mm
6x1	6x1 mm
8x1,25	8x1.25 mm
10x1,5	10x1.5 mm
12x2	12x2 mm
14x2	14x2 mm
16x2,5	16x2.5 mm

003	Tubing type
	Standard
DUO	DUO pneumatic tubing

004	Colour
SW	Black
BL	Blue
SI	Silver
RT	Red
GN	Green
GE	Yellow
BS	Blue/black

005	Packaging unit [m]
	Standard
100	100 m
200	200 m
300	300 m
400	400 m
500	500 m

Datasheet


Plastic tubing PUN

Highly flexible plastic tubing



Operating and environmental conditions		
Temperature-dependent operating pressure	[bar]	-0.95 ... +10 → graph
Operating medium		Compressed air to ISO 8573-1:2010 [7:-:-]
PWIS conformity		VDMA24364-B2-L
Ambient temperature	[°C]	-35 ... +60
Material fire test		UL94 HB
Certification		German Technical Control Board (TÜV)
Tubing characteristics		Suitability for energy chains in applications with high cycle rates
Tubing test conditions		Suitability for energy chains: > 5 million cycles to Festo standard 942021

Operating pressure p as a function of temperature t



Accessories

Type	→ Internet
	Recommended fitting
	• Push-in fitting QS ¹⁾ qs
	Well suited
	• Push-in fitting CRQS ³⁾ crqs
	• Push-in fitting NPQH ²⁾ npqh
	• Push-in fitting NPQP ⁴⁾ npqp
	• Push-in fitting NPQM ²⁾ npqm
	• Push-in fitting NPQR ⁴⁾ npqr
	• Click fitting NPKA ⁵⁾ npka
	• Fitting NPCK ⁶⁾ npck
	• Quick connector CK ⁷⁾ ck
	• Barbed fitting CN ⁸⁾ cn
	Limited suitability
	• Push-in fitting QS-V0 ⁴⁾ qs-v0

- 1) Not for O.D. 14 mm
 2) Not for O.D. 3/16 mm
 3) Not for O.D. 3/14 mm
 4) Not for O.D. 3/14/16 mm

- 5) For O.D. 6 mm only
 6) For O.D. 4/6/8/10 mm only
 7) For O.D. 4/6/8 mm only
 8) For O.D. 3/4/6/8 mm only




Note

Greater force is required when assembling the fittings CK/CN. Expanding the tube ends using a tapered mandrel makes pushing them on easier.

Materials	
Shore hardness	D 52 ±3
Tubing	TPE-U(PU)
Note on materials	RoHS-compliant
	Free of copper and PTFE

Datasheet

Dimensions – Reel



Type	D1 ø	D2 ø	D3 ø	D4 ø	D5 ø	D6 ø	D7 ø	D8 ø	H1	H2	L1	L2	W1
For PUN-3x0.5-...-500	545	246	21	20	216	75	20	20	152.5	80.5	128	8	45°
For PUN-4x0.75-...-500	545	246	21	20	216	75	20	20	152.5	80.5	128	8	45°
For PUN-6x1-...-500	600	310	21	20	280	75	20	20	152.5	80.5	114	8	45°
For PUN-8x1.25-...-400	545	310	21	20	280	75	20	20	152.5	80.5	254	8	45°
For PUN-10x1.5-...-300	600	310	21	20	280	75	20	20	152.5	80.5	254	8	45°
For PUN-12x2-...-200	600	310	21	20	280	75	20	20	152.5	80.5	254	8	45°
For PUN-16x2.5-...-100	545	310	21	20	280	75	20	20	152.5	80.5	254	8	45°

Dimensions and ordering data

O.D. [mm]	I.D. [mm]	Min. bending radius [mm]	Flow-relevant bending radius [mm]	Weight [kg/m]	Colour	Part no.	Type	PU ¹⁾ [m]
3	2.1	9	12	0.0044	silver	152583	PUN-3x0.5-SI	50
					silver	525738	PUN-3x0.5-SI-500	500
					blue	159660	PUN-3x0.5-BL	50
					blue	525745	PUN-3x0.5-BL-500	500
					black	159661	PUN-3x0.5-SW	50
					black	553936	PUN-3x0.5-SW-500	500
					yellow	178416	PUN-3x0.5-GE	50
					green	178423	PUN-3x0.5-GN	50
					red	178409	PUN-3x0.5-RT	50
4	2.6	8	17	0.0089	silver	152584	PUN-4x0.75-SI	50
					silver	525739	PUN-4x0.75-SI-500	500
					blue	159662	PUN-4x0.75-BL	50
					blue	525746	PUN-4x0.75-BL-500	500
					black	159663	PUN-4x0.75-SW	50
					black	553937	PUN-4x0.75-SW-500	500
					yellow	178417	PUN-4x0.75-GE	50
					green	178424	PUN-4x0.75-GN	50
					red	178410	PUN-4x0.75-RT	50

1) Packaging unit

Datasheet


Dimensions and ordering data								
O.D.	I.D.	Min. bending radius	Flow-relevant bending radius	Weight	Colour	Part no.	Type	pU ¹⁾
[mm]	[mm]	[mm]	[mm]	[kg/m]				[m]
6	4.0	16	26.5	0.0192	silver	152586	PUN-6x1-SI	50
					silver	525740	PUN-6x1-SI-500	500
					blue	159664	PUN-6x1-BL	50
					blue	525747	PUN-6x1-BL-500	500
					black	159665	PUN-6x1-SW	50
					black	553938	PUN-6x1-SW-500	500
					yellow	178418	PUN-6x1-GE	50
					green	178425	PUN-6x1-GN	50
					red	178411	PUN-6x1-RT	50
8	5.7	24	37	0.0302	silver	152587	PUN-8x1.25-SI	1 ... 50
					silver	525741	PUN-8x1.25-SI-400	400
					blue	159666	PUN-8x1.25-BL	1 ... 50
					blue	525748	PUN-8x1.25-BL-400	400
					black	159667	PUN-8x1.25-SW	1 ... 50
					black	553939	PUN-8x1.25-SW-400	400
					yellow	178419	PUN-8x1.25-GE	1 ... 50
					green	178426	PUN-8x1.25-GN	1 ... 50
					red	178412	PUN-8x1.25-RT	1 ... 50
10	7.0	28	54	0.0489	silver	152588	PUN-10x1.5-SI	1 ... 50
					silver	525742	PUN-10x1.5-SI-300	300
					blue	159668	PUN-10x1.5-BL	1 ... 50
					blue	525749	PUN-10x1.5-BL-300	300
					black	159669	PUN-10x1.5-SW	1 ... 50
					black	553940	PUN-10x1.5-SW-300	300
					yellow	178420	PUN-10x1.5-GE	1 ... 50
					green	178427	PUN-10x1.5-GN	1 ... 50
					red	178413	PUN-10x1.5-RT	1 ... 50
12	8.0	33	62	0.0767	silver	152589	PUN-12x2-SI	1 ... 50
					silver	525743	PUN-12x2-SI-200	200
					blue	159670	PUN-12x2-BL	1 ... 50
					blue	525750	PUN-12x2-BL-200	200
					black	159671	PUN-12x2-SW	1 ... 50
					black	553941	PUN-12x2-SW-200	200
					yellow	178421	PUN-12x2-GE	1 ... 50
					green	178428	PUN-12x2-GN	1 ... 50
					red	178414	PUN-12x2-RT	1 ... 50
14	9.8	45	84	0.0949	silver	570389	PUN-14x2-SI	1 ... 50
					blue	570390	PUN-14x2-BL	1 ... 50
					black	570391	PUN-14x2-SW	1 ... 50
16	11.0	45	88	0.1294	silver	152590	PUN-16x2.5-SI	1 ... 50
					silver	525744	PUN-16x2.5-SI-100	100
					blue	159672	PUN-16x2.5-BL	1 ... 50
					blue	525751	PUN-16x2.5-BL-100	100
					black	159673	PUN-16x2.5-SW	1 ... 50
					black	553942	PUN-16x2.5-SW-100	100
					yellow	178422	PUN-16x2.5-GE	1 ... 50
					green	178429	PUN-16x2.5-GN	1 ... 50
					red	178415	PUN-16x2.5-RT	1 ... 50

1) Packaging unit
Can only be ordered by the metre.

Datasheet

DUO tubing PUN-DUO


Highly flexible paired plastic tubing characterised by great resistance to abrasion and kinks. Two lengths of tubing are fused together into a tubing pair. For fitting, the paired tubing is separated as required at both ends.



Operating and environmental conditions

Temperature-dependent operating pressure	[bar]	-0.95 ... +10 → graph
Operating medium		Compressed air to ISO 8573-1:2010 [7:-:-]
Ambient temperature	[°C]	-35 ... +60
Material fire test		UL94 HB
Certification		German Technical Control Board (TÜV)
Tubing characteristics		Suitability for energy chains in applications with high cycle rates
Tubing test conditions		Suitability for energy chains: > 5 million cycles to Festo standard 942021

Operating pressure p as a function of temperature t



Accessories

Type	→ Internet
	Recommended fitting
	• Push-in fitting QS
	qs
	Well suited
	• Push-in fitting CRQS
	crqs
	• Push-in fitting NPQH
	npqh
	• Push-in fitting NPQP
	npqp
	• Push-in fitting NPQM
	npqm
	• Push-in fitting NPQR
	npqr
	• Click fitting NPKA ¹⁾
	npka
	• Fitting NPCK
	npck
	• Quick connector CK ²⁾
	ck
	• Barbed fitting CN ²⁾
	cn
	Limited suitability
	• Push-in fitting QS-V0
	qs-v0

1) For O.D. 6 mm only

2) For O.D. 4/6/8 mm only



Note

Greater force is required when assembling the fittings CK/CN. Expanding the tube ends using a tapered mandrel makes pushing them on easier.

Materials

Shore hardness	D 52 ±3
Tubing	TPE-U(PU)
Note on materials	RoHS-compliant
	Free of copper and PTFE

Datasheet

Dimensions and ordering data								
O.D.	I.D.	Min. bending radius	Flow-relevant bending radius	Weight	Colour	Part no.	Type	PU ¹⁾
[mm]	[mm]	[mm]	[mm]	[kg/m]				[m]
4	2.6	8	17	0.0178	silver	152822	PUN-4x0.75-DUO-SI	50
					blue/black	159674	PUN-4x0.75-DUO-BS	50
6	4	16	26.5	0.0384	silver	152823	PUN-6x1-DUO-SI	50
					blue/black	159675	PUN-6x1-DUO-BS	50
8	5.7	24	37	0.0604	silver	152824	PUN-8x1.25-DUO-SI	1 ... 50
					blue/black	159676	PUN-8x1.25-DUO-BS	1 ... 50
10	7	28	54	0.0978	silver	152825	PUN-10x1.5-DUO-SI	1 ... 50
					blue/black	159677	PUN-10x1.5-DUO-BS	1 ... 50

1) Packaging unit
Can only be ordered by the metre.

Type codes

001	Series	
PUN	Plastic tubing, polyurethane	
002	Alternative material characteristic	
CM	Antistatic	

003	Tubing outside diameter	
12	12 mm	
4	4 mm	
6	6 mm	
8	8 mm	
10	10 mm	
004	Colour	
SW	Black	

Datasheet


Plastic tubing PUN-CM

Highly flexible plastic tubing,
electrically conductive.



Operating and environmental conditions		
Temperature-dependent operating pressure	[bar]	-0.95 ... +10 → graph
Operating medium		Compressed air to ISO 8573-1:2010 [7:-:-]
Ambient temperature	[°C]	-35 ... +60
Surface resistance	[Ω]	10 ⁴ ... 10 ⁷
Tubing characteristics		Suitability for energy chains in applications with high cycle rates
Tubing test conditions		Suitability for energy chains: > 5 million cycles to Festo standard 942021

Operating pressure p as a function of temperature t



Accessories

Type	→ Internet	
	Recommended fitting	
	• Push-in fitting NPQM	npqm
	Well suited	
	• Push-in fitting NPQH	npqh
	• Push-in fitting NPQR ²⁾	npqr
	• Fitting NPCK ¹⁾	npck
	Limited suitability	
	• Push-in fitting QS ²⁾	qs
	• Push-in fitting CRQS ²⁾	crqs
	• Push-in fitting QS-V0 ²⁾	qs-v0
	• Push-in fitting NPQP ²⁾	npqp
	• Click fitting NPKA ³⁾	npka
	• Quick connector CK ⁴⁾	ck
	• Barbed fitting CN ⁴⁾	cn

1) For O.D. 4/6/8/10 mm only

2) Not for O.D. 14 mm

3) For O.D. 6 mm only

4) For O.D. 4/6/8 mm only

Materials

Shore hardness	D 52 ±3
Tubing	TPE-U(PU)
Note on materials	RoHS-compliant
	Free of copper and PTFE

Datasheet

Dimensions and ordering data								
O.D.	I.D.	Min. bending radius	Flow-relevant bending radius	Weight	Colour	Part no.	Type	PJ ¹⁾
[mm]	[mm]	[mm]	[mm]	[kg/m]				[m]
4	2.5	8	17	0.0089	black	188882	PUN-CM-4-SW	50
6	4	14	28	0.0192		188883	PUN-CM-6-SW	50
8	5.5	20	37	0.0368		130816	PUN-CM-8-SW	1 ... 50
10	7	30	60	0.0544		130817	PUN-CM-10-SW	1 ... 50
12	8	30	70	0.0754		130818	PUN-CM-12-SW	1 ... 50
14	9.8	41	80	0.095		Modular product system → 49		

- 1) Packaging unit
Can only be ordered by the metre.

Type codes

001	Series
PUN	Plastic tubing, polyurethane
002	Alternative material characteristic
H	Hydrolysis-resistant
003	Pipe/tubing O.D. x wall thickness
2x0,4	2x0.4 mm
3x0,5	3x0.5 mm
4x0,75	4x0.75 mm
6x1	6x1 mm
8x1,25	8x1.25 mm
10x1,5	10x1.5 mm
12x2	12x2 mm
14x2	14x2 mm
16x2,5	16x2.5 mm
004	Tubing type
	Standard
DUO	DUO pneumatic tubing

005	Colour
NT	Natural
TBL	Translucent blue
SW	Black
BL	Blue
TSW	Translucent black
SI	Silver
RT	Red
TRT	Translucent red
GN	Green
TGN	Translucent green
GE	Yellow
TGE	Translucent yellow
BS	Blue/black
006	Packaging unit [m]
	Standard
100	100 m
200	200 m
300	300 m
400	400 m
500	500 m

Datasheet


Plastic tubing PUN-H

With O.D. 2 mm



Operating and environmental conditions		
Temperature-dependent operating pressure	[bar]	-0.95 ... +10 → graph
Operating medium		Compressed air to ISO 8573-1:2010 [7:-:-]
Ambient temperature	[°C]	-35 ... +60
Tubing characteristics		Suitability for energy chains in applications with high cycle rates
Tubing test conditions		Suitability for energy chains: > 5 million cycles to Festo standard 942021

Operating pressure p as a function of temperature t



Accessories

Type	→ Internet	
	Recommended fitting	
	• Push-in fitting QSM, mini	qsm

Materials	
Shore hardness	D 52 ±3
Tubing	TPE-U(PU)
Note on materials	RoHS-compliant
	Free of copper and PTFE

Dimensions and ordering data								
O.D.	I.D.	Min. bending radius	Flow-relevant bending radius	Weight	Colour	Part no.	Type	PU ¹⁾
[mm]	[mm]	[mm]	[mm]	[kg/m]				[m]
2	1.2	5	8	0.0024	natural	133038	PUN-H-2x0.4-NT	50
					black	133039	PUN-H-2x0.4-SW	50
					red	133040	PUN-H-2x0.4-RT	50

1) Packaging unit

Datasheet

Plastic tubing PUN-H

With O.D. 3 ... 16 mm




Operating and environmental conditions

Colour	natural, blue, black, silver, red, green, yellow	translucent blue, translucent black, translucent red, translucent green, translucent yellow
Temperature-dependent operating pressure [bar]	-0.95 ... +10 → graph	
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-] Water as per manufacturer's declaration ¹⁾	
PWIS conformity	VDMA24364-B2-L	
Ambient temperature [°C]	-35 ... +60	
Suitability for use in the food industry ¹⁾	See supplementary material information	–
Material fire test	UL94 HB	
Certification ¹⁾	German Technical Control Board (TÜV)	–
Tubing characteristics	Suitability for energy chains in applications with high cycle rates	
Tubing test conditions	Suitability for energy chains: > 5 million cycles to Festo standard 942021	

1) Additional information www.festo.com/catalogue/... → Support/Downloads.

Operating pressure p as a function of temperature t



Accessories

Type	→ Internet	
	Recommended fitting	
	• Push-in fitting QS ¹⁾	qs
	• Push-in fitting NPQH ²⁾	npqh
	• Push-in fitting NPQR ⁴⁾	npqr
	• Click fitting NPKA ⁵⁾	npka
	Well suited	
	• Push-in fitting CRQS ³⁾	crqs
	• Push-in fitting NPQP ⁴⁾	npqp
	• Push-in fitting NPQM ²⁾	npqm
	• Fitting NPCK ⁶⁾	npck
	• Quick connector CK ⁷⁾	ck
	Limited suitability	
	• Push-in fitting QS-V0 ⁴⁾	qs-v0

- 1) Not for O.D. 14 mm
 2) Not for O.D. 3/16 mm
 3) Not for O.D. 3/14 mm
 4) Not for O.D. 3/14/16 mm


- 5) For O.D. 6 mm only
 6) For O.D. 4/6/8/10 mm only
 7) For O.D. 4/6/8 mm only

Materials

Shore hardness	D 52 ±3
Tubing	TPE-U(PU)
Note on materials	RoHS-compliant
	Free of copper and PTFE

Datasheet

Dimensions – Reel



Type	D1 Ø	D2 Ø	D3 Ø	D4 Ø	D5 Ø	D6 Ø	D7 Ø	D8 Ø	H1	H2	L1	L2	W1
For PUN-H-3x0.5-...-500	545	246	21	20	216	75	20	20	152.5	80.5	128	8	45°
For PUN-H-4x0.75-...-500	545	246	21	20	216	75	20	20	152.5	80.5	128	8	45°
For PUN-H-6x1-...-500	545	246	21	20	216	75	20	20	152.5	80.5	128	8	45°
For PUN-H-8x1.25-...-400	545	310	21	20	280	75	20	20	152.5	80.5	254	8	45°
For PUN-H-10x1.5-...-300	600	310	21	20	280	75	20	20	152.5	80.5	254	8	45°
For PUN-H-12x2-...-200	600	310	21	20	280	75	20	20	152.5	80.5	254	8	45°
For PUN-H-16x2.5-...-100	545	310	21	20	280	75	20	20	152.5	80.5	254	8	45°

Dimensions and ordering data

O.D. [mm]	I.D. [mm]	Min. bending radius [mm]	Flow-relevant bending radius [mm]	Weight [kg/m]	Colour	Part no.	Type	PJ ¹⁾ [m]
3	2.1	6	12	0.0042	natural	197375	PUN-H-3x0.5-NT	50
					natural	558263	PUN-H-3x0.5-NT-500	500
					blue	197382	PUN-H-3x0.5-BL	50
					blue	558256	PUN-H-3x0.5-BL-500	500
					black	197389	PUN-H-3x0.5-SW	50
					black	558249	PUN-H-3x0.5-SW-500	500
					silver	558277	PUN-H-3x0.5-SI	50
					silver	558270	PUN-H-3x0.5-SI-500	500
					red	558284	PUN-H-3x0.5-RT	50
					green	558291	PUN-H-3x0.5-GN	50
					yellow	558298	PUN-H-3x0.5-GE	50

1) Packaging unit

Datasheet

Dimensions and ordering data								
O.D.	I.D.	Min. bending radius	Flow-relevant bending radius	Weight	Colour	Part no.	Type	pU ¹⁾
[mm]	[mm]	[mm]	[mm]	[kg/m]				[m]
4	2.6	8	16	0.0085	natural	★ 197376	PUN-H-4x0.75-NT	50
					natural	★ 558264	PUN-H-4x0.75-NT-500	500
					blue	★ 197383	PUN-H-4x0.75-BL	50
					blue	★ 558257	PUN-H-4x0.75-BL-500	500
					translucent blue	★ 8048671	PUN-H-4x0.75-TBL	50
					translucent blue	★ 8048672	PUN-H-4x0.75-TBL-500	500
					black	★ 197390	PUN-H-4x0.75-SW	50
					black	★ 558250	PUN-H-4x0.75-SW-500	500
					translucent black	★ 8048673	PUN-H-4x0.75-TSW	50
					translucent black	★ 8048674	PUN-H-4x0.75-TSW-500	500
					silver	★ 558278	PUN-H-4x0.75-SI	50
					silver	★ 558271	PUN-H-4x0.75-SI-500	500
					red	558285	PUN-H-4x0.75-RT	50
					translucent red	8048675	PUN-H-4x0.75-TRT	50
					translucent red	8048676	PUN-H-4x0.75-TRT-500	500
					green	558292	PUN-H-4x0.75-GN	50
					translucent green	8048677	PUN-H-4x0.75-TGN	50
					translucent green	8048678	PUN-H-4x0.75-TGN-500	500
					yellow	558299	PUN-H-4x0.75-GE	50
					translucent yellow	8048679	PUN-H-4x0.75-TGE	50
					translucent yellow	8048680	PUN-H-4x0.75-TGE-500	500
6	4	10	26	0.0183	natural	★ 197377	PUN-H-6x1-NT	50
					natural	★ 558265	PUN-H-6x1-NT-500	500
					blue	★ 197384	PUN-H-6x1-BL	50
					blue	★ 558258	PUN-H-6x1-BL-500	500
					translucent blue	★ 8048681	PUN-H-6x1-TBL	50
					translucent blue	★ 8048682	PUN-H-6x1-TBL-500	500
					black	★ 197391	PUN-H-6x1-SW	50
					black	★ 558251	PUN-H-6x1-SW-500	500
					translucent black	★ 8048683	PUN-H-6x1-TSW	50
					translucent black	★ 8048684	PUN-H-6x1-TSW-500	500
					silver	★ 558279	PUN-H-6x1-SI	50
					silver	★ 558272	PUN-H-6x1-SI-500	500
					red	558286	PUN-H-6x1-RT	50
					translucent red	8048685	PUN-H-6x1-TRT	50
					translucent red	8048686	PUN-H-6x1-TRT-500	500
					green	558293	PUN-H-6x1-GN	50
					translucent green	8048687	PUN-H-6x1-TGN	50
					translucent green	8048688	PUN-H-6x1-TGN-500	500
					yellow	558300	PUN-H-6x1-GE	50
					translucent yellow	8048689	PUN-H-6x1-TGE	50
					translucent yellow	8048690	PUN-H-6x1-TGE-500	500

1) Packaging unit

Datasheet

Dimensions and ordering data								
O.D.	I.D.	Min. bending radius	Flow-relevant bending radius	Weight	Colour	Part no.	Type	PJ ¹⁾
[mm]	[mm]	[mm]	[mm]	[kg/m]				[m]
8	5.7	21	37	0.0287	natural	★ 197378	PUN-H-8x1.25-NT	1 ... 50
					natural	★ 558266	PUN-H-8x1.25-NT-400	400
					blue	★ 197385	PUN-H-8x1.25-BL	1 ... 50
					blue	★ 558259	PUN-H-8x1.25-BL-400	400
					translucent blue	★ 8048691	PUN-H-8x1.25-TBL	50
					translucent blue	★ 8048692	PUN-H-8x1.25-TBL-400	400
					black	★ 197392	PUN-H-8x1.25-SW	1 ... 50
					black	★ 558252	PUN-H-8x1.25-SW-400	400
					translucent black	★ 8048693	PUN-H-8x1.25-TSW	50
					translucent black	★ 8048694	PUN-H-8x1.25-TSW-400	400
					silver	★ 558280	PUN-H-8x1.25-SI	1 ... 50
					silver	★ 558273	PUN-H-8x1.25-SI-400	400
					red	558287	PUN-H-8x1.25-RT	1 ... 50
					translucent red	8048695	PUN-H-8x1.25-TRT	50
					translucent red	8048696	PUN-H-8x1.25-TRT-400	400
					green	558294	PUN-H-8x1.25-GN	1 ... 50
					translucent green	8048697	PUN-H-8x1.25-TGN	50
					translucent green	8048698	PUN-H-8x1.25-TGN-400	400
					yellow	558301	PUN-H-8x1.25-GE	1 ... 50
					translucent yellow	8048699	PUN-H-8x1.25-TGE	50
					translucent yellow	8048700	PUN-H-8x1.25-TGE-400	400
10	7	28	52	0.0465	natural	★ 197379	PUN-H-10x1.5-NT	1 ... 50
					natural	★ 558267	PUN-H-10x1.5-NT-300	300
					blue	★ 197386	PUN-H-10x1.5-BL	1 ... 50
					blue	★ 558260	PUN-H-10x1.5-BL-300	300
					translucent blue	★ 8048701	PUN-H-10x1.5-TBL	50
					translucent blue	★ 8048702	PUN-H-10x1.5-TBL-300	300
					black	★ 197393	PUN-H-10x1.5-SW	1 ... 50
					black	★ 558253	PUN-H-10x1.5-SW-300	300
					translucent black	★ 8048703	PUN-H-10x1.5-TSW	50
					translucent black	★ 8048704	PUN-H-10x1.5-TSW-300	300
					silver	★ 558281	PUN-H-10x1.5-SI	1 ... 50
					silver	★ 558274	PUN-H-10x1.5-SI-300	300
					red	558288	PUN-H-10x1.5-RT	1 ... 50
					translucent red	8048705	PUN-H-10x1.5-TRT	50
					translucent red	8048706	PUN-H-10x1.5-TRT-300	300
					green	558295	PUN-H-10x1.5-GN	1 ... 50
					translucent green	8048707	PUN-H-10x1.5-TGN	50
					translucent green	8048708	PUN-H-10x1.5-TGN-300	300
					yellow	558302	PUN-H-10x1.5-GE	1 ... 50
					translucent yellow	8048709	PUN-H-10x1.5-TGE	50
					translucent yellow	8048710	PUN-H-10x1.5-TGE-300	300

1) Packaging unit
Can only be ordered by the metre.

Datasheet

Dimensions and ordering data								
O.D.	I.D.	Min. bending radius	Flow-relevant bending radius	Weight	Colour	Part no.	Type	pU ¹⁾
[mm]	[mm]	[mm]	[mm]	[kg/m]				[m]
12	8	33	62	0.0729	natural	★ 197380	PUN-H-12x2-NT	1 ... 50
					natural	★ 558268	PUN-H-12x2-NT-200	200
					blue	★ 197387	PUN-H-12x2-BL	1 ... 50
					blue	★ 558261	PUN-H-12x2-BL-200	200
					translucent blue	★ 8048711	PUN-H-12x2-TBL	50
					translucent blue	★ 8048712	PUN-H-12x2-TBL-200	200
					black	★ 197394	PUN-H-12x2-SW	1 ... 50
					black	★ 558254	PUN-H-12x2-SW-200	200
					translucent black	★ 8048713	PUN-H-12x2-TSW	50
					translucent black	★ 8048714	PUN-H-12x2-TSW-200	200
					silver	★ 558282	PUN-H-12x2-SI	1 ... 50
					silver	★ 558275	PUN-H-12x2-SI-200	200
					red	558289	PUN-H-12x2-RT	1 ... 50
					translucent red	8048715	PUN-H-12x2-TRT	50
					translucent red	8048716	PUN-H-12x2-TRT-200	200
					green	558296	PUN-H-12x2-GN	1 ... 50
					translucent green	8048717	PUN-H-12x2-TGN	50
					translucent green	8048718	PUN-H-12x2-TGN-200	200
					yellow	558303	PUN-H-12x2-GE	1 ... 50
					translucent yellow	8048719	PUN-H-12x2-TGE	50
					translucent yellow	8048720	PUN-H-12x2-TGE-200	200
14	9.8	38	78	0.091	natural	570388	PUN-H-14x2-NT	1 ... 50
					blue	570386	PUN-H-14x2-BL	1 ... 50
					black	570387	PUN-H-14x2-SW	1 ... 50
16	11	38	88	0.123	natural	197381	PUN-H-16x2.5-NT	1 ... 50
					natural	558269	PUN-H-16x2.5-NT-100	100
					blue	197388	PUN-H-16x2.5-BL	1 ... 50
					blue	558262	PUN-H-16x2.5-BL-100	100
					black	197395	PUN-H-16x2.5-SW	1 ... 50
					black	558255	PUN-H-16x2.5-SW-100	100
					silver	558283	PUN-H-16x2.5-SI	1 ... 50
					silver	558276	PUN-H-16x2.5-SI-100	100
					red	558290	PUN-H-16x2.5-RT	1 ... 50
					green	558297	PUN-H-16x2.5-GN	1 ... 50
					yellow	558304	PUN-H-16x2.5-GE	1 ... 50

1) Packaging unit
Can only be ordered by the metre.

Datasheet

DUO tubing
PUN-H-DUO


Highly flexible paired plastic tubing characterised by great resistance to abrasion and kinks. Two lengths of tubing are fused together into a tubing pair. For fitting, the paired tubing is separated as required at both ends.



Operating and environmental conditions		
Temperature-dependent operating pressure	[bar]	−0.95 ... +10 → graph
Operating medium	Compressed air to ISO 8573-1:2010 [7:--:-] Water as per manufacturer's declaration ¹⁾	
Ambient temperature	[°C]	−35 ... +60
Suitability for use in the food industry ¹⁾	See supplementary material information	
Material fire test	UL94 HB	
Certification ¹⁾	German Technical Control Board (TÜV)	
Tubing characteristics	Suitability for energy chains in applications with high cycle rates	
Tubing test conditions	Suitability for energy chains: > 5 million cycles to Festo standard 942021	

1) Additional information www.festo.com/catalogue/... → Support/Downloads.

Operating pressure p as a function of temperature t



Accessories

Type	→ Internet	
	Recommended fitting	
	• Push-in fitting QS	qs
	• Push-in fitting NPQH	npqh
	• Push-in fitting NPQR	npqr
	Well suited	
	• Push-in fitting CRQS	crqs
	• Push-in fitting NPQP	npqp
	• Push-in fitting NPQM	npqm
	• Click fitting NPKA ¹⁾	npka
	• Fitting NPCK	npck
	• Quick connector CK ²⁾	ck
Limited suitability		
• Push-in fitting QS-V0	qs-v0	

1) For O.D. 6 mm only

2) For O.D. 4/6/8 mm only

Materials	
Shore hardness	D 52 ±3
Tubing	TPE-U(PU)
Note on materials	RoHS-compliant
	Free of copper and PTFE

Datasheet

Dimensions and ordering data								
O.D.	I.D.	Min. bending radius	Flow-relevant bending radius	Weight	Colour	Part no.	Type	PU ¹⁾
[mm]	[mm]	[mm]	[mm]	[kg/m]				[m]
4	2.6	8	16	0.017	blue/black	197396	PUN-H-4x0.75-DUO	50
6	4	10	26	0.0366		197397	PUN-H-6x1-DUO	50
8	5.7	21	37	0.0574		197398	PUN-H-8x1.25-DUO	1 ... 50
10	7	28	52	0.093		197399	PUN-H-10x1.5-DUO	1 ... 50

1) Packaging unit
Can only be ordered by the metre.

Type codes

001	Series
PUN	Plastic tubing, polyurethane

002	Alternative material characteristic
V0	Flame-retardant

003	Pipe/tubing O.D. x wall thickness
4x1	4x1 mm
6x1	6x1 mm
6x2	6x2 mm
8x1,25	8x1.25 mm
8x2	8x2 mm
10x1,5	10x1.5 mm
10x2	10x2 mm
12x2	12x2 mm
14x2	14x2 mm
16x2	16x2 mm
16x2,5	16x2.5 mm

004	Colour
SW	Black
BL	Blue
RT	Red
GN	Green
GE	Yellow
BR	Brown
WS	White

005	Version
C	Broader wall thickness

Datasheet

Plastic tubing PUN-V0


Highly flexible single-sheath plastic tubing, flame-retardant

For use in the close vicinity of welding applications



Note

As this tubing is flame retardant, the colours differ from the standard colours.




Operating and environmental conditions

Temperature-dependent operating pressure	[bar]	-0.95 ... +10 → graph
Operating medium		Compressed air to ISO 8573-1:2010 [7:-:-] Water as per manufacturer's declaration ¹⁾
Ambient temperature	[°C]	-35 ... +60
Fire test ¹⁾		DIN 5510-2 S4/SR2/ST2
Material fire test		UL94 V-0 (for test specimen 3 mm thick) UL94 V-2 (for test specimen 0.75 mm thick)
Certification		German Technical Control Board (TÜV)
Tubing characteristics		Suitability for energy chains in applications with high cycle rates
Tubing test conditions		Suitability for energy chains: > 5 million cycles to Festo standard 942021

1) Additional information www.festo.com/catalogue/... → Support/Downloads.

Operating pressure p as a function of temperature t



Accessories

Type	→ Internet
	Recommended fitting
	• Push-in fitting NPQM ¹⁾ npqm
	Well suited
	• Push-in fitting CRQS crqs
	• Push-in fitting NPQH ¹⁾ npqh
	• Push-in fitting NPQR ¹⁾ npqr
	• Fitting NPCK ²⁾ npck
	• Quick connector CK ³⁾ ck
	Limited suitability
	• Push-in fitting QS qs
	• Push-in fitting QS-V0 ¹⁾ qs-v0
	• Push-in fitting NPQP ¹⁾ npqp
	• Click fitting NPKA ⁴⁾ npka
	• Barbed fitting CN ³⁾ cn

1) Not for O.D. 16 mm

2) For O.D. 6/8/10 mm only

3) For O.D. 6/8 mm only

4) For O.D. 6 mm only



Note

Greater force is required when assembling the fittings CK/CN.

Materials

Shore hardness	D 54 ±3
Tubing	TPE-U(PU)
Note on materials	RoHS-compliant
	Free of copper and PTFE

Datasheet

Dimensions and ordering data								
O.D.	I.D.	Min. bending radius	Flow-relevant bending radius	Weight	Colour	Part no.	Type	pU ¹⁾
[mm]	[mm]	[mm]	[mm]	[kg/m]				[m]
6	4	12	26.5	0.02	black	525438	PUN-V0-6x1-SW	1 ... 50
					blue	525442	PUN-V0-6x1-BL	1 ... 50
					green	525446	PUN-V0-6x1-GN	1 ... 50
					red	525450	PUN-V0-6x1-RT	1 ... 50
					white	525454	PUN-V0-6x1-WS	1 ... 50
					yellow	525458	PUN-V0-6x1-GE	1 ... 50
					brown	525462	PUN-V0-6x1-BR	1 ... 50
8	5.7	18	37	0.031	black	525439	PUN-V0-8x1.25-SW	1 ... 50
					blue	525443	PUN-V0-8x1.25-BL	1 ... 50
					green	525447	PUN-V0-8x1.25-GN	1 ... 50
					red	525451	PUN-V0-8x1.25-RT	1 ... 50
					white	525455	PUN-V0-8x1.25-WS	1 ... 50
					yellow	525459	PUN-V0-8x1.25-GE	1 ... 50
					brown	525463	PUN-V0-8x1.25-BR	1 ... 50
10	7	20	54	0.051	black	525440	PUN-V0-10x1.5-SW	1 ... 50
					blue	525444	PUN-V0-10x1.5-BL	1 ... 50
					green	525448	PUN-V0-10x1.5-GN	1 ... 50
					red	525452	PUN-V0-10x1.5-RT	1 ... 50
					white	525456	PUN-V0-10x1.5-WS	1 ... 50
					yellow	525460	PUN-V0-10x1.5-GE	1 ... 50
					brown	525464	PUN-V0-10x1.5-BR	1 ... 50
16	11.8	50	90	0.122	black	570767	PUN-V0-16x2-SW	1 ... 50
					blue	570768	PUN-V0-16x2-BL	1 ... 50


1) Packaging unit
Can only be ordered by the metre.

Datasheet

Plastic tubing PUN-V0-C


Highly flexible single-sheath plastic tubing, flame-retardant

For use in the immediate vicinity of welding applications.



Note

As this tubing is flame retardant, the colours differ from the standard colours.




Operating and environmental conditions

Type	PUN-V0-4	PUN-V0-6	PUN-V0-8	PUN-V0-10	PUN-V0-12	PUN-V0-14	PUN-V0-16
Temperature-dependent operating pressure [bar]	-0.95 ... +10 → graph	-0.95 ... +30 ¹⁾ → graph	-0.95 ... +20 ¹⁾ → graph	-0.95 ... +16 ¹⁾ → graph	-0.95 ... +10 → graph	-0.95 ... +9 → graph	-0.95 ... +10 → graph
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-] Water as per manufacturer's declaration ²⁾						
Ambient temperature [°C]	-35 ... +60						
Fire test ²⁾	DIN 5510-2 S3/SR2/ST1						
Material fire test	UL94 V-0 (for test specimen 3 mm thick) UL94 V-2 (for test specimen 0.75 mm thick)						
Certification ²⁾	German Technical Control Board (TÜV)						
Tubing characteristics	Suitability for energy chains in applications with high cycle rates						
Tubing test conditions	Suitability for energy chains: > 5 million cycles to Festo standard 942021						

1) Limited to 10 bar for applications involving welding spatter.

2) Additional information www.festo.com/catalogue/... → Support/Downloads.

Operating pressure p as a function of temperature t



— PUN-V0-...-C

- - - PUN-V0-14x2-...-C

For applications without welding spatter

— — — PUN-V0-6x2-...-C

..... PUN-V0-8x2-...-C

- . - . - PUN-V0-10x2-...-C

Accessories

Type	→ Internet
	Recommended fitting
	• Push-in fitting NPQH ¹⁾ npqh
	Well suited
	• Push-in fitting CRQS ²⁾ crqs
	• Push-in fitting NPQM ¹⁾ npqm
	• Push-in fitting NPQR ³⁾ npqr
	Limited suitability
	• Push-in fitting QS ²⁾ qs
	• Push-in fitting QS-V0 ³⁾ qs-v0
	• Push-in fitting NPQP ³⁾ npqp

1) Not for O.D. 16 mm

3) Not for O.D. 14/16 mm

2) Not for O.D. 14 mm

Materials

Shore hardness	D 54 ±3
Tubing	TPE-U(PU)
Note on materials	RoHS-compliant
	Free of copper and PTFE

Datasheet

Dimensions and ordering data								
O.D.	I.D.	Min. bending radius	Flow-relevant bending radius	Weight	Colour	Part no.	Type	PJ ¹⁾
[mm]	[mm]	[mm]	[mm]	[kg/m]				[m]
4	2	10	20	0.012	black	570349	PUN-V0-4x1-SW-C	1 ... 50
					blue	570350	PUN-V0-4x1-BL-C	1 ... 50
6	2	7	24	0.032	black	561698	PUN-V0-6x2-SW-C	1 ... 50
					blue	561702	PUN-V0-6x2-BL-C	1 ... 50
					green	561706	PUN-V0-6x2-GN-C	1 ... 50
					red	561710	PUN-V0-6x2-RT-C	1 ... 50
					white	561714	PUN-V0-6x2-WS-C	1 ... 50
					yellow	561718	PUN-V0-6x2-GE-C	1 ... 50
					brown	561722	PUN-V0-6x2-BR-C	1 ... 50
8	4	9	35	0.049	black	561699	PUN-V0-8x2-SW-C	1 ... 50
					blue	561703	PUN-V0-8x2-BL-C	1 ... 50
					green	561707	PUN-V0-8x2-GN-C	1 ... 50
					red	561711	PUN-V0-8x2-RT-C	1 ... 50
					white	561715	PUN-V0-8x2-WS-C	1 ... 50
					yellow	561719	PUN-V0-8x2-GE-C	1 ... 50
					brown	561723	PUN-V0-8x2-BR-C	1 ... 50
10	6	12	42	0.064	black	561700	PUN-V0-10x2-SW-C	1 ... 50
					blue	561704	PUN-V0-10x2-BL-C	1 ... 50
					green	561708	PUN-V0-10x2-GN-C	1 ... 50
					red	561712	PUN-V0-10x2-RT-C	1 ... 50
					white	561716	PUN-V0-10x2-WS-C	1 ... 50
					yellow	561720	PUN-V0-10x2-GE-C	1 ... 50
					brown	561724	PUN-V0-10x2-BR-C	1 ... 50
12	8	19	55	0.08	black	561701	PUN-V0-12x2-SW-C	1 ... 50
					blue	561705	PUN-V0-12x2-BL-C	1 ... 50
					green	561709	PUN-V0-12x2-GN-C	1 ... 50
					red	561713	PUN-V0-12x2-RT-C	1 ... 50
					white	561717	PUN-V0-12x2-WS-C	1 ... 50
					yellow	561721	PUN-V0-12x2-GE-C	1 ... 50
					brown	561725	PUN-V0-12x2-BR-C	1 ... 50
14	9.8	45	70	0.096	black	570351	PUN-V0-14x2-SW-C	1 ... 50
					blue	570352	PUN-V0-14x2-BL-C	1 ... 50
16	11	50	90	0.147	black	570353	PUN-V0-16x2.5-SW-C	1 ... 50
					blue	570354	PUN-V0-16x2.5-BL-C	1 ... 50

1) Packaging unit
Can only be ordered by the metre.

Ordering data – Modular product system

Ordering table (minimum order quantity 3000 m with tubing O.D. < 8 mm, 1500 mm with tubing O.D. > 8 mm, rounded value 25 m)											
Size	3	4	6	8	10	12	14	16	Conditions	Code	Enter code
Module no.	553573										
Function	Polyurethane tubing, standard O.D.									PUN	PUN
Alternative material characteristic	Standard										
	Hydrolysis-resistant									-H	
	– Antistatic									-CM	
	– Flame-retardant									-VO	
	– Resistant to welding spatter									-VOC	
Tubing O.D. [mm]	3	–	–	–	–	–	–	–		-3	
	–	4	–	–	–	–	–	–		-4	
	–	–	6	–	–	–	–	–		-6	
	–	–	–	8	–	–	–	–		-8	
	–	–	–	–	10	–	–	–		-10	
	–	–	–	–	–	12	–	–		-12	
	–	–	–	–	–	–	14	–		-14	
	–	–	–	–	–	–	–	16		-16	
Colour	silver								[1] [2]	-SI	
	blue								[1] [3]	-BL	
	translucent blue								[4]	-TBL	
	black								[3]	-SW	
	translucent black								[4]	-TSW	
	yellow								[1]	-GE	
	translucent yellow								[4]	-TGE	
	green								[1]	-GN	
	translucent green								[4]	-TGN	
	red								[1]	-RT	
	translucent red								[4]	-TRT	
	brown								[1]	-BR	
	white								[1]	-WS	
	natural								[1] [3] [4]	-NT	
Labelling text (on request)	Standard										
	Customer-specific tubing inscription								[5]	-TXT	
Packaging unit [m]	25									-25	
	50									-50	
	100									-100	
	200									-200	
	300									-300	
	400									-400	
	500									-500	
	–									–	
Packaging	Cardboard box								[6]	-CB	
	Reel								[7]	-HA	

[1] **SI, BL, GE, GN, RT, BR, WS, NT**

Not with alternative material characteristic CM

[2] **SI** Not with alternative material characteristic VO, VOC[3] **BL, SW, NT** In combination with alternative material characteristic H: food-safe[4] **TBL, TSW, TGE, TGN, TRT, NT**
Only with alternative material characteristic H[5] **TXT** Not in the online shop.

Festo logo, order code, TÜV, operating pressure, dimensions omitted

[6] **CB** Only with packaging unit 25, 50[7] **HA** Not in packaging unit 25, 50
Not with alternative material characteristic VO, VOC, CM