

Pressure regulators LR/LRS/LRB/LRBS, D series









FESTO



Pressure regulators LR/LRS/LRB/LRBS, D series, metal design

FESTO

Product range overview D series service units, metal design

Type	Size	Pneumatic connection										Pressure regulation range [bar]			Grade of filtration [µm]				
		M5	M7	G1/8	G1/4	G3/8	G1/2	G3/4	G1	QS4	QS6	0.5 ...	0.5 ...	2.5 ...	0.01	1	5	40	
Service units																			
FRC/FRCS		Micro	■	■	■	–	–	–	–	–	■	■	■	–	–	–	–	■	–
		Mini	–	–	■	■	■	–	–	–	–	■	■	–	–	–	–	■	■
		Midi	–	–	–	■	■	■	■	–	–	■	■	–	–	–	–	■	■
		Maxi	–	–	–	–	–	■	■	■	–	–	■	■	–	–	–	■	■
Service unit combinations																			
FRC-K		Micro	–																
		Mini	–	–	■	■	–	–	–	–	–	–	■	■	–	–	–	■	
		Midi	–	–	–	■	■	■	–	–	–	–	■	■	–	–	–	■	
		Maxi	–	–	–	–	–	■	■	–	–	–	■	■	–	–	–	■	
LFR-K LFRS-K		Micro	–																
		Mini	–	–	■	■	–	–	–	–	–	–	■	■	–	–	–	■	
		Midi	–	–	–	■	■	■	–	–	–	–	■	■	–	–	–	■	
		Maxi	–	–	–	–	–	■	■	–	–	–	■	■	–	–	–	■	
Individual devices																			
Filter regulators LFR/LFRS		Micro	■	■	■	–	–	–	–	–	■	■	■	–	–	–	–	■	–
		Mini	–	–	■	■	■	–	–	–	–	■	■	–	–	–	–	■	■
		Midi	–	–	–	■	■	■	■	–	–	■	■	–	–	–	–	■	■
		Maxi	–	–	–	–	–	■	■	■	–	–	■	■	–	–	–	■	■
Filters LF		Micro	■	■	■	–	–	–	–	–	■	■	–	–	–	–	–	■	–
		Mini	–	–	■	■	■	–	–	–	–	–	–	–	–	–	–	■	■
		Midi	–	–	–	■	■	■	■	–	–	–	–	–	–	–	–	■	■
		Maxi	–	–	–	–	–	■	■	■	–	–	–	–	–	–	–	■	■
Fine and micro filters LFMA/LFMB		Micro	–																
		Mini	–	–	■	■	■	–	–	–	–	–	–	–	■	■	–	–	
		Midi	–	–	–	■	■	■	■	–	–	–	–	–	■	■	–	–	
		Maxi	–	–	–	–	–	■	■	■	–	–	–	–	■	■	–	–	
Active carbon filters LFX		Micro	–																
		Mini	–	–	■	■	■	–	–	–	–	–	–	–	–	–	–	–	
		Midi	–	–	–	■	■	■	■	–	–	–	–	–	–	–	–	–	
		Maxi	–	–	–	–	–	■	■	■	–	–	–	–	–	–	–	–	
Filter combinations LFMBA		Micro	–																
		Mini	–	–	■	■	■	–	–	–	–	–	–	–	■	■	–	–	
		Midi	–	–	–	■	■	■	■	–	–	–	–	–	■	■	–	–	
		Maxi	–	–	–	–	–	■	■	■	–	–	–	–	■	■	–	–	
Pressure regulators LR/LRS		Micro	■	■	■	–	–	–	–	–	■	■	■	–	–	–	–	–	
		Mini	–	–	■	■	■	–	–	–	–	■	■	–	–	–	–	–	
		Midi	–	–	–	■	■	■	■	–	–	■	■	–	–	–	–	–	
		Maxi	–	–	–	–	–	■	■	■	–	–	■	■	–	–	–	–	

Pressure regulators LR/LRS/LRB/LRBS, D series, metal design

FESTO











Product range overview D series service units, metal design

Type	Size	Bowl guard		Condensate drain			Pressure indication		Actuator lock		Supply voltage			Options			→ Page/ Internet
		Metal bowl guard	Plastic bowl	Manual rotary	Semi-automatic	Fully automatic	With pressure gauge	Without pressure gauge	Rotary knob with detent	Rotary knob with integrated lock	24 V DC	110 V AC	230 V AC	Directly actuated pressure regulator with integrated return flow function	Pilot actuated pressure regulator with integrated return flow function	Differential pressure indicator	
Service units																	
FRC/FRCS	Micro	-	■	■	■	-	■	■	■	-	-	-	-	-	-	-	frc
	Mini	■	-	■	-	■	■	■	■	■	-	-	-	-	-	-	
	Midi	■	-	■	-	■	■	■	■	■	-	-	-	-	-	-	
	Maxi	■	-	■	-	■	■	■	■	■	-	-	-	■	■	-	
Service unit combinations																	
FRC-K	Micro																frc
	Mini	■	-	■	-	■	■	-	■	-	■	-	-	-	-	-	
	Midi	■	-	■	-	■	■	-	■	-	■	-	-	-	-	-	
	Maxi	■	-	■	-	■	■	-	■	-	■	-	-	■	■	-	
LFR-K LFRS-K	Micro																lfr
	Mini	■	-	■	-	■	■	-	■	■	■	-	-	-	-	-	
	Midi	■	-	■	-	■	■	-	■	■	■	-	-	-	-	-	
	Maxi	■	-	■	-	■	■	-	■	■	■	-	-	■	■	-	
Individual devices																	
Filter regulators LFR/LFRS	Micro	-	■	■	■	-	■	■	■	-	-	-	-	-	-	-	lfr
	Mini	■	-	■	-	■	■	■	■	■	-	-	-	-	-	-	
	Midi	■	-	■	-	■	■	■	■	■	-	-	-	-	-	-	
	Maxi	■	-	■	-	■	■	■	■	■	-	-	-	■	■	-	
Filters LF	Micro	-	■	■	■	-	-	-	-	-	-	-	-	-	-	-	lf
	Mini	■	-	■	-	■	-	-	-	-	-	-	-	-	-	-	
	Midi	■	-	■	-	■	-	-	-	-	-	-	-	-	-	-	
	Maxi	■	-	■	-	■	-	-	-	-	-	-	-	-	-	-	
Fine and micro filters LFMA/LFMB	Micro																lfma, lfmb
	Mini	■	-	■	-	■	-	-	-	-	-	-	-	-	-	■	
	Midi	■	-	■	-	■	-	-	-	-	-	-	-	-	-	■	
	Maxi	■	-	■	-	■	-	-	-	-	-	-	-	-	-	■	
Active carbon filters LFX	Micro																lfx
	Mini	■	-	-	-	-	-	-	-	-	-	-	-	-	-	-	
	Midi	■	-	-	-	-	-	-	-	-	-	-	-	-	-	-	
	Maxi	■	-	-	-	-	-	-	-	-	-	-	-	-	-	-	
Filter combinations LFMBA	Micro																lfmba
	Mini	■	-	■	-	■	-	-	-	-	-	-	-	-	-	■	
	Midi	■	-	■	-	■	-	-	-	-	-	-	-	-	-	■	
	Maxi	■	-	■	-	■	-	-	-	-	-	-	-	-	-	■	
Pressure regulators LR/LRS	Micro	-	-	-	-	-	■	■	■	-	-	-	-	-	-	-	6
	Mini	-	-	-	-	-	■	■	■	■	-	-	-	■	-	-	
	Midi	-	-	-	-	-	■	■	■	■	-	-	-	■	-	-	
	Maxi	-	-	-	-	-	■	■	■	■	-	-	-	■	■	-	

Pressure regulators LR/LRS/LRB/LRBS, D series, metal design

FESTO

Product range overview D series service units, metal design

Type		Size	Pneumatic connection										Pressure regulation range [bar]	
			M5	M7	G1/8	G1/4	G3/8	G1/2	G3/4	G1	QS4	QS6	0.5 ... 7	0.5 ... 12
Individual devices														
Pressure regulators LRB/LRBS		Micro	—											
		Mini	—	—	—	■	—	—	—	—	—	—	■	■
		Midi	—	—	—	—	■	—	—	—	—	—	■	■
		Maxi	—											
Pressure regulator combinations LRB-K		Micro	—											
		Mini	—	—	—	■	■	—	—	—	—	—	■	■
		Midi	—	—	—	—	■	■	—	—	—	—	■	■
		Maxi	—											
Lubricators LOE		Micro	■	■	■	—	—	—	—	—	■	■	—	—
		Mini	—	—	■	■	■	—	—	—	—	—	—	—
		Midi	—	—	—	■	■	■	■	—	—	—	—	—
		Maxi	—	—	—	—	—	■	■	■	—	—	—	—
On-off valves HE		Micro	—											
		Mini	—	—	■	■	■	—	—	—	—	—	—	—
		Midi	—	—	—	■	■	■	■	—	—	—	—	—
		Maxi	—	—	—	—	—	■	■	■	—	—	—	—
On-off valves, electrical HEE		Micro	—											
		Mini	—	—	■	■	■	—	—	—	—	—	—	—
		Midi	—	—	—	■	■	■	■	—	—	—	—	—
		Maxi	—	—	—	—	—	■	■	■	—	—	—	—
On-off valves, pneumatic HEP		Micro	—											
		Mini	—	—	■	■	■	—	—	—	—	—	—	—
		Midi	—	—	—	■	■	■	■	—	—	—	—	—
		Maxi	—	—	—	—	—	■	■	■	—	—	—	—
Soft-start valves HEL		Micro	—											
		Mini	—	—	■	■	■	—	—	—	—	—	—	—
		Midi	—	—	—	■	■	■	■	—	—	—	—	—
		Maxi	—	—	—	—	—	■	■	■	—	—	—	—
Membrane air dryers LDM1		Micro	—											
		Mini	—											
		Midi	—											
		Maxi	—	—	—	—	—	■	■	■	—	—	—	—
Branching modules FRM		Micro	—											
		Mini	—	—	■	■	■	—	—	—	—	—	—	—
		Midi	—	—	—	■	■	■	■	—	—	—	—	—
		Maxi	—	—	—	—	—	■	■	■	—	—	—	—
Distributor block FRZ		Micro	—	—	—	—	—	—	—	—	—	—	—	
		Mini	—	—	—	—	—	—	—	—	—	—	—	
		Midi	—	—	—	—	—	—	—	—	—	—	—	
		Maxi	—	—	—	—	—	—	—	—	—	—	—	

Pressure regulators LR/LRS/LRB/LRBS, D series, metal design

FESTO

Product range overview D series service units, metal design

Type	Size	Bowl guard		Pressure indication		Actuator lock		Supply voltage			Options		→ Page/ Internet
		Metal bowl guard	Plastic bowl	With pressure gauge	Without pressure gauge	Rotary knob with detent	Rotary knob with integrated lock	24 V DC	110 V AC	230 V AC	Non-return function	Pressure switch	
Individual devices													
Pressure regulators LRB/LRBS	Micro	-											20
	Mini	-	-	-	■	■	■	-	-	-	-	-	
	Midi	-	-	-	■	■	■	-	-	-	-	-	
	Maxi	-											
Pressure regulator combinations LRB-K	Micro	-											28
	Mini	-	-	-	■	■	-	-	-	-	-	-	
	Midi	-	-	-	■	■	-	-	-	-	-	-	
	Maxi	-											
Lubricators LOE	Micro	-	■	-	■	-	-	-	-	-	-	-	loe
	Mini	■	-	-	■	-	-	-	-	-	-	-	
	Midi	■	-	-	■	-	-	-	-	-	-	-	
	Maxi	■	-	-	■	-	-	-	-	-	-	-	
On-off valves HE	Micro	-											he
	Mini	-	-	-	■	■	-	-	-	-	-	-	
	Midi	-	-	-	■	■	-	-	-	-	-	-	
	Maxi	-	-	-	■	■	-	-	-	-	-	-	
On-off valves, electrical HEE	Micro	-											hee
	Mini	-	-	-	■	-	-	■	■	■	-	-	
	Midi	-	-	-	■	-	-	■	■	■	-	-	
	Maxi	-	-	-	■	-	-	■	■	■	-	-	
On-off valves, pneumatic HEP	Micro	-											hep
	Mini	-	-	-	■	-	-	-	-	-	-	-	
	Midi	-	-	-	■	-	-	-	-	-	-	-	
	Maxi	-	-	-	■	-	-	-	-	-	-	-	
Soft-start valves HEL	Micro	-											hel
	Mini	-	-	-	■	-	-	-	-	-	-	-	
	Midi	-	-	-	■	-	-	-	-	-	-	-	
	Maxi	-	-	-	■	-	-	-	-	-	-	-	
Membrane air dryers LDM1	Micro	-											ldm1
	Mini	-											
	Midi	-											
	Maxi	■	-	-	■	-	-	-	-	-	-	-	
Branching modules FRM	Micro	-											frm
	Mini	-	-	-	■	-	-	-	-	-	■	■	
	Midi	-	-	-	■	-	-	-	-	-	■	■	
	Maxi	-	-	-	■	-	-	-	-	-	■	■	
Distributor block FRZ	Micro	-	-	-	■	-	-	-	-	-	-	-	frz
	Mini	-	-	-	■	-	-	-	-	-	-	-	
	Midi	-	-	-	■	-	-	-	-	-	-	-	
	Maxi	-	-	-	■	-	-	-	-	-	-	-	

Pressure regulators LR/LRS, D series, metal design



FESTO

Peripherals overview

Micro

Individual unit with connection plates,
connection size G $\frac{1}{8}$, QS-4 or QS-6

Individual unit without connection plates, for service unit combination
connection thread M5 or M7 in housing



Mounting attachments and accessories					
	Individual unit		Combination		→ Page/ Internet
	with connection plates	without connection plates	with connection plates	without connection plates	
1 Mounting bracket HFOE	■	■	■	■	hfoe-d
2 Connecting plate kit PBL	–	■	–	■	pbl
3 Mounting bracket HRS	■	■	■	■	hrs-d
4 Pressure gauge MA-27	■	■	■	■	52

Pressure regulators LR/LRS, D series, metal design


Peripherals overview

FESTO

Mini/Midi/Maxi

Pressure regulator LR

Pressure regulator LRS, lockable



Mounting attachments and accessories

	Rotary knob with detent	Rotary knob, lockable	→ Page/ Internet
1 Mounting bracket HFOE	■	■	hfoe-d
2 Regulator lock LRVS	■	—	lrvs-d
3 Padlock LRVS-D	■	—	lrvs-d
4 Mounting bracket HR-D	■	■	hr-d
5 Pressure gauge MA/PAGN	■	■	52
6 Knurled nut (included in scope of delivery) HMR	■	■	—

Pressure regulators LR/LRS, D series, metal design

FESTO

Type codes

		LR	-	1/2	-	D	-	7	-	0	-	DI	-	MAXI	-	
--	--	----	---	-----	---	---	---	---	---	---	---	----	---	------	---	--

Basic function	
LR	Pressure regulator
LRS	Pressure regulator, lockable

Pneumatic connection	
MICRO (LR only)	
M5	Connecting thread M5 in housing
M7	Connecting thread M7 in housing
1/8	Connecting plates with connecting thread G1/8
QS4	Connecting plates with push-in connector QS-4
QS6	Connecting plates with push-in connector QS-6
MINI	
1/8	Connecting plates with connecting thread G1/8
1/4	Connecting plates with connecting thread G1/4
3/8	Connecting plates with connecting thread G3/8
MIDI	
1/4	Connecting plates with connecting thread G1/4
3/8	Connecting plates with connecting thread G3/8
1/2	Connecting plates with connecting thread G1/2
3/4	Connecting plates with connecting thread G3/4
MAXI	
1/2	Connecting plates with connecting thread G1/2
3/4	Connecting plates with connecting thread G3/4
1	Connecting plates with connecting thread G1

Series	
D	Series

Pressure regulation range	
7	0.5 ... 7 bar (0.05 ... 0.7 MPa)
MINI/MIDI/MAXI	
	0.5 ... 12 bar (0.05 ... 1.2 MPa)

Pressure gauge	
	With pressure gauge
0	Without pressure gauge

Functions (optional)	
MINI/MIDI	
I	With integrated return flow function
MAXI	
DI	Directly actuated pressure regulator with integrated return flow function

Size	
MICRO	Grid dimension 25 mm (without connecting plates)
MINI	Grid dimension 40 mm (without connecting plates)
MIDI	Grid dimension 55 mm (without connecting plates)
MAXI	Grid dimension 66 mm (without connecting plates)


Display unit of the pressure gauge	
	Outer scale in bar
MPa	Outer scale in MPa

Pressure regulators LR/LRS, D series, metal design


FESTO

Technical data

LR/LRS
with pressure gauge



LR/LRS-...-I-MINI/MIDI,
LR/LRS-...-DI-MAXI
with pressure gauge



-  - Flow rate
120 ... 12,500 l/min
-  - Temperature range
-10 ... +60 °C
-  - Operating pressure
1 ... 16 bar (0.1 ... 1.6 MPa)



- Also suitable for front panel mounting
- Two pressure gauge connections for different fitting options
- Good regulating characteristics with minimal pressure hysteresis
- High flow rate
- Two pressure regulation ranges:
0.5 ... 7 bar (0.05 ... 0.7 MPa) and
0.5 ... 12 bar (0.05 ... 1.2 MPa)
- Setting values are secured by locking the rotary knob
- Return flow option for venting from output 2 to input 1
- Pressure sensor (optional) → 52

General technical data				
Size	Micro	Mini	Midi	Maxi
Pneumatic connection 1, 2 ¹⁾	M5 ²⁾ , M7 ²⁾ , G1/8, QS-4 ³⁾ , QS-6 ³⁾	G1/8, G1/4, G3/8	G1/4, G3/8, G1/2, G3/4	G1/2, G3/4, G1
Constructional design	Directly actuated diaphragm regulator	Directly actuated diaphragm regulator		Pilot actuated piston regulator
				Directly actuated diaphragm regulator LR/LRS-...-DI
Regulating function	With secondary venting	Output pressure constant, with secondary venting, with primary pressure compensation, with return flow action ⁴⁾		Output pressure constant, with secondary venting, with primary pressure compensation ⁵⁾ , with return flow action ⁵⁾
Type of mounting	Via accessories			
	In-line installation			
	Front panel mounting			
Assembly position	Any			
Regulator lock	Rotary knob with detent			
	–	Rotary knob with integrated lock		
Pressure regulation range [bar]	0.5 ... 7 (0.05 ... 0.7 MPa)	0.5 ... 7 (0.05 ... 0.7 MPa)		
		0.5 ... 12 (0.05 ... 1.2 MPa)		
Max. hysteresis [bar]	0.3 (0.03 MPa)	0.2 (0.02 MPa)		0.4 (0.04 MPa)
Pressure indication	Via pressure gauge			
	M5 prepared	G1/8 prepared	G1/4 prepared	G1/4 prepared

1) Connecting plates with connecting thread

2) Without connecting plates, connecting thread in housing

3) Connecting plates with push-in connector

4) For the LR/LRS-...-I.

5) For the LR/LRS-...-DI.

-  - Note: This product conforms to ISO 1179-1 and to ISO 228-1

Pressure regulators LR/LRS, D series, metal design

FESTO

Technical data

Standard nominal flow rate $q_{nN}^{1)}$ [l/min]					
Size	Micro				
Pneumatic connection 1, 2	M5	M7	G $\frac{1}{8}$	QS-4	QS-6
Pressure	0.5 ... 7 bar	120	300	450	160
regulation range	(0.05 ... 0.7 MPa)				450

1) Measured at $p_1 = 10$ bar (1 MPa), $p_2 = 6$ bar (0.6 MPa) and $\Delta p = 1$ bar (0.1 MPa).

Standard nominal flow rate $q_{nN}^{1)}$ [l/min]											
Size	Mini			Midi				Maxi			
Pneumatic connection 1, 2	G $\frac{1}{8}$	G $\frac{1}{4}$	G $\frac{3}{8}$	G $\frac{1}{4}$	G $\frac{3}{8}$	G $\frac{1}{2}$	G $\frac{3}{4}$	G $\frac{1}{2}$	G $\frac{3}{4}$	G1	
Pressure	0.5 ... 7 bar	1,000	1,600	1,800	2,200	3,300	4,000	4,500	10,700	12,000	12,500
regulation range	(0.05 ... 0.7 MPa)								(7,300) ²⁾	(8,350) ²⁾	(8,400) ²⁾
	0.5 ... 12 bar (0.05 ... 1.2 MPa)	800	1,500	1,700	2,100	3,200	3,500	3,500	10,500	11,000	11,500
									(5,400) ²⁾	(6,800) ²⁾	(7,000) ²⁾

1) Measured at $p_1 = 10$ bar (1 MPa), $p_2 = 6$ bar (0.6 MPa) and $\Delta p = 1$ bar (0.1 MPa).

2) For the LR/LRS-...-DI.

Operating and environmental conditions				
Size	Micro	Mini	Midi	Maxi
Operating pressure [bar]	1 ... 10 (0.1 ... 1 MPa)		1 ... 16 (0.1 ... 1.6 MPa)	
Operating medium	Compressed air in accordance with ISO 8573-1:2010 [7:4:4]			
	Inert gases			
Note on operating/pilot medium	–	Operation with lubricated medium possible (in which case lubricated operation will always be required)		
Ambient temperature [°C]	–10 ... +60			
Temperature of medium [°C]	–10 ... +60			
Storage temperature [°C]	–10 ... +60			
Corrosion resistance class CRC ¹⁾	2			
Certification	Germanischer Lloyd			

1) Corrosion resistance class CRC 2 to Festo standard FN 940070

Moderate corrosion stress. Indoor applications in which condensation may occur. External visible parts with primarily decorative requirements for the surface and which are in direct contact with the ambient atmosphere typical for industrial applications.

Weight [g]					
Size	Micro		Mini	Midi	Maxi
	Connecting thread	Connecting plate			
With pressure gauge					
LR	90	110	350	720	1,200 (1,400) ¹⁾
LRS	–	–	520	1,250	1,290 (1,680) ¹⁾
Without pressure gauge					
LR	80	100	300	660	1,100 (1,330) ¹⁾
LRS	–	–	470	1,180	1,215 (1,610) ¹⁾

1) For the LR/LRS-...-DI.


Pressure regulators LR/LRS, D series, metal design

FESTO

Technical data

Materials


Sectional view




Size	Micro	Mini/Midi/Maxi	
		With pressure gauge	Without pressure gauge
1 Housing	Die-cast zinc	Die-cast zinc/aluminium	
2 Connecting plates	Wrought aluminium alloy	Die-cast zinc/aluminium	
3 Regulating knob	POM	PA	
4 Knurled nut	–	Aluminium	
5 Plug cap	PC	PC	
– Seals	NBR	NBR	
Note on materials	RoHS-compliant	RoHS-compliant	
	–	–	Free of copper and PTFE

Standard flow rate q_n as a function of the output pressure p_2


LR-M5-...-MICRO




LR-M7-...-MICRO B



LR-QS4-...-MICRO



LR-QS6-...-MICRO and LR-1/8-...-MICRO



Primary pressure $p_1 = 10$ bar (1 MPa)


Pressure regulators LR/LRS, D series, metal design

FESTO


Technical data

Standard flow rate q_n as a function of the output pressure p_2


LR/LRS-1/4-D-MINI




LR/LRS-1/2-D-MIDI




LR/LRS-1-D-MAXI



LR/LRS-1-D-DI-MAXI



Primary pressure $p_1 = 10 \text{ bar (1 MPa)}$



Note

In order to improve control behaviour, primary-pressure dependent internal air consumption is provided on the LR/LRS-...-MAXI.

Pressure regulators LR/LRS, D series, metal design


FESTO

Technical data

Dimensions

Download CAD data → www.festo.com

Micro



Type	B1	B2	D1	H1
Micro				
LR-M5-D-7-MICRO	25	-	M5	-
LR-M7-D-7-MICRO B			M7	
LR-1/8-D-7-MICRO	45	-	G1/8	-
LR-QS4-D-7-MICRO		~2.5	QS-4	~8
LR-QS6-D-7-MICRO			QS-6	~10

· || · Note: This product conforms to ISO 1179-1 and to ISO 228-1

Pressure regulators LR/LRS, D series, metal design


Technical data

FESTO

Dimensions

Download CAD data → www.festo.com

Mini/Midi/Maxi



Type	B1	B2	B3	B4	D1	D2 Ø	D3	D4	D5 Ø
Mini									
LR/LRS-1/8-D-(I)-MINI	64	52	40	76	G1/8	31	M4	M36x1.5	41
LR/LRS-1/4-D-(I)-MINI					G1/4				
LR/LRS-3/8-D-(I)-MINI					G3/8				
Midi									
LR/LRS-1/4-D-(I)-MIDI	85	70	55	95	G1/4	50	M5	M52x1.5	50
LR/LRS-3/8-D-(I)-MIDI					G3/8				
LR/LRS-1/2-D-(I)-MIDI					G1/2				
LR/LRS-3/4-D-(I)-MIDI					G3/4				
Maxi									
LR/LRS-1/2-D-MAXI	96	80	66	107	G1/2	31	M5	M36x1.5	50
LR/LRS-1/2-D-DI-MAXI						49		M52x1.5	
LR/LRS-3/4-D-MAXI					G3/4	31		M36x1.5	
LR/LRS-3/4-D-DI-MAXI						49		M52x1.5	
LR/LRS-1-D-MAXI	116	91			G1	31		M36x1.5	
LR/LRS-1-D-DI-MAXI						49		M52x1.5	

• Note: This product conforms to ISO 1179-1 and to ISO 228-1

Pressure regulators LR/LRS, D series, metal design

FESTO

Technical data

Type	H1	H2	L1	L4	L5 max.	L6	L7	T1	⊃ 1	⊃ 2
Mini										
LR/LRS-1⁄8-D-MINI	20	11	96	68	3	98	60	7	14	17
LR/LRS-1⁄4-D-MINI										
LR/LRS-3⁄8-D-MINI										
Midi										
LR/LRS-1⁄4-D-MIDI	32	22	135	99	5	130	60	8	14	36
LR/LRS-3⁄8-D-MIDI										
LR/LRS-1⁄2-D-MIDI										
LR/LRS-3⁄4-D-MIDI										
Maxi										
LR/LRS-1⁄2-D-MAXI	32	22	125	82	4	111	60	8	14	22
LR/LRS-1⁄2-D-DI-MAXI			148	105		135				
LR/LRS-3⁄4-D-MAXI			125	82		111				
LR/LRS-3⁄4-D-DI-MAXI			148	105		135				
LR/LRS-1-D-MAXI	40		125	82		111				
LR/LRS-1-D-DI-MAXI			148	105		135				

Ordering data		
Size	Connection	Pressure regulation range 0.5 ... 7 bar (0.05 ... 0.7 MPa)
		Part No. Type
With pressure gauge, outer scale in bar		
Micro	Without connecting plates, connecting thread in housing	
	M5	526261 LR-M5-D-7-MICRO
	M7	534180 LR-M7-D-7-MICRO-B
	Connecting plates with connecting thread	
	G1/8	526263 LR-1/8-D-7-MICRO
	Connecting plates with push-in connector	
	QS-4	526269 LR-QS4-D-7-MICRO
	QS-6	526271 LR-QS6-D-7-MICRO
Without pressure gauge		
Micro	Without connecting plates, connecting thread in housing	
	M5	526262 LR-M5-D-O-7-MICRO
	M7	534181 LR-M7-D-O-7-MICRO-B
	Connecting plates with connecting thread	
	G1/8	526264 LR-1/8-D-O-7-MICRO
	Connecting plates with push-in connector	
	QS-4	526270 LR-QS4-D-O-7-MICRO
	QS-6	526272 LR-QS6-D-O-7-MICRO

Pressure regulators LR/LRS, D series, metal design

FESTO

Technical data

Ordering data					
Rotary knob with detent, connecting plates with connecting thread					
Size	Connection	Pressure regulation range 0.5 ... 7 bar (0.05 ... 0.7 MPa)		Pressure regulation range 0.5 ... 12 bar (0.05 ... 1.2 MPa)	
		Part No.	Type	Part No.	Type
With pressure gauge, outer scale in bar, inner scale in psi					
Mini	G1/8	162582	LR-1/8-D-7-MINI	159624	LR-1/8-D-MINI
	G1/4	162583	LR-1/4-D-7-MINI	159625	LR-1/4-D-MINI
	G3/8	162584	LR-3/8-D-7-MINI	162580	LR-3/8-D-MINI
Midi	G1/4	186453	LR-1/4-D-7-MIDI	186451	LR-1/4-D-MIDI
	G3/8	162585	LR-3/8-D-7-MIDI	159580	LR-3/8-D-MIDI
	G1/2	162586	LR-1/2-D-7-MIDI	159581	LR-1/2-D-MIDI
	G3/4	162587	LR-3/4-D-7-MIDI	162581	LR-3/4-D-MIDI
Maxi	G1/2	186457	LR-1/2-D-7-MAXI	186455	LR-1/2-D-MAXI
	G3/4	162588	LR-3/4-D-7-MAXI	159626	LR-3/4-D-MAXI
	G1	162589	LR-1-D-7-MAXI	159627	LR-1-D-MAXI
With pressure gauge, outer scale in MPa, inner scale in bar					
Mini	G1/8	8002288	LR-1/8-D-7-MINI-MPA	8002274	LR-1/8-D-MINI-MPA
	G1/4	8002289	LR-1/4-D-7-MINI-MPA	8002275	LR-1/4-D-MINI-MPA
	G3/8	8002290	LR-3/8-D-7-MINI-MPA	8002286	LR-3/8-D-MINI-MPA
Midi	G1/4	8002369	LR-1/4-D-7-MIDI-MPA	8002368	LR-1/4-D-MIDI-MPA
	G3/8	8002291	LR-3/8-D-7-MIDI-MPA	8002256	LR-3/8-D-MIDI-MPA
	G1/2	8002292	LR-1/2-D-7-MIDI-MPA	8002257	LR-1/2-D-MIDI-MPA
	G3/4	8002293	LR-3/4-D-7-MIDI-MPA	8002287	LR-3/4-D-MIDI-MPA
Maxi	G1/2	8002371	LR-1/2-D-7-MAXI-MPA	8002370	LR-1/2-D-MAXI-MPA
	G3/4	8002294	LR-3/4-D-7-MAXI-MPA	8002276	LR-3/4-D-MAXI-MPA
	G1	8002295	LR-1-D-7-MAXI-MPA	8002277	LR-1-D-MAXI-MPA
Without pressure gauge					
Mini	G1/8	162598	LR-1/8-D-7-O-MINI ¹⁾	162590	LR-1/8-D-O-MINI ¹⁾
	G1/4	162599	LR-1/4-D-7-O-MINI ¹⁾	162591	LR-1/4-D-O-MINI ¹⁾
	G3/8	162600	LR-3/8-D-7-O-MINI ¹⁾	162592	LR-3/8-D-O-MINI ¹⁾
Midi	G1/4	186454	LR-1/4-D-7-O-MIDI ¹⁾	186452	LR-1/4-D-O-MIDI ¹⁾
	G3/8	162601	LR-3/8-D-7-O-MIDI ¹⁾	162593	LR-3/8-D-O-MIDI ¹⁾
	G1/2	162602	LR-1/2-D-7-O-MIDI ¹⁾	162594	LR-1/2-D-O-MIDI ¹⁾
	G3/4	162603	LR-3/4-D-7-O-MIDI ¹⁾	162595	LR-3/4-D-O-MIDI ¹⁾
Maxi	G1/2	186458	LR-1/2-D-7-O-MAXI ¹⁾	186456	LR-1/2-D-O-MAXI ¹⁾
	G3/4	162604	LR-3/4-D-7-O-MAXI ¹⁾	162596	LR-3/4-D-O-MAXI ¹⁾
	G1	162605	LR-1-D-7-O-MAXI ¹⁾	162597	LR-1-D-O-MAXI ¹⁾

1) Free of copper and PTFE

Pressure regulators LR/LRS, D series, metal design

Technical data

FESTO

Ordering data					
With integrated return flow function, rotary knob with detent, connecting plates with connecting thread					
Size	Connection	Pressure regulation range 0.5 ... 7 bar (0.05 ... 0.7 MPa)		Pressure regulation range 0.5 ... 12 bar (0.05 ... 1.2 MPa)	
		Part No.	Type	Part No.	Type
With pressure gauge, outer scale in bar, inner scale in psi					
Mini	G ¹ / ₈	192299	LR- ¹ / ₈ -D-7-I-MINI	192298	LR- ¹ / ₈ -D-I-MINI
	G ¹ / ₄	192301	LR- ¹ / ₄ -D-7-I-MINI	192300	LR- ¹ / ₄ -D-I-MINI
	G ³ / ₈	192303	LR- ³ / ₈ -D-7-I-MINI	192302	LR- ³ / ₈ -D-I-MINI
Midi	G ¹ / ₄	192311	LR- ¹ / ₄ -D-7-I-MIDI	192310	LR- ¹ / ₄ -D-I-MIDI
	G ³ / ₈	192313	LR- ³ / ₈ -D-7-I-MIDI	192312	LR- ³ / ₈ -D-I-MIDI
	G ¹ / ₂	192315	LR- ¹ / ₂ -D-7-I-MIDI	192314	LR- ¹ / ₂ -D-I-MIDI
	G ³ / ₄	192317	LR- ³ / ₄ -D-7-I-MIDI	192316	LR- ³ / ₄ -D-I-MIDI
With pressure gauge, outer scale in MPa, inner scale in bar					
Mini	G ¹ / ₈	8002389	LR- ¹ / ₈ -D-7-I-MINI-MPA	8002388	LR- ¹ / ₈ -D-I-MINI-MPA
	G ¹ / ₄	8002391	LR- ¹ / ₄ -D-7-I-MINI-MPA	8002390	LR- ¹ / ₄ -D-I-MINI-MPA
	G ³ / ₈	8002393	LR- ³ / ₈ -D-7-I-MINI-MPA	8002392	LR- ³ / ₈ -D-I-MINI-MPA
Midi	G ¹ / ₄	8037017	LR- ¹ / ₄ -D-7-I-MIDI-MPA	8002394	LR- ¹ / ₄ -D-I-MIDI-MPA
	G ³ / ₈	8002395	LR- ³ / ₈ -D-7-I-MIDI-MPA	8037018	LR- ³ / ₈ -D-I-MIDI-MPA
	G ¹ / ₂	8037019	LR- ¹ / ₂ -D-7-I-MIDI-MPA	8002396	LR- ¹ / ₂ -D-I-MIDI-MPA
	G ³ / ₄	—	—	8002397	LR- ³ / ₄ -D-I-MIDI-MPA
Without pressure gauge					
Mini	G ¹ / ₈	192305	LR- ¹ / ₈ -D-7-O-I-MINI ¹⁾	192304	LR- ¹ / ₈ -D-O-I-MINI ¹⁾
	G ¹ / ₄	192307	LR- ¹ / ₄ -D-7-O-I-MINI ¹⁾	192306	LR- ¹ / ₄ -D-O-I-MINI ¹⁾
	G ³ / ₈	192309	LR- ³ / ₈ -D-7-O-I-MINI ¹⁾	192308	LR- ³ / ₈ -D-O-I-MINI ¹⁾
Midi	G ¹ / ₄	192319	LR- ¹ / ₄ -D-7-O-I-MIDI ¹⁾	192318	LR- ¹ / ₄ -D-O-I-MIDI ¹⁾
	G ³ / ₈	192321	LR- ³ / ₈ -D-7-O-I-MIDI ¹⁾	192320	LR- ³ / ₈ -D-O-I-MIDI ¹⁾
	G ¹ / ₂	192323	LR- ¹ / ₂ -D-7-O-I-MIDI ¹⁾	192322	LR- ¹ / ₂ -D-O-I-MIDI ¹⁾
	G ³ / ₄	192325	LR- ³ / ₄ -D-7-O-I-MIDI ¹⁾	192324	LR- ³ / ₄ -D-O-I-MIDI ¹⁾

1) Free of copper and PTFE

Ordering data				
Directly actuated pressure regulator with integrated return flow function, rotary knob with detent, connecting plates with connecting thread				
Size	Connection	Pressure regulation range 0.5 ... 7 bar (0.05 ... 0.7 MPa)		Pressure regulation range 0.5 ... 12 bar (0.05 ... 1.2 MPa)
		Part No.	Type	Part No. Type
With pressure gauge, outer scale in bar, inner scale in psi				
Maxi	G ¹ / ₂	192358	LR- ¹ / ₂ -D-7-DI-MAXI	192356 LR- ¹ / ₂ -D-DI-MAXI
	G ³ / ₄	192362	LR- ³ / ₄ -D-7-DI-MAXI	192360 LR- ³ / ₄ -D-DI-MAXI
	G1	192366	LR-1-D-7-DI-MAXI	192364 LR-1-D-DI-MAXI
With pressure gauge, outer scale in MPa, inner scale in bar				
Maxi	G ³ / ₄	–	–	8002398 LR- ³ / ₄ -D-DI-MAXI-MPA
Without pressure gauge				
Maxi	G ¹ / ₂	192359	LR- ¹ / ₂ -D-7-O-DI-MAXI ¹⁾	192357 LR- ¹ / ₂ -D-O-DI-MAXI ¹⁾
	G ³ / ₄	192363	LR- ³ / ₄ -D-7-O-DI-MAXI ¹⁾	192361 LR- ³ / ₄ -D-O-DI-MAXI ¹⁾
	G1	192367	LR-1-D-7-O-DI-MAXI ¹⁾	192365 LR-1-D-O-DI-MAXI ¹⁾

1) Free of copper and PTFE

Pressure regulators LR/LRS, D series, metal design

FESTO

Technical data

Ordering data					
Rotary knob with integrated lock, connecting plates with connecting thread					
Size	Connection	Pressure regulation range 0.5 ... 7 bar (0.05 ... 0.7 MPa)		Pressure regulation range 0.5 ... 12 bar (0.05 ... 1.2 MPa)	
		Part No.	Type	Part No.	Type
With pressure gauge, outer scale in bar, inner scale in psi					
Mini	G1/8	194606	LRS-1/8-D-7-MINI	194602	LRS-1/8-D-MINI
	G1/4	194614	LRS-1/4-D-7-MINI	194610	LRS-1/4-D-MINI
	G3/8	194622	LRS-3/8-D-7-MINI	194618	LRS-3/8-D-MINI
Midi	G1/4	194630	LRS-1/4-D-7-MIDI	194626	LRS-1/4-D-MIDI
	G3/8	194638	LRS-3/8-D-7-MIDI	194634	LRS-3/8-D-MIDI
	G1/2	194646	LRS-1/2-D-7-MIDI	194642	LRS-1/2-D-MIDI
	G3/4	194656	LRS-3/4-D-7-MIDI	194650	LRS-3/4-D-MIDI
Maxi	G1/2	194660	LRS-1/2-D-7-MAXI	194658	LRS-1/2-D-MAXI
	G3/4	194662	LRS-3/4-D-7-MAXI	194664	LRS-3/4-D-MAXI
	G1	194668	LRS-1-D-7-MAXI	194666	LRS-1-D-MAXI
With pressure gauge, outer scale in MPa, inner scale in bar					
Mini	G1/8	–	–	8037013	LRS-1/8-D-MINI-MPA
	G1/4	8037015	LRS-1/4-D-7-MINI-MPA	–	–
Without pressure gauge					
Mini	G1/8	194608	LRS-1/8-D-7-O-MINI	194604	LRS-1/8-D-O-MINI
	G1/4	194616	LRS-1/4-D-7-O-MINI	194612	LRS-1/4-D-O-MINI
	G3/8	194624	LRS-3/8-D-7-O-MINI	194620	LRS-3/8-D-O-MINI
Midi	G1/4	194632	LRS-1/4-D-7-O-MIDI	194628	LRS-1/4-D-O-MIDI
	G3/8	194640	LRS-3/8-D-7-O-MIDI	194636	LRS-3/8-D-O-MIDI
	G1/2	194648	LRS-1/2-D-7-O-MIDI	194644	LRS-1/2-D-O-MIDI
	G3/4	194654	LRS-3/4-D-7-O-MIDI	194652	LRS-3/4-D-O-MIDI
Maxi	G1/2	194661	LRS-1/2-D-7-O-MAXI	194659	LRS-1/2-D-O-MAXI
	G3/4	194663	LRS-3/4-D-7-O-MAXI	194665	LRS-3/4-D-O-MAXI
	G1	194669	LRS-1-D-7-O-MAXI	194667	LRS-1-D-O-MAXI

Ordering data					
With integrated return flow function, rotary knob with integrated lock, connecting plates with connecting thread					
Size	Connection	Pressure regulation range 0.5 ... 7 bar (0.05 ... 0.7 MPa)		Pressure regulation range 0.5 ... 12 bar (0.05 ... 1.2 MPa)	
		Part No.	Type	Part No.	Type
With pressure gauge, outer scale in bar, inner scale in psi					
Mini	G1/8	194607	LRS-1/8-D-7-I-MINI	194603	LRS-1/8-D-I-MINI
	G1/4	194615	LRS-1/4-D-7-I-MINI	194611	LRS-1/4-D-I-MINI
	G3/8	194623	LRS-3/8-D-7-I-MINI	194619	LRS-3/8-D-I-MINI
Midi	G1/4	194631	LRS-1/4-D-7-I-MIDI	194627	LRS-1/4-D-I-MIDI
	G3/8	194639	LRS-3/8-D-7-I-MIDI	194635	LRS-3/8-D-I-MIDI
	G1/2	194647	LRS-1/2-D-7-I-MIDI	194643	LRS-1/2-D-I-MIDI
	G3/4	194657	LRS-3/4-D-7-I-MIDI	194651	LRS-3/4-D-I-MIDI
With pressure gauge, outer scale in MPa, inner scale in bar					
Mini	G1/8	8037014	LRS-1/8-D-7-I-MINI-MPA	8002400	LRS-1/8-D-I-MINI-MPA
	G1/4	8037016	LRS-1/4-D-7-I-MINI-MPA	—	—
Without pressure gauge					
Mini	G1/8	194609	LRS-1/8-D-7-O-I-MINI	194605	LRS-1/8-D-O-I-MINI
	G1/4	194617	LRS-1/4-D-7-O-I-MINI	194613	LRS-1/4-D-O-I-MINI
	G3/8	194625	LRS-3/8-D-7-O-I-MINI	194621	LRS-3/8-D-O-I-MINI
Midi	G1/4	194633	LRS-1/4-D-7-O-I-MIDI	194629	LRS-1/4-D-O-I-MIDI
	G3/8	194641	LRS-3/8-D-7-O-I-MIDI	194637	LRS-3/8-D-O-I-MIDI
	G1/2	194649	LRS-1/2-D-7-O-I-MIDI	194645	LRS-1/2-D-O-I-MIDI
	G3/4	194655	LRS-3/4-D-7-O-I-MIDI	194653	LRS-3/4-D-O-I-MIDI

Pressure regulators LR/LRS, D series, metal design

FESTO

Technical data

Ordering data					
Directly actuated pressure regulator with integrated return flow function, rotary knob with integrated lock, connecting plates with connecting thread					
Size	Connection	Pressure regulation range 0.5 ... 7 bar (0.05 ... 0.7 MPa)		Pressure regulation range 0.5 ... 12 bar (0.05 ... 1.2 MPa)	
		Part No.	Type	Part No.	Type
With pressure gauge, outer scale in bar, inner scale in psi					
Maxi	G1½	194672	LRS-½-D-7-DI-MAXI	194670	LRS-½-D-DI-MAXI
	G¾	194676	LRS-¾-D-7-DI-MAXI	194674	LRS-¾-D-DI-MAXI
	G1	194680	LRS-1-D-7-DI-MAXI	194678	LRS-1-D-DI-MAXI
Without pressure gauge					
Maxi	G1½	194673	LRS-½-D-7-O-DI-MAXI	194671	LRS-½-D-O-DI-MAXI
	G¾	194677	LRS-¾-D-7-O-DI-MAXI	194675	LRS-¾-D-O-DI-MAXI
	G1	194681	LRS-1-D-7-O-DI-MAXI	194679	LRS-1-D-O-DI-MAXI


Pressure regulators LRB/LRBS, D series, metal design

Peripherals overview


FESTO

Mini/Midi

Pressure regulator LRB – pressure output at rear



Pressure regulator LRB – pressure output at front



Pressure regulators LRB/LRBS, D series, metal design

FESTO

Peripherals overview

Mounting attachments and accessories			
Pressure regulator LRB	Pressure output at rear	Pressure output at front	→ Page/ Internet
1 Mounting bracket HRB	■	–	hrb-d
2 Mounting bracket HFOE	–	■	hfoe-d
3 Connection plates LRBAS	■	■	lrbas
4 Adapter kit HRBC	■	■	hrbc-d
5 Mounting bracket HRBK	■ ¹⁾	–	hrbk-d
6 Regulator lock LRVS	■	■	lrvs-d
7 Padlock LRVS-D	■	■	lrvs-d
8 Mounting bracket HR-D	–	■	hr-d
9 Pressure gauge MA/PAGN	■	–	52
10 Knurled nut (included in scope of delivery) HMR	■	■	–

1) The mounting bracket must be mounted after every second pressure regulator.


Pressure regulators LRB/LRBS, D series, metal design

Peripherals overview


FESTO

Mini/Midi

Pressure regulator LRBS lockable – pressure output at rear



Pressure regulator LRBS lockable – pressure output at front



Pressure regulators LRB/LRBS, D series, metal design

Peripherals overview

FESTO

Mounting attachments and accessories			
Pressure regulator LRBS, lockable	Pressure output at rear	Pressure output at front	→ Page/ Internet
1 Mounting bracket HRB	■	–	hrb-d
2 Mounting bracket HFOE	–	■	hfoe-d
3 Connection plates LRBAS	■	■	lrbas
4 Adapter kit HRBC	■	■	hrbc-d
5 Mounting bracket HRBK	■ ¹⁾	–	hrbk-d
6 Mounting bracket HR-D	–	■	hr-d
7 Pressure gauge MA/PAGN	■	–	52
8 Knurled nut (included in scope of delivery) HMR	■	■	–

1) The mounting bracket must be mounted after every second pressure regulator.

Pressure regulators LRB/LRBS, D series, metal design

FESTO

Type codes


		LRB	–	D	–	7	–	0	–	MINI
Basic function										
LRB	Pressure regulator for manifold assembly									
LRBS	Pressure regulator for manifold assembly, lockable									
Series										
D	Series									
Pressure regulation range										
7	0.5 ... 7 bar (0.05 ... 0.7 MPa)									
	0.5 ... 12 bar (0.05 ... 1.2 MPa)									
Pressure gauge										
0	Without pressure gauge									
Size										
MINI	Grid dimension 40 mm (without connecting plates)									
MIDI	Grid dimension 55 mm (without connecting plates)									

Pressure regulators LRB/LRBS, D series, metal design

FESTO

Technical data

Function



-  Flow rate
1,600 ... 3,800 l/min
-  Temperature range
-10 ... +60 °C
-  Operating pressure
1 ... 16 bar (0.1 ... 1.6 MPa)



The pressure regulator is suitable for manifold assemblies with through air supply on both sides, for configuring a regulator manifold with separate, independent pressure ranges. Pressure output is at the front or rear.

- Good control characteristics with low hysteresis and primary pressure compensation
- Manifold assembly with through air supply
- For configuring a regulator manifold with independent pressure ranges
- Two pressure regulation ranges: 0.5 ... 7 bar (0.05 ... 0.7 MPa) and 0.5 ... 12 bar (0.05 ... 1.2 MPa)
- Settings secured via detent on knob and push-in adjustment lock

General technical data				
Size	Mini		Midi	
Pneumatic connection 1	_1)	_1)	_1)	_1)
Pneumatic connection 2	G¼		G¾	
Constructional design	Directly actuated diaphragm regulator with through pressure supply			
Regulating function	Output pressure constant, with secondary venting, with primary pressure compensation			
Type of mounting	Via accessories			
	In-line installation			
Assembly position	Any			
Regulator lock	Rotary knob with detent			
	Rotary knob with integrated lock			
Pressure regulation range	[bar]	0.5 ... 7 (0.05 ... 0.7 MPa)		
		0.5 ... 12 (0.05 ... 1.2 MPa)		
Max. hysteresis	[bar]	0.2 (0.02 MPa)		
Pressure indication	G¾ prepared		G¼ prepared	

1) Dependent on connecting plate selected, must be ordered separately as an accessory → Internet: Irbas

-  Note: This product conforms to ISO 1179-1 and to ISO 228-1

Standard nominal flow rate ¹⁾ qnN [l/min]			
Size	Mini		Midi
Pressure regulation range	0.5 ... 7 bar (0.05 ... 0.7 MPa)	1,800	3,800
	0.5 ... 12 bar (0.05 ... 1.2 MPa)	1,600	3,200

1) Measured at p1 = 10 bar (1 MPa), p2 = 6 bar (0.6 MPa) and Δp = 1 bar (0.1 MPa).

Pressure regulators LRB/LRBS, D series, metal design

FESTO

Technical data

Operating and environmental conditions	
Operating pressure [bar]	1 ... 16 (0.1 ... 1.6 MPa)
Operating medium	Compressed air in accordance with ISO 8573-1:2010 [7:4:4] Inert gases
Ambient temperature [°C]	-10 ... +60
Temperature of medium [°C]	-10 ... +60
Storage temperature [°C]	-10 ... +60
Corrosion resistance class CRC ¹⁾	2


1) Corrosion resistance class CRC 2 to Festo standard FN 940070

Moderate corrosion stress. Indoor applications in which condensation may occur. External visible parts with primarily decorative requirements for the surface and which are in direct contact with the ambient atmosphere typical for industrial applications.

Weight [g]		
Size	Mini	Midi
LRB	250	700
LRBS	350	940


Materials

Sectional view



Pressure regulator	LRB	LRBS
1 Housing	Die-cast zinc	
2 Connecting plates	Die-cast zinc	
3 Regulating knob	PA	Aluminium
4 Knurled nut	Aluminium	
5 Plug cap	PC	
– Seals	NBR	
Note on materials	RoHS-compliant	
	Free of copper and PTFE	

Standard flow rate q_n as a function of the output pressure p_2



Input pressure $p_1 = 10$ bar (1 MPa)

Pressure regulators LRB/LRBS, D series, metal design

FESTO


Technical data

Dimensions

Download CAD data → www.festo.com

LRB

LRBS



Type	B3	D2	D3	D4	D7	L1	L2	L4	L5 max.	L6	L7 min.	≈ 2
Mini												
LRB-D-...-MINI	40	31	G1/8	M36x1.5	G1/4	~95.4	3	~68.9	3	98	60	17
LRBS-D-...-MINI												
Midi												
LRB-D-...-MIDI	55	49.3	G1/4	M52x1.5	G3/8	~135.8	3	~100.3	5	129.2	60	36
LRBS-D-...-MIDI												

• Note: This product conforms to ISO 1179-1 and to ISO 228-1

Ordering data

Pressure regulator for manifold assembly

Size	Pressure regulation range 0.5 ... 7 bar (0.05 ... 0.7 MPa)		Pressure regulation range 0.5 ... 12 bar (0.05 ... 1.2 MPa)	
	Part No.	Type	Part No.	Type
Rotary knob with detent				
Mini	197534	LRB-D-7-O-MINI	197535	LRB-D-O-MINI
Midi	197538	LRB-D-7-O-MIDI	197539	LRB-D-O-MIDI
Rotary knob with integrated lock				
Mini	194683	LRBS-D-7-O-MINI	194682	LRBS-D-O-MINI
Midi	194687	LRBS-D-7-O-MIDI	194686	LRBS-D-O-MIDI


Pressure regulator combinations LRB-K, D series, metal design

FESTO

Peripherals overview

Mini/Midi

Pressure regulator combination LRB-K



Mounting attachments and accessories

	→ Page/ Internet
1) Mounting bracket (included in scope of delivery) HRBK ¹⁾	hrbk-d
2) Regulator lock LRVS	lrvs-d
3) Padlock LRVS-D	lrvs-d
4) Hex nut (for front panel mounting) HMR	hmr-d
5) Pressure gauge MA/PAGN	52

1) The mounting bracket must be mounted after every second pressure regulator.

Pressure regulator combinations LRB-K, D series, metal design

FESTO

Type codes


		LRB	–	1/4	–	D	–	7	–	0	–	K2	–	MINI
Basic function														
LRB	Pressure regulator combination													
Pneumatic connection														
MINI														
1/4	Connecting plates with connecting thread G1/4													
3/8	Connecting plates with connecting thread G3/8													
MIDI														
3/8	Connecting plates with connecting thread G3/8													
1/2	Connecting plates with connecting thread G1/2													
Series														
D	Series													
Pressure regulation range														
7	0.5 ... 7 bar (0.05 ... 0.7 MPa)													
	0.5 ... 12 bar (0.05 ... 1.2 MPa)													
Pressure gauge														
0	Without pressure gauge													
Functions														
K2	Manifold with 2 pressure regulators													
K3	Manifold with 3 pressure regulators													
K4	Manifold with 4 pressure regulators													
K5	Manifold with 5 pressure regulators													
Size														
MINI	Grid dimension 40 mm (without connecting plates)													
MIDI	Grid dimension 55 mm (without connecting plates)													

Pressure regulator combinations LRB-K, D series, metal design

FESTO

Technical data

Function



-  - Flow rate
1,600 ... 3,800 l/min

-  - Temperature range
-10 ... +60 °C

-  - Operating pressure
1 ... 16 bar (0.1 ... 1.6 MPa)

Pressure regulator combinations

LRB-...-D-...-O-K2

LRB-...-D-...-O-K3

LRB-...-D-...-O-K4

LRB-...-D-...-O-K5

with through pressure supply for
manifold assembly



- Good control characteristics with low hysteresis and primary pressure compensation
- Manifold assembly with through air supply
- For configuring a regulator manifold with independent pressure ranges
- Two pressure regulation ranges: 0.5 ... 7 bar (0.05 ... 0.7 MPa) and 0.5 ... 12 bar (0.05 ... 1.2 MPa)
- Settings secured via detent on knob and push-in adjustment lock
- Directly actuated diaphragm regulator

General technical data				
Size	Mini		Midi	
Pneumatic connection 1	G $\frac{1}{4}$	G $\frac{3}{8}$	G $\frac{3}{8}$	G $\frac{1}{2}$
Pneumatic connection 2	G $\frac{1}{4}$		G $\frac{3}{8}$	
Design	Directly actuated diaphragm regulator with through pressure air supply			
Regulator type	Output pressure constant, with primary pressure compensation, with secondary venting			
Type of mounting	Via accessory (mounting bracket HRB or HRBK included in scope of delivery)			
Assembly position	Any			
Regulator lock	Rotary knob with detent			
Pressure regulation range [bar]	0.5 ... 7 (0.05 ... 0.7 MPa)			
	0.5 ... 12 (0.05 ... 1.2 MPa)			
Max. hysteresis [bar]	0.2 (0.02 MPa)			
Pressure indication	G $\frac{1}{8}$ prepared		G $\frac{1}{4}$ prepared	

-  Note: This product conforms to ISO 1179-1 and to ISO 228-1

Standard nominal flow rate q _N ¹⁾ [l/min]		
Size	Mini	Midi
Pressure regulation range	0.5 ... 7 bar (0.05 ... 0.7 MPa)	3,800
	0.5 ... 12 bar (0.05 ... 1.2 MPa)	3,200

1) Measured at p₁ = 10 bar (1 MPa), p₂ = 6 bar (0.6 MPa) and Δp = 1 bar (0.1 MPa).

Pressure regulator combinations LRB-K, D series, metal design

FESTO


Technical data

Operating and environmental conditions		
Operating pressure	[bar]	1 ... 16 (0.1 ... 1.6 MPa)
Operating medium		Compressed air in accordance with ISO 8573-1:2010 [7:4:4]
Ambient temperature	[°C]	-10 ... +60
Temperature of medium	[°C]	-10 ... +60

Weight [g]		
Size	Mini	Midi
Manifold with 2 pressure regulators		
LRB-...-K2	760	1,950
Manifold with 3 pressure regulators		
LRB-...-K3	1,090	3,144
Manifold with 4 pressure regulators		
LRB-...-K4	1,480	3,834
Manifold with 5 pressure regulators		
LRB-...-K5	1,860	4,828

Materials

Sectional view



Pressure regulator	Mini/Midi
1 Housing	Die-cast zinc
2 Connecting plates	Die-cast zinc
3 Regulating knob	PA
4 Plug cap	PC
- Seals	NBR

Pressure regulator combinations LRB-K, D series, metal design


FESTO

Technical data

Dimensions

Download CAD data → www.festo.com

LRB-...-D-...-K2-...



Type	B1	B2	B3	B4	B5	B6	B7	B8	D1	D2	D3	D4
Mini												
LRB-1/4-D-...-K2-MINI	119	~107	40	80.7	59.2	2.5	5	3	G1/4	31	G1/4	M36x1.5
LRB-3/8-D-...-K2-MINI	125								G3/8			
Midi												
LRB-3/8-D-...-K2-MIDI	159	~144	55	99.9	70.6	3	5	3	G3/8	49.3	G3/8	M52x1.5
LRB-1/2-D-...-K2-MIDI							6		G1/2			

Type	D5	D6	H1	H2 ±0.2	H3 ±0.5	L1	L2	L4	L5 max.	L8	≅ 2
Mini											
LRB-1/4-D-...-K2-MINI	G1/8	4.3	20	35	47.3	~95.4	3	~68.9	3	17.5	17
LRB-3/8-D-...-K2-MINI											
Midi											
LRB-3/8-D-...-K2-MIDI	G1/4	5.3	32	49	62	~135.8	3	~100.3	5	24.5	36
LRB-1/2-D-...-K2-MIDI											

- || - Note: This product conforms to ISO 1179-1 and to ISO 228-1

Pressure regulator combinations LRB-K, D series, metal design


FESTO

Technical data

Dimensions

Download CAD data → www.festo.com

LRB-...-D-...-K3-...



- 1 Pressure gauge connection
2 Connecting kit HRBC-D-...

- 4 Mounting bracket HRB-D-...
5 Mounting bracket HRBK-D-...

- 6 Knurled nut or hex nut (not included in scope of delivery) for front panel mounting

→ Flow direction, both directions possible

Type	B1	B2	B3	B4	B5	B6	B7	B8	B9	D1	D2	D3	D4
Mini													
LRB-1/4-D-...-K3-MINI	174	~162	40	80.7	59.2	2.5	5	3	108.5	G1/4	31	G1/4	M36x1.5
LRB-3/8-D-...-K3-MINI	180									G3/8			
Midi													
LRB-3/8-D-...-K3-MIDI	233	~218	55	99.9	70.6	3	5	3	146	G3/8	49.3	G3/8	M52x1.5
LRB-1/2-D-...-K3-MIDI							6			G1/2			

Type	D5	D6	H1	H2 ±0.2	H3 ±0.5	L1	L2	L4	L5 max.	L8	≅ 2
Mini											
LRB-1/4-D-...-K3-MINI	G1/8	4.3	20	35	47.3	~95.4	3	~68.9	3	17.5	17
LRB-3/8-D-...-K3-MINI											
Midi											
LRB-3/8-D-...-K3-MIDI	G1/4	5.3	32	49	62	~135.8	3	~100.3	5	24.5	36
LRB-1/2-D-...-K3-MIDI											

• Note: This product conforms to ISO 1179-1 and to ISO 228-1

Pressure regulator combinations LRB-K, D series, metal design


FESTO

Technical data

Dimensions

Download CAD data → www.festo.com

LRB-...-D-...-K4-...



Type	B1	B2	B3	B4	B5	B6	B7	B8	B9	D1	D2	D3	D4
Mini													
LRB-1/4-D-...-K4-MINI	229	~217	40	80.7	59.2	2.5	5	3	108.5	G1/4	31	G1/4	M36x1.5
LRB-3/8-D-...-K4-MINI	235									G3/8			
Midi													
LRB-3/8-D-...-K4-MIDI	307	~292	55	99.9	70.6	3	5	3	146	G3/8	49.3	G3/8	M52x1.5
LRB-1/2-D-...-K4-MIDI							6			G1/2			

Type	D5	D6	H1	H2 ±0.2	H3 ±0.5	L1	L2	L4	L5 max.	L8	≈ 2
Mini											
LRB-1/4-D-...-K4-MINI	G1/8	4.3	20	35	47.3	~95.4	3	~68.9	3	17.5	17
LRB-3/8-D-...-K4-MINI											
Midi											
LRB-3/8-D-...-K4-MIDI	G1/4	5.3	32	49	62	~135.8	3	~100.3	5	24.5	36
LRB-1/2-D-...-K4-MIDI											

· Note: This product conforms to ISO 1179-1 and to ISO 228-1

Pressure regulator combinations LRB-K, D series, metal design


FESTO

Technical data

Dimensions

Download CAD data → www.festo.com

LRB-...-D-...-K5-...



Type	B1	B2	B3	B4	B5	B6	B7	B8	B9	B10	D1	D2	D3	D4
Mini														
LRB-1/4-D-...-K5-MINI	284	~272	40	80.7	59.2	2.5	5	3	108.5	163.5	G1/4	31	G1/4	M36x1.5
LRB-3/8-D-...-K5-MINI	290										G3/8			
Midi														
LRB-3/8-D-...-K5-MIDI	381	~366	55	99.9	70.6	3	5	3	146	220	G3/8	49.3	G3/8	M52x1.5
LRB-1/2-D-...-K5-MIDI							6				G1/2			

Type	D5	D6	H1	H2 ±0.2	H3 ±0.5	L1	L2	L4	L5 max.	L8	≈ 2
Mini											
LRB-1/4-D-...-K5-MINI	G1/8	4.3	20	35	47.3	~95.4	3	~68.9	3	17.5	17
LRB-3/8-D-...-K5-MINI											
Midi											
LRB-3/8-D-...-K5-MIDI	G1/4	5.3	32	49	62	~135.8	3	~100.3	5	24.5	36
LRB-1/2-D-...-K5-MIDI											

Note: This product conforms to ISO 1179-1 and to ISO 228-1

Pressure regulator combinations LRB-K, D series, metal design

FESTO

Technical data

Ordering data					
Connecting kits, connecting plates with connecting thread and mounting brackets					
Size	Connection	Pressure regulation range 0.5 ... 7 bar (0.05 ... 0.7 MPa)		Pressure regulation range 0.5 ... 12 bar (0.05 ... 1.2 MPa)	
		Part No.	Type	Part No.	Type
Manifold with 2 pressure regulators					
Mini	G1/4	528952	LRB-1/4-D-7-O-K2-MINI	528954	LRB-1/4-D-O-K2-MINI
	G3/8	528953	LRB-3/8-D-7-O-K2-MINI	528955	LRB-3/8-D-O-K2-MINI
Midi	G3/8	528956	LRB-3/8-D-7-O-K2-MIDI	528958	LRB-3/8-D-O-K2-MIDI
	G1/2	528957	LRB-1/2-D-7-O-K2-MIDI	528959	LRB-1/2-D-O-K2-MIDI
Manifold with 3 pressure regulators					
Mini	G1/4	528968	LRB-1/4-D-7-O-K3-MINI	528970	LRB-1/4-D-O-K3-MINI
	G3/8	528969	LRB-3/8-D-7-O-K3-MINI	528971	LRB-3/8-D-O-K3-MINI
Midi	G3/8	528972	LRB-3/8-D-7-O-K3-MIDI	528974	LRB-3/8-D-O-K3-MIDI
	G1/2	528973	LRB-1/2-D-7-O-K3-MIDI	528975	LRB-1/2-D-O-K3-MIDI
Manifold with 4 pressure regulators					
Mini	G1/4	528984	LRB-1/4-D-7-O-K4-MINI	528986	LRB-1/4-D-O-K4-MINI
	G3/8	528985	LRB-3/8-D-7-O-K4-MINI	528987	LRB-3/8-D-O-K4-MINI
Midi	G3/8	528988	LRB-3/8-D-7-O-K4-MIDI	528990	LRB-3/8-D-O-K4-MIDI
	G1/2	528989	LRB-1/2-D-7-O-K4-MIDI	528991	LRB-1/2-D-O-K4-MIDI
Manifold with 5 pressure regulators					
Mini	G1/4	529000	LRB-1/4-D-7-O-K5-MINI	529002	LRB-1/4-D-O-K5-MINI
	G3/8	529001	LRB-3/8-D-7-O-K5-MINI	529003	LRB-3/8-D-O-K5-MINI
Midi	G3/8	529004	LRB-3/8-D-7-O-K5-MIDI	529006	LRB-3/8-D-O-K5-MIDI
	G1/2	529005	LRB-1/2-D-7-O-K5-MIDI	529007	LRB-1/2-D-O-K5-MIDI

Pressure regulator combinations LRB-K, D series, metal design





Technical data

FESTO

Pressure regulators LR/LRB, D series, polymer

FESTO

Product range overview D series service units, polymer

Type		Size	Pneumatic connection		Pressure regulation range [bar]	Grade of filtration [µm]	
			G¼	G½	0.5 ... 7	5	40
Service units							
FRC		Mini	■	–	■	■	■
Service unit combinations							
FRC-K		Mini	■	–	■	–	■
LFR-K		Mini	■	–	■	–	■
Individual devices							
Filter regulators LFR		Mini	■	–	■	■	■
Pressure regulators LR		Mini	■	–	■	–	–
Pressure regulator combinations LRB-K		Mini	–	■	■	–	–
On-off valves HE		Mini	■	–	–	–	–

Pressure regulators LR/LRB, D series, polymer

FESTO


Product range overview D series service units, polymer

Type	Size	Condensate drain		Pressure display		Actuator lock	Regulating functions		→ Page/ Internet
		Manual rotary	Semi-automatic	With pressure gauge	Without pressure gauge	Rotary knob with detent	With secondary venting	With return flow function	
Service units									
FRC	Mini	■	■	■	-	■	■	■	frc
Service unit combinations									
FRC-K	Mini	■	-	■	-	■	■	■	frc
LFR-K	Mini	■	-	■	-	■	■	■	lfr
Individual devices									
Filter regulators LFR	Mini	■	■	■	■	■	■	■	lfr
Pressure regulators LR	Mini	-	-	■	■	■	■	■	40
Pressure regulator combinations LRB-K	Mini	-	-	-	■	■	■	■	45
On-off valves HE	Mini	-	-	-	■	-	-	-	he

Pressure regulators LR, D series, polymer

Peripherals overview

FESTO



Mounting attachments and accessories		→ Page/ Internet
1	Connecting plate kit PBL	pbl
2	Mounting bracket HFOE	hfoe-d
3	Mounting bracket HR-D	hr-d
4	Knurled nut (included in scope of delivery) LRVS	–
5	Pressure gauge MA/PAGN	52

Pressure regulators LR, D series, polymer

FESTO

Type codes


		LR	–	1/4	–	DB	–	7	–	0	–	MINI
Basic function												
LR	Pressure regulator											
Pneumatic connection												
1/4	Thread G1/4											
Series												
DB	Series											
Pressure regulation range												
7	0.5 ... 7 bar (0.05 ... 0.7 MPa)											
Pressure gauge												
	With pressure gauge											
0	Without pressure gauge											
Size												
	MINI											

Pressure regulators LR, D series, polymer


Technical data

FESTO

with pressure gauge



without pressure gauge



-  - Flow rate
800 ... 1,300 l/min
-  - Temperature range
-5 ... +50 °C
-  - Operating pressure
1.5 ... 10 bar (0.15 ... 1 MPa)



- Setting values are secured by locking the rotary knob
- High flow rate
- Good regulating characteristics with minimal pressure hysteresis

General technical data		
Size	Mini	
	With pressure gauge	Without pressure gauge
Pneumatic connection	G $\frac{1}{4}$	
Design	Pressure regulator with pressure gauge	Pressure regulator without pressure gauge
Regulating function	With return flow function	
	With secondary venting	
Type of mounting	Inline installation	
	Via through-holes	
	Via mounting bracket	
	Front panel mounting	
Assembly position	Any	
Regulator lock	Rotary knob with detent	
Max. hysteresis [bar]	0.5 (0.05 MPa)	
Pressure regulation range [bar]	0.5 ... 7 (0.05 ... 0.7 MPa)	
Pressure indication	Via pressure gauge	G $\frac{1}{8}$ prepared
Pressure gauge connection	G $\frac{1}{8}$	

Standard nominal flow rate ¹⁾ qnN [l/min]	
Size	Mini
Pressure regulation range 0.5 ... 7 bar (0.05 ... 0.7 MPa)	≥ 1,300

1) Measured at p₁ = 10 bar (1 MPa), p₂ = 6 bar (0.6 MPa) and Δp = 1 bar (0.1 MPa).

Pressure regulators LR, D series, polymer

FESTO

Technical data

Operating and environmental conditions		
Size		Mini
Operating pressure	[bar]	1.5 ... 10 (0.15 ... 1 MPa)
Operating medium		Compressed air in accordance with ISO 8573-1:2010 [–:–:–]
Ambient temperature	[°C]	–5 ... +50
Temperature of medium	[°C]	–5 ... +50
Corrosion resistance class CRC ¹⁾		1


1) Corrosion resistance class CRC 1 to Festo standard FN 940070

Low corrosion stress. For dry indoor applications or transport and storage protection. Also applies to parts behind covers, in the non-visible interior area, and parts which are covered in the application (e.g. drive trunnions).

Weight [g]	
Size	Mini
Pressure regulator	150

Materials


Sectional view



Pressure regulator		Mini
1	Housing	PA reinforced
2	Rotary knob	POM
–	Seals	NBR
Note on materials		RoHS-compliant

Standard flow rate q_n as a function of output pressure p_2

Operating pressure $p_1 = 10$ bar
(1 MPa)



-  - Note

Slight leakage at the output has been taken into account in the design. It improves the control behaviour of the non pre-pressure compensated controller.

In a few cases leakage may amount to 500 l/h.

Pressure regulators LR, D series, polymer


Technical data

FESTO

Dimensions

Download CAD data → www.festo.com

Mini



Type	D1
Mini	
LR-1/4-DB	G1/4

Ordering data

Pressure regulation range 0.5 ... 7 bar (0.05 ... 0.7 MPa)

Size	Connection	Part No.	Type
With pressure gauge, outer scale in bar, inner scale in psi			
Mini	G1/4	539682	LR-1/4-DB-7-MINI
Without pressure gauge			
Mini	G1/4	537643	LR-1/4-DB-7-O-MINI

Pressure regulator combinations LRB-K, D series, polymer



FESTO

Peripherals overview

Mini

With mounting bracket

Front panel mounting



Mounting attachments and accessories				
	With mounting bracket	Front panel mounting		→ Page/ Internet
1 Mounting bracket kit HRBS-DB-MINI	■	–		hrbs-db
2 Push-in T-fitting QSTF	■	–		52
3 Pressure gauge MA/PAGN	■	–		52
4 Mounting bracket HR-D	■	–		hr-d
5 Hex nut HMR	■	■		hmr-d
6 Push-in Y-fitting QSYLV	–	■		52
7 Plastic tubing PUN-E	–	■		pun-e
8 Push-in fitting QSF	–	■		52
9 Flanged pressure gauge FMA	–	■		52

Pressure regulator combinations LRB-K, D series, polymer

FESTO

Type codes


		LRB	–	1/4	–	DB	–	7	–	0	–	K2	–	MINI
Basic function														
LRB	Pressure regulator combination													
Pneumatic connection 2														
1/4	Thread G1/4													
Series														
DB	Series													
Pressure regulation range														
7	0.5 ... 7 bar (0.05 ... 0.7 MPa)													
Pressure gauge														
0	Without pressure gauge													
Regulator														
K2	Manifold with 2 pressure regulators													
K3	Manifold with 3 pressure regulators													
K4	Manifold with 4 pressure regulators													
K5	Manifold with 5 pressure regulators													
Size														
MINI														

Pressure regulator combinations LRB-K, D series, polymer


FESTO

Technical data

Function



-  Flow rate
1,000 l/min
-  Temperature range
-5 ... +50 °C
-  Operating pressure
1.5 ... 10 bar (0.15 ... 1 MPa)



- Good control characteristics with low hysteresis and primary pressure compensation
- Manifold assembly with through air supply
- For the configuration of a regulator manifold with independent pressure ranges
- Setting values are secured by locking the rotary knob

General technical data	
Size	Mini
Pneumatic connection 1	G½
Pneumatic connection 2	G¼
Design	Directly actuated piston regulator On P-manifold
Regulating functions	Output pressure constant With return flow function With secondary venting
Type of mounting	Front panel mounting Via accessories
Assembly position	Any
Regulator lock	Rotary knob with detent
Max. hysteresis [bar]	0.5 (0.05 MPa)
Pressure regulation range [bar]	0.5 ... 7 (0.05 ... 0.7 MPa)

Standard nominal flow rate ¹⁾ qnN [l/min]	
Size	Mini
Pressure regulation range 0.5 ... 7 bar (0.05 ... 0.7 MPa)	≥ 1,000

1) Measured at p₁ = 10 bar (1 MPa), p₂ = 6 bar (0.6 MPa) and Δp = 1 bar (0.1 MPa).

Operating and environmental conditions	
Size	Mini
Operating pressure [bar]	1.5 ... 10 (0.15 ... 1 MPa)
Operating medium	Compressed air in accordance with ISO 8573-1:2010 [–:–:–]
Ambient temperature [°C]	–5 ... +50
Temperature of medium [°C]	–5 ... +50
Corrosion resistance class CRC ¹⁾	1

1) Corrosion resistance class CRC 1 to Festo standard FN 940070
Low corrosion stress. For dry indoor applications or transport and storage protection. Also applies to parts behind covers, in the non-visible interior area, and parts which are covered in the application (e.g. drive trunnions).

Pressure regulator combinations LRB-K, D series, polymer


FESTO

Technical data

Weight [g]	
Size	Mini
Manifold with 2 pressure regulators	
LRB-...-K2	500
Manifold with 3 pressure regulators	
LRB-...-K3	750
Manifold with 4 pressure regulators	
LRB-...-K4	1,000
Manifold with 5 pressure regulators	
LRB-...-K5	1,250

Materials

Sectional view



Pressure regulator	Mini
1 Housing	PA reinforced
2 Rotary knob	POM
3 Sealing ring	PVC
4 Manifold strip	Wrought aluminium alloy
5 Spacing bolt	Wrought aluminium alloy
– Seals	NBR

Pressure regulator combinations LRB-K, D series, polymer

FESTO


Technical data

Dimensions


Download CAD data → www.festo.com

With mounting bracket


LRB-...-K5




LRB-...-K4



LRB-...-K3



LRB-...-K2



→ Flow direction

FESTO

Pressure regulator combinations LRB-K, D series, polymer

FESTO

Technical data

Ordering data			
Size	Connection	Pressure regulation range 0.5 ... 7 bar (0.05 ... 0.7 MPa)	
		Part No.	Type
Manifold with 2 pressure regulators			
Mini	G1/4	540040	LRB-1/4-DB-7-O-K2-MINI
Manifold with 3 pressure regulators			
Mini	G1/4	540041	LRB-1/4-DB-7-O-K3-MINI
Manifold with 4 pressure regulators			
Mini	G1/4	540042	LRB-1/4-DB-7-O-K4-MINI
Manifold with 5 pressure regulators			
Mini	G1/4	540043	LRB-1/4-DB-7-O-K5-MINI

Pressure regulators LR/LRS/LRB/LRBS, D series

FESTO

Accessories

Ordering data – Pressure gauge MA						
	Nominal size	Pneumatic connection	Indicating range		Part No.	Type
			Outer scale	Inner scale		
	Pressure gauge MA				Technical data → Internet: ma	
	27	M5	0 ... 10 bar	–	526323	MA-27-10-M5
	40	G $\frac{1}{8}$	0 ... 10 bar	0 ... 145 psi	359874	MA-40-10- $\frac{1}{4}$
			0 ... 16 bar	0 ... 232 psi	345395	MA-40-16- $\frac{1}{4}$
	50	G $\frac{1}{4}$	0 ... 10 bar	0 ... 145 psi	359873	MA-50-10- $\frac{1}{4}$
			0 ... 16 bar	0 ... 232 psi	356759	MA-50-16- $\frac{1}{4}$
	Pressure gauge PAGN				Technical data → Internet: pagn	
	40	G $\frac{1}{8}$	0 ... 1 MPa	0 ... 10 bar	8000222	PAGN-40-1M-G18
			0 ... 1.6 MPa	0 ... 16 bar	8000223	PAGN-40-1.6M-G18
	50	G $\frac{1}{4}$	0 ... 1 MPa	0 ... 10 bar	8000224	PAGN-50-1M-G14
			0 ... 1.6 MPa	0 ... 16 bar	8000225	PAGN-50-1.6M-G14
	Pressure gauge MA, DIN EN 837-1				Technical data → Internet: ma	
	40	R $\frac{1}{8}$	0 ... 10 bar	0 ... 145 psi	162835	MA-40-10- $\frac{1}{8}$ -EN
		G $\frac{1}{4}$	0 ... 10 bar	0 ... 145 psi	183900	MA-40-10-G $\frac{1}{4}$ -EN
	Flanged pressure gauge FMA, DIN EN 837-1				Technical data → Internet: fma	
	40	G $\frac{1}{4}$	0 ... 10 bar	0 ... 145 psi	159596	FMA-40-10- $\frac{1}{4}$ -EN
			0 ... 16 bar	0 ... 232 psi	159597	FMA-40-16- $\frac{1}{4}$ -EN
	50	G $\frac{1}{4}$	0 ... 10 bar	0 ... 145 psi	159599	FMA-50-10- $\frac{1}{4}$ -EN
			0 ... 16 bar	0 ... 232 psi	159600	FMA-50-16- $\frac{1}{4}$ -EN

Ordering data – Pressure sensor SPAU						Technical data → Internet: spau	
	Pneumatic connection	Switching output	Display type	Electrical connection	Part No.	Type	
Pressure sensor SPAU for direct mounting on the service unit with pressure gauge connection (adapter for pneumatic connection included in scope of delivery), pressure measuring range 0 ... 10 bar, relative pressure measurement							
	Male thread R1/8	2x PNP or 2x NPN, switchable	Illuminated LCD	M8x1, 4-pin	8001203	SPAU-P10R-T-R18M-L-PNLK-PNVBA-M8D	
	Male thread R1/4			M12x1, 4-pin	8001206	SPAU-P10R-T-R18M-L-PNLK-PNVBA-M12D	
				M8x1, 4-pin	8001209	SPAU-P10R-T-R14M-L-PNLK-PNVBA-M8D	
				M12x1, 4-pin	8001208	SPAU-P10R-T-R14M-L-PNLK-PNVBA-M12D	

Ordering data – Push-in fitting					
	Pneumatic connection	Tubing O.D.	Part No.	Type	PU ¹⁾
Push-in fitting QSF, female thread with external hex Technical data → Internet: qsf					
	G $\frac{1}{4}$	8	153026	QSF- $\frac{1}{4}$ -8-B	10
Push-in T-fitting QSTF, 360° rotatable, with male and female thread Technical data → Internet: qstf					
	G $\frac{1}{4}$	8	186203	QSTF-G $\frac{1}{4}$ -8	1
Push-in Y-fitting QSYLV, 360° rotatable, male thread with external hex Technical data → Internet: qsyv					
	G $\frac{1}{4}$	8	186210	QSYLV-G $\frac{1}{4}$ -8	1

1) Packaging unit quantity

Festo - Your Partner in Automation



1 Festo Inc.
5300 Explorer Drive
Mississauga, ON L4W 5G4
Canada

Festo Customer Interaction Center
Tel: 1 877 463 3786
Fax: 1 877 393 3786
Email: customer.service.ca@festo.com



2 Festo Pneumatic
Av. Ceylán 3,
Col. Tequesquináhuac
54020 Tlalnepantla,
Estado de México

Multinational Contact Center
01 800 337 8669
ventas.mexico@festo.com



3 Festo Corporation
1377 Motor Parkway
Suite 310
Islandia, NY 11749

Festo Customer Interaction Center
1 800 993 3786
1 800 963 3786
customer.service.us@festo.com



4 Regional Service Center
7777 Columbia Road
Mason, OH 45040

Connect with us

www.festo.com/socialmedia



www.festo.com

Subject to change