

Tie rod cylinders DNG/DNGL/DNGZK – Inch Series

FESTO



- Piston Ø 1-1/4" to 6"
- Strokes up to 78.7"
- Double-acting
- Robust tie rod design
- Comprehensive range of accessories
- Repairable
- Non-rotating piston rod version available (DNGL)
- Adjustable trunnion mounting version available (DNGZK)

Product range overview									
Function	Version	Type	Piston Ø [in]	Stroke [in]	Force [lbf]	Variants			
						PPV	A	S2	S6
Double-acting	Basic version	DNG	1-1/4, 1-5/8, 2, 2-1/2, 3, 4, 5, 6	0.4 ... 78.7	108.3 ... 10,846	■	■	■	■
	Single-ended non-rotating piston rod	DNGL	1-1/4, 1-5/8, 2, 2-1/2, 3, 4	0.4 ... 24	108.3 ... 1,059	■	■	–	–
	With adjustable central trunnion mounting	DNGZK	1-1/4, 1-5/8, 2, 2-1/2, 3, 4, 5, 6	0.4 ... 78.7	108.3 ... 10,846	■	■	–	–

Variants									
PPV	Adjustable air cushioning at both ends	A	Magnet for position sensing	S6	Heat-resistant up to 150 °C				
		S2	Through piston rod						

Tie rod cylinders DNG/DNGL/DNGZK - Inch Series

FESTO

Technical data


Double-acting



-N- Diameter
1-1/4 ... 6 in
-T- Stroke length
0.4 ... 78.7 in

Variants

- Through piston rod (S2)
- Heat resistant seals (S6)



General technical data								
Piston Ø	1-1/4	1-5/8	2	2-1/2	3	4	5	6
Pneumatic connection	1/8 NPT	1/4 NPT	1/4 NPT	3/8 NPT	3/8 NPT	1/2 NPT	1/2 NPT	3/4 NPT
Piston rod thread	3/8-24 UNF	1/2-20 UNF	5/8-18 UNF	5/8-18 UNF	3/4-16 UNF	3/4-16 UNF	1-12 UNF	1-1/2-12 UNF
Operating medium	Filtered compressed air, lubricated or unlubricated							
Design	Piston							
	Piston rod							
	Profile barrel							
Cushioning	Adjustable air cushioning at both ends							
Cushioning length [in]	0.7	0.8	0.9	0.9	1.2	1.2	1.6	1.6
Magnet for position sensing ¹⁾	Standard							

1) Position sensing via magnetic proximity sensor (ordered separately, see accessories).

Operating and environmental conditions								
Piston Ø	1-1/4	1-5/8	2	2-1/2	3	4	5	6
Operating pressure [psi]	176.4							147.0
Ambient temperature ¹⁾ [°F]	-4 ... +176							

1) Note operating range of proximity sensors



Forces [lbf]								
Piston Ø	1-1/4	1-5/8	2	2-1/2	3	4	5	6
Theoretical force at 90 psi, extending	108	169	256	420	678	1,060	1,655	2,712
Theoretical force at 90 psi, retracting	93	142	223	378	512	994	1,547	2,543

Tie rod cylinders DNG/DNGL/DNGZK - Inch Series

Technical data

FESTO

Lateral force F_Q as a function of the stroke length l




Weights [oz]								
Piston $\varnothing$	1-1/4	1-5/8	2	2-1/2	3	4	5	6
DNG/DNGL								
Product weight at 0 inch stroke	19.9	27.9	49.4	60.8	101.4	144.6	257.7	609.0
Additional weight per 1 inch stroke	2.7	3.6	4.5	5.4	7.2	9.0	12.5	17.0
DNGZK								
Product weight at 0 inch stroke	28.9	45.0	68.6	97.5	139.7	219.0	360.3	688.2
Additional weight per 1 inch stroke	2.7	3.6	4.5	5.4	7.2	9.0	12.5	17.0

Tie rod cylinders DNG/DNGL/DNGZK - Inch Series


Technical data

Materials

Sectional view DNG/DNGL



Sectional view DNGZK



Standard cylinder	DNG/DNGL	DNGZK
1 Bearing and end caps	Aluminum	Die-cast aluminum
2 Cylinder barrel	Aluminum	Aluminum (Ø 6": brass)
3 Piston rod, tie rod	High-alloy steel	
- Seals	Polyurethane, nitrile rubber	


Tie rod cylinders DNG/DNGL/DNGZK - Inch Series

Technical data


FESTO

Dimensions


DNG/DNGL



Variant S2 – Through piston rod



DNGZK



Tie rod cylinders DNG/DNGL/DNGZK - Inch Series

Technical data

FESTO

Ø [in]	AM	B Ø d11	B1 f9	BG	C2	C3	D4 Ø	D5 Ø	E	EE	J2	J3
1-1/4	0.9	1.2	0.4	0.7	2.8	3.4	1.5	0.2	2.0	1/8 NPT	0.3	-
1-5/8	0.9	1.4	0.5	0.6	3.4	4.1	1.8	0.2	2.2	1/4 NPT	0.4	0.10
2	1.3	1.6	0.6	0.7	3.9	4.6	2.2	0.3	2.6	1/4 NPT	0.5	0.22
2-1/2	1.3	1.8	0.6	0.8	4.6	5.4	2.7	0.3	3.0	3/8 NPT	0.6	0.2
3	1.6	1.8	0.8	0.8	5.4	6.1	3.4	0.4	3.9	3/8 NPT	0.6	0.3
4	1.6	2.2	0.8	0.8	6.1	7.4	4.2	0.4	4.7	1/2 NPT	0.5	0.3
5	2.1	2.4	-	1.0	7.4	8.5	5.2	0.5	5.7	1/2 NPT	0.5	0.3
6	2.8	2.6	-	0.9	8.5	11.	6.6	0.6	7.3	3/4 NPT	0.9	0.9

Ø [in]	KK	L1	L2	L7	MM Ø	PL	RT	TD Ø e9	TG	TK	TL
1-1/4	3/8-24 UNF	0.7	3.7 ±0.02	0.23	0.5	0.3	M6	0.5	1.3	0.8	0.5
1-5/8	1/2-20 UNF	0.8	4.1 ±0.03	0.21	0.6	0.4	M6	0.6	1.5	1.0	0.6
2	5/8-18 UNF	1.1	4.2 ±0.03	0.08	0.8	0.7	M8	0.6	1.8	1.1	0.6
2-1/2	5/8-18 UNF	1.1	4.8 ±0.03	0.2	0.8	0.7	M8	0.8	2.2	1.2	0.8
3	3/4-16 UNF	1.4	5.0 ±0.03	0.3	1.0	0.7	M10	0.8	2.8	1.3	0.8
4	3/4-16 UNF	1.5	5.4 ±0.03	0.5	1.0	0.7	M10	1.0	3.5	1.5	1.0
5	1-12 UNF	1.8	6.3 ±0.03	0.6	1.3	0.7	M12	1.0	4.3	1.7	1.0
6	1-1/2-12 UNF	2.2	7.1 ±0.03	-	1.6	1.0	M16	1.3	5.5	1.9	1.3

Ø [in]	TM	UW	VA	VD	WH	XG	XJ	XV	ZJ	ZM	≈C1 [mm]	≈C3 [mm]	≈C4 [mm]
1-1/4	2.0	2.7	0.2	0.41	1.0	2.4 ±0.07	3.3 ±0.07	2.9 ±0.07	4.7	5.7	10	6	-
1-5/8	2.5	2.8	0.2	0.41	1.2	2.7 ±0.07	3.8 ±0.07	3.2 ±0.07	5.3	6.5	13	6	-
2	3.0	3.4	0.2	0.47	1.5	3.1 ±0.07	3.9 ±0.07	3.5 ±0.07	5.6	7.1	17	8	-
2-1/2	3.5	3.9	0.2	0.49	1.5	3.4 ±0.09	4.3 ±0.09	3.8 ±0.09	6.2	7.7	17	8	-
3	4.3	4.3	0.2	0.65	1.8	4.0 ±0.09	4.7 ±0.09	4.3 ±0.09	6.9	8.7	22	-	17
4	5.2	5.4	0.2	0.61	2.0	4.4 ±0.09	5.0 ±0.09	4.7 ±0.09	7.4	9.4	22	-	17
5	6.3	6.3	0.2	0.81	2.6	5.4 ±0.09	6.1 ±0.09	5.7 ±0.09	8.9	11.4	27	-	19
6	7.9	7.9	0.2	-	3.1	6.1 ±0.10	6.7 ±0.10	6.7 ±0.10	10.2	13.4	36	-	32

Dimensions are in inches, unless otherwise noted.

Tie rod cylinders DNG - Inch Series

Ordering data

FESTO

M Mandatory data					O Options	
Function	Piston Ø	Stroke	Cushioning	Magnet for position sensing	Type of piston rod	Temperature-resistant
DNG	1 1/4 1 5/8 2 2 1/2 3 4 5 6	0.4 ... 78.7	PPV	A	S2	S6
DNG	- 3	- 60	- PPV	- A	-	- S6

Ordering table											
Size	1 1/4	1 5/8	2	2 1/2	3	4	5	6	Conditions	Code	Enter code
M Function	Basic version, standard cylinder, double-acting									DNG	DNG
Piston Ø [in]	1 1/4	1 5/8	2	2 1/2	3	4	5	6		-...	
Stroke [in]	0.4 ... 78.7									-...	
Cushioning	Adjustable air cushioning at both ends									-PPV	-PPV
Magnet for position sensing	For use with magnetic proximity sensor									-A	-A
O Type of piston rod	Through piston rod									-S2	
Temperature-resistant	Heat-resistant seals up to max. 302 °F								1	-S6	

1 Not available in combination with -S2

Transfer order code

DNG - - - PPV - A -

Tie rod cylinders, non-rotating version DNGL - Inch Series

FESTO

Ordering data

M Mandatory data				
Function	Piston Ø	Stroke	Cushioning	Magnet for position sensing
DNGL	1 1/4 1 5/8 2 2 1/2 3 4	0.4 ... 24	PPV	A
DNGL	- 3	- 20	- PPV	- A

Ordering table									
Size	1 1/4	1 5/8	2	2 1/2	3	4	Code		Enter code
M Function	Non-rotating piston rod, standard cylinder, double-acting						DNGL		DNGL
Piston Ø [in]	1 1/4	1 5/8	2	2 1/2	3	4	- ...		
Stroke [in]	0.4 ... 12	0.4 ... 16	0.4 ... 20		0.4 ... 24		- ...		
Cushioning	Adjustable air cushioning at both ends						-PPV		-PPV
Magnet for position sensing ¹⁾	Standard						-A		-A

1) Position sensing via magnetic proximity sensor (ordered separately, see accessories).

Transfer order code

DNGL	-		-		-	PPV	-	A
-------------	---	--	---	--	---	------------	---	----------

Tie rod cylinders, with adjustable trunnion mounting DNGZK - Inch Series

FESTO

Ordering data

M Mandatory data				
Function	Piston Ø	Stroke	Cushioning	Magnet for position sensing
DNGZK	1 1/4 1 5/8 2 2 1/2 3 4 5 6	0.4 ... 78.7	PPV	A
DNGZK	- 3	- 60	- PPV	- A

Ordering table										
Size	1 1/4	1 5/8	2	2 1/2	3	4	5	6	Code	Enter code
M Function	Adjustable standard cylinder, double-acting, with central trunnion mounting								DNGZK	DNGZK
Piston Ø [in]	1 1/4	1 5/8	2	2 1/2	3	4	5	6	-...	
Stroke [in]	0.4 ... 78.7								-...	
Cushioning	Adjustable air cushioning at both ends								-PPV	-PPV
Magnet for position sensing ¹⁾	For use with magnetic proximity sensor								-A	-A


Transfer order code

DNGZK	-		-		-	PPV	-	A
-------	---	--	---	--	---	-----	---	---

Tie rod cylinders DNG/DNGL/DNGZK - Inch Series

Accessories overview

FESTO



Mounting attachments and accessories	
	Description
[1] Adapter kit DPNG	For connecting two DNG cylinders with identical piston $\varnothing$ to form a multi-position cylinder
[2] Foot mounting HNG	For bearing and end caps
[3] Flange mounting FNG	For bearing or end caps
[4] Trunnion flange ZNG	For bearing or end caps
[5] Trunnion support	For bearing or end caps
[6] Swivel flange SNG	For end caps

Tie rod cylinders DNG/DNGL/DNGZK - Inch Series

Accessories overview

FESTO

Mounting attachments and accessories	
	Description
7 Clevis foot mounting LSNG	With spherical bearing
8 Clevis foot mounting LSNSG	Weld-on, with spherical bearing
9 Swivel flange SSNG	With spherical bearing for clevis foot mounting LBG
10 Clevis foot mounting LBG	With non-rotating pivot pin
11 Swivel flange SNGL	For end caps
12 Swivel flange SNGB	For end caps
13 Clevis foot mounting LNG	For swivel flange SNGB
14 Clevis foot mounting LSN	With spherical bearing
15 One-way flow control valve GRLA	For speed regulation
16 Push-in fitting QS	For connecting compressed air tubing with standard O.D.
17 Plug socket with cable, straight SIM-M8	–
18 Plug socket with cable, angled SIM-M8	–
19 Proximity sensors SMEO-1/SMTO-1/SMPO-1-H-B	–
20 Sensor mounting kit SMB	For proximity sensor SMEO-1/SMTO-1
21 Sensor mounting kit SMBS	For proximity sensor SMPO-1-H-B
22 Rod eye SGS	With spherical bearing
23 Coupling piece KSZ	For compensating radial deviations
24 Rod clevis SG	Permits a swivelling movement of the cylinder in one plane
25 Self-aligning rod coupler FK	For compensating radial and angular deviations
26 Guided unit FENG	To protect against torsion at high torque loads
27 Right-angle clevis foot LQG	With non-rotating pivot pin

Tie rod cylinders DNG/DNGL/DNGZK - Inch Series

FESTO

Accessories

Adapter kit DPNG



for piston $\varnothing$ 1-1/4 ... 4 inch

Material:

Flange: Wrought aluminum alloy;

Threaded studs, hex nuts: Galvanized steel

Free of copper, PTFE and silicone



Dimensions and ordering data							
For $\varnothing$ [in]	F1	ZJ	Max. overall stroke length [in]	CRC ¹⁾	Weight [oz]	Part No.	Type
1-1/4	1.1	4.7	39.4	2	3.0	159485	DPNG-32
1-5/8	1.1	5.3	39.4	2	4.1	159486	DPNG-40
2	1.3	5.6	39.4	2	7.4	159487	DPNG-50
2-1/2	1.1	6.2	39.4	2	12.7	159488	DPNG-63
3	1.5	6.9	39.4	2	21.9	159489	DPNG-80
4	1.5	7.4	39.4	2	42.0	159490	DPNG-100

1) Corrosion resistance class 2 according to Festo standard 940 070

Components with moderate corrosion resistance for use in normal industrial environments subjected to contact with coolants or lubricating agents.

Connecting two cylinders with identical piston $\varnothing$ as a 3 or 4-position cylinder


A 3 or 4-position cylinder consists of two separate cylinders whose piston rods advance in opposing directions. This means that depending upon actuation and stroke pattern, this type

of cylinder can assume up to four positions. In each case the cylinder is driven precisely against a stop. Note that when one end of the piston rod is

fixed, the cylinder barrel executes the movement. The cylinder must be connected with flexible line connections.

To achieve 3 positions

Two cylinders with identical stroke length must be connected together.




Note

Do not exceed the maximum overall stroke length listed when combining cylinders and the adapter kit.

To achieve 4 positions

Two cylinders with different stroke lengths must be connected together.



Dimensions are in inches, unless otherwise noted.

Tie rod cylinders DNG/DNGL/DNGZK - Inch Series

Accessories


FESTO

Foot mounting HNG

Material:

Galvanized steel

Free of copper, PTFE and silicone



Dimensions and ordering data													
For Ø [in]	AB Ø	AH	AO	AT	AU	SA	TR	US	XA	CRC ¹⁾	Weight [oz]	Part No.	Type
1-1/4	0.3	1.3	0.3	0.2	0.9	5.6	1.3	1.8	5.7	2	7.9	32947	HNG-32
1-5/8	0.4	1.4	0.4	0.2	1.1	6.3	1.4	2.1	6.4	2	9.5	32948	HNG-40
2	0.4	1.8	0.4	0.2	1.3	6.7	1.8	2.5	6.9	2	14.1	32949	HNG-50
2-1/2	0.4	2.0	0.5	0.2	1.3	7.3	2.0	3.0	7.5	2	16.9	32950	HNG-63
3	0.5	2.5	0.6	0.2	1.6	8.3	2.5	3.7	8.5	2	38.1	32951	HNG-80
4	0.6	2.8	0.7	0.2	1.6	8.7	3.0	4.3	9.1	2	44.1	32952	HNG-100
5	0.6	3.5	0.9	0.3	1.8	9.8	3.5	5.2	10.6	2	71.4	32953	HNG-125
6	0.7	4.5	0.8	0.4	2.4	11.8	4.5	6.7	12.6	2	77.6	34476	HNG-160

1) Corrosion resistance class 2 according to Festo standard 940 070

Components with moderate corrosion resistance for use in normal industrial environments subjected to contact with coolants or lubricating agents.



Flange mounting FNG

Material:

FNG-32 ... 100: Galvanized steel

FNG-125 ... 160: Painted nodular
graphite cast iron

Free of copper, PTFE and silicone



Dimensions and ordering data												
For Ø [in]	E	FB Ø	MF	R	TF	UF	W	ZF	CRC ¹⁾	Weight [oz]	Part No.	Type
1-1/4	1.8	0.3	0.4	1.3	2.5	3.1	0.6	5.1	2	8.6	32940	FNG-32
1-5/8	2.1	0.4	0.4	1.4	2.8	3.5	0.8	5.7	2	10.2	32941	FNG-40
2	2.6	0.4	0.5	1.8	3.5	4.3	1.0	6.1	2	18.3	32942	FNG-50
2-1/2	3.0	0.4	0.5	2.0	3.9	4.7	1.0	6.7	2	24.3	32943	FNG-63
3	3.7	0.5	0.6	2.5	5.0	5.9	1.2	7.5	2	58.6	32944	FNG-80
4	4.3	0.6	0.6	3.0	5.9	6.9	1.4	8.1	2	84.5	32945	FNG-100
5	5.5	0.6	0.8	3.5	7.1	8.7	1.8	9.6	2	160.8	32946	FNG-125
6	7.1	0.7	0.8	4.5	9.1	11.0	2.4	11.0	2	218.7	34478	FNG-160

1) Corrosion resistance class 2 according to Festo standard 940 070

Components with moderate corrosion resistance for use in normal industrial environments subjected to contact with coolants or lubricating agents.

Dimensions are in inches, unless otherwise noted.

Tie rod cylinders DNG/DNGL/DNGZK - Inch Series

Accessories

FESTO


Trunnion flange ZNG

for trunnion mounting

Material:

Corrosion resistant cast steel

Free of copper, PTFE and silicone



+ = plus stroke length

Dimensions and ordering data													
For Ø [in]	C2	C3	TD Ø	TK	TL	TM	UW	XH	XL	CRC ¹⁾	Weight [oz]	Part No.	Type
1-1/4	2.8	3.4	0.5	0.6	0.5	2.0	2.0	0.7	5.0	2	6.7	31754	ZNG-32
1-5/8	3.4	4.1	0.6	0.8	0.6	2.5	2.2	0.8	5.7	2	11.6	31755	ZNG-40
2	3.9	4.6	0.6	0.9	0.6	3.0	2.6	1.0	6.1	2	18.9	31756	ZNG-50
2-1/2	4.6	5.4	0.8	0.9	0.8	3.5	3.0	1.0	6.7	2	28.2	31757	ZNG-63
3	5.4	6.1	0.8	1.1	0.8	4.3	3.9	1.3	7.4	2	48.7	31758	ZNG-80
4	6.5	7.4	1.0	1.5	1.0	5.2	4.7	1.3	8.2	2	96.8	31759	ZNG-100
5	7.6	8.5	1.0	2.0	1.0	6.3	5.9	1.6	9.8	2	179.9	31760	ZNG-125


1) Corrosion resistance class 2 according to Festo standard 940 070

Components with moderate corrosion resistance for use in normal industrial environments subjected to contact with coolants or lubricating agents.

Trunnion support LN2G

Material:

Galvanized steel



Dimensions and ordering data													
For Ø [in]	CR Ø	DA Ø	FK Ø	FN	FS	H1	HB Ø	KE	NH	TH	UL	CRC ¹⁾	Weight [oz]
1-1/4	0.5	0.4	0.6	1.2	0.4	0.6	0.3	0.3	0.7	1.3	1.8	2	4.4
1-5/8, 2	0.6	0.6	0.7	1.4	0.5	0.7	0.4	0.4	0.8	1.4	2.2	2	14.1
2-1/2, 3	0.8	0.7	0.8	1.6	0.5	0.8	0.4	0.4	0.9	1.7	2.6	2	16.9
4, 5	1.0	0.8	1.0	2.0	0.6	1.0	0.5	0.5	1.1	2.0	3.0	2	33.9
6	1.3	1.0	1.2	2.4	0.9	1.4	0.7	0.7	1.6	2.4	3.6	2	69.3

1) Corrosion resistance class 2 according to Festo standard 940 070

Components with moderate corrosion resistance for use in normal industrial environments subjected to contact with coolants or lubricating agents.

Dimensions are in inches, unless otherwise noted.

Tie rod cylinders DNG/DNGL/DNGZK - Inch Series

Accessories


FESTO

Swivel flange SNG

for clevis foot LSNG/LSNSG

Material:

Die-cast aluminum



Dimensions and ordering data											
For Ø [in]	CG	CP	EK Ø	FL	L	SR	XC	CRC ¹⁾	Weight [oz]	Part No.	Type
1-1/4	0.6	1.3	0.4	0.9	0.5	0.4	5.6	2	6.7	32968	SNG-32
1-5/8	0.6	1.6	0.5	1.0	0.6	0.5	6.3	2	9.5	32969	SNG-40
2	0.8	1.8	0.6	1.1	0.6	0.6	6.7	2	15.7	32970	SNG-50
2-1/2	0.8	2.0	0.6	1.3	0.8	0.7	7.5	2	23.8	32971	SNG-63
3	1.0	2.6	0.8	1.4	0.9	0.8	8.3	2	44.6	32972	SNG-80
4	1.0	3.0	0.8	1.6	1.1	0.9	9.1	2	63.1	32973	SNG-100
5	1.5	3.8	1.2	2.0	1.2	1.0	10.8	2	141.1	32974	SNG-125
6	1.7	4.8	1.4	2.2	1.4	1.3	12.4	2	231.3	152597	SNG-160

1) Corrosion resistance class 2 according to Festo standard 940 070


Components with moderate corrosion resistance for use in normal industrial environments subjected to contact with coolants or lubricating agents.

Swivel flange SNGB

for clevis foot LN/LSN

Material:

Die-cast aluminum



Dimensions and ordering data											
For Ø [in]	CB Ø	CD Ø	FL	L	ML	MR	UB	XC	CRC ¹⁾	Weight [oz]	Part No. Type
1-1/4	1.0	0.4	0.9	0.5	2.2	0.4	1.8	5.6	2	4.4	34540 SNGB-32
1-5/8	1.1	0.5	1.0	0.6	2.5	0.5	2.0	6.3	2	6.2	34541 SNGB-40
2	1.3	0.5	1.1	0.6	2.8	0.5	2.4	6.7	2	8.6	34542 SNGB-50
2-1/2	1.6	0.6	1.3	0.8	3.3	0.6	2.8	7.5	2	13.4	34543 SNGB-63
3	2.0	0.6	1.4	0.9	4.1	0.6	3.5	8.3	2	21.5	34544 SNGB-80
4	2.4	0.8	1.6	1.1	5.0	0.8	4.3	9.1	2	36.7	34545 SNGB-100
5	2.8	1.0	2.0	1.2	5.8	1.0	5.1	10.8	2	61.7	34546 SNGB-125
6	3.5	1.2	2.2	1.4	7.4	1.0	6.7	12.4	2	109.3	34547 SNGB-160

1) Corrosion resistance class 2 according to Festo standard 940 070

Components with moderate corrosion resistance for use in normal industrial environments subjected to contact with coolants or lubricating agents.

Dimensions are in inches, unless otherwise noted.

Tie rod cylinders DNG/DNGL/DNGZK - Inch Series


Accessories

FESTO

Swivel flange SSNG

with spherical bearing
for clevis foot LBG

Material:
Nodular graphite cast iron




Dimensions and ordering data

For Ø [in]	CN Ø	EP	EX	FL	LT	MS	XC	CRC ¹⁾	Weight [oz]	Part No.	Type
1-1/4	0.4	0.4	0.6	0.9	-	0.6	5.6	2	6.9	34291	SSNG-32
1-5/8	0.5	0.5	0.6	1.0	-	0.7	6.3	2	9.0	34292	SSNG-40
2	0.6	0.6	0.8	1.1	-	0.8	6.7	2	15.2	34293	SSNG-50
2-1/2	0.6	0.6	0.8	1.3	0.7	0.9	7.5	2	19.9	34294	SSNG-63
3	0.8	0.7	1.0	1.4	0.8	1.1	8.3	2	33.2	34295	SSNG-80
4	0.8	0.7	1.0	1.6	0.9	1.2	9.1	2	53.3	34296	SSNG-100
5	1.2	1.0	1.5	2.0	1.1	1.6	10.8	2	108.7	34568	SSNG-125

1) Corrosion resistance class 2 according to Festo standard 940 070
Components with moderate corrosion resistance for use in normal industrial environments subjected to contact with coolants or lubricating agents.

Swivel flange SNGL

Material:
Die-cast aluminum



Dimensions and ordering data

For Ø [in]	CD Ø	EW	FL	L	MR	XC	CRC ¹⁾	Weight [oz]	Part No.	Type
1-1/4	0.4	1.0	0.9	0.5	0.4	5.6	2	2.6	151527	SNGL-32
1-5/8	0.5	1.1	1.0	0.6	0.5	6.3	2	3.7	151528	SNGL-40
2	0.5	1.3	1.1	0.6	0.5	6.7	2	6.5	151529	SNGL-50
2-1/2	0.6	1.6	1.3	0.8	0.6	7.5	2	9.5	151530	SNGL-63
3	0.6	2.0	1.4	0.9	0.6	8.3	2	17.7	151531	SNGL-80
4	0.8	2.4	1.6	1.1	0.8	9.1	2	27.1	151532	SNGL-100
5	1.0	2.8	2.0	1.2	1.0	10.8	2	50.5	151533	SNGL-125
6	1.2	3.5	2.2	1.4	1.0	12.4	2	79.4	151534	SNGL-160


1) Corrosion resistance class 2 according to Festo standard 940 070
Components with moderate corrosion resistance for use in normal industrial environments subjected to contact with coolants or lubricating agents.

Dimensions are in inches, unless otherwise noted.

Tie rod cylinders DNG/DNGL/DNGZK - Inch Series

Accessories

FESTO


Ordering data – Mounting attachments							
Designation	For Ø [in]	Part No.	Type	Designation	For Ø [in]	Part No.	Type
Clevis foot LSNG				Weld-on clevis foot LSNSG			
	1-1/4	31740	LSNG-32		1-1/4	31747	LSNSG-32
	1-5/8	31741	LSNG-40		1-5/8	31748	LSNSG-40
	2	31742	LSNG-50		2	31749	LSNSG-50
	2-1/2	31743	LSNG-63		2-1/2	31750	LSNSG-63
	3	31744	LSNG-80		3	31751	LSNSG-80
	4	31745	LSNG-100		4	31752	LSNSG-100
	5	31746	LSNG-125		5	31753	LSNSG-125
	6	152599	LSNG-160		6	–	
Clevis foot LBG				Clevis foot LNG			
	1-1/4	31761	LBG-32		1-1/4	33890	LNG-32
	1-5/8	31762	LBG-40		1-5/8	33891	LNG-40
	2	31763	LBG-50		2	33892	LNG-50
	2-1/2	31764	LBG-63		2-1/2	33893	LNG-63
	3	31765	LBG-80		3	33894	LNG-80
	4	31766	LBG-100		4	33895	LNG-100
	5	31767	LBG-125		5	33896	LNG-125
	6	–			6	–	
Clevis foot LSN				Clevis foot, right-angled LQG			
	1-1/4	5561	LSN-32		1-1/4	31768	LQG-32
	1-5/8	5562	LSN-40		1-5/8	31769	LQG-40
	2	5563	LSN-50		2	31770	LQG-50
	2-1/2	5564	LSN-63		2-1/2	31771	LQG-63
	3	5565	LSN-80		3	31772	LQG-80
	4	5566	LSN-100		4	31773	LQG-100
	5	6987	LSN-125		5	31774	LQG-125
	6	6988	LSN-160		6	–	


Ordering data – One-way flow control valves				
	Connection		Part No.	Type
	Thread	For tubing OD		
	1/8 NPT	5/32"	165009	GRLA-1/8-NPT-QS-5/32-U
		3/16"	190941	GRLA-1/8-NPT-QS-3/16-U
		1/4"	165010	GRLA-1/8-NPT-QS-1/4-U
		5/16"	165013	GRLA-1/8-NPT-QS-5/16-U
	1/4 NPT	3/16"	190944	GRLA-1/4-NPT-QS-3/16-U
		1/4"	165011	GRLA-1/4-NPT-QS-1/4-U
		5/16"	165014	GRLA-1/4-NPT-QS-5/16-U
		3/8"	190947	GRLA-1/4-NPT-QS-3/8-U
	3/8 NPT	1/4"	165012	GRLA-3/8-NPT-QS-1/4-U
		5/16"	165015	GRLA-3/8-NPT-QS-5/16-U
		3/8"	190950	GRLA-3/8-NPT-QS-3/8-U
		1/2"	190951	GRLA-3/8-NPT-QS-1/2-U
	1/2 NPT	3/8"	190952	GRLA-1/2-NPT-QS-3/8-U
		1/2"	190953	GRLA-1/2-NPT-QS-1/2-U

Tie rod cylinders DNG/DNGL/DNGZK - Inch Series

Accessories

FESTO

Ordering data – Piston rod attachments							
Designation	For Ø [in]	Part No.	Type	Designation	For Ø [in]	Part No.	Type
Rod eye SGS				Self-aligning rod coupler FK			
	1-1/4	532696	SGS-3/8-24		1-1/4	532705	FK-3/8-24
	1-5/8	532697	SGS-1/2-20		1-5/8	532706	FK-1/2-20
	2	532698	SGS-5/8-18		2	532707	FK-5/8-18
	2-1/2				2-1/2		
	3	532699	SGS-3/4-16		3	532708	FK-3/4-16
	4				4		
	5	532700	SGS-1-12		4	532709	FK-1-12
	6	532701	SGS-1 1/2-12		6	532710	FK-1 1/2-12
Rod clevis SG				Coupling piece KSZ			
	1-1/4	546540	SG-3/8"-24-B		1-1/4	36129	KSZ-3/8-24-UNF
	1-5/8	546545	SG-1/2-20-B		1-5/8	36130	KSZ-1/2-20-UNF
	2	546575	SG-5/8-18-B		2	36131	KSZ-5/8-18-UNF
	2-1/2				2-1/2		
	3	546576	SG-3/4-16-B		3	36132	KSZ-3/4-16-UNF
	4				4		
	5	-	-		5	-	-
	6						

Ordering data – Guide units for variable strokes					
	For Ø [in]	Stroke [in]	With recirculating ball bearing guide		With plain bearing guide
			Part No.	Type	Part No. Type
	1-1/4	0.39 ... 20	151746	FENG-1 1/4"-...-KF	151740 FENG-1 1/4"-...-
	1-5/8	0.39 ... 20	151747	FENG-1 5/8"-...-KF	151741 FENG-1 5/8"-...-
	2	0.39 ... 20	151748	FENG-2"-...-KF	151742 FENG-2"-...-
	2-1/2	0.39 ... 20	151749	FENG-2 1/2"-...-KF	151743 FENG-2 1/2"-...-
	3	0.39 ... 20	151750	FENG-3"-...-KF	151744 FENG-3"-...-
	4	0.39 ... 20	151751	FENG-4"-...-KF	151745 FENG-4"-...-

Tie rod cylinders DNG/DNGL/DNGZK - Inch Series

Accessories

FESTO

Ordering data – Block-shaped proximity sensor, magneto-resistive							
	Mounting	Switch output	Electrical connection		Cable length [ft]	Part No.	Type
			Cables	M8 plug			
NO contact							
	Via mounting kit	PNP	3-wire	–	8.2	151683	SMT0-1-PS-K-LED-24-C
			–	3-pin	–	151685	SMT0-1-PS-S-LED-24-C
		NPN	3-wire	–	8.2	151684	SMT0-1-NS-K-LED-24-C
			–	3-pin	–	151686	SMT0-1-NS-S-LED-24-C

Ordering data – Block-shaped proximity sensor, magnetic reed						
	Mounting	Electrical connection		Cable length [ft]	Part No.	Type
		Cables	M8 plug			
NO contact						
	Via mounting kit	3-wire	–	8.2	30459	SME0-1-LED-24-B
		3-wire	–	16.4	151672	SME0-1-LED-24-K5-B
		–	3-pin	–	150848	SME0-1-S-LED-24-B

Ordering data – Block-shaped proximity sensor, pneumatic				
	Mounting	Pneumatic connection	Part No.	Type
3/2-way valve, normally closed				
	Via mounting kit	Barbed fitting for tubing ID of 1/8 inch	31008	SMPO-1-H-B

Ordering data – Sensor mounting kit				
	For Ø [in]	Mounting	Part No.	Type
	1-1/4 ... 2	Directly on the mounting or tie rod	36162	SMB-2-B
	5 ... 6			
	2-1/2 ... 4		36163	SMB-3-B
	1-1/4 ... 4	On the cylinder barrel via clamping strap	151226	SMBS-2

Ordering data – Plug sockets							
	Mounting	Switch output		Connection	Cable length [ft]	Part No.	Type
		PNP	NPN				
Straight socket							
	M8 union nut			3-pin	8.2	159420	SIM-M8-3GD-2.5-PU
					16.4	159421	SIM-M8-3GD-5-PU
Angled plug socket							
	M8 union nut			3-pin	8.2	159422	SIM-M8-3WD-2.5-PU
					16.4	159423	SIM-M8-3WD-5-PU

Festo - Your Partner in Automation



1 Festo Inc.
5300 Explorer Drive
Mississauga, ON L4W 5G4
Canada

Festo Customer Interaction Center
Tel: 1 877 463 3786
Fax: 1 877 393 3786
Email: customer.service.ca@festo.com



2 Festo Pneumatic
Av. Ceylán 3,
Col. Tequesquináhuac
54020 Tlalnepantla,
Estado de México

Multinational Contact Center
01 800 337 8669
ventas.mexico@festo.com



3 Festo Corporation
1377 Motor Parkway
Suite 310
Islandia, NY 11749

Festo Customer Interaction Center
1 800 993 3786
1 800 963 3786
customer.service.us@festo.com



4 Regional Service Center
7777 Columbia Road
Mason, OH 45040

Connect with us

www.festo.com/socialmedia



www.festo.com

Subject to change