




Shut-off valves HE

FESTO



Product range overview and type codes

Product range overview

Design	Type	Pneumatic connection		Valve function		qnN
		1	2	2/2-way valve	3/2-way valve	[l/min]
Push-in connector at both ends						
	HE	QS-6	QS-6	■	■	256.5
		QS-8	QS-8			415.8
		QS-10	QS-10			752.4
		QS-12	QS-12			788.4
Male thread/push-in connector						
	HE	R1/8	QS-6	■	■	279.9
		R1/4	QS-8			423.9
		R3/8	QS-10			760.5
		R1/2	QS-12			834.3
Male thread at both ends						
	HE	R1/8	R1/8	-	■	369.9
		R1/4	R1/4			625.5
		R3/8	R3/8			797.4

Type codes

001	Series
HE	Shut-off valve


002	Valve function
2	2/2-way valve
3	3/2-way valve

003	Pneumatic connection 1
1/8	Male thread R1/8
1/4	Male thread R1/4
3/8	Male thread R3/8
1/2	Male thread R1/2
QS-6	Push-in connector 6 mm
QS-8	Push-in connector 8 mm
QS-10	Push-in connector 10 mm
QS-12	Push-in connector 12 mm


004	Pneumatic connection 2
	Same size push-in connector as pneumatic connection 1
1/8	Male thread R1/8
1/4	Male thread R1/4
3/8	Male thread R3/8
QS-6	Push-in connector 6 mm
QS-8	Push-in connector 8 mm
QS-10	Push-in connector 10 mm
QS-12	Push-in connector 12 mm

Data sheet


HE-2



HE-3



- - Standard nominal flow rate
256.5 ... 834.3 l/min
- - Temperature range
0 ... +60°C
- - Operating pressure
-0.095 ... 1 MPa



General technical data – HE-2

General technical data – HE 2		QS-6	QS-8	QS-10	QS-12	R1/8	R1/4	R3/8	R1/2
Pneumatic connection 1		QS-6	QS-8	QS-10	QS-12	QS-6	QS-8	QS-10	QS-12
Pneumatic connection 2		QS-6	QS-8	QS-10	QS-12	QS-6	QS-8	QS-10	QS-12
Nominal width	Diameter [mm]	4.6	3.2	3.5	4.6	4.7	2.4	3.2	3.5
Design		Piston spool valve							
Type of mounting		In-line installation				Direct mounting via thread			
		Direct mounting via through-hole							
Mounting position		Any							
Valve function		2/2-way, bistable							
Actuation type		Manual							
Type of control		Direct							
Flow direction		Non-reversible							
Sealing principle		Soft							

General technical data – HE-3

General technical data – NE 5		QS-6	QS-8	QS-10	QS-12	R1/8		R1/4		R3/8		R1/2
Pneumatic connection 1												
Pneumatic connection 2		QS-6	QS-8	QS-10	QS-12	QS-6	R1/8	QS-8	R1/4	QS-10	R3/8	QS-12
Pneumatic connection 3		Not ducted										
Nominal width	Diameter [mm]	4.5	4.7	2.6	3.3	4.6	3	4.7	3.5	3.5	4.6	3.6
Design		Piston spool valve										
Type of mounting		In-line installation					Direct mounting via thread					
		Direct mounting via through-hole										
Mounting position		Any										
Valve function		3/2-way, bistable										
Actuation type		Manual										
Exhaust function		Cannot be throttled										
Type of control		Direct										
Flow direction		Non-reversible										
Sealing principle		Soft										

Operating and environmental conditions

Operating pressure	[MPa]	-0.095 ... 1
	[bar]	-0.95 ... 10
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-]	
Note on operating/ pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)	
Ambient temperature	[°C]	0 ... +60
Temperature of medium	[°C]	0 ... +60
Corrosion resistance class CRC ¹⁾	2	

1) Corrosion resistance class CRC 2 to Festo standard FN 940070


Moderate corrosion stress. Indoor applications in which condensation can occur. External visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment.

Materials

Materials								
Pneumatic connection 1	QS-6	QS-8	QS-10	QS-12	R1/8	R1/4	R3/8	R1/2
Housing	Reinforced PBT							
Screwed trunnion	–				Nickel-plated brass			
Seals	NBR							
Note on materials	RoHS-compliant							

Data sheet


Dimensions – Push-in connector, both ends

Download CAD data → www.festo.com

→ Flow direction (indicated by the arrow)

Type	B1	D1 ø	D2 ø	D3 ø	D4 ø	D5 ø	D6 ø	H1	H2	H3	L1	L2	L3	L4
HE-...-QS-6	17	6	6	4.2	16.5	12.5	12.5	40.5	8	10.5	52.7	26.4	26.4	18
HE-...-QS-8	17	8	8	4.2	16.5	15	15	40.5	8	10.5	55.4	27.7	27.7	18
HE-...-QS-10	21.7	10	10	4.2	19.5	17.5	17.5	41	11	10.5	64.4	32.2	32.2	24
HE-...-QS-12	21.7	12	12	4.2	19.5	21	21	41	11	10.5	69.8	34.9	34.9	24

Dimensions – Male thread/push-in connector


Download CAD data → www.festo.com

→ Flow direction (indicated by the arrow)

Type	B1	D1	D2 ø	D3 ø	D4 ø	D6 ø	H1	H2	H3	L1	L2	L3	L4	L5	≈G 1
HE-...-1/8-QS-6	17	R1/8	6	4.2	16.5	12.5	40.5	8	10.5	59.9	29.5	26.4	18	8	12
HE-...-1/4-QS-8	17	R1/4	8	4.2	16.5	15	40.5	8	10.5	64.2	30.5	27.7	18	11	14
HE-...-3/8-QS-10	21.7	R3/8	10	4.2	19.5	17.5	41	11	10.5	75.7	37	32.2	24	12	17
HE-...-1/2-QS-12	21.7	R1/2	12	4.2	19.5	21	41	11	10.5	81.4	38.5	34.9	24	15	21

Data sheet






Dimensions – Male thread at both ends

Download CAD data → www.festo.com

→ Flow direction (indicated by the arrow)

Type	B1	D1	D2	D3 ø	D4 ø	H1	H2	H3	L1	L2	L3	L4	L5	L6	1	2
HE-3-1/8-1/8	17	R1/8	R1/8	4.2	16.5	40.5	8	10.5	67	29.5	29.5	18	8	8	12	12
HE-3-1/4-1/4	21.7	R1/4	R1/4	4.2	19.5	41	11	10.5	85	36.5	36.5	24	11	11	14	14
HE-3-3/8-3/8	21.7	R3/8	R3/8	4.2	19.5	41	11	10.5	87	37.2	37.2	24	12	12	17	17

Ordering data

Design		Pneumatic connection		Standard nominal flow rate q _{nN} [l/min]	Weight [g]	Part no.	Type
		1	2				
2/2-way valve							
	Push-in connector at both ends	QS-6	QS-6	256.5	23	153467	HE-2-QS-6
		QS-8	QS-8	415.8	26	153468	HE-2-QS-8
		QS-10	QS-10	752.4	41	153469	HE-2-QS-10
		QS-12	QS-12	788.4	47	153470	HE-2-QS-12
	Male thread/push-in connector	R1/8	QS-6	279.9	29	153471	HE-2-1/8-QS-6
		R1/4	QS-8	423.9	36	153472	HE-2-1/4-QS-8
		R3/8	QS-10	760.5	60	153473	HE-2-3/8-QS-10
		R1/2	QS-12	834.3	86	153474	HE-2-1/2-QS-12
3/2-way valve							
	Push-in connector at both ends	QS-6	QS-6	256.5	23	153475	HE-3-QS-6
		QS-8	QS-8	415.8	26	153476	HE-3-QS-8
		QS-10	QS-10	752.4	41	153477	HE-3-QS-10
		QS-12	QS-12	788.4	47	153478	HE-3-QS-12
	Male thread/push-in connector	R1/8	QS-6	279.9	29	153479	HE-3-1/8-QS-6
		R1/4	QS-8	423.9	36	153480	HE-3-1/4-QS-8
		R3/8	QS-10	760.5	60	153481	HE-3-3/8-QS-10
		R1/2	QS-12	834.3	86	153482	HE-3-1/2-QS-12
	Male thread at both ends	R1/8	R1/8	369.9	35	153296	HE-3-1/8-1/8
		R1/4	R1/4	625.5	58	153297	HE-3-1/4-1/4
		R3/8	R3/8	797.4	79	153298	HE-3-3/8-3/8

Festo - Your Partner in Automation



1 Festo Inc.
5300 Explorer Drive
Mississauga, ON L4W 5G4
Canada

Festo Customer Interaction Center
Tel: 1 877 463 3786
Fax: 1 877 393 3786
Email: customer.service.ca@festo.com



2 Festo Pneumatic
Av. Ceylán 3,
Col. Tequesquináhuac
54020 Tlalnepantla,
Estado de México

Multinational Contact Center
01 800 337 8669
ventas.mexico@festo.com



3 Festo Corporation
1377 Motor Parkway
Suite 310
Islandia, NY 11749

Festo Customer Interaction Center
1 800 993 3786
1 800 963 3786
customer.service.us@festo.com



4 Regional Service Center
7777 Columbia Road
Mason, OH 45040

Connect with us

www.festo.com/socialmedia



www.festo.com

Subject to change