

Connecting cables for valves, plug pattern ZC, self-tapping screw

Type codes

		NEBV	-	Z3	WA	2	L	-	R	-	E	-	5	-	N	-	LE	2	-	S1
Function																				
NEBV	Connecting cables for valves																			
Connection technology on left, field device side																				
Z3	Socket, plug pattern ZC, self-tapping screw																			
Cable outlet left																				
WA	Angled 45°																			
Number of pins/wires, left																				
2	2-pin																			
Display																				
L	Signal status LED																			
Circuitry																				
R	Holding current reduction with integrated protective circuit																			
Cable characteristic																				
E	Suitable for energy chains																			
Cable length																				
2,5	2.5 m																			
5	5 m																			
10	10 m																			
Cable designation																				
N	Without inscription label holder																			
Connection technology on right, controller side																				
LE	Open end																			
Number of pins/wires, right																				
2	2-wire																			
Degree of protection for electrics																				
S1	IP65																			


Connecting cables for valves, plug pattern ZC, self-tapping screw

FESTO

Technical data

Connecting cable NEBV-Z3WA2L

- Connecting cable
- Pre-assembled at both ends
- For connecting valves



General technical data	
Electrical connection 1	
Function	Field device side
Connection type	Socket
Cable outlet	Angled
Constructional design	Square
Connection technology	Plug pattern ZC, self-tapping screw
Number of pins/wires	2
Assigned pins/wires	2
Type of mounting	On solenoid valve via self-tapping screw
Signal status display	Yellow LED
Additional functions	Holding current reduction, protective circuit
Electrical connection 2	
Function	Controller side
Connection type	Cable
Connection technology	Open end
Number of pins/wires	2
Assigned pins/wires	2

Technical data – Electrical		
Nominal operating voltage	[V DC]	24
Operating voltage range	[V DC]	20.4 ... 26.4
Surge resistance	[kV]	2.4
Degree of contamination		3
Connection frequency		50
Protection against polarity reversal		Bipolar
Protective earth connection		Not present

Technical data – Cable		
Cable composition	[mm ²]	2 x 0.14
Cable diameter	[mm]	2.9
Cable diameter tolerance	[%]	±0.1
Conductor nominal cross section	[mm ²]	0.14
Cable characteristic		Suitable for use with energy chains
Cable test conditions		Test conditions on request
Bending radius, flexible cable installation	[mm]	≥29
Cable identification		Without inscription label holder

Connecting cables for valves, plug pattern ZC, self-tapping screw

FESTO

Technical data

Materials	
Housing	TPE-U(PU)
Housing colour	Black
Insulating sheath	PP
Screws	Steel
Pin contacts	Tin-plated copper alloy
Cable sheath	TPE-U (PUR)
Cable sheath colour	Grey
Note on materials	RoHS compliant

Operating and environmental conditions	
Ambient temperature [°C]	−10 ... +50
CE marking (see declaration of conformity)	To EU EMC Directive ¹⁾
Degree of protection	IP65
Note on degree of protection	In mounted state


- 1) For information about the applicability of the component see the manufacturer's EC declaration of conformity at: www.festo.com/sp → User documentation.
If the component is subject to restrictions on usage in residential, office or commercial environments or small businesses, further measures to reduce the emitted interference may be necessary.

Circuitry(socket/plug view)				
Electrical connection 1	Pin	Wire colour ¹⁾	Pin	Electrical connection 2
	1	BK	–	Open end
	2	BK	–	

- 1) To IEC 757

Dimensions

[Download CAD data → www.festo.com](http://www.festo.com)



1 Mounting screw

2 Wire-end sleeve

3 Cable, length depending on order

Type	B1	D1 Ø	H1	H2	L1	L2	L3	L5
NEBV-Z3WA2L	9.7	2.9	12	17.5	26.9	19	50	8.4

Connecting cables for valves, plug pattern ZC, self-tapping screw

Technical data

Ordering data				
Electrical connection	Cable length [m]	Weight [g]	Part No.	Type
Angled socket, plug pattern ZC, self-tapping screw	2.5	50	8047676	NEBV-Z3WA2L-R-E-2.5-N-LE2-S1
	5	90	8047677	NEBV-Z3WA2L-R-E-5-N-LE2-S1
	10	170	8047675	NEBV-Z3WA2L-R-E-10-N-LE2-S1

Connecting cables for valves, plug pattern ZC, self-tapping screw

Ordering data – Modular product system

Ordering table				
		Condi- tions	Code	Entry code
[M] Module no.	8003577			
Connecting cable	Connecting cables for valves		NEBV	NEBV
Connection technology on left, field device side	Socket, plug pattern ZC, self-tapping screw		-Z3	-Z3
Cable outlet, left	Angled 45°		WA	WA
Number of pins/wires, left	2-pin		2	2
Display	Signal status LED		L	L
Circuitry	Holding current reduction with integrated protective circuit		-R	-R
Cable characteristic	Suitable for use with energy chains		-E	-E
Line length	[m] 2.5		-2,5	
	[m] 5		-5	
	[m] 10		-10	
Cable identification	Without inscription label holder		-N	-N
Connection technology on right, control side	Open end		-LE	-LE
Number of pins/wires, right	2-pin		2	2
Degree of protection for electrics	IP65		-S1	-S1

[M] Mandatory data

[O] Options

Transfer order code

8003577 NEBV - Z3 WA 2 L - R - E - N - LE 2 - S1

Festo - Your Partner in Automation



1 Festo Inc.
5300 Explorer Drive
Mississauga, ON L4W 5G4
Canada

Festo Customer Interaction Center
Tel: 1 877 463 3786
Fax: 1 877 393 3786
Email: customer.service.ca@festo.com



2 Festo Pneumatic
Av. Ceylán 3,
Col. Tequesquináhuac
54020 Tlalnepantla,
Estado de México

Multinational Contact Center
01 800 337 8669
ventas.mexico@festo.com



3 Festo Corporation
1377 Motor Parkway
Suite 310
Islandia, NY 11749

Festo Customer Interaction Center
1 800 993 3786
1 800 963 3786
customer.service.us@festo.com



4 Regional Service Center
7777 Columbia Road
Mason, OH 45040

Connect with us

www.festo.com/socialmedia



www.festo.com

Subject to change