





Pressure regulator VRPA

FESTO



Product range overview and type codes

Product range overview

Design	Version	Type	Pneumatic connection		Standard nominal flow rate [l/min]	
			1	2		
Inline	Without pressure gauge					
		VRPA-C	QS-4	QS-4	80	
			QS-6	QS-6	90	
			QS-8	QS-8	130	
	With pressure gauge, pressure gauge scale in MPa					
		VRPA-CM	QS-4	QS-4	80	
			QS-6	QS-6	90	
			QS-8	QS-8	130	
	L-shape	With pressure gauge, pressure gauge scale in MPa				
			VRPA-LM	M5	QS-4	80
QS-6					90	
R1/8				QS-4	90	
				QS-6	100	
R1/4				QS-8	130	
				QS-6	115	
		QS-8	130			


Type codes

001	Series	
VRPA	Pressure regulator	
002	Design	
C	Inline	
L	L-shape	
003	Pressure indication	
	Without pressure gauge	
M	With pressure gauge	

004	Pneumatic connection 1	
Q4	Push-in connector 4 mm	
Q6	Push-in connector 6 mm	
Q8	Push-in connector 8 mm	
M5	M5	
R18	R1/8	
R14	R1/4	
005	Pneumatic connection 2	
Q4	Push-in connector 4 mm	
Q6	Push-in connector 6 mm	
Q8	Push-in connector 8 mm	
E	Same size as connection 1	

Data sheet


Inline, with/without pressure gauge



-  - Standard nominal flow rate
80 ... 130 l/min



L-shape, with pressure gauge



-  - Standard nominal flow rate
80 ... 130 l/min



General technical data

General technical data						
Pneumatic connection 1	QS-4	QS-6	QS-8	M5	R1/8	R1/4
Pneumatic connection 2	QS-4	QS-6	QS-8	QS-4, QS-6	QS-4, QS-6, QS-8	QS-6, QS-8
Controller function	Outlet pressure constant, with secondary venting, with return flow action					
Pressure regulation range	[MPa]	0.1 ... 0.8				
Actuation type	Manual					
Mounting position	Any					
Adjusting element	Rotary knob with detent					
Pressure indicator	With/without pressure gauge			With pressure gauge		
Type of mounting	With through-hole			Screw-in		
Type of seal on screwed trunnion	–			Sealing ring	Coating	
Rotatability	–			360°/continuous rotation not permitted		
Nominal tightening torque	[Nm]	–		0.8 ±20%	–	

Operating and environmental conditions


Operating pressure	See graph → page 4
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on the operating/pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Ambient temperature [°C]	0 ... +60

Materials

Pneumatic connection 1	QS-4	QS-6	QS-8	M5	R1/8	R1/4
Housing	PBT					
Screwed trunnion	–			Nickel-plated brass		
Threaded seal	–				PTFE	
Static seals	NBR					
Note on materials	RoHS-compliant					

Data sheet


Operating pressure p as a function of temperature t




Dimensions – Inline

Download CAD data → www.festo.com

VRPA-C, without pressure gauge



VRPA-CM, with pressure gauge



Type	B1	B2	B3	B4	B5	B6	B7	B8	B9	B10	B11	D1 ø	D2 ø
VRPA-C-Q4-E	44.4	22.2	30	15	20.6	10.3	9	1	15	–	–	4	11.5
VRPA-C-Q6-E	44.6	22.3	30	15	20.6	10.3	9	1	15	–	–	6	11.5
VRPA-C-Q8-E	57.2	28.6	39.6	19.8	23.4	11.7	13	1	19	–	–	8	15.5
VRPA-CM-Q4-E	53.4	22.2	30	15	20.2	10.1	9	1	15	10.2	1	4	11.5
VRPA-CM-Q6-E	53.6	22.3	30	15	20.2	10.1	9	1	15	10.2	1	6	11.5
VRPA-CM-Q8-E	61.5	28.6	39.7	19.9	23.2	11.6	13	1	19	9.1	0	8	15.5


Type	D3 ø	D4 ø	D5 ø	D6 ø	L1		L2	L3	L4	L5	L6	L7	T1
					Unlocked	Locked							
VRPA-C-Q4-E	15	14.2	3.3	–	61.4	58.9	24.5	13	18.8	17	4.2	–	11.6
VRPA-C-Q6-E	15	14.2	3.3	–	61.4	58.9	24.5	13	18.8	17	4.2	–	11.9
VRPA-C-Q8-E	19	14.2	3.3	–	65.5	63	28.4	15	22.5	21.5	4	–	18.1
VRPA-CM-Q4-E	15	14.2	3.3	15	61.4	58.9	24.5	13	18.8	17	4.2	43.3	11.6
VRPA-CM-Q6-E	15	14.2	3.3	15	61.4	58.9	24.5	13	18.8	17	4.2	43.3	11.9
VRPA-CM-Q8-E	19	14.2	3.3	15	65.5	63	28.4	15	22.5	21.3	4.1	49.8	18.1

Data sheet

Dimensions – L-shape

Download CAD data → www.festo.com




VRPA-LM, with pressure gauge



Type	B2	B12	D1 ø	D2 ø	D3 ø	D4 ø	D6 ø
VRPA-LM-M5-Q4	26.9	16.2	4	11.5	15	14.2	15
VRPA-LM-M5-Q6	27	16.2	6	11.5	15	14.2	15
VRPA-LM-R18-Q4	26.9	16.2	4	11.5	15	14.2	15
VRPA-LM-R18-Q6	27	16.2	6	11.5	15	14.2	15
VRPA-LM-R18-Q8	28.4	16.2	8	15.5	15	14.2	15
VRPA-LM-R14-Q6	30	17.7	6	15.5	19	14.2	15
VRPA-LM-R14-Q8	29.9	17.7	8	15.5	19	14.2	15

Type	L1		L4	L7	L8		L9	L10	R1	T1	≈ 1
	Unlocked	Locked			Unlocked	Locked					
VRPA-LM-M5-Q4	69.8	67.3	24.2	48.7	66.8	64.3	3	6	M5x0.8	11.6	14
VRPA-LM-M5-Q6	69.8	67.3	24.2	48.7	66.8	64.3	3	6	M5x0.8	11.9	14
VRPA-LM-R18-Q4	71.3	68.8	24.7	49.2	67.3	64.8	8	5	R1/8	11.6	14
VRPA-LM-R18-Q6	71.3	68.8	24.7	49.2	67.3	64.8	8	5	R1/8	11.9	14
VRPA-LM-R18-Q8	71.3	68.8	24.7	52	67.3	64.8	8	5	R1/8	18.1	14
VRPA-LM-R14-Q6	78	75.5	29	56.3	72	69.5	11	6	R1/4	17	17
VRPA-LM-R14-Q8	78	75.5	29	56.3	72	69.5	11	6	R1/4	18.1	17

Data sheet

Ordering data						
	Pneumatic connection		Standard nominal flow rate [l/min]	Weight [g]	Part no.	Type
	1	2				
Inline, without pressure gauge						
	QS-4	QS-4	80	19	8086000	VRPA-C-Q4-E
	QS-6	QS-6	90	20	8086001	VRPA-C-Q6-E
	QS-8	QS-8	130	33	8086002	VRPA-C-Q8-E
Inline, with pressure gauge, pressure gauge scale in MPa						
	QS-4	QS-4	80	23	8086003	VRPA-CM-Q4-E
	QS-6	QS-6	90	23	8086004	VRPA-CM-Q6-E
	QS-8	QS-8	130	36	8086005	VRPA-CM-Q8-E
L-shape, with pressure gauge, pressure gauge scale in MPa						
	M5	QS-4	80	29	8086007	VRPA-LM-M5-Q4
		QS-6	90	29	8086008	VRPA-LM-M5-Q6
	R1/8	QS-4	90	29	8086009	VRPA-LM-R18-Q4
		QS-6	100	29	8086010	VRPA-LM-R18-Q6
		QS-8	130	31	8086011	VRPA-LM-R18-Q8
	R1/4	QS-6	115	49	8086012	VRPA-LM-R14-Q6
		QS-8	130	49	8086013	VRPA-LM-R14-Q8

Festo - Your Partner in Automation



1 Festo Inc.
5300 Explorer Drive
Mississauga, ON L4W 5G4
Canada

Festo Customer Interaction Center
Tel: 1 877 463 3786
Fax: 1 877 393 3786
Email: customer.service.ca@festo.com



2 Festo Pneumatic
Av. Ceylán 3,
Col. Tequesquináhuac
54020 Tlalnepantla,
Estado de México

Multinational Contact Center
01 800 337 8669
ventas.mexico@festo.com



3 Festo Corporation
1377 Motor Parkway
Suite 310
Islandia, NY 11749

Festo Customer Interaction Center
1 800 993 3786
1 800 963 3786
customer.service.us@festo.com



4 Regional Service Center
7777 Columbia Road
Mason, OH 45040

Connect with us

www.festo.com/socialmedia



www.festo.com

Subject to change