
FESTO



FESTO

Technical data

Function



- 11 -

Flow rate 5,200 ... 10,000 l/min



Temperature range −10 ... +60 °C



Operating pressure 1 ... 10 bar





Note

The shut-off valve may not be used as an emergency stop valve.

For units that require a pneumatic shut-off in order to carry out maintenance or repair work, for example.

The valve is installed into the air supply line and fulfils requirements set forth by OSHA 29 CFR 147, "Controlling Dangerous Energy Sources", issued by the United States Department of Labor.

Function

The valve is used for shutting off the compressed air supply, while simultaneously exhausting systems which are powered using compressed air.

Flow from port 1 to port 2 is blocked when the actuator knob is pressed, and flow from port 2 to port 3 is opened.

The largest exhaust flow rate is achieved by keeping the actuating knob in the actuated position until the connected system is completely exhausted.

The valve can be locked in the closed position using a padlock.
This ensures that a decommissioned system (e.g. during maintenance work) cannot be pressurised without authorisation.

General technical data						
Туре	HE-G3/8-LO	HE-G1/2-LO	HE-G3/4-LO	HE-G1-LO		
Pneumatic connection 1, 2	G3/8	G ³ / ₈ G ³ / ₄		G1		
Pneumatic connection 3	G1			·		
Design	Piston spool valve					
Actuation type	Manual	Manual				
Type of mounting	In-line installation					
	Via through-hole					
Assembly position	Any					
Valve function	3/2-way valve, bistable					
Exhaust function	No flow control					
Direction of flow	Non-reversible					
Manual override	None					
Sealing principle	Soft					

Note: This product conforms to ISO 1179-1 and to ISO 228-1

Flow rate characteristic values					
Туре	HE-G3/8-L0	HE-G1/2-LO	HE-G3/4-L0	HE-G1-LO	
Standard nominal flow rate qnN ¹⁾ [l/min]					
1> 2	5,200	6,200	8,000	10,000	
2 3	12,000		<u> </u>		
C value [l/s*bar]					
1> 2	20.95	28.13	36.28	38.47	
			·		
b value					
1> 2	0.42	0.28	0.21	0.47	

¹⁾ Measured at p1 = 6 bar and p2 = 5 bar, Δp = 1 bar



Technical data


Operating and environmental conditions			
Operating pressure	[bar]	110	
Operating medium		Compressed air in accordance with ISO 8573-1:2010 [7:4:4]	
Ambient temperature	[°C]	-10 +60	
Temperature of medium	[°C]	-10 +60	
Corrosion resistance class (CRC ¹⁾	3	

1) Corrosion resistance class CRC 3 to Festo standard FN 940070
High corrosion stress. Outdoor exposure under moderate corrosive conditions. External visible parts with primarily functional requirements for the surface and which are in direct contact with a normal industrial

Weights					
Туре		HE-G3/8-LO	HE-G1/2-LO	HE-G3/4-LO	HE-G1-LO
Product weight	[g]	1,100		1,000	

Materials


Sectional view



Shu	Shut-off valve				
1	Housing	Die-cast aluminium, PBT			
		Colour: yellow			
2	Piston spool	Aluminium			
3	Guide	PTFE			
4	0-ring	PU			
5	Actuating knob	Die-cast aluminium, PBT			
		Colour: red			
_	Seals	NBR, TPE-U(PU)			



Technical data



Туре	D1
HE-G3/8-LO	G3/8
HE-G1/2-L0	G1/2
HE-G3/4-LO	G3/4
HE-G1-LO	G1

Note: This product conforms to ISO 1179-1 and to ISO 228-1

Ordering data		
Pneumatic connection 1, 2	Part No.	Туре
G3/8	197133	HE-G3/8-LO
G ¹ / ₂	197134	HE-G1/2-LO
G ³ / ₄	197135	HE-G3/4-LO
G1	197136	HE-G1-LO

FESTO

Accessories

Padlock LRVS-D for shut-off valve

Material: Housing: Brass



Ordering data			
	Weight	Part No.	Туре
	[g]		
Padlock	120	193786	LRVS-D