Membrane air dryers LDM1, D series

FESTO





Туре		Size	Pneun	natic co	onnectio	on								ure ation ra	nge		of filtra	ation	
													[bar]			[µm]			
			M5	M7	G½8	G½	G ³ /8	G½	G3/4	G1	QS4	QS6	0.5 7	0.5 12	2.5 12	0.01	1	5	40
Service units																			
FRC/FRCS	Ma.	Micro				-	-	-	-	-				-	-	-	-		-
		Mini	-	-				-	-	-	-	-		-	-	-	ı		-
		Midi	-	-	-					-	-	-			-	-	-		
	- Ma	Maxi	-	-	-	-	-				-	-			-	-	-		
.	1																		
Service unit con	nbinations	Micro																	
rkc-k		Micro Mini	-	_			_		_	_	_	_	_			_	_	_	
		Midi						-											
			-	-	-				-	-	-	-	-	-		-	_	-	-
LFR-K	9	Maxi	-	-	-	-	-			-	-	-	-	•	•	-	_	-	•
LFRS-K		Micro	-		-						1		1		-				
LFKS-K		Mini	-	-			-	-	-	-	-	-	-			-	-	-	
		Midi	-	-	-				-	-	-	-	-	-	-	-	_	-	-
	Y	Maxi	-	-	-	-	-			-	-	_	-		-	_	-	-	
Individual devic	·oc																		
Filter	Ω	Micro				_	_	_	_	_				I -	I -	_	_		_
regulators		Mini	_	_				_	_	-	_	_			_	_	_		
LFR/LFRS	100	Midi	_	_	_					_	_	_			_	_	_		
	j	Maxi	_	_	_	_	_			-	_	_			_	_	_		
	•	1																	
Filters		Micro		-	-	_	_	_	-	-		•	_	-	_	-	_	•	-
LF		Mini	_	_				_	-	_	_	-	_	_	_	-	_	•	
		Midi	_	-	-	-		-	-	-	_	-	_	-	_	-	-	-	
	l 🐧	Maxi	_	_	_	_	_		•	•	_	-	_	-	_	-	-	-	
Fine and micro		Micro	_	I	I	I .	I .	I	I	1	1	1	1	1	1	1	1	I	
filters		Mini	-	-				-	-	-	-	-	-	-	-	•		-	-
LFMA/LFMB		Midi	-	-	-					-	-	-	-	-	-	-		-	-
	U	Maxi	-	-	-	-	-				-	-	-	-	-	•		-	-
Active carbon		Micro	-																
filters		Mini	-	-				-	-	-	-	-	-	-	-	-	-	-	-
LFX		Midi	-	-	-					-	-	-	-	-	-	-	-	-	-
			-	-	-	-	-				-	-	-	-	-	-	-	-	-
Filter	mbinations		-								•	•	•	•	•	•			
combinations			-	-				-	-	-	-	-	-	-	-			-	-
LFMBA		Midi	-	-	-					ı	-	-	-	-	-			-	-
	(A)	Maxi	-	-	-	-	-				-	-	-	-	-	•		-	-
									_									_	
Pressure	Micro	•	-	-	-	-	-	-	-		•		-	-	-	-	-	-	
regulators		Mini	-	-	-			-	-	-	-	-		•	-	-	-	-	-
LR/LRS		Midi	-	-	-					-	-	-			-	-	Ī	-	-
		Maxi	-	-	-	-	-				-	-			-	-	-	-	-



Туре	Size	Bowl g	guard	Conde	nsate di	rain	Pressi		Actua	tor lock	Supply	y voltage	e	Options			→ Page/ Internet
		Metal bowl guard	Plastic bowl	Manual rotary	Semi-automatic	Fully automatic	With pressure gauge	Without pressure gauge	Rotary knob with detent	Rotary knob with integrated lock	24 V DC	110 V AC	230 V AC	Directly actuated pressure regulator with integrated return flow function	Pilot actuated pressure regulator with integrated return flow function	Differential pressure indicator	
Service units																	
FRC/FRCS	Micro	-				-				-	-	-	-	-	-	-	frc
	Mini		-		-						-	-	-	-	-	-	
	Midi		-		-	-	•				-	-	-	-	-	-	
	Maxi		-		-			•			-	-	-			-	
Service unit cor	nbination	S															
FRC-K	Micro	_															frc
	Mini		-		-			-		-		-	-	-	-	-	
	Midi		-		-	•	•	-		-	-	-	-	-	-	-	
	Maxi		-		-	•	•	-		-	-	-	-	-	-	-	
LFR-K	Micro	-				1	1			1					I .		lfr
LFRS-K	Mini		-		-	•		-			•	-	-	-	-	-	
	Midi		-		-		•	-	•	•		-	-	-	-	-	
	Maxi		_		-			_				-	_	•	•	_	
	I.	ļ		II.					1				ll		I	Į.	
Individual device	es																
Filter	Micro	-				-				-	-	-	-	-	-	-	lfr
regulators	Mini		-		-						-	-	-	-	-	-	
LFR/LFRS	Midi		-		-						-	-	-	-	-	-	
	Maxi		-		-						-	-	-			-	
					•	•	•			•		•					
Filters	Micro	-				-	-	-	-	-	-	-	-	-	-	-	lf
LF	Mini		-		-		-	-	-	-	-	-	-	-	-	-	
	Midi		-		-		-	-	-	-	-	-	-	-	-	-	
	Maxi		-		-		-	-	-	-	-	-	-	-	-	-	
Fine and micro	Micro	-		1	1				Т		1	1	T	1	ı	Т	lfma, lfmb
filters	Mini		-		-		-	-	-	-	-	-	-	-	-		
LFMA/LFMB	Midi	•	-		-	•	-	-	-	-	-	-	-	-	-		
	Maxi		-		-		-	-	-	-	-	-	-	-	-		
Active carbon	Micro	-													1		lfx
filters	Mini		-	-	-	-	-	-	-	-	-	-	-	-	-	-	
LFX	Midi		-	-	-	-	-	-	-	-	-	-	-	-	-	-	
	Maxi		-	-	-	-	-	-	-	-	-	-	-	-	-	-	
Filter	Micro	_		T _					1				ı	1	ı		lfmba
combinations	Mini		-	-	-	-	-	-	-	-	-	-	-	-	-	-	
LFMBA	Midi		-	-	-	-	-	-	-	-	-	-	-	-	-	-	
	Maxi		-		-		_	-	-	-	-	-	-	-	-		
Pressure	Micro							_	_								le.
regulators		-	-	-	-	-	-	-		-	-	-	-	-	-	-	lr
LR/LRS	Mini Midi	-	-	-	-	-					-	-	-	-	-	-	-
LK/LK3		-	-	-	-	-					-	-	-	-	-	-	
	Maxi	-	-	-	-	-				_	-	-	-			-	



Micro	Туре		Size	Pneumat connection										Pressure regulatio [bar]	
Micro															
Individual devices															0.5
Micro				M5	M7	G½8	G1/4	G3/8	G½	G3/4	G1	QS4	QS6	7	12
Mini		es	Micro	T _											
Midi					_	_		_	_	_	_	_	_		
Maxi															
Pressure regulator combinations Micro		SOL O													
Regulator combinations Mini	Pressure	\odot													
Midi				_	_	_			_	_	_	_	_		
Lubricators Micro				_	_	_	_			_	_	_	_		
Mini	LRB-K		Maxi	-											
Mini	Luhricators	A	Micro				_	_	_	_	_			_	_
Midi															_
Maxi															_
Micro															_
Mini			maxii						_	_	_				
Mini	On-off valves		Micro	_											
Midi				_	_	•			_	_	_	_	_	_	_
Maxi				-	_	_					_	_	-	_	_
Micro				_	_	_	_	_				_	_	_	_
Midi	On-off valves,	14		-		1									
Maxi	electrical		Mini	-	-				-	-	-	-	-	-	-
Micro -	HEE			-	-	-					-	-	-	_	_
Mini			Maxi	-	-	-	-	_				-	-	-	-
Midi	On-off valves,	(E)	Micro	-	I.		I.	I		I			I.		I.
Maxi	pneumatic		Mini	-	-				_	_	-	-	-	-	-
Micro			Midi	-	-	-					-	-	-	_	_
Mini			Maxi	-	-	-	-	-				-	-	_	_
Mini	Soft-start				I	1	I	1	1	1	1	1	I .	1	I
Maxi				-	_				_	-	-	-	-	_	-
Micro	HEL		Midi	-	-	-					-	-	-	-	_
Mini			Maxi	-	-	-	-	-				-	-	-	-
Mini	Mambra:!::		M:												
Midi															
Maxi															
Micro - Micro - Midi - - - - - - - - -	FDIMIT								_	_	_				
Mini -		U	INIGXI		_	_	_	_	•	•	•	_	_		-
Mini -	Branching		Micro	_											
FRM Midi - <td></td> <td></td> <td></td> <td></td> <td>_</td> <td>-</td> <td></td> <td></td> <td>_</td> <td>_</td> <td>_</td> <td>_</td> <td>_</td> <td>_</td> <td>_</td>					_	-			_	_	_	_	_	_	_
Maxi - - - - - - - Distributor block Micro - - - - - - - - -															_
Distributor block															_
block Mini	Distributor														_
															_
															_
Maxi															_




Туре	Size	Bowl guar	rd	Pressure i	ndication	Actuator l	ock	Supply vo	ltage		Options		→ Page/ Internet
		Metal bowl guard	Plastic bowl	With pressure gauge	Without pressure gauge	Rotary knob with detent	Rotary knob with integrated lock	24 V DC	110 V AC	230 V AC	Non-return function	Pressure switch	
Individual devi	ces	•	'	•	'	•	•	<u> </u>	•				
Pressure	Micro	-											lrb
regulators	Mini	-	-	-				-	-	-	-	-	
LRB/LRBS	Midi	-	-	-				-	-	-	-	-	
	Maxi	-	_										
Pressure	Micro	-											lrb
regulator	Mini	-	-	-			-	-	-	-	-	-	1
combinations	Midi	-	-	-		•	-	-	-	-	-	_	1
LRB-K	Maxi	-	-	1	1	1	П		П	4	1	1	1
	-1	1	1										1
Lubricators	Micro	_		_	•	-	-	-	-	-	_	_	loe
LOE	Mini		_	-		_	_	_	_	-	-	-	
	Midi		_	-	-	_	_	_	_	_	_	-	1
	Maxi		_	_	-	-	_	-	_	-	_	_	
			1	1	1		1	1	1			1	1
On-off valves	Micro	-											he
HE	Mini	_	_	_			_	_	_	_	_	_	
	Midi	_	_	_			_	_	_	_	_	_	
	Maxi	_	_	_			_	_	_	_	_	_	
On-off valves,	Micro	_											hee
electrical	Mini	_	_	_		_	_				_	_	-
HEE	Midi	_	_	_	•	_	_	•		•	_	_	
	Maxi	_	_	_	-	_	_	-	_	-	_	_	-
On-off valves,	Micro	_											hep
pneumatic	Mini	_	_	_		_	_	_	_	_	_	_	ПСР
HEP	Midi	_	_	_	-	_	_	_	_	_	_	_	-
IILI	Maxi	_	_	_	_	_							
Soft-start	Micro	_	_	_	-	_	_	-	_	-	-	-	hel
valves	Mini	_	_	_		_	_		_	_	_	_	IICI
HEL	Midi				-			_					=
IILL	Maxi	_	-	-		-	_	_	_	_	-	-	=
	IVIdXI				_						-		
Membrane air	Micro												6
dryers	Mini	-											-
LDM1	Midi												-
FDIMIT		-		1	_					1			-
	Maxi	-	-	-		-	-	-	-	-	-	-	
Dranchina	Micro												frm
Branching modules	Micro Mini	-			_					T	_	_	- 111111
FRM		_	-	-		-	-	-	-	-	-	-	-
LKINI	Midi	-	-	-	-	_	-	_	-	-	-	-	-
Di ett.	Maxi	-	-	-	-	-	-	-	-	-	-	•	6
Distributor	Micro	-	-	-	-	-	-	-	-	-	-	-	frz
block	Mini	-	-	-		-	-	-	-	-	-	-	
FRZ	Midi	-	-	-	-	-	-	-	-	-	-	-	
	Maxi	-	-	-		-	-	-	-	-	-	-	

Membrane air dryers LDM1, D series, metal design Peripherals overview and Type codes



Maxi Individual unit with connection plates Individual unit without connection plates, for service unit combination

Mounting attachments and accessories					
	Individual unit		Combination		→ Page/
	with connection	without connection	with connection	without connection	Internet
	plates	plates	plates	plates	
Mounting bracket			_		hfoe-d
HFOE	-	_	-	_	
2 Threaded pin (included in scope of delivery)			_	_	frb-d
FRB	_	_	-	-	




Membrane air dryers LDM1, D series, metal design



Technical data

Function



Flow rate 300 ... 1,000 l/min

Temperature range +2 ... +50 °C

Operating pressure 3 ... 12.5 bar

Pressure dew point reduction: LDM1-...-300/600: 20 K LDM1-...-1000: 17 K



- Optimum final dryer with excellent operational reliability
- Suitable for use as an individual device or for integration in existing service unit combinations
- Flow rate-dependent dew point reduction
- Wear-free function requiring no external energy
- The composition of the compressed air remains almost unchanged due to the drying process
- 15% purge air flow rate with the LDM1-...-300/600 and 20% with the LDM1-...-1000

Typical areas of application:

- Drying, cleaning of precision parts
- Measuring technology
- Rinsing of precision glass scales
- Painting systems
- Paper and packaging machines



Note

Prefiltration of the compressed air using a micro filter LFMA-D-MAXI, grade of filtration 0.01 µm (residual particles < 0.1 µm, residual oil content $< 0.1 \text{ mg/m}^3$) is vital for flawless functioning of the unit.

General technical data									
Size	Maxi								
Pneumatic connection 1, 2	G½	G3/4	G1	_1)					
Design	Membrane dryer	Membrane dryer with internal air consumption							
Type of mounting	Via accessories								
	In-line installation	In-line installation							
Assembly position	Vertical ±5°	Vertical ±5°							

- 1) Without connection plates
- Note: This product conforms to ISO 1179-1 and to ISO 228-1

Standard flow rate qn [l/min]			
Туре	LDM1300 ¹⁾	LDM1600 ¹⁾	LDM11000 ²⁾
Input q _{n In}	353	706	1,250
Output q _{n Out}	300	600	1,000
Purge air q _{n Purge}	52.9	105.9	250

- 1) Measured at $p_1 = 6.9$ bar, $\vartheta_{pd \, ln} = 25$ °C, $\vartheta_{pd \, Out} = 5$ °C ± 1.5 °C ($\vartheta_{pA \, Out} = -21.5$ °C ± 1.2 °C), $\vartheta_{amb} = 25$ °C 2) Measured at $p_1 = 6.9$ bar, $\vartheta_{pd \, ln} = 25$ °C, $\vartheta_{pd \, Out} = 8$ °C ± 1.5 °C ($\vartheta_{pA \, Out} = -19.1$ °C ± 1.2 °C), $\vartheta_{amb} = 25$ °C ± 1.5 °C ($\vartheta_{pA \, Out} = -19.1$ °C ± 1.2 °C), $\vartheta_{amb} = 25$ °C ± 1.5 °C ($\vartheta_{pA \, Out} = -19.1$ °C ± 1.2 °C), $\vartheta_{amb} = 25$ °C

Operating and environmental	conditions			
Туре		LDM1300	LDM1600	LDM11000
Operating pressure	[bar]	3 12,5		
Operating medium		Compressed air in accordance with ISO 8	3573-1:2010 [1:3:1]	
Pressure dew point reduction	[K]	20	20	17
Ambient temperature	[°C]	+2 +50		
Temperature of medium	[°C]	+2 +50		
Storage temperature	[°C]	-20 +60		
Corrosion resistance class CRC	(1)	2		

Corrosion resistance class CRC 2 to Festo standard FN 940070 Moderate corrosion stress. Indoor applications in which condensation may occur. External visible parts with primarily decorative requirements for the surface and which are in direct contact with the ambient atmosphere typical for industrial applications.


Membrane air dryers LDM1, D series, metal design Technical data



Weights [g]								
Port Without connection plates Connecting plates with connecting thread								
		G½	G3/4	G1				
LDM1300	1,650	1,800	1,900	2,000				
LDM1600	2,100	2,250	2,350	2,450				
LDM11000	2,100	2,250	2,350	2,450				

Materials

Sectional view



Mem	brane air dryer	
1	Housing	Die-cast zinc
2	Bowl	Wrought aluminium alloy
-	Seals	NBR


Membrane air dryers LDM1, D series, metal design




Technical data


Pressure dew point t_{pd} (output) as a function of the standard flow rate at output $q_n^{\ 1)}$

LDM1-...-300 LDM1-...-600






LDM1-...-1000




1) Measured at pressure dew point t_{pd} (supply) = 25 °C.
Example LDM1-...-1000 with 10 bar supply pressure: the pressure dew point reduction at a nominal flow rate of q_n = 1,200 l/min is 25 K.


Differential pressure Δp as a function of the standard flow rate at output qn

LDM1-...-300






LDM1-...-1000



Membrane air dryers LDM1, D series, metal design



Technical data



 $^{\|\}cdot\|$ Note: This product conforms to ISO 1179-1 and to ISO 228-1

Ordering dat	Ordering data									
Size	e Connection LDM1300		00		LDM16	00		LDM11	000	
		Part No. Type			Part No.	Туре		Part No.	Туре	
Without conn	Without connecting plates									
Maxi	-	543664	LDM1-D-MAXI-300		543665	LDM1-D-MAXI-600		543666	LDM1-D-MAXI-1000	
Connecting p	lates with conne	cting thread								
Maxi	G ¹ / ₂	543667	LDM1-1/2-D-MAXI-300		543668	LDM1-1/2-D-MAXI-600		543669	LDM1-1/2-D-MAXI-1000	
	G ³ / ₄	543670	LDM1-3/4-D-MAXI-300		543671	LDM1-3/4-D-MAXI-600		543672	LDM1-3/4-D-MAXI-1000	
	G1	543673	LDM1-1-D-MAXI-300		543674	LDM1-1-D-MAXI-600		543675	LDM1-1-D-MAXI-1000	