
## Data sheet

## Connecting cable MHJ9-KMH

- With control electronics for valves MHI9
- With plug sockets KMH
- Cable lengths 0.5 and 2.5 m



| General technical data           |        |  |                       |  |  |  |  |  |  |  |
|----------------------------------|--------|--|-----------------------|--|--|--|--|--|--|--|
| Туре                             |        | MHJ9-KMHMF   | MHJ9-KMHHF            |  |  |  |  |  |  |  |
| Electrical connection            |        | 2x straight socket KMH, 2-pin  |                       |  |  |  |  |  |  |  |
|                                  |        | Cable, 4-wire  |                       |  |  |  |  |  |  |  |
| Operating voltage range          | [V DC] | 12 53  |                       |  |  |  |  |  |  |  |
| Trigger signal range             | [V DC] | 330  |                       |  |  |  |  |  |  |  |
| Input resistance                 | [kΩ]   | 34   |                       |  |  |  |  |  |  |  |
| Note on input current            |        | Linear rise  |                       |  |  |  |  |  |  |  |
|                                  |        | 0.09 0.44 mA at a trigger signal of 3 15 V DC  |                       |  |  |  |  |  |  |  |
|                                  |        | 0.44 15.44 mA at a trigger signal of 15 30 V DC  |                       |  |  |  |  |  |  |  |
| Note on power consumption per    | [W]    | Low-current phase 2  | Low-current phase 2.8 |  |  |  |  |  |  |  |
| channel                          | [W]    | High-current phase 7 High-current phase 17.1   |                       |  |  |  |  |  |  |  |
| Notes on operation               |        | Power supply unit must be able to supply at least 1.7 A without Power supply unit must be able to supply at least 1.85 A without |                       |  |  |  |  |  |  |  |
|                                  |        | voltage drop. voltage drop.  |                       |  |  |  |  |  |  |  |
| Additional functions             |        | Spark arresting  |                       |  |  |  |  |  |  |  |
|                                  |        | Holding current reduction with energy recovery   |                       |  |  |  |  |  |  |  |
|                                  |        | Safety shut-off  |                       |  |  |  |  |  |  |  |
| Reverse polarity protection      |        | For operating voltage  |                       |  |  |  |  |  |  |  |
| Duty cycle                       | [%]    | 100  |                       |  |  |  |  |  |  |  |
|                                  |        | Observe the notes on operating the solenoid valves.  |                       |  |  |  |  |  |  |  |
| Cable characteristic             |        | For static applications  |                       |  |  |  |  |  |  |  |
| Type of mounting                 |        | With H-rail  |                       |  |  |  |  |  |  |  |
|                                  |        | With through-hole  |                       |  |  |  |  |  |  |  |
| Mounting position                |        | Any  |                       |  |  |  |  |  |  |  |
| Degree of protection to EN 60529 |        | IP40   |                       |  |  |  |  |  |  |  |

| Materials         |                |
|-------------------|----------------|
| Housing           | POM            |
| Cable sheath      | PVC            |
| Note on materials | RoHS-compliant |

| Operating and environmental conditions                   |                                   |  |  |  |  |  |  |  |
|--|-----------------------------------|--|--|--|--|--|--|--|
| Ambient temperature [°C]                                 | −5 +50                            |  |  |  |  |  |  |  |
| Corrosion resistance class CRC <sup>1)</sup>             | 2                                 |  |  |  |  |  |  |  |
| CE marking (see declaration of conformity) <sup>3)</sup> | To EU EMC Directive <sup>2)</sup> |  |  |  |  |  |  |  |
| KC mark  | KCEMC                             |  |  |  |  |  |  |  |
| Certification  | RCM compliance mark               |  |  |  |  |  |  |  |
| PWIS conformity  | VDMA24364-B2-L                    |  |  |  |  |  |  |  |

<sup>1)</sup> Corrosion resistance class CRC 2 to Festo standard FN 940070


Moderate corrosion stress. Indoor applications in which condensation can occur. External visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment.

<sup>2)</sup> For information about the area of use, see the EC declaration of conformity at: www.festo.com/catalogue/... → Support/Downloads.

If the devices are subject to usage restrictions in residential, commercial or light-industrial environments, further measures for the reduction of the emitted interference may be necessary.

Additional information www.festo.com/catalogue/... → Support/Downloads.

## Data sheet



## Download CAD data → www.festo.com

Wire allocation:

BU = GND

BN = Operating voltage positive

BK = Trigger 1

WH = Trigger 2

- [1] H-rail
- [2] Hole for wall mounting

| Туре         | B1 | B2 | В3 | D1 | D2  | D3  | H1 | H2 | Н3 | L1   | L2  | L3 | L4 | L5 | L6 | L7 | L8 | L9 |
|--------------|----|----|----|----|-----|-----|----|----|----|------|-----|----|----|----|----|----|----|----|
| MHJ9-KMH-0.5 | 10 | 8  | 4  | 5  | 3.4 | 3.3 | 27 | 23 | 13 | 500  | 200 | 65 | 50 | 30 | 35 | 8  | 7  | 8  |
| WHIO KWH 3 E |    |    |    |    |     |     |    |    |    | 2500 | 1   |    |    |    |    |    |    |    |

| Ordering data    |   |        |        |          |                 |
|------------------|---|--------|--------|----------|-----------------|
|                  |   | Length | Weight | Part no. | Туре            |
| Connecting cable |   |        |        |          |                 |
|                  | With control electronics for 2 valves LF-, MF/LP, MF- and HF/LP | 0.5 m  | 40 g   | 553121   | MHJ9-KMH-0.5-MF |
|                  |   | 2.5 m  | 98 g   | 565519   | MHJ9-KMH-2.5-MF |
|                  | With control electronics for 2 valves HF                        | 0.5 m  | 40 g   | 562170   | MHJ9-KMH-0.5-HF |
|                  |   | 2.5 m  | 98 g   | 567505   | MHJ9-KMH-2.5-HF |
| H-rail           |   |        |        |          |                 |
|                  | H-rail to EN 60715, galvanised steel                            | 2 m    | 600 g  | 35430    | NRH-35-2000     |