Proximity switches for T-slot

FESTO



Proximity switches

Product range overview


esign	Type of mounting	Measuring principle	Туре	Operating voltage range	Switching output	Switching element function	→ Page
or T-slot	Standard						
	Screw-clamped, inserted in the slot from above	Magnetic Hall	SDBT-MSX	10 30 V DC	PNP/NPN, switchable	N/O/ N/C contact, switchable	-,
	Inserted in the slot from above, flush with the	Magneto-resistive	SMT-8M-A	5 30 V DC	PNP	N/O contact N/C contact	-
	cylinder profile				NPN Non-contacting, 2-wire	N/O contact	
	Inserted in the slot from above, flush with the cylinder profile	Magnetic reed	SME-8M	5 30 V AC/DC	Contacting, bipolar	N/O contact N/C contact	_
	Inserted in the slot lengthwise, flush with the cylinder profile	Magnetic reed	SME-8	12 30 V AC/DC	Contacting, bipolar	N/O contact N/C contact	-,
	Inserted in the slot	NA to a state	SMT-8G	3 230 V AC/DC	DND NDN	N/O contact	-
	lengthwise	Magneto-resistive Magneto-resistive	SMT-8-SL	10 30 V DC	PNP, NPN PNP	N/O contact	-
		Magnetic reed	SME-8-SL	10 30 V AC/DC	Contacting, bipolar	N/O contact	-
	Inserted in the slot from above	Magnetic reed	SME-8-FM	10 30 V AC/DC	Contacting, bipolar	N/O contact	-
	With accessories	Magneto-resistive	SMTO-8E	10 30 V DC	PNP NPN	N/O contact	-
		Magnetic reed	SMEO-8E	12 30 V DC 3 250 V DC 3 230 V AC	Contacting, bipolar	N/O contact	7
	Comments on an electrical		I	15257.1			I
	Corrosion-resistant Inserted in the slot from above, flush with the cylinder profile	Magneto-resistive	CRSMT-8M	5 30 V DC	PNP	N/O contact	_
	Welding-field-resistant						
	Inserted in the slot from above, screw-clamped	Magneto-resistive	SDBT-BSW	10 30 V DC	PNP NPN Non-contacting, 2-wire	N/O contact	_
	With accessories	Magneto-inductive	SMTSO-8E	10 30 V DC	PNP NPN	N/O contact	-
	Heat-resistant up to 120°	C					
	Inserted in the slot lengthwise, flush with the cylinder profile	Magnetic reed	SME-8S6	0 30 V AC/DC	Contacting, bipolar	N/O contact	_
	With accessories	Magnetic reed	SMEO-8ES6	0 30 V DC 0 30 V AC	Contacting	N/O contact	7
	To EU Explosion Protectio	n Directive (ATEX)					
	Inserted in the slot from above, screw-clamped	Magneto-resistive	SDBT-MSEX6	8.2 V DC	NAMUR	NAMUR	-

Product range overview

Design	Type of mounting	Measuring principle	Туре	Operating voltage range	Switching output	Switching element function	→ Page
For C-slot	Standard						
	Inserted in the slot from	Magneto-resistive	SMT-10M	10 30 V DC	PNP	N/O contact	C-slot
	above, flush with the				NPN		
	cylinder profile				Non-contacting, 2-wire		
		Magnetic reed	SME-10M	5 30 V AC/DC	Contacting, bipolar	N/O contact	
	Inserted in the slot	Magneto-resistive	SMT-10G	10 30 V DC	PNP	N/O contact	
	lengthwise	Magnetic reed	SME-10	12 27 V AC/DC	Contacting	N/O contact	

T-slot switches can be used for drives with T-slot

Exceptions



- DFM-B: SMTO-8E, SMTSO-8E, SMEO-8E and SMPO-8E cannot be used
- DHDS: SME-8M can only be used on Ø 50
- DHPS: SME-8M can only be used on Ø 20 ... 35
- HGDD-63-A: SMT-8M-A cannot be used
- HGPT-B: only SMT-8G can be used from size 40 and upwards
- SDBT-BSW- ... -PU/NU can only be used on a limited number of drive series. Page → 53

C-slot switches can be used for drives with C-slot

Exceptions



- ADVC Ø 100: SMT-10M and SME-10M cannot be used (ADVC has a T-slot and C-slot)
- DSM/DSM-B-6/8/10: SME-10M cannot be used
- DSM/DSM-B-10/16: SMT-10M cannot be used
- HGPT-B: only SMT-10G can be used for sizes up to and including size 35

For drives with sensor rail: these are available with 2 cylinder barrel contours

Only T-slot switches CRSMT-8M, SMT-8M-A and SDBT-MS- ... -EX6 can be used, and only with the identified profile. CRSMT-8M and SMT-8M-A can be used for all diameters; SDBT-MS- ... -EX6 cannot be used for diameters 40 and 50.

Example: DSBF








Suitable

Not suitable

Peripherals overview



Peripherals overview

Mounting components and accessories → Page				Mountin	g components and accessories	→ Page
Proxi	Proximity switches			Mountin	g kits and accessories	
[1]	SMEO-8E, with cable or plug	7	1	[4]	Mounting kit SMBR-8-8/100-S6, heat resistant	11
			1	[5]	Mounting kit SMB-8E	11
				[6]	Mounting SMBZ-8	12
				[7]	Sensor tester SM-TEST-1	13
				-	Positioning element SMM-8	12
				-	Clip SMBK-8	13
				-	Inscription label ASLR	13
				-	Safety clip NEAU	13
Conn	ecting cables		1	Drives		
[2]	NEBU-MG	13	1	[8]	Round cylinder	-
[3]	NEBU-MW	13	1	[9]	Standards-based cylinder DSBC	-
		•	L	[10]	Drives with tie or mounting rod	-

Proximity switch SMEO-8E, for T-slot


Type codes

001	Series					
SMEO	Proximity sensor, magnetic, reed					
002	Design type					
8	For T-slot					
003	Sensor version					
E	Mounting with accessories					
004	Electrical connection, cable length					
K	Cable, 2.5 m or 7.5 m					
S	Plug M8x1 with cable, 0.3 m					
M12						


005	Switching status indication				
	None				
LED	Yellow LED				
006	Rated operating voltage				
24	24 V DC				
230	230 V AC				
007	Variant				
S6	Heat-resistant				
	•				


Data sheet – Magnetic reed

N/O contact, 3-wire, with plug



N/O contact, 2-wire, with cable





- Magnetic reed measuring principle
- · Heat resistant variant



General technical data			
	SMEO-8E24	SMEO-8E24-S6, heat-resistant	SMEO-8E230
Design	For T-slot	For T-slot	For T-slot
Conforms to standard	EN 60947-5-2	-	EN 60947-5-2
Certification	RCM compliance mark	-	RCM compliance mark
CE marking	To EU EMC Directive ¹⁾	-	To EU EMC Directive ¹⁾
(see declaration of conformity)	-		To EU Low Voltage Directive
Note on materials	Free of copper and PTFE	Free of copper and PTFE	Free of copper and PTFE
	RoHS-compliant	-	-

1) For information about the area of use, see the EC declaration of conformity at: www.festo.com/sp \rightarrow Certificates. If the devices are subject to usage restrictions in residential, commercial or light-industrial environments, further measures for the reduction of the emitted interference may be necessary.

Input signal/measuring element					
	SMEO-8E24	SMEO-8E24-S6, heat-resistant	SMEO-8E230		
Measuring principle	Magnetic reed	Magnetic reed	Magnetic reed		
Ambient temperature [°C]	-40 +60	-40 +120	-20 +60		

Switching output					
		SMEO-8E-S	SMEO-8E-M-12	SMEO-8E24-S6, heat-resistant	SMEO-8E230
Switching output	*	Contacting, bipolar		Contacting	Contacting, bipolar
		-		-	Without LED function
Switching element function		N/O contact		•	•
Repetition accuracy		-	0.2	-	0.2
Reproducibility of switching value	[mm]	±0.1	-	±0.1	-
Switch-on time	[ms]	0 0.5		0 0.5	0 2
Switch-off time	[ms]	0.03		0.03	0.03
Max. switching frequency	[Hz]	800		500	500
Max. output current	[mA]	500		500	120
Max. switching capacity DC [W] 10			10	10	
Max. switching capacity AC	[VA]	10		10	10
Voltage drop	[V]	-		0.5	3.9

Output, additional data	Output, additional data			
Short circuit current rating	No			
Overload protection	Not provided			

Electronics				
		SMEO-8E24	SMEO-8E24-S6, heat-resistant	SMEO-8E230
Operating voltage range DC	[V]	12 30	0 30	3 250
Operating voltage range AC	[V]	12 30	0 30	3 230
Reverse polarity protection	'	No	For all electrical connections	No

Data sheet – Magnetic reed

Electromechanics				
Туре	SMEO-8E-S-LED-24	SMEO-8E-M12-LED-24	SMEO-8E-K-24-S6, heat-resistant	SMEO-8E-M12-LED-230
Electrical connection	Plug M8x1, 3-pin	Plug M12x1, 3-pin	Cable, 2-wire	Plug M12x1, 3-pin
Connection technology	-	M12x1, A-coded to EN 61076-2-101	-	M12x1, A-coded to EN 61076-2-101
Number of pins/wires	-	3	-	3
Type of mounting	-	Screw-type lock	-	Screw-type lock
Outlet direction of connection	Lateral	Lateral	Lateral	In-line
Information on materials: Pin contacts	Nickel-plated brass	Brass	-	-
Cable length [m] -	-	2.5	-
Information on materials: Cable sheath	-	PUR	TPE-S	-

Pin allocation to EN 6096 M12x1, 3-pin N/O contact	47-5-2		
	Pin	Wire colour	Allocation
	1	Brown	+
3(+ +)1	3	Blue	-
+	4	Black	Output
4			

M8x1, 3-pin, 24 V N/O contact			
	Pin	Wire colour	Allocation
4	1	Brown	+
1(+++)3	3	Blue	-
	4	Black	Output

Pin allocation to EN 60947-5-2			
M12x1, 3-pin, 230 V N/O contact			
N/O contact			
	Pin	Wire colour	Allocation
	4	Black	~/+
3(+ +)	3	Blue	~/-
4			

Mechanics					
Туре		SMEO-8E-S-LED-24	SMEO-8E-M12-LED-24	SMEO-8E-K-24-S6,	SMEO-8E-M12-LED-230
				heat-resistant	
Type of mounting		With accessories		With accessories	With accessories
Tightening torque	[Nm]	0.5	0.5	0.5	0.5
Information on materials: Housing		TPE-U(PU)	TPE-U(PU)	TPE-U(PU)	TPE-U(PU)
		High-alloy stainless steel	High-alloy stainless steel	-	High-alloy stainless steel
		Wrought aluminium alloy	Wrought aluminium alloy		Wrought aluminium alloy
		Nickel-plated brass	_		-


Display/operation			
	SMEO-8E24	SMEO-8E24-S6, heat-resistant	SMEO-8E230
Switching status indication	Yellow LED	1	Yellow LED

Immission/emission			
	SMEO-8E24	SMEO-8E24-S6, heat-resistant	SMEO-8E230
Ambient temperature with flexible cable [°C]	-	-40 +120	-
installation			
Degree of protection	IP65	IP65	IP65
	IP67	IP67	IP67
Insulation voltage [V]	_	50	-
Surge resistance [kV]	0.8	-	4
Pollution degree	3	3	3

Data sheet - Magnetic reed

Dimensions

SMEO-8E-S-LED-24 - Plug M8x1




Download CAD data → www.festo.com

- [1] Suitable for plug socket type SIM-M8
- [2] Yellow light emitting diode
- [3] Socket head screw M3x25 DIN 912, max. tightening torque 1 Nm
- [4] Theoretical switching point
- [5] Mounting kit SMB-8E (not included in scope of delivery)
- [6] Installation space for angled plug socket 90°
- [7] Installation space for straight plug socket

	B1 ±0.3	B2	D1	H1	H2 ±0.27	Н3	H4	Н5	Н6	H7	L1 ±0.3	L2	L3	L4
SMEO-8ES-LED-24	20	28	M8x1	19.2	11.5	4.4	4	2.2	~32	~46	20	5	4	~26

Dimensions

SMEO-8E-M12-LED-24 - Plug M12x1



Download CAD data → www.festo.com

- [1] Suitable for plug socket type SIM-M12
- [2] Yellow light emitting diode
- [3] Socket head screw M3x25 DIN 912, max. tightening torque
- [4] Theoretical switching point
- [5] Mounting kit SMB-8E (not included in scope of delivery)
- [6] Installation space for angled plug socket 90°
- Installation space for straight plug socket


	B1 ±0.3	B2	D1	H1 ±0.34	H2 ±0.27	Н3	H4	H5	Н6	H7	L1 ±0.3	L2	L3	L4
SMEO-8EM12-LED-24	20	28	M12x1	22.5	11.5	4.4	4	2.2	~36	~59	20	5	4	~36.5


జ

Data sheet – Magnetic reed

Dimensions

SMEO-8E-K24-S6 - Cable, heat-resistant up to 120°C





Download CAD data → www.festo.com

- [1] Cable, 2.5 m long, 2×0.14 mm²
- [3] Socket head screw M3x25
 DIN 912, max. tightening torque
 1 Nm
- [5] Mounting kit SMB-8E (not included in scope of delivery)

	B1 ±0.3	B2	D1	H2 ±0.27	Н3	H4	L1 ±0.3	L2	L3
SMEO-8E-K24-S6	20	28	2.9	11.5	4.4	4	20	5	4

Ordering data							
	Switching output	Electrical connect	ion	Cable length	Product	Part no.	Туре
		Plug M8x1	Plug M12x1		weight		
				[m]	[g]		
N/O contact, basic	c version						
	Contacting, bipolar	3-pin	-		10	171163	SMEO-8E-S-LED-24
		_	3-pin		9	171164	SMEO-8E-M12-LED-24
N/O contact, heat	-resistant						
	Contacting, bipolar	2-wire	-	2.5	40	171158	SMEO-8E-K-24-S6
N/O contact oper	ating voltage range 3	250 V AC/DC					
The second of th	Contacting, bipolar	-	3-pin	-	9	171160	SMEO-8E-M12-LED-230

→ Internet: www.festo.com/catalogue/...

Accessories

Mounting kit SMBR-8-8/100-S6

Material:


Rail: Anodised wrought aluminium

Clamping strap, screws: High-alloy

stainless steel

Free of copper and PTFE RoHS-compliant





Dimensions and	Dimensions and ordering data													
For piston Ø	B1	B2	D1	H1	L1	L2	L3	=© 1	CRC ¹⁾	Part no.	Туре			
8 100	27.4	0.2	M3	22.4	34	10	7.9	2.5	4	★ 538937	SMBR-8-8/100-S6			

¹⁾ Corrosion resistance class CRC 4 to Festo standard FN 940070
Particularly high corrosion stress. Outdoor exposure under extreme corrosive conditions. Parts exposed to aggressive media, e.g. in the chemical or food industries. Such applications may need to be safeguarded by means of special testing (→ also FN 940082), using appropriate media.


Mounting kit SMB-8E

Material:

Anodised aluminium, stainless steel

Note on materials: RoHS-compliant





Ordering data												
For piston Ø	B1	B2	D1	H1	H2	L1	= ©1	Part no.	Туре			
10 125	21.5	5.1	M3	11.5	3	8	2.5	178230	SMB-8E			

Accessories

Mounting SMBZ-8-...

Design: For tie rods
Mounting position: Any
Type of mounting: Clamped
Tightening torque: ≤ 0.5 Nm
Ambient temperature:
-40 ... +120°C
PWIS conformity:
VDMA24364-B2-L

Material:


Housing: Anodised wrought aluminium

alloy

Screws: High-alloy stainless steel

Free of copper and PTFE RoHS-compliant





Dimensions and	Dimensions and ordering data												
For piston Ø	B1	D1	D2	H1	L1	L2	=©1	Weight [g]	CRC ¹⁾	Part no.	Туре		
32 100	31	M5	M3	30	22	20	1.5	1.6	2	537806	SMBZ-8-32/100		
125 320	32.3	INIO	IVIO	22))	20	2.5	14	2	537808	SMBZ-8-125/320		

¹⁾ Corrosion resistance class CRC 2 to Festo standard FN 940070

Moderate corrosion stress. Indoor application where condensation is allowed to occur. External visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment.

Positioning element SMM

Inserted in the slot lengthwise


Ambient temperature: -40 ... +120°C

Materials:

Housing: Anodised wrought aluminium

Screws: High-alloy stainless steel Note on materials: RoHS-compliant





Dimensions and order	rs and ordering data										
B1	H1	H2	L1	= ©1	CRC ¹⁾	Part no.	Туре	PU ²⁾			
6.3	5.0	4.0	4.0	1.5	3	547941	SMM-8	10			

¹⁾ Corrosion resistance class CRC 3 to Festo standard FN 940070

High corrosion stress. Outdoor exposure under moderate corrosive conditions. Externally visible parts with primarily functional surface requirements which are in direct contact with a normal industrial environment.

2) Packaging unit

Accessories

Ordering da	ta – Connecting cables				Data sheets •	→ Internet: nebu/s
		Number of wires	Cable length [m]	Part no.	Туре	
ocket M8x	1, 3-pin					
	For SMT/SME-8 and	3	2.5	★ 541333	NEBU-M8G3-K-2.5-LE3	
	SMTO/SMTSO/SMEO-8E		5	★ 541334	NEBU-M8G3-K-5-LE3	
	For SMT/SME-8 and	3	2.5	★ 541338	NEBU-M8W3-K-2.5-LE3	
&	SMTO/SMTSO/SMEO-8E		5	★ 541341	NEBU-M8W3-K-5-LE3	
cket M12	x1, 5-pin					
	For SMT/SME-8M and	3	2.5	★ 541363	NEBU-M12G5-K-2.5-LE3	
	SMTO/SMTSO/SMEO-8E		5	★ 541364	NEBU-M12G5-K-5-LE3	
	For SMT/SME-8M and	3	2.5	541367	NEBU-M12W5-K-2.5-LE3	
<u> </u>	SMTO/SMTSO/SMEO-8E		5	541370	NEBU-M12W5-K-5-LE3	
cket M12	x1, resistant to welding spatter					
9	For SDBT and SMTSO	3	3	30450	SIM-M12-RS-3GD-3	
<u> </u>	For SDBT and SMTSO	3	3	30451	SIM-M12-RS-3WD-3	
		connection gory: gas: II 3G / dust: II 3D		548068	NEAU-M12-GD	1
	W12	301y. gus. 11 70 / dust. 11 70		348008	NLAU-M12-GD	1
Packaging u	init			•		·
rdering da	ta – Mounting components Description			Part no.	Туре	
^	·	-1			SMBK-8	
	For fixing connecting cables in	piace	534254	SMBK-8		
rdering da	ta – Sensor tester					
iaering ua	Description		Part no.	Туре		
ēΠ	Testing the functionality of p	roximity switches using the integrated volta	158481	SM-TEST-1		
	Adjusting proximity switches	on the cylinder				
dering da	ta – Inscription labels					
	Size			Part no.	Туре	PU ¹⁾
	23x4 mm			541598	ASLR-L-423	34

Packaging unit