


Data sheet

Electronics modules VAVE

- For the electrical control of piezo valves VEMP and VEMC
- For the electrical control of piezo valves VEMR and VEAE via an adapter of type NEFV-V13/NEFV-V14
- With protective circuit
- Cable length 0.5 m



General technical data		
Operating voltage range	[V DC]	12 ... 24
Product weight	[g]	35
Type of mounting		With H-rail
		Via through-hole
Mounting position		Any
Degree of protection		IP40
Protective earth connection		Not provided
Additional functions		Protective circuit
Power consumption at 24 V DC	[W]	1.2
Max. output current	[mA]	5
Adjustable output voltage	[V DC]	0 ... 310
Nominal operating voltage	[V DC]	12 ... 24
Reverse polarity protection		For operating voltage
Voltage of external setpoint input	[V DC]	0 ... 10
Input resistance	[kΩ]	10
Maximum tightening torque	[Ncm]	52.5
Bending radius, fixed cable installation	[mm]	13.5
Bending radius, flexible cable installation	[mm]	45

Technical data – Electrical connection 1	
Connection type	Socket
Function	Field device side
Design	Rectangular
Connection technology	Festo-specific coding
Number of pins/wires	3
Assigned pins/wires	3
Type of mounting	Plug-in



Technical data – Electrical connection 2	
Connection type	Cable
Function	Controller side
Cable outlet	Straight
Number of pins/wires	4
Assigned pins/wires	4
Cable diameter	[mm] 4.5
Wire ends	Wire end sleeve

Data sheet

Materials	
Housing	PA
Housing colour	Black
Cable sheath	PVC
Note on materials	RoHS-compliant
Information about materials: Cover	PA


Operating and environmental conditions	
Ambient temperature [°C]	-10 ... +60
Storage temperature [°C]	-40 ... +80
Corrosion resistance class CRC ¹⁾	1
CE marking (see declaration of conformity) ²⁾	To EU EMC Directive
UKCA marking (see declaration of conformity) ²⁾	To UK instructions for EMC
KC mark	KC EMC
Certification	RCM

- 1) Corrosion resistance class CRC 1 to Festo standard FN 940070
 Low corrosion stress. Dry indoor application or transport and storage protection. Also applies to parts behind covers, in the non-visible interior area, and parts which are covered in the application (e.g. drive trunnions).
- 2) For information about the area of use, see the EC declaration of conformity at: www.festo.com/catalogue/... → Support/Downloads.
 If the devices are subject to usage restrictions in residential, commercial or light-industrial environments, further measures for the reduction of the emitted interference may be necessary.

Wiring allocation (socket view)						
Electrical connection 1	Pin	Function VEMP	VEAE	VEMR	VEMC	Output [V DC]
VAVE-P12-TP-5YL1-P						
	1	Earth	Earth	Earth	-	0
	2	Piezo actuator 1	Piezo valve 1	Piezo valve 1	-	0 ... 310
	3	Piezo actuator 2	Piezo valve 2	Piezo valve 2	-	0 ... 310
VAVE-P17-TP-5YL1-P						
	1	-	-	-	Piezo actuator 1	0 ... 310
	2	-	-	-	Earth	0
	3	-	-	-	Piezo actuator 2	0 ... 310

Dimensions


Download CAD data → www.festo.com



[1] VAVE-P17 (VEMC only)
 [2] VAVE-P12 (VEMP, VEAE, VEMR only)

Type	B1	B2	B3	D1 ∅	D2 ∅	D3 ∅	H1	H2	H3	L1	L2	L3	L4	L5	L6	L7	L8	L9
VAVE-P12-TP-5YL1-P	10	16.9	8	4.5	3.4	3.4	26.8	23.3	13.5	500	130	65	33.9	30	7.7	50	7	30
VAVE-P17-TP-5YL1-P																		

Data sheet

Ordering data	Description	Part no.	Type
	<ul style="list-style-type: none"> • For the electrical control of piezo valve VEMP • For the electrical control of piezo valves VEMR and VEAE via an adapter of type NEFV-V13/NEFV-V14 	8109875	VAVE-P12-TP-5YL1-P
	<ul style="list-style-type: none"> • For the electrical control of piezo valve VEMC 	8109876	VAVE-P17-TP-5YL1-P