


Hand lever valves VHER

FESTO



Hand lever valves VHER/HS

Key features

FESTO



Powerful

-  - Flow rate
130 ... 4,300 l/min

Versatile

- 4/3-way valve
mid-position closed
mid-position exhausted
- Connections: M5, G $\frac{1}{8}$, G $\frac{1}{4}$, G $\frac{1}{2}$
- 3/3-way valve
The hand lever valves VHER and HS can be used as 3/3-way valves by sealing port 2

Practical

With these valves it is possible to stop single-acting cylinders (3/3-way valve) or double-acting cylinders (4/3-way valve) within the stroke range.




In mid-position closed, the drive piston moves until the forces are balanced.




In mid-position exhausted the piston can be moved manually; only the frictional forces have to be overcome.

Hand lever valves VHER

Product range overview

FESTO







Function	Version	Type	Nominal flow rate	Lever				Connection				→ Page/ Internet	
			[l/min]	Plastic		Metal		M5	G1/8	G1/4	G1/2		
				small	large	small	large						
		Ports underneath											
		VHER-AH-M04C-G18-UD	800	–	–	■	–	–	■	–	–	8	
		VHER-AH-M04C-G14-UD	1,500	–	–	–	■	–	–	■	–		
		VHER-AH-M04C-G12-UD	4,300	–	–	–	■	–	–	–	■		
			VHER-BH-M04C-M05-UD	260	■	–	–	–	■	–	–	–	15
			VHER-BH-M04C-G18-UD	800	■	–	–	–	–	■	–	–	
			VHER-BH-M04C-G14-UD	1,500	–	■	–	–	–	–	■	–	
			VHER-BH-M04C-G12-UD	4,300	–	■	–	–	–	–	–	■	
	Ports at side												
		VHER-AH-M04C-G18-LD	600	–	–	■	–	–	■	–	–	8	
		VHER-AH-M04C-G14-LD	1,150	–	–	–	■	–	–	■	–		
		VHER-AH-M04C-G12-LD	3,500	–	–	–	■	–	–	–	■		
			VHER-BH-M04C-M05-LD	170	■	–	–	–	■	–	–	–	15
			VHER-BH-M04C-G18-LD	600	■	–	–	–	–	■	–	–	
			VHER-BH-M04C-G14-LD	1,150	–	■	–	–	–	–	■	–	
			VHER-BH-M04C-G12-LD	3,500	–	■	–	–	–	–	–	■	

		Ports underneath											
		VHER-AH-M04E-G18-UD	800	–	–	■	–	–	■	–	–	8	
		VHER-AH-M04E-G14-UD	1,500	–	–	–	■	–	–	■	–		
		VHER-AH-M04E-G12-UD	4,300	–	–	–	■	–	–	–	■		
			VHER-BH-M04E-M05-UD	260	■	–	–	–	■	–	–	–	15
			VHER-BH-M04E-G18-UD	800	■	–	–	–	–	■	–	–	
			VHER-BH-M04E-G14-UD	1,500	–	■	–	–	–	–	■	–	
			VHER-BH-M04E-G12-UD	4,300	–	■	–	–	–	–	–	■	
	Ports at side												
		VHER-AH-M04E-G18-LD	600	–	–	■	–	–	■	–	–	8	
		VHER-AH-M04E-G14-LD	1,150	–	–	–	■	–	–	■	–		
		VHER-AH-M04E-G12-LD	3,500	–	–	–	■	–	–	–	■		
			VHER-BH-M04E-M05-LD	170	■	–	–	–	■	–	–	–	15
			VHER-BH-M04E-G18-LD	600	■	–	–	–	–	■	–	–	
			VHER-BH-M04E-G14-LD	1,150	–	■	–	–	–	–	■	–	
			VHER-BH-M04E-G12-LD	3,500	–	■	–	–	–	–	–	■	

Hand lever valves HS/HSO

Product range overview

FESTO

Function	Version	Type	Nominal flow rate [l/min]	Lever		Connection				→ Page/ Internet	
				Plastic		Metal	M5	G1/8	G1/4		G1/2
				small	large	large					
	Ports underneath										
		HS-4/3-M5	130	■	-	-	■	-	-	-	15
		HS-4/3-1/8-B	700	■	-	-	-	■	-	-	
		HS-4/3-1/4	1,200	-	■	-	-	-	■	-	
	HS-4/3-1/2-B	3,500	-	-	■	-	-	-	■		
	Ports underneath										
		HSO-4/3-M5	130	■	-	-	■	-	-	-	15
		HSO-4/3-1/8-B	700	■	-	-	-	■	-	-	
		HSO-4/3-1/4	1,200	-	■	-	-	-	■	-	
	HSO-4/3-1/2-B	3,500	-	-	■	-	-	-	■		

Hand lever valves VHER

Type codes

FESTO


		VHER	-	BH	-	M04C	-	M05	-	LD
Type										
VHER	Hand lever valve with detent									
Construction										
AH	Lever in metal version									
BH	Lever in polymer version									
Valve function										
M04C	4/3-way valve, mid-position closed									
M04E	4/3-way valve, mid-position exhausted									
Connection										
M05	M5 (polymer version only)									
G18	G $\frac{1}{8}$									
G14	G $\frac{1}{4}$									
G12	G $\frac{1}{2}$									
Connection type										
LD	To the side									
UD	Underneath									

Hand lever valves VHER

Peripherals overview

FESTO

Control panel installation




Component parts and accessories	Brief description	→ Page/Internet
1 Hand lever valves VHER	Connection size G1/8 and G1/2	8
2 Actuating lever	Large, polymer	–
3 Lever securing clip	Large	–
4 Inscription label		–
5 Control panel	Not included in scope of delivery	–
6 Mounting screws	Not included in scope of delivery	–
7 Proximity sensor SME-10-L, SME-10-Q	Not included in scope of delivery	sme
8 Hand lever valves VHER	Connection size M5 and G1/8	8
9 Knurled nut	Control panel mounting	–
10 Actuating lever	Small, polymer	–
11 Lever securing clip	Small	–
12 Actuating lever	Small, metal	–
13 Actuating lever	Large, metal	–

Hand lever valves VHER

Peripherals overview

FESTO

Assembled valves with accessories



Component parts and accessories	Brief description	→ Page/Internet
1 Hand lever valves VHER	Connection size G $\frac{1}{4}$ and G $\frac{1}{2}$ with polymer lever	15
2 Padlock	Not included in scope of delivery	–
3 Hand lever valves VHER	Connection size M5 and G $\frac{1}{8}$ with polymer lever	15
4 Proximity sensor SME-10F-... L-... , SME-10F-... Q-...	Not included in scope of delivery	sme
5 Hand lever valves VHER	Connection size G $\frac{1}{8}$ with metal lever	8
6 Hand lever valves VHER	Connection size G $\frac{1}{4}$ and G $\frac{1}{2}$ with metal lever	8

Hand lever valves VHER-AH

Technical data VHER with metal lever

FESTO

-  Flow rate
600 ... 4,300 l/min
-  Pressure
-0.95 ... +10 bar
-  Temperature range
-20 ... +80 °C



General technical data						
Pneumatic connection			G1/8	G1/4	G1/2	
Valve function			4/3-way, closed or exhausted			
Design			Rotary slide valve			
Sealing principle			Hard			
Type of mounting			Option of front panel mounting or through-holes			
Pilot control mode			Direct			
Actuation type			Manual			
Actuating lever			Metal			
Switching position display			Via accessories			
Assembly position			Any			
Direction of flow			Reversible			
Non-overlapping			Yes			
Exhaust function			Flow control			
Standard nominal flow rate	Ports at side	[l/min]	600	1,150	3,500	
	Ports underneath	[l/min]	800	1,500	4,300	
Nominal size		[mm]	6	8	12	
Pneumatic connection 1,2,3,4			G1/8	G1/4	G1/2	
Actuating torque at 10 bar		[Nm]	1.1	2.8	5	

Operating and environmental conditions		
Operating medium		Filtered compressed air, lubricated or unlubricated, grade of filtration 40µm
Operating pressure	[bar]	-0.95 ... 10
Ambient temperature	[°C]	-20 ... +80
Corrosion resistance class	[CRC]	2 ¹⁾

1) Corrosion resistance class 2 according to Festo standard 940 070

Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

Proximity sensors for switching position display			
Pneumatic connection	Connection direction	Type SME-10F-... L-... SME-10F-... Q-...	
G1/8	Underneath (UD)	■	■
	Side (LD)	-	■
G1/4	Underneath	■	■
	Side	-	■
G1/2	Underneath	■	■
	Side	-	■


Hand lever valves VHER-AH

Technical data VHER with metal lever

FESTO

Sectional view

Hand lever valves VHER-AH-...



Materials

1	Housing	Die-cast aluminium
-	Seals	Nitrile rubber
-		Contains PWIS (paint wetting impairment substances)
-		Free of copper and PTFE

Hand lever valves VHER-AH


Technical data VHER with metal lever

FESTO

Dimensions

Download CAD data → www.festo.com

Ports G $\frac{1}{8}$, side



Type	B1	B2	B3	D1	D2 Ø	H1	H2	H3	H4	L1	L2	L3	L4	T1
VHER-AH-...-G18-LD	51	45	28.5	G $\frac{1}{8}$	3	94	45	15	7.5	85	60.5	54.5	3	2 ... 4

Hand lever valves VHER-AH


Technical data VHER with metal lever

FESTO

Dimensions

Download CAD data → www.festo.com

Ports G $\frac{1}{8}$, underneath



Type	B1	B3	B4	D1	D3 Ø	D4	H1	H2	H5	L1	L2	L5	L6	T1
VHER-AH-...-G18-UD	42	24	32	G $\frac{1}{8}$	5.5	M30	87	37	32.5	79	45	24	9	2 ... 4

Hand lever valves VHER-AH


Technical data VHER with metal lever

FESTO

Dimensions

Download CAD data → www.festo.com

Ports G $\frac{1}{4}$ and G $\frac{1}{2}$, side



1 Sensor slot for SME-10-...

Type	B1	B2	B3	D1	D2 Ø	H1	H2	H3	H4	L1	L2	L3	L4
VHER-AH-...-G14-LD	66	57.5	37.5	G $\frac{1}{4}$	4.5	136	56	20.5	10.3	165	77	69.2	4
VHER-AH-...-G12-LD	95	85	57	G $\frac{1}{2}$	5.5	149	68	29	14.5	180	108.5	97.3	5.5

Hand lever valves VHER-AH


Technical data VHER with metal lever

FESTO

Dimensions

Download CAD data → www.festo.com

Ports G $\frac{1}{4}$ and G $\frac{1}{2}$, underneath





1 Sensor slot for SME-10-...

Type	B1	B2	B3	B4	D1	D2	D3 Ø	D4 Ø	H1	H2	H5	L1	L2	L3	L4	L5	L6	T1
VHER-AH-...-G14-UD	56	42	33	42	G $\frac{1}{4}$	M5	5.5	40	130	49	43.5	157	60	42	7.2	33	11.4	12
VHER-AH-...-G12-UD	80	60	50	60	G $\frac{1}{2}$	M6	6.4	50	137	55.8	49.8	169	85	60	10	50	15	13

Hand lever valves VHER-AH

FESTO

Technical data VHER with metal lever

Ordering data						
Circuit symbol	Description	Weight [g]	Connection direction	Pneumatic connection	Part No.	Type
4/3-way valve ¹⁾						
	Mid-position closed	260	Side	G $\frac{1}{8}$	538 178	VHER-AH-M04C-G18-LD
		560		G $\frac{1}{4}$	538 180	VHER-AH-M04C-G14-LD
		1,010		G $\frac{1}{2}$	538 182	VHER-AH-M04C-G12-LD
		220	Underneath	G $\frac{1}{8}$	538 179	VHER-AH-M04C-G18-UD
		510		G $\frac{1}{4}$	538 181	VHER-AH-M04C-G14-UD
		860		G $\frac{1}{2}$	538 183	VHER-AH-M04C-G12-UD
	Mid-position exhausted	260	Side	G $\frac{1}{8}$	538 184	VHER-AH-M04E-G18-LD
		560		G $\frac{1}{4}$	538 186	VHER-AH-M04E-G14-LD
		1,010		G $\frac{1}{2}$	538 188	VHER-AH-M04E-G12-LD
		220	Underneath	G $\frac{1}{8}$	538 185	VHER-AH-M04E-G18-UD
		510		G $\frac{1}{4}$	538 187	VHER-AH-M04E-G14-UD
		860		G $\frac{1}{2}$	538 189	VHER-AH-M04E-G12-UD

1) The hand lever valve can be used as a 3/3-way valve by sealing port 2.

Hand lever valves VHER-BH

Technical data VHER with plastic lever

FESTO

-  Flow rate
170 ... 4,300 l/min

-  Pressure
-0.95 ... +10 bar

-  Temperature range
-20 ... +80 °C



General technical data						
Pneumatic connection			M5	G1/8	G1/4	G1/2
Valve function			4/3-way, closed or exhausted			
Design			Rotary slide valve			
Sealing principle			Hard			
Type of mounting			Front panel mounting	Option of front panel mounting or through-holes		
Pilot control mode			Direct			
Actuation type			Manual			
Actuating lever			Polymer			
Actuator lock			Lockable with accessories			
Switching position display			Via accessories			
Assembly position			Any			
Direction of flow			Reversible			
Standard nominal flow rate	Ports at side	[l/min]	170	600	1,150	3,500
	Ports underneath	[l/min]	260	800	1,500	4,300
Nominal size		[mm]	4	6	8	12
Pneumatic connection 1,2,3,4			M5	G1/8	G1/4	G1/2
Actuating force at 6 bar		[N]				
Actuating torque at 10 bar		[Nm]	0.6	1.1	2.8	–

Operating and environmental conditions		
Operating medium		Filtered compressed air, lubricated or unlubricated, grade of filtration 40µm
Operating pressure	[bar]	–0.95 ... 10
Ambient temperature	[°C]	–20 ... +80
Corrosion resistance class	[CRC]	2 ¹⁾

1) Corrosion resistance class 2 according to Festo standard 940 070
Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

Proximity sensors for switching position display			
Pneumatic connection	Connection direction	Type	
		SME-10F-... L-...	SME-10F-... Q-...
M5	Underneath (UD)	■	■
	Side (LD)	–	■
G1/8	Underneath	■	■
	Side	–	■
G1/4	Underneath	■	■
	Side	–	■
G1/2	Underneath	■	■
	Side	–	■


Hand lever valves VHER-BH

Technical data VHER with plastic lever

FESTO

Sectional view

Hand lever valves VHER-BH-...



Materials		
1	Housing	Reinforced PA or die-cast aluminium
-	Seals	Nitrile rubber
-		Contains PWIS (paint wetting impairment substances)
-		Free of copper and PTFE (paint wetting impairment substances)

Hand lever valves VHER-BH


Technical data VHER with plastic lever

FESTO

Dimensions

Download CAD data → www.festo.com

Ports M5 and G $\frac{1}{8}$, side



1 Sensor slot for SME-10-...

2 Hole for padlock, dia. 7.2

3 Locking button, lockable

6 Lever securing clip, detachable

Type	B1	B2	B3	D1	D2 Ø	H1	H2	H3	H4	L1	L2	L3	L4
VHER-BH-...-M05-LD	37	32	17.4	M5	2.5	82	32	10	5	78	45	40	2.5
VHER-BH-...-G18-LD	51	45	28.5	G $\frac{1}{8}$	3	94	45	15	7.5	85	60.5	54.5	3

Hand lever valves VHER-BH


Technical data VHER with plastic lever

FESTO

Dimensions

Download CAD data → www.festo.com

Ports M5 and G $\frac{1}{8}$, underneath



- 1 Sensor slot for SME-10-...
- 2 Hole for padlock, dia. 7.2

- 3 Locking button, lockable

- 4 Material thickness for control panel installation

- 5 Knurled nut
- 6 Lever securing clip, detachable

Type	B1	B3	B4	D1	D3 Ø	D4	H1	H2	H5	L1	L2	L5	L6	T1
VHER-BH-...-M05-UD	30	17	-	M5	-	M22	79	28.6	-	73	33.8	17	6.5	2 ... 4
VHER-BH-...-G18-UD	42	24	32	G $\frac{1}{8}$	5.5	M30	86	37	32.5	79	45	24	9	1.5 ... 4.5

Hand lever valves VHER-BH


Technical data VHER with plastic lever

FESTO

Dimensions

Download CAD data → www.festo.com

Ports G $\frac{1}{4}$ and G $\frac{1}{2}$, side



Type	B1	B2	B3	D1	D2 Ø	H1	H2	H3	H4	L1	L2	L3	L4
VHER-BH-...-G14-LD	66	57.5	37.5	G $\frac{1}{4}$	4.3	136	55.5	20.5	10.25	166	77	69.2	4
VHER-BH-...-G12-LD	96	85	57	G $\frac{1}{2}$	5.3	148	67.8	29	14.5	180	108.5	97.3	5.5

Hand lever valves VHER-BH


Technical data VHER with plastic lever

FESTO

Dimensions

Download CAD data → www.festo.com

Ports G $\frac{1}{4}$ and G $\frac{1}{2}$, underneath



2 Hole for padlock, dia. 7.2

3 Locking button, lockable



6 Lever securing clip, detachable

Type	B1	B2	B3	B4	D1	D2	D3 Ø	D4	H1	H2	H5	L1	L2	L3	L4	L5	L6	T1
VHER-BH-...-G14-UD	56.3	42	33	42	G $\frac{1}{4}$	M5	5.4	40.5	129	49	43.5	157	60.2	42	7.2	33	11.7	13
VHER-BH-...-G12-UD	80	60	50	60	G $\frac{1}{2}$	M6	6.5	51	137	55.8	49.8	169	84.8	60	10	50	15	16

Hand lever valves VHER-BH

Technical data VHER with plastic lever

FESTO

Ordering data						
Circuit symbol	Description	Weight [g]	Connection direction	Pneumatic connection	Part No.	Type
4/3-way valve ¹⁾						
	Mid-position closed	95	Side	M5	538 190	VHER-BH-M04C-M05-LD
		165		G1/8	538 192	VHER-BH-M04C-G18-LD
		435		G1/4	538 194	VHER-BH-M04C-G14-LD
		900		G1/2	538 196	VHER-BH-M04C-G12-LD
		80	Underneath	M5	538 191	VHER-BH-M04C-M05-UD
		125		G1/8	538 193	VHER-BH-M04C-G18-UD
		375		G1/4	538 195	VHER-BH-M04C-G14-UD
		740		G1/2	538 197	VHER-BH-M04C-G12-UD
	Mid-position exhausted	95	Side	M5	538 198	VHER-BH-M04E-M05-LD
		165		G1/8	538 200	VHER-BH-M04E-G18-LD
		435		G1/4	538 202	VHER-BH-M04E-G14-LD
		900		G1/2	538 204	VHER-BH-M04E-G12-LD
		80	Underneath	M5	538 199	VHER-BH-M04E-M05-UD
		125		G1/8	538 201	VHER-BH-M04E-G18-UD
		375		G1/4	538 203	VHER-BH-M04E-G14-UD
		740		G1/2	538 205	VHER-BH-M04E-G12-UD


1) The hand lever valve can be used as a 3/3-way valve by sealing port 2.

Hand lever valves HS/HSO

FESTO

Technical data


-  Flow rate
130 ... 3,500 l/min
-  Pressure
-0.95 ... +10 bar
-  Temperature range
-10 ... +60 °C



General technical data					
Pneumatic connection		M5	G1/8	G1/4	G-1/2
Operating medium		Filtered compressed air, lubricated or unlubricated Vacuum ¹⁾			
Design		Flat slide valve			
Type of mounting		Front panel mounting	Front panel mounting, mounting holes	Front panel mounting	
Nominal size	[mm]	3.6	6	8	12
Standard nominal flow rate 1 4	[l/min]	130	700	1,200	3,500
Operating pressure range		[bar] -0.95 ... +10 bar			
Actuating force at 6 bar		[N] -	-	12	26
Actuating torque at 6 bar		[Nm] 0.3	1	-	-
Temperature range		[°C] -20 ... +60			-20 ... +80
Materials	Housing	Die-cast aluminium, plastic			
	Seals	Nitrile rubber			
Weight	[g]	35	120	390	1,350

- 1) M5: vacuum at ports 1 and 3
 G1/8: vacuum at port 3
 G1/4: vacuum at ports 1 and 3
 G1/2: vacuum at port 3


HS...-...1/4




- 1 = Supply port
- 4, 2 = Working or outlet ports
- 3 = Exhaust

Ports underneath

HS



HSO



Hand lever valves HS/HSO

Technical data

FESTO




Dimensions

Download CAD data → www.festo.com

Port M5

Mounting aperture

Lever position



1 Lever can be repositioned by 180°

s = Front panel thickness
1.5 ... 6 mm

2 Max. tightening torque: 3 Nm

Hand lever valves HS/HSO


Technical data

FESTO

Dimensions

Download CAD data → www.festo.com

Port G1/8




- 1 Lever can be repositioned by 180°
- 2 Max. tightening torque: 3 Nm



s = Front panel thickness
2 ... 5 mm

Mounting aperture

Lever position



Technical data

Port G^{1/4}Port G^{1/2}

Circuit symbol	Description	Pneumatic connection	Part No.	Type
4/3-way valve ¹⁾				
	Mid-position closed	M5	34 639	HS-4/3-M5
		G1/8	151 842	HS-4/3-1/8-B
		G1/4	9 339	HS-4/3-1/4
		G1/2	9 784	HS-4/3-1/2-B
	Mid-position exhausted	M5	34 539	HSO-4/3-M5
		G1/8	151 843	HSO-4/3-1/8-B
		G1/4	9 340	HSO-4/3-1/4
		G1/2	9 785	HSO-4/3-1/2-B

1) The hand lever valve HS can be used as a 3/3-way valve by sealing port 2, blanking plugs → 26

Hand lever valves HS/HSO/VHER

Accessories

FESTO

Ordering data				
	Description	Pneumatic connection	Part No.	Type
Blanking plugs				
	For sealing ports	M5	3 843	B-M5 ¹⁾
		G1/8	3 568	B-1/8 ¹⁾
		G1/4	3 569	B-1/4 ¹⁾
		G1/2	3 571	B-1/2 ¹⁾
Silencers				
	For fitting in exhaust ports	–	➔ Internet: u	
Push-in fittings QS				
	For connecting compressed air tubing with standard O.D.	–	➔Internet: quick star	

Permissible QS fittings ¹⁾ for VHER							
Part No.	Type	Part No.	Type	Part No.	Type	Part No.	Type
VHER-...-M05-UD		VHER-...-M05-LD		VHER-...-G18-UD		VHER-...-G18-LD	
153 302	QSM-M5-3	153 313	QSM-M5-3-I	186 264	QSM-G $\frac{1}{8}$ -4	186 266	QSM-G $\frac{1}{8}$ -4-I
153 304	QSM-M5-4	153 315	QSM-M5-4-I	186 265	QSM-G $\frac{1}{8}$ -6	186 267	QSM-G $\frac{1}{8}$ -6-I
153 306	QSM-M5-6			186 266	QSM-G $\frac{1}{8}$ -4-I	186 106	QS-G $\frac{1}{8}$ -4-I
153 313	QSM-M5-3-I			186 267	QSM-G $\frac{1}{8}$ -6-I	186 107	QS-G $\frac{1}{8}$ -6-I
153 315	QSM-M5-4-I			186 095	QS-G $\frac{1}{8}$ -4	186 109	QS-G $\frac{1}{8}$ -8-I
153 317	QSM-M5-6-I			186 096	QS-G $\frac{1}{8}$ -6		
				186 098	QS-G $\frac{1}{8}$ -8		
				186 106	QS-G $\frac{1}{8}$ -4-I		
				186 107	QS-G $\frac{1}{8}$ -6-I		
				186 109	QS-G $\frac{1}{8}$ -8-I		
VHER-...-G14-UD		VHER-...-G14-LD		VHER-...-G12-UD		VHER-...-G12-LD	
186 097	QS-G $\frac{1}{4}$ -6	186 108	QS-G $\frac{1}{4}$ -6-I	186 104	QS-G $\frac{1}{2}$ -12	186 115	QS-G $\frac{1}{2}$ -12-I
186 099	QS-G $\frac{1}{4}$ -8	186 110	QS-G $\frac{1}{4}$ -8-I	186 105	QS-G $\frac{1}{2}$ -16		
186 101	QS-G $\frac{1}{4}$ -10	186 112	QS-G $\frac{1}{4}$ -10-I	186 115	QS-G $\frac{1}{2}$ -12-I		
186 108	QS-G $\frac{1}{4}$ -6-I						
186 110	QS-G $\frac{1}{4}$ -8-I						
186 112	QS-G $\frac{1}{4}$ -10-I						

1) Scope of delivery 10 pieces

Permissible silencers for VHER							
Part No.	Type	Part No.	Type	Part No.	Type	Part No.	Type
VHER-....M05-UD		VHER-...-M05-LD		VHER-....G18-UD		VHER-....G18-LD	
4 645	U-M5	4 645	U-M5	6 841	U-1/8-B	161 419	UC-1/8
165 003	UC-M5	165 003	UC-M5	161 419	UC-1/8		
				2 307	U-1/8		
VHER-....G14-UD		VHER-...-G14-LD		VHER-....G12-UD		VHER-....G12-LD	
6 842	U-1/4-B	165 004	UC-1/4	6 844	U-1/2-B	6 844	U-1/2-B
165 004	UC-1/4						
2 316	U-1/4						

Hand lever valves VHER

Accessories

FESTO

Ordering data – Proximity sensors for VHER						
	Electrical connection		Cable length [m]	Connection direction	Part No.	Type
	Cable	Plug M8x1				
	N/O contact					
	3-wire	–	2.5	In-line	173 210	SME-10-KL-LED-24
				Lateral	173 211	SME-10-KQ-LED-24
	–	3-pin	0.3	In-line	173 212	SME-10-SL-LED-24
				Lateral	173 213	SME-10-SQ-LED-24

Product Range and Company Overview

A Complete Suite of Automation Services

Our experienced engineers provide complete support at every stage of your development process, including: conceptualization, analysis, engineering, design, assembly, documentation, validation, and production.



Custom Automation Components
Complete custom engineered solutions



Custom Control Cabinets
Comprehensive engineering support
and on-site services



Complete Systems
Shipment, stocking and storage services

The Broadest Range of Automation Components

With a comprehensive line of more than 30,000 automation components, Festo is capable of solving the most complex automation requirements.



Electromechanical
Electromechanical actuators, motors,
controllers & drives



Pneumatics
Pneumatic linear and rotary actuators,
valves, and air supply



PLCs and I/O Devices
PLC's, operator interfaces, sensors
and I/O devices

Supporting Advanced Automation... As No One Else Can!

Festo is a leading global manufacturer of pneumatic and electromechanical systems, components and controls for industrial automation, with more than 12,000 employees in 56 national headquarters serving more than 180 countries. For more than 80 years, Festo has continuously elevated the state of manufacturing with innovations and optimized motion control solutions that deliver higher performing, more profitable automated manufacturing and processing equipment. Our dedication to the advancement of automation extends beyond technology to the education and development of current and future automation and robotics designers with simulation tools, teaching programs, and on-site services.

Quality Assurance, ISO 9001 and ISO 14001 Certifications

Festo Corporation is committed to supply all Festo products and services that will meet or exceed our customers' requirements in product quality, delivery, customer service and satisfaction.

To meet this commitment, we strive to ensure a consistent, integrated, and systematic approach to management that will meet or exceed the requirements of the ISO 9001 standard for Quality Management and the ISO 14001 standard for Environmental Management.



© Copyright 2008, Festo Corporation. While every effort is made to ensure that all dimensions and specifications are correct, Festo cannot guarantee that publications are completely free of any error, in particular typing or printing errors. Accordingly, Festo cannot be held responsible for the same. For Liability and Warranty conditions, refer to our "Terms and Conditions of Sale", available from your local Festo office. All rights reserved. No part of this publication may be reproduced, distributed, or transmitted in any form or by any means, electronic, mechanical, photocopying or otherwise, without the prior written permission of Festo. All technical data subject to change according to technical update.



Printed on recycled paper at New Horizon Graphic, Inc., FSC certified as an environmentally friendly printing plant.

Festo North America

United States

Customer Resource Center

502 Earth City Expy., Suite 125
Earth City, MO 63045

For ordering assistance, or to find
your nearest Festo Distributor,

Call: 1.800.99.FESTO

Fax: 1.800.96.FESTO

Email: customer.service@us.festo.com

For technical support,

Call: 1.866.GO.FESTO

Fax: 1.800.96.FESTO

Email: product.support@us.festo.com

Headquarters

Festo Corporation
395 Moreland Road
P.O. Box 18023
Hauppauge, NY 11788
www.festo.com/us

Sales Offices

Appleton

N. 922 Tower View Drive, Suite N
Greenville, WI 54942

Boston

120 Presidential Way, Suite 330
Woburn, MA 01801

Chicago

1441 East Business Center Drive
Mt. Prospect, IL 60056

Dallas

1825 Lakeway Drive, Suite 600
Lewisville, TX 75057

Detroit - Automotive Engineering Center

2601 Cambridge Court, Suite 320
Auburn Hills, MI 48326

New York

395 Moreland Road
Hauppauge, NY 11788

Silicon Valley

4935 Southfront Road, Suite F
Livermore, CA 94550

Design and Manufacturing Operations



East: 395 Moreland Road, Hauppauge, NY 11788



Central: 1441 East Business Center Drive, Mt. Prospect, IL 60056



West: 4935 Southfront Road, Suite F, Livermore, CA 94550

Mexico

Headquarters

Festo Pneumatic, S.A.
Av. Ceylán 3, Col. Tequesquihuac
54020 Tlalnepantla, Edo. de México
Call: 011 52 [55] 53 21 66 00
Fax: 011 52 [55] 53 21 66 65
Email: festo.mexico@mx.festo.com
www.festo.com/mx



Canada

Headquarters

Festo Inc.
5300 Explorer Drive
Mississauga, Ontario L4W 5G4
Call: 1.905.624.9000
Fax: 1.905.624.9001
Email: info.ca@ca.festo.com
www.festo.com/ca



Festo Worldwide

Argentina Australia Austria Belarus Belgium Brazil Bulgaria Canada Chile China Colombia Croatia Czech Republic Denmark
Estonia Finland France Germany Great Britain Greece Hong Kong Hungary India Indonesia Iran Ireland Israel Italy Japan
Latvia Lithuania Malaysia Mexico Netherlands New Zealand Norway Peru Philippines Poland Romania Russia Serbia Singapore
Slovakia Slovenia South Africa South Korea Spain Sweden Switzerland Taiwan Thailand Turkey Ukraine United States Venezuela

www.festo.com