

Proportional directional control valves VPWS

FESTO




Key features

General

The solenoid valves VPWS are proportional directional control valves. This means that the flow rate of suitable media can be controlled proportionally. Approved operating media include air, oxygen and inert gases.

The solenoid valve VPWS should only be operated within the limits defined in the technical data. The specific on-site operating conditions are to be observed.

Overview of valve with manifold block



- [1] Solenoid valve VPWS
- [2] Manifold block
- [3] Pneumatic connection
- [4] Mounting hole for M3 screws
- [5] Mounting
- [6] Socket head screw M4

Note

The product has no redundancy and no error detection. When malfunctions need to be detected, this must be done by implementing the necessary measures in the customer product.

Type codes

001	Series
VPWS	Proportional directional control valve

002	Nominal width [mm]
1.5	1.5
2.2	2.2
6	6

003	Directional control valve type
B	Sub-base valve




004	Valve function
6	2/2-way valve, normally closed



005	Pneumatic connection
PC15	Cartridge 15 mm

006	Pressure range [bar]
3	0 ... 3
8	0 ... 8

007	Sealant
V	FPM

Technical data

-  Flow rate
46 ... 220 l/min
-  Diameter of cartridge
7.5 ... 15 mm
-  Voltage
≤19 ... 19.9 V DC


General technical data

Nominal width DN	1.5 mm	2.2 mm	6 mm	
Valve function	2/2-way proportional directional control valve, closed			
Reset method	Mechanical spring			
Design	Directly actuated poppet valve			
Sealing principle	Soft			
Actuation type	Electrical			
Type of control	Direct			
Direction of flow	Not reversible			
Mounting position	Any			
Type of mounting	On sub-base Plug-in With accessories			
Pneumatic connection 1	Cartridge 15 mm		Cartridge 7.5 mm	
Pneumatic connection 2	Cartridge 7.2 mm		Cartridge 15 mm	
Flow rate q	[l/min]	82 ... 98	46 ... 56	200 ... 220
Product weight	[g]	23		25
Degree of protection to EN 60529	IP60			
Note on degree of protection	IP65 with suitable plug In assembled state			

Operating and environmental conditions

Nominal width DN	1.5 mm	2.2 mm	6 mm	
Medium	Inert gases Air Oxygen			
Note on the medium	Lubricated operation not possible			
Note on the medium, maximum particle size	[µm]	10		
Operating pressure	[MPa]	0 ... 0.8	0 ... 0.3	
	[bar]	0 ... 8	0 ... 3	
Nominal operating pressure	[MPa]	0 ... 0.8	0.3	0.2
	[bar]	8	3	2
	[psi]	116	43.5	29
Ambient temperature	[°C]	+5 ... +50		
Temperature of medium	[°C]	+5 ... +50		
Storage temperature	[°C]	-40 ... +80		
Corrosion resistance class CRC ¹⁾		1		

1) Corrosion resistance class CRC 1 to Festo standard FN 940070

Low corrosion stress. Dry indoor application or transport and storage protection. Also applies to parts behind covers, in the non-visible interior area, and parts which are covered in the application (e.g. drive trunnions).

Technical data

Electrical data		
Nominal width DN		1.5 mm 2.2 mm
Continuous operating voltage at 20°C without inflow	[V DC]	≤ 16.5
Continuous operating voltage at 50°C without inflow	[V DC]	≤ 14.5
Typical continuous operating voltage at 50 °C with inflow	[V DC]	≤ 19.0
Max. switching frequency	[Hz]	18
Hysteresis	[mA]	16
Coil resistance	[Ω]	60.5
Max. electrical power consumption	[W]	2.5
Current regulating range	[mA]	0 ... 200
Duty cycle ED	[%]	100 (see assembly instructions)

Nominal width DN		6 mm	
		Air	Oxygen
Continuous operating voltage at 20°C without inflow	[V DC]	≤ 14.5	≤ 11.4
Continuous operating voltage at 50°C without inflow	[V DC]	≤ 13.3	≤ 9.6
Typical continuous operating voltage at 50°C with inflow (≥ 30 l/min)	[V DC]	≤ 19.9	
Switching time on	[ms]	10	
Hysteresis	[mA]	22.5	
Coil resistance	[Ω]	60.5	
Max. electrical power consumption	[W]	3	
Current regulating range	[mA]	0 ... 225	
Duty cycle ED	[%]	100 (see assembly instructions)	


Electrical connection		
Electrical connection	Connection technology	Open end
	Number of pins/wires	2
	Connection type	Cable
Cable length	[mm]	70 ... 80

Materials	
Housing	High-alloy steel
Seals	FPM
Note on materials	RoHS-compliant
PWIS conformity	VDMA24364-Zone III

Technical data


Flow rate/current characteristic curves

Nominal width 1.5 mm




[1] Characteristic curve for 1 bar

[3] Characteristic curve for 3 bar




[2] Characteristic curve for 2 bar

[4] Characteristic curve for 4 bar



[5] Characteristic curve for 5 bar

[7] Characteristic curve for 7 bar



[6] Characteristic curve for 6 bar

[8] Characteristic curve for 8 bar


Note

Resonance may occur during operation at a low frequency and this may affect the flow rate. Operation at very low flow rates may generate noise. No resonance occurs during operation at a frequency of 0.3 Hz or higher.


Technical data

Flow rate/current characteristic curves


Nominal width 2.2 mm



[1] Characteristic curve for 0.5 bar [3] Characteristic curve for 1.5 bar




[2] Characteristic curve for 1.0 bar [4] Characteristic curve for 2.5 bar



[5] Characteristic curve for 2.0 bar [7] Characteristic curve for 3.0 bar

Flow rate/pressure characteristic curve at 200 mA




— VPWS-DN 1.5
 - - - VPWS-DN 2.2

Technical data


Flow rate/current characteristic curves

Nominal width 6 mm



[1] Characteristic curve for 0.5 bar


[3] Characteristic curve for 1 bar



[2] Characteristic curve for 2 bar

[4] Characteristic curve for 3 bar

Flow rate/pressure characteristic curve at 225 mA




Technical data

Dimensions

 Download CAD data → www.festo.com

Proportional directional control valve


 [1] Pneumatic connection 1
(with VPWS-6 as connection 2)


 [2] Pneumatic connection 2
(with VPWS-6 as connection 1)

Type	D1 ∅	D2 ∅	D3 ∅	L1	L2	L3	L4	L5
VPWS-1.5-B-6-PC15-8-V	15	7.2	15	31	17.5	70 ... 80	5.5	3.2
VPWS-2.2-B-6-PC15-3-V	15	7.2	15	31	17.5	70 ... 80	5.5	3.2
VPWS-6-B-6-PC15-3-V	15	7.5	15	36.4	22.9	70 ... 80	7.23	2.9

Dimensions

 Download CAD data → www.festo.com

Manifold block



[1] Socket head screw M4X8


Type	B1	D1	D2	D3 ∅	H1	H2	H3	H4	H5	L1	L2	T1	T2
VABS-P4-10S-G14	21	G1/4	G1/4	3.4	40	35	10	29	17.5	44	34	13	13
VABS-P4-20S-G38	25	G3/8	G3/8	3.4	47	42	11.5	36	19	44	34	13	13

Technical data

Dimensions

Download CAD data → www.festo.com

Mounting



Type	B1	D1	H1	L1
VAME-P4-PC15-P-P10	17	4.5	1	15.2

Ordering data

			Part No.	Type	PU ¹⁾
Proportional directional control valve					
	2/2-way proportional directional control valve, closed	Nominal width 1.5 mm	8074075	VPWS-1.5-B-6-PC15-8-V	1
		Nominal width 2.2 mm	8074074	VPWS-2.2-B-6-PC15-3-V	1
		Nominal width 6 mm	8074537	VPWS-6-B-6-PC15-3-V	1
Manifold block					
	Suitable for proportional directional control valves with nominal width 1.5 and 2.2 mm Set for 2/2-way proportional directional control valve VPWS, comprising: <ul style="list-style-type: none"> Manifold block VABS-P4-10S-G14 1 mounting component from the set VAME-P4-PC15-P-P10 Socket head screw M4x8 		8087327	VABS-P4-10S-G14	1
		Suitable for proportional directional control valve with nominal width 6 mm Set for 2/2-way proportional directional control valve VPWS, comprising: <ul style="list-style-type: none"> Manifold block VABS-P4-20S-G38 1 mounting component from the set VAME-P4-PC15-P-P10 Socket head screw M4x8 		8087328	VABS-P4-20S-G38
Mounting					
	For 2/2-way proportional directional control valve VPWS in manifold block VABS (set comprises 10 mountings for 10 proportional directional control valves VPWS)		8087347	VAME-P4-PC15-P-P10	1

1) Packaging unit.