

Solenoid valves MFHE/Pneumatic valves VLHE

FESTO




- 1 - Type discontinued
Available up until 2016

Solenoid valves MFHE/Pneumatic valves VLHE

Peripherals overview

FESTO




Accessories			
	MFHE	VLHE	→ Page/Internet
1 Solenoid coil MSFG/MSFW	■	–	8
2 Plug socket with cable KMF	■	–	8
3 Illuminating seal MF-LD	■	–	8
4 Plug socket MSSD-F	■	–	8
5 Silencer U	■	■	8


Solenoid valves MFHE

Technical data

Function



-  - Flow rate
1,200 ... 2,900 l/min
-  - Temperature range
-10 ... +60 °C
-  - Operating pressure
2 ... 10 bar/28 ... 145 psi
-  - www.festo.com



Solenoid actuated soft start valve for gradual pressure build-up in pneumatic systems. This ensures safe start-up of pneumatic systems. A minimal amount of air flows into the system via an adjustable flow control valve. Output pressure is built up slowly. Downstream cylinders and working devices are slowly advanced to their initial positions. When the

output pressure reaches approx. 50% of the supply pressure, the valve switches to full flow.

- For F solenoid coils
 - 12, 24, 42 V DC
 - 24, 42, 48, 110, 230, 240 V AC (50 ... 60 Hz)
- On-off valve in combination with service units
- Manual override, detenting

- - Note

Manual override can be detented and secured in the initial position. In the depressed position, the manual override is advanced automatically to its initial position when the valve is actuated.

- - Note

Control voltage should not be switched to downstream solenoid valves until after pressure has been built up.

General technical data			
Type	MFHE-3-1/4-B	MFHE-3-3/8	MFHE-3-1/2
Pneumatic connection 1, 2	G1/4	G3/8	G1/2
Pneumatic connection 3	G1/4	G3/8	G1/2
Nominal diameter [mm]	8	9	12
Design	Disk seat		
Type of mounting	Via through-holes		
Mounting position	Any		
Valve function	3/2-way valve, closed, single solenoid		
Exhaust function	Without flow control		
Reset method	Mechanical spring		
Actuation type	Direct		
Direction of flow	Non-reversible		
Sealing principle	Soft		
Response time on/off [ms]	12/80	20/94	28/76

Standard nominal flow rate q _N [l/min]			
Pneumatic connection	G1/4	G3/8	G1/2
In flow direction			
1 → 2 unthrottled	1,200	2,100	2,900
1 → 2 throttled	max. 150	max. 450	max. 450
In venting direction			
2 → 3	1,600	2,700	3,400

- 1 - Type discontinued
Available up until 2016

Solenoid valves MFHE

Technical data


FESTO

Operating and environmental conditions		
Operating pressure	[bar]	2 ... 10
	[psi]	28 ... 145
Operating medium	Compressed air in accordance with ISO 8573-1:2010 [7:4:4]	
Note on operating/pilot medium	Operation with lubricated medium possible (in which case lubricated operation will always be required)	
Ambient temperature	[°C]	-5 ... +40
Temperature of medium	[°C]	-10 ... +60

Weights [g]			
Pneumatic connection	G $\frac{1}{4}$	G $\frac{3}{8}$	G $\frac{1}{2}$
Solenoid valve MFHE	550	800	1,000

Materials

Sectional view



Solenoid valve	
1 Housing	POM, aluminium, steel, brass
- Seals	NBR
Note on materials	RoHS-compliant (only MFHE-3- $\frac{1}{4}$ -B)


Solenoid valves MFHE

Technical data

FESTO

Dimensions

Download CAD data → www.festo.com



Type	B1	B2	B3	B4	B5	B6	D1 Ø	D2 Ø	E1	H1
MFHE-3-1/4-B	27	71	36.55	16.4	85.05	22	5.5	10	G1/4	82
MFHE-3-3/8	29.7	86	43	15.7	91.5	28.2	5.5	10	G3/8	95
MFHE-3-1/2	29.7	90.7	45.3	20.3	93.8	30.5	6.5	11	G1/2	98.2

Type	H2	H3	H4	H5	L1	L2	L3	L4	L5	L6
MFHE-3-1/4-B	10	40	132	116	55.6	64.3	10	14.3	47.2	16.5
MFHE-3-3/8	10	47	145	129	63.4	70.1	10	14.3	56.6	18.7
MFHE-3-1/2	10.1	46.7	148	132	71.6	76	10	14.7	63.7	22.9

Ordering data


Pneumatic connection	Part No.	Type
G1/4	14329	MFHE-3-1/4-B
G3/8	12908	MFHE-3-3/8
G1/2	10421	MFHE-3-1/2

- 1 - Type discontinued
Available up until 2016

Pneumatic valves VLHE

Technical data

Function



-  - Flow rate
1,200 ... 2,900 l/min
-  - Temperature range
-10 ... +60 °C
-  - Operating pressure
2 ... 12 bar/28 ... 180 psi
-  - www.festo.com



Pneumatically actuated soft start valve for gradual pressure build-up in pneumatic systems. This ensures safe start-up of pneumatic systems. A minimal amount of air flows into the system via an adjustable flow control valve. Output pressure is built up slowly. Downstream cylinders and

work devices are slowly advanced to their initial positions. When the output pressure reaches approx. 50% of the supply pressure, the valve switches to full flow.

- On-off valve in combination with service units
- Manual override, detenting

-  - Note

Manual override can be detented and secured in the initial position. In the depressed position, the manual override is advanced automatically to its initial position when the valve is actuated.

General technical data			
Type	VLHE-3-1/4-B	VLHE-3-3/8	VLHE-3-1/2
Pneumatic connection 1, 2	G1/4	G3/8	G1/2
Pneumatic connection 3	G1/4	G3/8	G1/2
Pneumatic connection 12 (pilot air)	G1/8	G1/8	G1/8
Nominal diameter [mm]	8	9	12
Design	Disk seat		
Type of mounting	Via through-holes		
Mounting position	Any		
Valve function	3/2-way valve, closed, single solenoid		
Exhaust function	With flow control		
Sealing principle	Soft		
Response time on/off [ms]	8/23	8.5/19.5	25/39

Standard nominal flow rate q _N [l/min]			
Pneumatic connection	G1/4	G3/8	G1/2
In flow direction			
1 → 2	1,200	2,100	2,900
throttled	max. 150	max. 450	max. 450
In venting direction			
2 → 3	1,600	2,700	3,400

Operating and environmental conditions		
Operating pressure	[bar]	2 ... 12
	[psi]	28 ... 180
Operating medium	Compressed air in accordance with ISO 8573-1:2010 [7:4:4]	
Note on operating/pilot medium	Operation with lubricated medium possible (in which case lubricated operation will always be required)	
Ambient temperature	[°C]	-10 ... +60
Temperature of medium	[°C]	-10 ... +60

Weights [g]			
Pneumatic connection	G1/4	G3/8	G1/2
Pneumatic valve VLHE	430	790	980


Pneumatic valves VLHE

Technical data

FESTO

Materials


Sectional view



Pneumatic valve		
1	Housing	POM, aluminium, steel, brass
-	Seals	NBR
Note on materials		RoHS-compliant (only VLHE-3-1/4-B)

Dimensions

Download CAD data → www.festo.com



Type	B1	B2	B3	B4	B5	B6	D1 Ø	D2 Ø	E1
VLHE-3-1/4-B	27	71	36.5	16.5	40	22	5.5	10	G1/4
VLHE-3-3/8	29.7	86	43	15.7	48.2	28	5.5	10	G3/8
VLHE-3-1/2	29.7	90.7	45.3	20.2	51	30.5	6.5	11	G1/2

Type	H1	H2	H3	L1	L2	L3	L4	L5	L6
VLHE-3-1/4-B	82	10	40	55.6	64.3	10	14.3	47.2	16.5
VLHE-3-3/8	95	10	47	63.4	70.1	10	14.3	56.6	18.7
VLHE-3-1/2	98.2	10.1	46.7	71.6	76	10	14.7	63.7	22.9


Ordering data


Pneumatic connection	Part No.	Type
G1/4	14330	VLHE-3-1/4-B
G3/8	12909	VLHE-3-3/8
G1/2	10420	VLHE-3-1/2

Solenoid valves MFHE/Pneumatic valves VLHE

Accessories

FESTO

Ordering data – Solenoid coils MSFG/MSFW				Technical data → Internet: msf	
	Description	Operating voltage		Part No.	Type
		V DC	V AC (50 ... 60 Hz)		
	F solenoid coil, with spring washer and knurled nut, without plug socket	12	–	34410	MSFG-12DC-OD
		24	42	34411	MSFG-24DC/42AC-OD
		42	–	34413	MSFG-42DC-OD
		–	24	34415	MSFW-24AC-OD
		–	48	34418	MSFW-48AC-OD
		–	110	34420	MSFW-110AC-OD
		–	230	34422	MSFW-230AC-OD
		–	240	34424	MSFW-240AC-OD

Ordering data – Plug sockets with cable KMF				Technical data → Internet: kmf	
	Nominal operating voltage	Switching status display	Cable length [m]	Part No.	Type
	24 V DC	LED	2.5	30935	KMF-1-24DC-2,5-LED
			5	30937	KMF-1-24DC-5-LED
			10	193458	KMF-1-24-10-LED
	230 V AC	–	2.5	30936	KMF-1-230AC-2,5
			5	30938	KMF-1-230AC-5

Ordering data – Illuminating seal MF-LD			Technical data → Internet: mlf	
	Operating voltage range		Part No.	Type
	12 ... 24 V DC		19143	MF-LD-12-24DC
	230 V DC/V AC ±10%		19144	MF-LD-230AC

Ordering data – Plug sockets MSSD-F			Technical data → Internet: mssd	
	Type of mounting: cable connection		Part No.	Type
	Cable conduit fitting Pg9		34431	MSSD-F
	Cable conduit fitting M16		539710	MSSD-F-M16
	Insulation displacement connector		192746	MSSD-F-S-M16

Ordering data – Silencers U			Technical data → Internet: u	
	Pneumatic connection		Part No.	Type
	G1/4		6842	U-1/4-B
	G3/8		6843	U-3/8-B
	G1/2		6844	U-1/2-B


Product Range and Company Overview

A Complete Suite and Company Overview

Our experienced engineers provide complete support at every stage of your development process, including: conceptualization, analysis, engineering, design, assembly, documentation, validation, and production.



Custom Automation Components
Complete custom engineered solutions



Custom Control Cabinets
Comprehensive engineering support
and on-site services



Complete Systems
Shipment, stocking and storage services

The Broadest Range of Automation Components

With a comprehensive line of more than 30,000 automation components, Festo is capable of solving the most complex automation requirements.



Electromechanical
Electromechanical actuators, motors,
controllers & drivers



Pneumatics
Pneumatic linear and rotary actuators,
valves, and air supply



PLCs and I/O Devices
PLC's, operator interfaces, sensors
and I/O devices

Supporting Advanced Automation... As No One Else Can!

Festo is a leading global manufacturer of pneumatic and electromechanical systems, components and controls for industrial automation, with more than 16,000 employees in 60 national headquarters serving more than 180 countries. For more than 80 years, Festo has continuously elevated the state of manufacturing with innovations and optimized motion control solutions that deliver higher performing, more profitable automated manufacturing and processing equipment. Our dedication to the advancement of automation extends beyond technology to the education and development of current and future automation and robotics designers with simulation tools, teaching programs, and on-site services.

Quality Assurance, ISO 9001 and ISO 14001 Certifications

Festo Corporation is committed to supply all Festo products and services that will meet or exceed our customers' requirements in product quality, delivery, customer service and satisfaction.

To meet this commitment, we strive to ensure a consistent, integrated, and systematic approach to management that will meet or exceed the requirements of the ISO 9001 standard for Quality Management and the ISO 14001 standard for Environmental Management.




© Copyright 2013, Festo Corporation. While every effort is made to ensure that all dimensions and specifications are correct, Festo cannot guarantee that publications are completely free of any error, in particular typing or printing errors. Accordingly, Festo cannot be held responsible for the same. For Liability and Warranty conditions, refer to our "Terms and Conditions of Sale", available from your local Festo office. All rights reserved. No part of this publication may be reproduced, distributed, or transmitted in any form or by any means, electronic, mechanical, photocopying or otherwise, without the prior written permission of Festo. All technical data subject to change according to technical update.



Printed on recycled paper at New Horizon Graphic, Inc., FSC certified as an environmental friendly printing plant.

Festo North America



**1 Festo Canada
Headquarters**
Festo Inc.
5300 Explorer Drive
Mississauga, ON
L4W 5G4

2 Montréal
5600, Trans-Canada
Pointe-Claire, QC
H9R 1B6

3 Québec City
2930, rue Watt#117
Québec, QC
G1X 4G3



**4 Festo United States
Headquarters**
Festo Corporation
395 Moreland Road
Hauppauge, NY
11788

5 Appleton
North 922 Tower View Drive, Suite N
Greenville, WI
54942

7 Detroit
1441 West Long Lake Road
Troy, MI
48098

6 Chicago
85 W Algonquin - Suite 340
Arlington Heights, IL
60005

8 Silicon Valley
4935 Southfront Road, Suite F
Livermore, CA
94550

Festo Regional Contact Center

Canadian Customers

Commercial Support:
Tel: 1 877 GO FESTO (1 877 463 3786)
Fax: 1 877 FX FESTO (1 877 393 3786)
Email: festo.canada@ca.festo.com

Technical Support:
Tel: 1 866 GO FESTO (1 866 463 3786)
Fax: 1 877 FX FESTO (1 877 393 3786)
Email: technical.support@ca.festo.com

USA Customers

Commercial Support:
Tel: 1 800 99 FESTO (1 800 993 3786)
Fax: 1 800 96 FESTO (1 800 963 3786)
Email: customer.service@us.festo.com

Technical Support:
Tel: 1 866 GO FESTO (1 866 463 3786)
Fax: 1 800 96 FESTO (1 800 963 3786)
Email: product.support@us.festo.com

Subject to change

Internet: www.festo.com/us