


Plastic tubing PUN-H-F

FESTO



Characteristics

At a glance

Flexible and hydrolysis-resistant tubing with standard O.D. in various colours

- Polyurethane
- Highly resistant to microbes and hydrolysis
- Suitable for contact with food.
- Food grade see www.festo.com/certificates/PUN_H
- Suitable for energy chains
- Also available as DUO plastic tubing
- Operating medium: compressed air, vacuum, water
- Very easy installation thanks to “one-click” principle

Diagrams

Further information → [pun-h-f](#)



The diagrams shown in this document are also available online. These can be used to display precise values.

Alternative material characteristic

[H] Hydrolysis-resistant

Hydrolysis-resistant and suitable for water applications. Combination suitable for use in cleanrooms, FDA-compliant and corrosion-resistant because it's 100% polymer.

Additional features

Further information → [pun-h-f](#)

[F] Food-safe



Suitable for contact with food.

Declaration of conformity to EU Regulation EC 1935/2004.

Pipe/tubing O.D. x wall thickness

For standard O.D. tubing, the outside diameter of the tube and the wall thickness are given as the tube size.

Type code

001	Series
PUN	Plastic tubing, polyurethane
002	Alternative material characteristic
H	Hydrolysis-resistant
003	Additional features
F	Food-safe

004	Pipe/tubing O.D. x wall thickness
4x0,75	4x0.75 mm
6x1	6x1 mm
8x1,25	8x1.25 mm
10x1,5	10x1.5 mm
12x2	12x2 mm
14x2	14x2 mm
16x2,5	16x2.5 mm

005	Colour
NT	Natural
TBL	Translucent blue
SW	Black
BL	Blue
RT	Red
GN	Green
GE	Yellow

Datasheet


Operating and environmental conditions

Outside diameter	4 mm	6 mm	8 mm	10 mm	12 mm	14 mm	16 mm
Inside diameter	2.6 mm	4 mm	5.7 mm	7 mm	8 mm	9.8 mm	11 mm
Pneumatic connection	For push-in connector O.D. 4 mm For barbed fitting I.D. 3 mm with union nut	For push-in connector O.D. 6 mm For barbed fitting I.D. 4 mm with union nut	For push-in connector O.D. 8 mm For barbed fitting inside diameter of 6 mm with union nut	For push-in connector O.D. 10 mm	For push-in connector outside diameter of 12 mm	For push-in connector outer diameter of 14 mm	For push-in connector O.D. 16 mm
Flow-relevant bending radius	16 mm	26 mm	37 mm	52 mm	62 mm	78 mm	88 mm
Min. bending radius	8 mm	10 mm	21 mm	28 mm	33 mm	38 ... 39 mm	38 mm
Temperature-dependent operating pressure	-0.095 ... 1 MPa						
Temperature-dependent operating pressure	-0.95 ... 10 bar						
Temperature-dependent operating pressure	-13.775 ... 145 psi						
Operating pressure complete temperature range	-0.095 ... 0.6 MPa						
Operating pressure complete temperature range	-0.95 ... 6 bar						
Operating pressure complete temperature range	-13.775 ... 87 psi						
Note on operating pressure	Water: temperature-dependent operating pressure, see diagram, max. 0.3 MPa at 0 - 60°C						
Operating medium ¹⁾	Compressed air to ISO 8573-1:2010 [7:::], Oxygen	Oxygen, Compressed air to ISO 8573-1:2010 [7:::]	Compressed air to ISO 8573-1:2010 [7:::], Oxygen				Oxygen, Compressed air to ISO 8573-1:2010 [7:::]
Suitable for use with food ²⁾	See declaration of conformity						
Ambient temperature	-35 ... 60°C						
Fire test material	UL94 HB						
Tubing characteristics	Suitable for energy chains						

1) Oxygen: Applies only to NT variants (colour: natural). More information www.festo.com/catalogue/pun-h-f → Support/Downloads.


2) More information www.festo.com/catalogue/pun-h-f → Support/Downloads.

Operating pressure p as a function of temperature t



Datasheet

Operating pressure p as a function of temperature t (medium: water)




Deviating maximum operating pressures apply to the medium water, with a safety factor of $s=4$.

Materials

Shore hardness	D 52 +/-3
Material tubing ¹⁾	TPE-U(PU)
Note on materials	RoHS-compliant
LABS (PWIS) conformity	VDMA24364-B2-L
Cleanroom class	Element installed statically, no meaningful evaluation possible according to ISO 14644-1

¹⁾ TPE-U Ether-based, tube without printing

Ordering data

Ordering data						
	Outside diameter	Packaging unit [m] ¹⁾	Product weight according to length	Colour	Part no.	Type
	4 mm	Standard	0.008 kg/m	Blue	8153381	PUN-H-F-4X0,75-BL
				Yellow	8153384	PUN-H-F-4X0,75-GE
				Green	8153383	PUN-H-F-4X0,75-GN
				Natural	8153378	PUN-H-F-4X0,75-NT
				Red	8153379	PUN-H-F-4X0,75-RT
				Black	8153385	PUN-H-F-4X0,75-SW
				Translucent blue	8153382	PUN-H-F-4X0,75-TBL
	6 mm	0.018 kg/m	Blue	8153388	PUN-H-F-6X1-BL	
			Yellow	8153391	PUN-H-F-6X1-GE	
			Green	8153390	PUN-H-F-6X1-GN	
			Natural	8153428	PUN-H-F-6X1-NT	
			Red	8153386	PUN-H-F-6X1-RT	
			Black	8153392	PUN-H-F-6X1-SW	
			Translucent blue	8153389	PUN-H-F-6X1-TBL	
	8 mm	0.029 kg/m	Blue	8153395	PUN-H-F-8X1,25-BL	
			Yellow	8153398	PUN-H-F-8X1,25-GE	
			Green	8153397	PUN-H-F-8X1,25-GN	
			Natural	8153429	PUN-H-F-8X1,25-NT	
			Red	8153393	PUN-H-F-8X1,25-RT	
			Black	8153399	PUN-H-F-8X1,25-SW	
			Translucent blue	8153396	PUN-H-F-8X1,25-TBL	
	10 mm	0.046 kg/m	Blue	8153402	PUN-H-F-10X1,5-BL	
			Yellow	8153405	PUN-H-F-10X1,5-GE	
			Green	8153404	PUN-H-F-10X1,5-GN	
			Natural	8153430	PUN-H-F-10X1,5-NT	
			Red	8153400	PUN-H-F-10X1,5-RT	
			Black	8153406	PUN-H-F-10X1,5-SW	
			Translucent blue	8153403	PUN-H-F-10X1,5-TBL	
	12 mm	0.072 kg/m	Blue	8153410	PUN-H-F-12X2-BL	
			Yellow	8153413	PUN-H-F-12X2-GE	
			Green	8153412	PUN-H-F-12X2-GN	
			Natural	8153407	PUN-H-F-12X2-NT	
			Red	8153408	PUN-H-F-12X2-RT	
			Black	8153414	PUN-H-F-12X2-SW	
			Translucent blue	8153411	PUN-H-F-12X2-TBL	
	14 mm	0.091 kg/m	Blue	8153417	PUN-H-F-14X2-BL	
			Natural	8153415	PUN-H-F-14X2-NT	
			Red	8153416	PUN-H-F-14X2-RT	
			Black	8153418	PUN-H-F-14X2-SW	
	16 mm	0.122 kg/m	Blue	8153422	PUN-H-F-16X2,5-BL	
			Yellow	8153425	PUN-H-F-16X2,5-GE	
			Green	8153424	PUN-H-F-16X2,5-GN	
Natural			8153419	PUN-H-F-16X2,5-NT		
Red			8153420	PUN-H-F-16X2,5-RT		
Black			8153426	PUN-H-F-16X2,5-SW		
Translucent blue			8153423	PUN-H-F-16X2,5-TBL		

1) Standard: 50 m