

Checkbox CHB-C, Compact



- 1 - Type discontinued
Available up until 2015

Checkbox CHB-C, Compact

Key features


FESTO

High functionality

The integrated inspection units in detail

The Checkbox CHB-C consists of a housing which comprises all the necessary components. In addition to the user interface (keys, LEDs, displays), the connectors for the electrical connection of actuators, buffer zone sensors, diagnostics PC, voltage supply, encoder and master PLC, there is the entire imaging sensor system (optics, lighting and camera).

The optical channel underneath the Checkbox CHB-C is open towards the rear side, thus it can be easily integrated in the material flow.




- 1 Optical channel
- 2 Mounting elements
 - 6xM5 threaded hole
 - Dowel pins
 - Dovetail guide for connecting kit HMSV-12
- 3 Electrical connections
 - Digital I/O
 - Diagnostic interface
 - Encoder
 - Voltage supply
- 4 Front plate with the user interface
 - Buttons
 - Control LEDs
 - Display

Optimum inspection of parts

Economical, variable, reliable

Components are scanned as they pass through the "optical channel". Compared with recognition by means of an area scan camera, this image detection concept has major advantages: A mixture of any number of parts as well as objects of considerable length (up to 1 000 mm) can be recognized and processed without the need to observe minimum distances.

In order to obtain a reliable and reproducible inspection result, the speed of the parts to be checked must be constant and their position stable. A fluctuating object speed can be compensated by means of connecting an encoder.



Checkbox CHB-C, Compact

Key features

Which parts are suitable?



Here is a small selection of the many possibilities:

- Axes
- Bolts
- Brushes
- Buttons
- Ceramic seals
- Curtain hangers
- Drill bits
- Drills
- Fuses
- Game pieces
- Glass ampoules
- Inserts
- Insulating terminals
- Lever stoppers
- Link plates
- Lipstick casings
- Lock nuts
- Mouldings
- Mountings
- Needles
- O-rings
- Pen tops
- Plastic housings
- Plug connectors
- Screws
- Self-locking nuts
- Sensor housings
- Shafts
- Sleeves
- Small wares
- Sockets
- Spring washers
- Springs
- Stampings
- Switch contacts
- Tablets
- Threaded pins
- Toothbrush components
- Turned parts
- Wall plugs
- Washers
- Wooden dowels
- Zip-fastener components

In which branches of industry is the Checkbox CHB-C used?

- Metalworking industry
- Electrical engineering industry
- Woodworking industry
- Electroplating industry
- Injection moulding industry
- Packaging industry
- Pharmaceutical industry
- Cosmetics industry
- Jewellery industry
- Textile and clothing industry
- Assembly-systems industry
- Food industry
- Precision engineering industry

- 1 - Type discontinued
Available up until 2015

FESTO

Checkbox CHB-C, Compact

Key features

What does the camera see?


Part to be checked

Insulating terminal insert



Camera image

Insulating terminal insert




Part to be checked

Valve spring



Camera image

Valve spring



Part to be checked

Glass ampoule



Camera image

Glass ampoule




Part to be checked

Glow bar



Camera image

Glow bar



Part to be checked

O-ring



Camera image

O-ring



Part to be checked

Aroma valve




Camera image

Aroma valve



Checkbox CHB-C, Compact

Peripherals overview



Mounting attachments and accessories		→ Page/Internet
1	DUO cable KM12-DUO-M8-GDGD	10
2	Plug SEA	10
3	Programming cable KDI-SB202-BU9	10
4	Socket NTSD	10
5	Adapter kit SBOA-HMSV	10
-	Connecting cable KM12-M12-GSGD	10
-	Software	9

- 1 - Type discontinued
Available up until 2015

Checkbox CHB-C, Compact

Technical data

FESTO

Checkbox CHB-C-X



General technical data		
Min. component \varnothing	[mm]	0.5
Max. component \varnothing	[mm]	25
Min. component length	[mm]	1
Max. component length		Dependent on belt speed and required resolution
Component range		Rotationally symmetrical parts and pre-oriented parts of any shape
Internal passage of optical channel	[mm]	60
Internal height of optical channel	[mm]	40
Camera resolution	[mm]	0.06
Exposure time	[μ s]	128 ... 1 024
Number of part memories		12
Counting function		Yes
Quantity pre-selection		CheckKon software
Counting range		1 ... 2 billion
Max. number of different orientations per memorised part		8
Orientation		Part orientation function within checking and counting process can be switched off via diagnostic interface

Electrical data		
Operating voltage DC	[V]	24
Permissible voltage fluctuation		$\pm 15\%$
Current consumption at load-free outputs	[mA]	750
Internal fuse protection		8 A fuse


Operating and environmental conditions		
Ambient temperature	[$^{\circ}$ C]	-5 ... +50
Storage temperature	[$^{\circ}$ C]	-20 ... +70
Protection class		IP64
CE marking (see declaration of conformity)		To EU EMC Directive
Installation site		Dry, screened from extreme external light sources, cleanest possible ambient air


- 1 - Type discontinued
Available up until 2015

FESTO

Checkbox CHB-C, Compact

Technical data

Ordering data			
Designation		Part No.	Type
	Checkbox CHB-C-X	536084	CHB-C-X


Ordering data – Documentation				
Description		Language	Part No.	Type
	User documentation included in scope of delivery	German	533411	P.BE-CB-COMP-DE
		English	533412	P.BE-CB-COMP-EN

Checkbox CHB-C, Compact

Accessories

Software to meet individual requirements

CheckKon




Performance characteristics

Using this software the processes within the Checkbox CHB-C can be displayed, logged and adapted from the camera image evaluation through to the I/O parameters.

This means:

- Transfer of new programs to the Checkbox CHB-C
- Display and editing of system parameters
- Display of the evaluation of the last inspected parts recorded
- Display and logging of part contour and characteristics derived
- Display and print-out of system configuration

CheckOpti



Software program



“CheckOpti” is used in cases where the standard Checkbox CHB-C learning program reaches its limits due to the fact that contour differences are too small, meaning that part orientation or quality features cannot be reliably recognised.

“CheckOpti” enables a complete analysis of the Checkbox CHB-C recognition processes based on the contour data of the parts to be inspected.

Additional, high performance test features can be defined and optimised if necessary. The new configuration can subsequently be transferred to the Checkbox CHB-C. Further product information

→ Internet: [sbox-q](#)

Ordering data – Software







	Version	Language	Part No.	Type
	CheckKon software	German, english	194496	P.SW-KON
	CheckOpti software	German, english	568339	P.SW-OPTI


 Type discontinued
Available up until 2015

FESTO

Checkbox CHB-C, Compact

Accessories

Ordering data					
	Application	Connection	Cable length [m]	Part No.	Type
DUO cable				Technical data → Internet: km12-duo	
	Connection actuator or buffer/feeder	Straight plug, M12x1, 4-pin 2x straight socket, M8x1, 3-pin	0.6	18685	KM12-DUO-M8-GDGD
Connecting cable				Technical data → Internet: km12-m12	
	Connection actuator or buffer/feeder	Straight plug, M12x1, 4-pin Straight socket, M12x1, 4-pin	2.5	18684	KM12-M12-GSGD-2,5
			5	18686	KM12-M12-GSGD-5
Plug				Technical data → Internet: sea	
	Connection actuator or buffer/feeder	Straight plug, M12x1, 4-pin Type A, screw terminal	-	192008	SEA-4GS-7-2,5
				18666	SEA-GS-7
				18779	SEA-GS-11-DUO
Programming cable				Technical data → Internet: kdi	
	On diagnosis	Straight socket, M12x1, 4-pin Straight socket, Sub-D, 9-pin	5	150268	KDI-SB202-BU9
Socket				Technical data → Internet: ntsc	
	For supplying the operating voltage	Straight socket, M18x1, 4-pin Screw terminal	-	18493	NTSD-GD-9
				18526	NTSD-GD-13,5
		Angled socket, 4-pin Screw terminal		18527	NTSD-WD-9

Ordering data – Accessories					
	Description	Part No.	Type		
Connecting kit				Technical data → Internet: hmsv-12	
	With screw-on adapter plate	177658	HMSV-12		

Checkbox CHB-C, Compact

Application examples


Application examples

Orientation detection and quality inspection of electrocoils

The Checkbox CHB-C checks the electrocoils and controls the complete supply process, e.g. a following turning station for turning incorrectly orientated good parts and a reject nozzle for sorting out bad parts.

The following features are checked:

- Orientation
- Diameter
- Length




Position and quality check of fibre optic parts

The Checkbox CHB-C checks the transparent display elements, controls the parts flow and removes incorrectly orientated or faulty parts reliably by means of reject nozzles.

The following features are checked:

- Orientation
- Form
- Diameter



Product Range and Company Overview

A Complete Suite and Company Overview

Our experienced engineers provide complete support at every stage of your development process, including: conceptualization, analysis, engineering, design, assembly, documentation, validation, and production.



Custom Automation Components
Complete custom engineered solutions



Custom Control Cabinets
Comprehensive engineering support and on-site services



Complete Systems
Shipment, stocking and storage services

The Broadest Range of Automation Components

With a comprehensive line of more than 30,000 automation components, Festo is capable of solving the most complex automation requirements.



Electromechanical
Electromechanical actuators, motors, controllers & drivers



Pneumatics
Pneumatic linear and rotary actuators, valves, and air supply



PLCs and I/O Devices
PLC's, operator interfaces, sensors and I/O devices


Supporting Advanced Automation... As No One Else Can!

Festo is a leading global manufacturer of pneumatic and electromechanical systems, components and controls for industrial automation, with more than 16,000 employees in 60 national headquarters serving more than 180 countries. For more than 80 years, Festo has continuously elevated the state of manufacturing with innovations and optimized motion control solutions that deliver higher performing, more profitable automated manufacturing and processing equipment. Our dedication to the advancement of automation extends beyond technology to the education and development of current and future automation and robotics designers with simulation tools, teaching programs, and on-site services.

Quality Assurance, ISO 9001 and ISO 14001 Certifications

Festo Corporation is committed to supply all Festo products and services that will meet or exceed our customers' requirements in product quality, delivery, customer service and satisfaction.

To meet this commitment, we strive to ensure a consistent, integrated, and systematic approach to management that will meet or exceed the requirements of the ISO 9001 standard for Quality Management and the ISO 14001 standard for Environmental Management.




© Copyright 2013, Festo Corporation. While every effort is made to ensure that all dimensions and specifications are correct, Festo cannot guarantee that publications are completely free of any error, in particular typing or printing errors. Accordingly, Festo cannot be held responsible for the same. For Liability and Warranty conditions, refer to our "Terms and Conditions of Sale", available from your local Festo office. All rights reserved. No part of this publication may be reproduced, distributed, or transmitted in any form or by any means, electronic, mechanical, photocopying or otherwise, without the prior written permission of Festo. All technical data subject to change according to technical update.



Printed on recycled paper at New Horizon Graphic, Inc., FSC certified as an environmental friendly printing plant.

Festo North America



**1 Festo Canada
Headquarters
Festo Inc.**
5300 Explorer Drive
Mississauga, ON
L4W 5G4

2 Montréal
5600, Trans-Canada
Pointe-Claire, QC
H9R 1B6

3 Québec City
2930, rue Watt#117
Québec, QC
G1X 4G3



**4 Festo United States
Headquarters
Festo Corporation**
395 Moreland Road
Hauppauge, NY
11788

5 Appleton
North 922 Tower View Drive, Suite N
Greenville, WI
54942

7 Detroit
1441 West Long Lake Road
Troy, MI
48098

6 Chicago
85 W Algonquin - Suite 340
Arlington Heights, IL
60005

8 Silicon Valley
4935 Southfront Road, Suite F
Livermore, CA
94550

Festo Regional Contact Center

Canadian Customers

Commercial Support:
Tel: 1 877 GO FESTO (1 877 463 3786)
Fax: 1 877 FX FESTO (1 877 393 3786)
Email: festo.canada@ca.festo.com

Technical Support:
Tel: 1 866 GO FESTO (1 866 463 3786)
Fax: 1 877 FX FESTO (1 877 393 3786)
Email: technical.support@ca.festo.com

USA Customers

Commercial Support:
Tel: 1 800 99 FESTO (1 800 993 3786)
Fax: 1 800 96 FESTO (1 800 963 3786)
Email: customer.service@us.festo.com

Technical Support:
Tel: 1 866 GO FESTO (1 866 463 3786)
Fax: 1 800 96 FESTO (1 800 963 3786)
Email: product.support@us.festo.com