






# Plug sockets with cable

Product range overview




Design	Type	For miniature valves	For fast-switching valves	For proportional valves	For valves with central plug M12x1		→ Page/Internet
		MHA1...-PI/ MHP1...-PI	MH2/MH3	MPPE/MPPES	ISO 15 407-1	ISO 5599-1	
	KMYZ-3	-	■	-	-	-	11
	KMYZ-4-...-B	-	■	-	-	-	12
	KMH	■	-	-	-	-	16
	KMPPE-B	-	-	■	-	-	18
	KM12-M12-GSWD-1-4	-	-	-	■	■	19

# Plug sockets with cable KMF

Technical data

•  Temperature range  
-20 ... +80°C


• For valves with F solenoid coils



General technical data						
Operating voltage		24 V DC			0 ... 240 V DC/AC	
Cable length	[m]	2.5	5	10	2.5	5
Wire cross section	[mm <sup>2</sup> ]	3x0.75				
Number of pins		3				
Switching status display		LED			-	
Type of mounting		M3 central screw				
Protection class to EN 60 529		IP67 (assembled)				
Mounting position		Any				
CE symbol		-			73/23/EEC (low voltage)	
Ambient temperature	[°C]	-20 ... +80				
Product weight	[g]	170	320	460	170	320
Material	Housing	Polymer				
	Cable sheath	Polyvinyl chloride				



## Dimensions

Download CAD data → [www.festo.com](http://www.festo.com)



- 1 LED illuminated area
- 2 Location for inscription label
- 3 3-wire cable
- 4 Connection pattern for F solenoid coil

## Ordering data

	Description	Operating voltage	Switching status display with LED	Cable length [m]	Part No.	Type
	Plug socket with cable for valves with F solenoid coils	24 V DC		2.5	30 935	KMF-1-24DC-2,5-LED
				5	30 937	KMF-1-24DC-5-LED
				10	193 458	KMF-1-24-10-LED
		0 ... 240 V DC/AC	-	2.5	30 936	KMF-1-230AC-2,5
				5	30 938	KMF-1-230AC-5


# Plug sockets with cable KMC

Technical data

FESTO



 - Temperature range  
 -20 ... +80°C


• For valves with D and N1 solenoid coils



General technical data						
Operating voltage		24 V DC			0 ... 240 V DC/AC	
Cable length		[m]	2.5	5	10	2.5    5
Wire cross section		[mm <sup>2</sup> ]	3x0.75			
Number of pins		3				
Switching status display		LED			-	
Type of mounting		M3 central screw				
Protection class to EN 60 529		IP67 (assembled)				
Mounting position		Any				
CE symbol		-			73/23/EEC (low voltage)	
Ambient temperature		[°C]	-20 ... +80			
Product weight		[g]	110	315	725	110    315
Material		Housing	Polymer			
		Cable sheath	Polyvinyl chloride			

## Dimensions Download CAD data → [www.festo.com](http://www.festo.com)



Ordering data						
	Description	Operating voltage	Switching status display with LED	Cable length [m]	Part No.	Type
	Plug socket with cable for valves with D and N1 solenoid coils	24 V DC	■	2.5	30 931	KMC-1-24DC-2,5-LED
				5	30 933	KMC-1-24DC-5-LED
				10	193 459	KMC-1-24-10-LED
		0 ... 240 V DC/AC	-	2.5	30 932	KMC-1-230AC-2,5
				5	30 934	KMC-1-230AC-5

# Plug sockets with cable KMV

Technical data

 Temperature range  
 -20 ... +80°C


• For valves with V solenoid coils



General technical data						
Operating voltage		24 V DC			0 ... 240 V DC/AC	
Cable length	[m]	2.5	5	10	2.5	5
Wire cross section	[mm <sup>2</sup> ]	3x0.75				
Number of pins		3				
Switching status display		LED			-	
Type of mounting		M3 central screw				
Protection class to EN 60 529		IP67 (assembled)				
Mounting position		Any				
CE symbol		-			73/23/EEC (low voltage)	
Ambient temperature	[°C]	-20 ... +80				
Product weight	[g]	165	320	630	165	320
Material	Housing	Polymer				
	Cable sheath	Polyvinyl chloride				

**Dimensions** Download CAD data → [www.festo.com](http://www.festo.com)

1 LED illuminated area  
 2 Location for inscription label  
 3 3-wire cable  
 4 Connection pattern to DIN EN 175 301-803, type B

Ordering data						
	Description	Operating voltage	Switching status display with LED	Cable length [m]	Part No.	Type
	Plug socket with cable for valves with V solenoid coils	24 V DC	■	2.5	30 939	KMV-1-24DC-2,5-LED
				5	30 941	KMV-1-24DC-5-LED
				10	193 456	KMV-1-24-10-LED
		0 ... 240 V DC/AC	-	2.5	30 940	KMV-1-230AC-2,5
				5	30 942	KMV-1-230AC-5

# Plug sockets with cable KME

Technical data



Temperature range  
 -20 ... +80°C

• For valves with E solenoid coils



General technical data			
Cable length	[m]	2.5	5   10
Wire cross section	[mm <sup>2</sup> ]	2x0.75	
Number of pins		2	
Switching status display		LED	
Type of mounting		M3 central screw	
Mounting position		Any	
Protection class to EN 60 529		IP67 (assembled)	
Ambient temperature	[°C]	-20 ... +80	
Product weight	[g]	135	280   570
Material	Housing	Polymer	
	Cable sheath	Polyvinyl chloride	

**Dimensions** Download CAD data → [www.festo.com](http://www.festo.com)

1 LED illuminated area  
 2 Location for inscription label  
 3 2-wire cable (2x 0,75 mm<sup>2</sup>)  
 4 Connection pattern for E solenoid coils  
 5 Seal


Ordering data						
	Description	Operating voltage	Switching status display with LED	Cable length [m]	Part No.	Type
	Plug socket with cable for valves with E solenoid coils	24 V DC		2.5	30 943	KME-1-24DC-2,5-LED
				5	30 945	KME-1-24DC-5-LED
				10	193 455	KME-1-24-10-LED

# Plug sockets with cable KMEB

Technical data

• Temperature range  
-20 ... +80°C


- For valves with EB solenoid coils
- KMEB-1 with PVC cable
- KMEB-2 with PUR cable
- KMEB-3 with PVC cable



General technical data – KMEB-1						
Operating voltage		24 V DC			0 ... 240 V DC/AC	
Cable length	[m]	2.5	5	10	2.5	5
Wire cross section	[mm <sup>2</sup> ]	3x0.5				
Number of pins		3				
Switching status display		LED			-	
Type of mounting		M2.5 central screw				
Protection class to EN 60 529		IP65 (assembled)				
Mounting position		Any				
CE symbol		-			73/23/EEC (low voltage)	
Ambient temperature	[°C]	-20 ... +80				
Product weight	[g]	125	230	460	125	230
Material	Housing	Polymer				
	Cable sheath	Polyvinyl chloride				

## Dimensions – KMEB-1

Download CAD data → [www.festo.com](http://www.festo.com)



- 1 LED illuminated area (only with 24 V)  
2 LED for cable 2.5 m and 5 m  
1 LED for cable 10 m
- 2 Location for inscription label
- 3 3-wire cable (3x0.5 mm<sup>2</sup>)
- 4 Connection pattern to DIN EN 175 301-803, type C
- 5 Seal

# Plug sockets with cable KMEB

Technical data

General technical data – KMEB-2					
Operating voltage		24 V DC		0 ... 240 V DC/AC	
Cable length	[m]	2.5	5	2.5	5
Wire cross section	[mm <sup>2</sup> ]	3x0.75			
Number of pins		3			
Switching status display		LED		-	
Type of mounting		M2.5 central screw			
Protection class to EN 60 529		IP65 (assembled)			
Mounting position		Any			
CE symbol		-		73/23/EEC (low voltage)	
Ambient temperature	[°C]	-20 ... +80			
Product weight	[g]	200	400	200	400
Material	Housing	Polymer			
	Cable sheath	Polyurethane			

**Dimensions – KMEB-2** Download CAD data → [www.festo.com](http://www.festo.com)

- 1 LED illuminated area
- 2 Location for inscription label
- 3 3-wire cable
- 4 Connection pattern to DIN EN 175 301-803, type C


Ordering data						
	Description	Operating voltage	Switching status display with LED	Cable length [m]	Part No.	Type
<b>KMEB-1 (PVC cable)</b>						
	Plug socket with cable for valves with EB solenoid coils	24 V DC	■	2.5	151 688	KMEB-1-24-2,5-LED
				5	151 689	KMEB-1-24-5-LED
				10	193 457	KMEB-1-24-10-LED
		0 ... 240 V DC/AC	-	2.5	151 690	KMEB-1-230AC-2,5
				5	151 691	KMEB-1-230AC-5
<b>KMEB-2 (PUR cable)</b>						
	Plug socket with cable for valves with EB solenoid coils	24 V DC	■	2.5	174 844	KMEB-2-24-2,5-LED
				5	174 845	KMEB-2-24-5-LED
		0 ... 240 V DC/AC	-	2.5	174 846	KMEB-2-230-2,5
				5	174 847	KMEB-2-230-5

**Do not use for new designs!**  
 -  - Type to be discontinued

## Plug sockets with cable KMY-1/KMYZ-1

**FESTO**

Technical data

-  - Temperature range  
 -25 ... +80 (KMY-1)  
 5 ... 50°C (KMYZ-1)

- For valves with Y and Z solenoid coils





General technical data					
Type		KMY-1	KMYZ-1		
Cable length	[m]	0.5	2.5	5	15
Wire cross section	[mm <sup>2</sup> ]	2x0.34			
Number of pins		2			
Type of mounting		Clip			
Protection class to EN 60 529		IP40 (assembled)			
Mounting position		Any			
Ambient temperature	[°C]	-20 ... +80	5 ... 50		
Product weight	[g]	4	70	155	325
Material	Housing	Polymer			
	Cable sheath	Polyvinyl chloride			

### Dimensions


Download CAD data → [www.festo.com](http://www.festo.com)


KMY-1





 2-wire cable

KMYZ-1



 2-wire cable

### Ordering data


	Description	Operating voltage	Cable length [m]	Part No.	Type
 	Plug socket with cable for valves with Y and Z solenoid coils	24 V DC	0.5	34 347	KMY-1-24-0,5
			2.5	30 446	KMYZ-1-24-2,5
			5	30 447	KMYZ-1-24-5
			15	193 454	KMYZ-1-24-15



# Plug sockets with cable KMYZ-2

Technical data

FESTO

 Temperature range  
 -10 ... +50 °C



• For valves with ZB solenoid coils



General technical data		
Wire cross section	[mm <sup>2</sup> ]	2x0.25
Number of pins		2
Switching status display		LED
Type of mounting		Self-tapping central screw
Protection class to EN 60 529		IP65 (assembled)
Mounting position		Any
Ambient temperature	[°C]	-10 ... +50
Material	Housing	Polymer
	Cable sheath	Polyvinyl chloride


**Dimensions** Download CAD data → [www.festo.com](http://www.festo.com)

1 LED illuminated area  
 2 Location for inscription label  
 3 2-wire cable  
 4 Connection pattern for ZB solenoid coils  
 5 Mounting screw  
 max. tightening torque 0.25 Nm

Ordering data							
	Description	Operating voltage	Switching status display with LED	Cable length [m]	Product weight [g]	Part No.	Type
	Plug socket with cable for valves with ZB solenoid coils	24 V DC		2.5	80	34 997	KMYZ-2-24-2,5-LED
				5	150	34 998	KMYZ-2-24-5-LED
				10	290	193 443	KMYZ-2-24-10-LED
	Plug socket with cable and plug M8x1 for valves with ZB solenoid coils			0.5		177 676	KMYZ-2-24-M8-0,5-LED
				2.5		177 678	KMYZ-2-24-M8-2,5-LED

# Plug sockets with cable KMYZ-3

Technical data

•  Temperature range  
-10 ... +50 °C


• For fast-switching valves MH2/MH3  
with metric ZC solenoid coils



General technical data				
Cable length	[m]	2.5	5	10
Wire cross section	[mm <sup>2</sup> ]	2x0.25		
Number of pins		2		
Switching status display		LED		
Type of mounting		M2 central screw		
Protection class to EN 60 529		IP65 (assembled)		
Mounting position		Any		
Ambient temperature	[°C]	-10 ... +50		
Product weight	[g]	44	82	154
Material	Housing	Polymer		
	Cable sheath	Polyurethane		

**Dimensions** Download CAD data → [www.festo.com](http://www.festo.com)


- 1 LED illuminated area
- 2 Location for inscription label
- 3 2-wire cable
- 4 Connection pattern for ZC solenoid coils
- 5 Mounting screw
- 6 Plug M8x1

Ordering data							
	Description	Operating voltage	Electrical connection	Switching status display with LED	Cable length [m]	Part No.	Type
	Plug socket with cable for fast-switching valves MH2/MH3 with metric ZC solenoid coils	24 V DC	Cable	■	2.5	193 693	KMYZ-3-24-2,5-LED-PUR-B
					5	193 695	KMYZ-3-24-5-LED-PUR-B
					10	196 066	KMYZ-3-24-10-LED-PUR-B
			Plug M8x1	■	0,5	525 654	KMYZ-3-24-M8-0,5-LED-PUR
					2,5	525 655	KMYZ-3-24-M8-2,5-LED-PUR


# Plug sockets with cable KMYZ-4

Technical data

FESTO

 Temperature range  
 -10 ... +50 °C

- For valves with ZB and ZC solenoid coils
- Variant KMYZ-4-...-B for fast-switching valves MH2/MH3
- Variant KMYZ-4-...-B-EX for use with intrinsically safe CPV valve terminals




General technical data		KMYZ-4-...-B	KMYZ-4	KMYZ-4-...-B-EX
Type				
Electrical connection		Angled socket, square design MSZB		
Cable design	[mm <sup>2</sup> ]	2x0.35		
Number of pins		2		
Type of mounting		Central screw M2	Self-tapping central screw	
Protection class to EN 60529		IP40 (assembled)		
Operating voltage range	[V DC]	3 ... 36		
Nominal operating voltage	[V DC]	24		
Mounting position		Any		
Ambient temperature	[°C]	-10 ... +50		
Material	Housing	Polyamide		
	Cable sheath	Polyvinyl chloride		
Note on material		Conforms to RoHS		
Corrosion resistance class CRC <sup>1)</sup>		1		
Certification				Germanischer Lloyd

1) Corrosion resistance class 1 to Festo standard 940 070

Components requiring low corrosion resistance. Transport and storage protection. Parts that do not have primarily decorative surface requirements, e.g. in internal areas that are not visible or behind covers.

## Dimensions




Download CAD data → [www.festo.com](http://www.festo.com)




- 1 Mounting screw
- 2 Slot for inscription label  
IBS-6x10 (not included in scope of delivery)
- 3 2-wire cable
- 4 Pin allocations for ZB solenoid coils
- 5 Pin allocations for ZC solenoid coils

# Plug sockets with cable KMYZ-4

Technical data


Ordering data					
	Description	Product weight [g]	Cable length [m]	Part No.	Type
<b>With central screw M2</b>					
	Plug socket with cable for valves with ZB and ZC solenoid coils	10	0.5	<b>193 690</b>	<b>KMYZ-4-24-0,5-B</b>
		33	2.5	<b>193 691</b>	<b>KMYZ-4-24-2,5-B</b>
<b>With self-tapping central screw</b>					
	Plug socket with cable for valves with ZB and ZC solenoid coils	10	0.5	<b>185 519</b>	<b>KMYZ-4-24-0,5</b>
		33	2.5	<b>185 520</b>	<b>KMYZ-4-24-2,5</b>
<b>With self-tapping central screw for use with intrinsically safe CPV valve terminals</b>					
	Plug socket with cable for CPV valves	12	0.5	<b>550 324</b>	<b>KMYZ-4-0.5-B-EX</b>
		34.5	2.5	<b>550 481</b>	<b>KMYZ-4-2.5-B-EX</b>
		62.5	5	<b>550 482</b>	<b>KMYZ-4-5.0-B-EX</b>

-  - Type discontinued  
Available up until 2006

FESTO

## Plug sockets with cable KMYZ-6

Technical data


-  - Temperature range  
-10 ... +50°C


• For valves with ZB solenoid coils



General technical data				
Cable length	[m]	2.5	5	10
Wire cross section	[mm <sup>2</sup> ]	2x0.25		
Number of pins		3		
Switching status display		LED		
Type of mounting		Self-tapping central screw		
Protection class to EN 60 529		IP65 (assembled)		
Mounting position		Any		
Coil management at 24 V DC		24 mA in 23 ms		
CE symbol		89/336/EEC (EMC)		
Ambient temperature	[°C]	-10 ... +50		
Product weight	[g]	44	81	154
Material	Housing	Polymer		
	Cable sheath	Polyurethane		

### Dimensions Download CAD data → [www.festo.com](http://www.festo.com)



Ordering data						
	Description	Operating voltage	Switching status display with LED	Cable length [m]	Part No.	Type
	Plug socket with cable for valves with ZB solenoid coils	24 V DC	■	2.5	193 679	KMYZ-6-24-2,5-LED-PUR
				5	193 681	KMYZ-6-24-5-LED-PUR
				10	196 068	KMYZ-6-24-10-LED-PUR

# Plug sockets with cable KMYZ-9

Technical data


-  Temperature range  
-10 ... +50°C
- For valves with ZC solenoid coils  
(CPE10/CPE14)



General technical data			
Wire cross section	[mm <sup>2</sup> ]	2x0.25	
Number of pins		2	
Switching status display		LED	
Type of mounting		M2 central screw	
Protection class to EN 60 529		IP65 (assembled)	
Mounting position		Any	
CE symbol		89/336/EEC (EMC)	
Coil management at 24 V DC		23 mA in 24 ms	
Ambient temperature	[°C]	-10 ... +50	
Product weight	[g]	46	82
Material	Housing	Polymer	
	Cable sheath	Polyurethane	

**Dimensions** Download CAD data → [www.festo.com](http://www.festo.com)


- 1 LED illuminated area
- 2 Location for inscription label
- 3 2-wire cable
- 4 Connection pattern for ZC solenoid coils
- 5 Mounting screw
- 6 Plug M8x1

Ordering data							
	Description	Operating voltage	Electrical connection	Switching status display with LED	Cable length [m]	Part No.	Type
	Plug socket with cable for valves with ZC solenoid coils	24 V DC	Cable	■	2.5	193 687	KMYZ-9-24-2,5-LED-PUR-B
					5	193 689	KMYZ-9-24-5-LED-PUR-B
					10	196 063	KMYZ-9-24-10-LED-PUR-B
			Plug M8x1	■	0,5	196 064	KMYZ-9-24-M8-0,5-LED-PUR-B
					2,5	196 065	KMYZ-9-24-M8-2,5-LED-PUR-B

# Plug sockets with cable KMH

Technical data

FESTO


 - Temperature range  
 -40 ... +80°C


- For miniature valves MHA1 and MHP1
- For fast-switching valves MHA2 and MHP2



General technical data		0.5	1	2.5	5
Cable length	[m]	0.5	1	2.5	5
Number of pins		2			
Type of mounting		Clip			
Protection class to EN 60 529		IP40 (assembled)			
Mounting position		Any			
Ambient temperature	[°C]	-40 ... +80			
Product weight	[g]	4	7	17	31
Material	Housing	Polyacetal			
	Cable sheath	Polyvinyl chloride			

**Dimensions** Download CAD data → [www.festo.com](http://www.festo.com)

L1 Cable length


Ordering data					
	Description	Operating voltage	Cable length [m]	Part No.	Type
	Plug socket with cable for miniature valves MHA1 and MHP1 and fast-switching valves MHA2 and MHP2	24 V DC	0.5	197 263	KMH-0,5
			1	197 264	KMH-1
			2.5	527 400	KMH-2,5
			5	527 401	KMH-5

# Plug sockets with cable NEBV

Technical data

 Temperature range  
-20 ... +70°C

• For miniature valves MHA1 and MHP1




General technical data		NEBV-H1G2-P...	NEBV-H1G2L-P...
Electrical connection		Socket, 2-pin	
Output current	[A]	2	
Protection class to EN 60 529		IP40 (assembled)	
Operating voltage	[V AC]	0 ... 30	4.5 ... 26.4
	[V DC]	0 ... 30	4.5 ... 26.4
Corrosion resistance class CRC		4 <sup>1)</sup>	
Ambient temperature	[°C]	-20 ... +70	
Material	Housing	Polyacetal	
	Cable sheath	Polyvinyl chloride	

1) CRC4: Corrosion resistance class to Festo standard 940 070

Components with very heavy corrosion exposure. Components in contact with aggressive media, e.g. in food or chemical industries. These applications must, if necessary, be verified by special tests with the media concerned.


## Dimensions

Download CAD data → [www.festo.com](http://www.festo.com)



- 1 LED
- 2 Identification clips
- L Cable length

## Ordering data

	Description	LED	Cable length [m]	Product weight [g]	Part No.	Type
	Plug socket with cable for miniature valves MHA1 and MHP1	–	0.5	12	552 001	NEBV-H1G2-P-0.5-LE2
		–	1	24	552 002	NEBV-H1G2-P-1-LE2
		–	2.5	60	552 003	NEBV-H1G2-P-2.5-LE2
		–	5	120	552 004	NEBV-H1G2-P-5-LE2
		■	0.5	12	554 029	NEBV-H1G2L-P-0.5-LE2
		■	1	24	554 030	NEBV-H1G2L-P-1-LE2
		■	2.5	60	554 031	NEBV-H1G2L-P-2.5-LE2
		■	5	120	554 032	NEBV-H1G2L-P-5-LE2



# Plug sockets with cable KMPPE

Technical data



- - Temperature range  
-30 ... +80°C

- For proportional pressure regulators MPPE and MPPES



General technical data			
Cable length	[m]	2.5	5
Wire cross section	[mm <sup>2</sup> ]	8x0.25	
Number of pins		8	
Type of mounting		Knurled locknut M16x0.75	
Mounting position		Any	
Ambient temperature	[°C]	-30 ... +80	
Product weight	[g]	243	459
Material	Cable sheath	Polyvinyl chloride	


**Dimensions** Download CAD data → [www.festo.com](http://www.festo.com)

1 PVC cable

Ordering data					
	Description	Operating voltage	Cable length [m]	Part No.	Type
	Plug socket with cable for proportional pressure regulators MPPE and MPPES	24 V DC	2.5	161 879	KMPPE-B-2,5
			5	161 878	KMPPE-B-5

# Plug sockets with cable KM12

Technical data


•  Temperature range  
-30 ... +70°C

- For valves to ISO 15 407-1 (VDMA 24 563) and ISO 5599-1 with central plug M12x1



General technical data			
Wire cross section	[mm <sup>2</sup> ]	4x0.34	
Number of pins		4	
Cable length	[m]	1	
Type of mounting		Knurled locknut M12x1	
Protection class to EN 60 529		IP67 (assembled)	
Mounting position		Any	
Operating voltage range	[V AC]	Max. 60	
Operating voltage range	[V DC]	Max. 75	
Ambient temperature	Fixed cable installation	[°C]	-30 ... +70
	Flexible cable installation	[°C]	-5 ... +70
Product weight	[g]	66	
Material	Housing	Polyurethane	
	Cable sheath	Polyurethane	


**Dimensions** Download CAD data → [www.festo.com](http://www.festo.com)

Ordering data				
	Description	Cable length [m]	Part No.	Type
	Plug socket with cable for valves to ISO 15 407-1 (VDMA 24 563) and ISO 5599-1 with central plug M12x1	1	185 499	KM12-M12-GSWD-1-4

# Plug sockets with cable NEBU

Technical data

FESTO

 Temperature range  
 -25 ... +90 °C

• For proportional valves from the  
 VPPM series




General technical data		
Electrical connection		Angled socket, 8-pin, M12x1
Cable design	[mm <sup>2</sup> ]	8x0.25, screened
Current-carrying capacity	[A]	1.5
Protection class to EN 60529		IP67 (assembled)
Minimum cable bending radius	[mm]	66
Operating voltage range	[V AC]	0 ... 30
	[V DC]	0 ... 36
Corrosion resistance class CRC <sup>1)</sup>		2
Ambient temperature	[°C]	-25 ... +90
Material	Housing	Polyurethane
	Cable sheath	Polyurethane
	Wire ends	Tin-plated


1) Corrosion resistance class 2 to Festo standard 940 070

Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

## Dimensions

Download CAD data → [www.festo.com](http://www.festo.com)



Ordering data					
	Description	Product weight [g]	Cable length [m]	Part No.	Type
	Plug socket with cable for proportional valves	140	2	542 256	NEBU-M12W8-2-N-LE8
		320	5	542 257	NEBU-M12W8-5-N-LE8

## **Plug Sockets with Cable**

# Product Range and Company Overview

## A Complete Suite of Automation Services

Our experienced engineers provide complete support at every stage of your development process, including: conceptualization, analysis, engineering, design, assembly, documentation, validation, and production.



**Custom Automation Components**  
Complete custom engineered solutions



**Custom Control Cabinets**  
Comprehensive engineering support and on-site services



**Complete Systems**  
Shipment, stocking and storage services

## The Broadest Range of Automation Components

With a comprehensive line of more than 30,000 automation components, Festo is capable of solving the most complex automation requirements.



**Electromechanical**  
Electromechanical actuators, motors, controllers & drives



**Pneumatics**  
Pneumatic linear and rotary actuators, valves, and air supply



**PLCs and I/O Devices**  
PLC's, operator interfaces, sensors and I/O devices

## Supporting Advanced Automation... As No One Else Can!

Festo is a leading global manufacturer of pneumatic and electromechanical systems, components and controls for industrial automation, with more than 12,000 employees in 56 national headquarters serving more than 180 countries. For more than 80 years, Festo has continuously elevated the state of manufacturing with innovations and optimized motion control solutions that deliver higher performing, more profitable automated manufacturing and processing equipment. Our dedication to the advancement of automation extends beyond technology to the education and development of current and future automation and robotics designers with simulation tools, teaching programs, and on-site services.

## Quality Assurance, ISO 9001 and ISO 14001 Certifications

Festo Corporation is committed to supply all Festo products and services that will meet or exceed our customers' requirements in product quality, delivery, customer service and satisfaction.

To meet this commitment, we strive to ensure a consistent, integrated, and systematic approach to management that will meet or exceed the requirements of the ISO 9001 standard for Quality Management and the ISO 14001 standard for Environmental Management.



© Copyright 2008, Festo Corporation. While every effort is made to ensure that all dimensions and specifications are correct, Festo cannot guarantee that publications are completely free of any error, in particular typing or printing errors. Accordingly, Festo cannot be held responsible for the same. For Liability and Warranty conditions, refer to our "Terms and Conditions of Sale", available from your local Festo office. All rights reserved. No part of this publication may be reproduced, distributed, or transmitted in any form or by any means, electronic, mechanical, photocopying or otherwise, without the prior written permission of Festo. All technical data subject to change according to technical update.



Printed on recycled paper at New Horizon Graphic, Inc., FSC certified as an environmentally friendly printing plant.

# Festo North America

## United States

**Customer Resource Center**  
502 Earth City Expy., Suite 125  
Earth City, MO 63045

For ordering assistance, or to find  
your nearest Festo Distributor,

**Call:** 1.800.99.FESTO  
**Fax:** 1.800.96.FESTO  
**Email:** customer.service@us.festo.com

For technical support,

**Call:** 1.866.GO.FESTO  
**Fax:** 1.800.96.FESTO  
**Email:** product.support@us.festo.com

### Headquarters

Festo Corporation  
395 Moreland Road  
P.O. Box 18023  
Hauppauge, NY 11788  
[www.festo.com/us](http://www.festo.com/us)

---

### Sales Offices

#### Appleton

N. 922 Tower View Drive, Suite N  
Greenville, WI 54942

#### Boston

120 Presidential Way, Suite 330  
Woburn, MA 01801

#### Chicago

1441 East Business Center Drive  
Mt. Prospect, IL 60056

#### Dallas

1825 Lakeway Drive, Suite 600  
Lewisville, TX 75057

**Detroit - Automotive Engineering Center**  
2601 Cambridge Court, Suite 320  
Auburn Hills, MI 48326

#### New York

395 Moreland Road  
Hauppauge, NY 11788

#### Silicon Valley

4935 Southfront Road, Suite F  
Livermore, CA 94550

## Design and Manufacturing Operations



**East:** 395 Moreland Road, Hauppauge, NY 11788



**Central:** 1441 East Business Center Drive, Mt. Prospect, IL 60056



**West:** 4935 Southfront Road, Suite F, Livermore, CA 94550

---

## Mexico

### Headquarters

Festo Pneumatic, S.A.  
Av. Ceylán 3, Col. Tequesquahuac  
54020 Tlalnepantla, Edo. de México  
**Call:** 011 52 [55] 53 21 66 00  
**Fax:** 011 52 [55] 53 21 66 65  
**Email:** festo.mexico@mx.festo.com  
[www.festo.com/mx](http://www.festo.com/mx)



## Canada

### Headquarters

Festo Inc.  
5300 Explorer Drive  
Mississauga, Ontario L4W 5G4  
**Call:** 1.905.624.9000  
**Fax:** 1.905.624.9001  
**Email:** info.ca@ca.festo.com  
[www.festo.com/ca](http://www.festo.com/ca)



---

## Festo Worldwide

Argentina Australia Austria Belarus Belgium Brazil Bulgaria Canada Chile China Colombia Croatia Czech Republic Denmark  
Estonia Finland France Germany Great Britain Greece Hong Kong Hungary India Indonesia Iran Ireland Israel Italy Japan  
Latvia Lithuania Malaysia Mexico Netherlands New Zealand Norway Peru Philippines Poland Romania Russia Serbia Singapore  
Slovakia Slovenia South Africa South Korea Spain Sweden Switzerland Taiwan Thailand Turkey Ukraine United States Venezuela

[www.festo.com](http://www.festo.com)