

**FESTO**

**Labels**




# Inscription labels

Technical data



Inscription labels for labelling, can be used in holders or carriers on suitably equipped components.

Inscription labels are arranged in a press-out frame, several of which are combined to form a delivery unit.



## General technical data

Type of mounting	Pressed into inscription label holders or suitable carriers on the components
Corrosion resistance class CRC <sup>1)</sup>	2

1) Corrosion resistance class 2 according to Festo standard 940 070

Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a surrounding industrial atmosphere or media such as cooling or lubricating agents.

## Ordering data


View	Inscription	Material	Number per frame	Dimensions (HxW)	Part No.	Type
				[mm]		
	Numbers 1...50	Polyvinyl chloride, soft	50	5.5x4.9	<b>6 888</b>	<b>BZ-NUM 1-50</b>
	Numbers 51...100		50	5.5x4.9	<b>6 889</b>	<b>BZ-NUM 51-100</b>
	By user	Polycarbonate (Lexan 920)	64	6x10	<b>18 576</b>	<b>IBS-6x10</b>
			24	9x17	<b>161 937</b>	<b>IBS-9x17</b>
		Polycarbonate (Lexan 920)	20	8x20	<b>539 388</b>	<b>IBS-8x20</b>
		Polycarbonate (Lexan 920)	20	9x20	<b>18 182</b>	<b>IBS-9x20</b>
			30	10x17	<b>160 238</b>	<b>IBS-10x17</b>
		Polyamide	35	11x17x8	<b>33 362</b>	<b>KMC/F/V-BZ-35X</b>
		Polycarbonate (Lexan)	80	4.5x9	<b>197 259</b>	<b>MH-BZ-80X</b>

# Inscription labels

Technical data – Inscription clips

Inscription clips for placing on a cable.

Inscription clips for cables can be applied to any cable according to the maximum diameter. Many pre-assembled cables already have a labelling option on the connection point (socket/plug).



General technical data	
Type	KM-BZ
Part No.	33 361
Type of mounting	Inscription clip is pressed onto a cable
Inscription	By user. The inscription label itself is not labelled. The inscription is made on an insertable label or paper/cardboard strip.
Cable diameter [mm]	5 ... 8
Corrosion resistance class CRC <sup>1)</sup>	2

1) Corrosion resistance class 2 according to Festo standard 940 070  
Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a surrounding industrial atmosphere or media such as cooling or lubricating agents.

## Inscription labels

Technical data – Inscription label holders

Inscription label holders enable inscription labels to be attached to components without pre-assembled carriers, or with special carriers for holders of this type.

If display components are concealed by the inscription label holder, the carrier is either transparent at these points or completely transparent.



### Inscription system

Inscription label holders enable inscription labels to be attached when there are no suitable holders on the component itself.

They can either be equipped with inscription labels or are designed to hold inscribed paper/cardboard or foil strips.

Due to their size, inscription label holders conceal part of the module to which they are attached. Depending on the type of inscription label holder, the display components either remain visible through a transparent surface or the carrier itself acts as a suitable cover.








 Note

The Word templates for inscription label holders/identification strips can be found at:

➔ [www.festo.com/en/engineering](http://www.festo.com/en/engineering)

# Inscription labels

Technical data – Inscription label holders

Ordering data							
View	Holders for inscription labels	Product weight [g]	Material	For module with the following number of valves	Type of mounting	Part No.	Type
	1 (9x17)	7	Polyamide	–	Pushed into carriers on the components	<b>161 936</b>	<b>MN2H-BZT-10X</b>
	1 (9x17)	19	Polyamide 6 (Miramid)	–		<b>18 575</b>	<b>MVH-BZ</b>
	3 (9x20)	47	Polycarbonate (Makrolon 2405), transparent	–	Placed on component	<b>158 968</b>	<b>IBT-02-E/A</b>
	1 (9x20) 8 (6x10)	38	Polycarbonate (Makrolon 2405), transparent	–	Placed on component	<b>18 183</b>	<b>IBT-03-E/A</b>
	Insertable label or paper/cardboard strips	6	Polypropylene (Novolen 3300 MC), transparent	–	Pushed into carriers on the components	<b>533 362</b>	<b>VMPA1-ST-1-4</b>
	Insertable label or paper/cardboard strips	5	Polypropylen (Moplen RP220M), transparent	–	Pushed into carriers on the components	<b>536 593</b>	<b>CPX-ST-1</b>
	Insertable label or paper/cardboard strips	2	Polyamide PACM12 (Trogamid), transparent	–	Pushed into carriers on the components	<b>658 807</b>	<b>MPA</b>
	Insertable label or paper/cardboard strips	7	Polyvinyl chloride (RAU-PVC 1107)	4	Pushed into carriers on the components	<b>527 631</b>	<b>CPVSC1-ST-4</b>
		9		8		<b>527 633</b>	<b>CPVSC1-ST-8</b>
		15		12		<b>527 635</b>	<b>CPVSC1-ST-12</b>
		20		16		<b>527 637</b>	<b>CPVSC1-ST-16</b>

# Inscription labels

Technical data – Inscription label holders




Ordering data							
View	Holders for inscription labels	Product weight [g]	Material	For module with the following number of valves	Type of mounting	Part No.	Type
	4 (6x10)	9	Polyvinyl chloride, hard	2	Pushed into carriers on the components	162 560	CPV10-VI-BZT-2
	6 (6x10)	10		3		162 561	CPV10-VI-BZT-3
	8 (6x10)	11		4		162 562	CPV10-VI-BZT-4
	10 (6x10)	15		5		162 563	CPV10-VI-BZT-5
	12 (6x10)	14		6		162 564	CPV10-VI-BZT-6
	14 (6x10)	15		7		162 565	CPV10-VI-BZT-7
	16 (6x10)	16		8		162 566	CPV10-VI-BZT-8
	4 (6x10)	10		2		162 567	CPV14-VI-BZT-2
	6 (6x10)	11		3		162 568	CPV14-VI-BZT-3
	8 (6x10)	13		4		162 569	CPV14-VI-BZT-4
	10 (6x10)	15		5		162 570	CPV14-VI-BZT-5
	12 (6x10)	16		6		162 571	CPV14-VI-BZT-6
	14 (6x10)	19		7		162 572	CPV14-VI-BZT-7
	16 (6x10)	21		8		162 573	CPV14-VI-BZT-8
	4 (6x10)	11		2		163 293	CPV18-VI-BZT-2
	6 (6x10)	12		3		163 294	CPV18-VI-BZT-3
	8 (6x10)	17		4		163 295	CPV18-VI-BZT-4
	10 (6x10)	18		5		163 296	CPV18-VI-BZT-5
	12 (6x10)	20		6		163 297	CPV18-VI-BZT-6
	14 (6x10)	23		7		163 298	CPV18-VI-BZT-7
16 (6x10)	29	8	163 299	CPV18-VI-BZT-8			
	Insertable label or paper/cardboard strips	8	2	194 066	CPV10-VI-ST-2		
		10	3	194 067	CPV10-VI-ST-3		
		11	4	194 068	CPV10-VI-ST-4		
		13	5	194 069	CPV10-VI-ST-5		
		14	6	194 070	CPV10-VI-ST-6		
		15	7	194 071	CPV10-VI-ST-7		
		16	8	194 072	CPV10-VI-ST-8		
		10	2	194 073	CPV14-VI-ST-2		
		11	3	194 074	CPV14-VI-ST-3		
		14	4	194 075	CPV14-VI-ST-4		
		15	5	194 076	CPV14-VI-ST-5		
		20	6	194 077	CPV14-VI-ST-6		
		19	7	194 078	CPV14-VI-ST-7		
		22	8	194 079	CPV14-VI-ST-8		
		11	2	194 080	CPV18-VI-ST-2		
		13	3	194 081	CPV18-VI-ST-3		
		15	4	194 082	CPV18-VI-ST-4		
		18	5	194 083	CPV18-VI-ST-5		
		21	6	194 084	CPV18-VI-ST-6		
		23	7	194 085	CPV18-VI-ST-7		
		28	8	194 086	CPV18-VI-ST-8		

# Inscription labels

Technical data – Inscription label holders

## Examples illustrating the attachment of inscription label holders

### CPV10-VI-...




- The inscription label holder is locked into recesses on the valve terminal
- The inscription is created using inscription labels or by inserting identification strips



Note


The inscription label holder cannot be used together with relay slices.

### CPVSC1-ST...



- The inscription label holder is clipped onto the valve terminal
- The inscription is created by inserting identification strips

### IBT-...



- The inscription label holder is pushed-in
- The inscription is created using inscription labels




# Inscription labels

Technical data – Inscription label holders

## Examples illustrating the attachment of inscription label holders


VMPA1-ST-...



Inscription label holder  
VMPA1-ST...

- The inscription label holder is locked into recesses on the valve terminal
- The inscription is created by inserting identification strips

MPA-...




Inscription label holder

Identification strips

- The inscription label holder is locked into recesses on the valve terminal (cover, plug)
- The inscription is created by inserting identification strips

MVH-BZ (similar to MN2H-BZT-...)



Inscription labels  
IBS 9x17

Inscription label holder  
MVH-BZ

- The inscription label holder is locked into recesses on the valve
- The inscription is created using inscription labels



# Product Range and Company Overview

## A Complete Suite of Automation Services

Our experienced engineers provide complete support at every stage of your development process, including: conceptualization, analysis, engineering, design, assembly, documentation, validation, and production.



**Custom Automation Components**  
Complete custom engineered solutions



**Custom Control Cabinets**  
Comprehensive engineering support and on-site services



**Complete Systems**  
Shipment, stocking and storage services

## The Broadest Range of Automation Components

With a comprehensive line of more than 30,000 automation components, Festo is capable of solving the most complex automation requirements.



**Electromechanical**  
Electromechanical actuators, motors, controllers & drives



**Pneumatics**  
Pneumatic linear and rotary actuators, valves, and air supply



**PLCs and I/O Devices**  
PLC's, operator interfaces, sensors and I/O devices

## Supporting Advanced Automation... As No One Else Can!

Festo is a leading global manufacturer of pneumatic and electromechanical systems, components and controls for industrial automation, with more than 12,000 employees in 56 national headquarters serving more than 180 countries. For more than 80 years, Festo has continuously elevated the state of manufacturing with innovations and optimized motion control solutions that deliver higher performing, more profitable automated manufacturing and processing equipment. Our dedication to the advancement of automation extends beyond technology to the education and development of current and future automation and robotics designers with simulation tools, teaching programs, and on-site services.

## Quality Assurance, ISO 9001 and ISO 14001 Certifications

Festo Corporation is committed to supply all Festo products and services that will meet or exceed our customers' requirements in product quality, delivery, customer service and satisfaction.

To meet this commitment, we strive to ensure a consistent, integrated, and systematic approach to management that will meet or exceed the requirements of the ISO 9001 standard for Quality Management and the ISO 14001 standard for Environmental Management.



© Copyright 2008, Festo Corporation. While every effort is made to ensure that all dimensions and specifications are correct, Festo cannot guarantee that publications are completely free of any error, in particular typing or printing errors. Accordingly, Festo cannot be held responsible for the same. For Liability and Warranty conditions, refer to our "Terms and Conditions of Sale", available from your local Festo office. All rights reserved. No part of this publication may be reproduced, distributed, or transmitted in any form or by any means, electronic, mechanical, photocopying or otherwise, without the prior written permission of Festo. All technical data subject to change according to technical update.



Printed on recycled paper at New Horizon Graphic, Inc., FSC certified as an environmentally friendly printing plant.

# Festo North America

## United States

### Customer Resource Center

502 Earth City Expy., Suite 125  
Earth City, MO 63045

For ordering assistance, or to find  
your nearest Festo Distributor,

**Call:** 1.800.99.FESTO

**Fax:** 1.800.96.FESTO

**Email:** [customer.service@us.festo.com](mailto:customer.service@us.festo.com)

For technical support,

**Call:** 1.866.GO.FESTO

**Fax:** 1.800.96.FESTO

**Email:** [product.support@us.festo.com](mailto:product.support@us.festo.com)

### Headquarters

Festo Corporation  
395 Moreland Road  
P.O. Box 18023  
Hauppauge, NY 11788  
[www.festo.com/us](http://www.festo.com/us)

---

## Sales Offices

### Appleton

N. 922 Tower View Drive, Suite N  
Greenville, WI 54942

### Boston

120 Presidential Way, Suite 330  
Woburn, MA 01801

### Chicago

1441 East Business Center Drive  
Mt. Prospect, IL 60056

### Dallas

1825 Lakeway Drive, Suite 600  
Lewisville, TX 75057

### Detroit - Automotive Engineering Center

2601 Cambridge Court, Suite 320  
Auburn Hills, MI 48326

### New York

395 Moreland Road  
Hauppauge, NY 11788

### Silicon Valley

4935 Southfront Road, Suite F  
Livermore, CA 94550

## Design and Manufacturing Operations



**East:** 395 Moreland Road, Hauppauge, NY 11788



**Central:** 1441 East Business Center Drive, Mt. Prospect, IL 60056



**West:** 4935 Southfront Road, Suite F, Livermore, CA 94550

---

## Mexico

### Headquarters

Festo Pneumatic, S.A.  
Av. Ceylán 3, Col. Tequesquahuac  
54020 Tlalnepantla, Edo. de México  
Call: 011 52 [55] 53 21 66 00  
Fax: 011 52 [55] 53 21 66 65  
Email: [festo.mexico@mx.festo.com](mailto:festo.mexico@mx.festo.com)  
[www.festo.com/mx](http://www.festo.com/mx)



## Canada

### Headquarters

Festo Inc.  
5300 Explorer Drive  
Mississauga, Ontario L4W 5G4  
Call: 1.905.624.9000  
Fax: 1.905.624.9001  
Email: [info.ca@ca.festo.com](mailto:info.ca@ca.festo.com)  
[www.festo.com/ca](http://www.festo.com/ca)



---

## Festo Worldwide

Argentina Australia Austria Belarus Belgium Brazil Bulgaria Canada Chile China Colombia Croatia Czech Republic Denmark  
Estonia Finland France Germany Great Britain Greece Hong Kong Hungary India Indonesia Iran Ireland Israel Italy Japan  
Latvia Lithuania Malaysia Mexico Netherlands New Zealand Norway Peru Philippines Poland Romania Russia Serbia Singapore  
Slovakia Slovenia South Africa South Korea Spain Sweden Switzerland Taiwan Thailand Turkey Ukraine United States Venezuela

[www.festo.com](http://www.festo.com)