Type codes

001	Series
NEBP	Connecting cable
002	Connection technology left, field device side
M16	M16
003	Cable outlet left
W	Angled
004	Number of pins/wires on the left
6	6
005	Cable characteristic
К	Standard

006	Cable length [m]	
2	2	
007	Connection technology right, controller side	
M9	M9	
008	Plug	
W	Angled	
009	Number of pins/wires on the right	
5	5	

Datasheet

Connecting cable NEBP-M16W6

- Connecting cable
- Pre-assembled at both ends
- For connecting measuring modules CPX-CMIX or proportional directional control valves VPWP to displacement encoders MME
- Cable lengths 2 m



General technical data	
Cable designation	Via accessories

Technical data – Electrical connection 1			
Function	Field device side		
Connection type	Socket		
Cable outlet	Angled		
Design	Round		
Connection technology	M16x0.75		
Number of pins/wires	6		
Assigned pins/wires	4		
Type of mounting	Screw-type lock		

Technical data – Electrical connection 2				
Function	Controller side			
Connection type	Plug			
Cable outlet	Angled/straight			
Design	Round			
Connection technology	M9x0.5			
Number of pins/wires	5			
Assigned pins/wires	4			
Type of mounting	Screw-type lock			

Technical data – Electrics				
Operating voltage range	[V DC]	0 30		
Surge resistance	[kV]	0.5		
Current rating at 40°C	[A]	3		
Note on current rating at 40°C		2.3 A for 0.34 mm ²		
		3.6 A for 0.49 mm ²		
Pollution degree		1		
Additional functions		Product-specific pin allocation		

Datasheet

Technical data – Cable

Cable diameter	[mm]	5.5				
Cable composition	[mm ²]	2x0.25 + 2x0.34 + 0.49				
		Shielded				
Nominal conductor cross section	[mm ²]	0.25 0.34 0.49				
Cable characteristic		Suitable for use with energy chains				
Bending radius, flexible cable	[mm]	≥75				
installation						
Test conditions, cable		Test conditions on request				

Materials	
Housing	TPE-U(PUR)
Housing colour	Black
Screw-type lock	Brass, nickel-plated
Pin contacts	Bronze, gold-plated
	Gold-plated brass
Cable sheath	TPE-U(PUR)
Cable sheath colour	Light grey
Insulating sheath	TPE-U(PUR)
Note on materials	RoHS-compliant
LABS (PWIS) conformity	VDMA24364-B2-L

Operating and environmental conditions				
Ambient temperature [°C]	−20 +70			
Ambient temperature with flexible [°C] cable installation	-5 +70			
Degree of protection	IP65			
	IP67			
Note on degree of protection	In mounted state			
Corrosion resistance class CRC ¹⁾	1			
CE marking (see declaration of conformity) ²⁾	To EU RoHS Directive			
UKCA marking (see declaration of conformity) ²⁾	To UK RoHS regulations			

¹⁾ Corrosion resistance class CRC 1 to Festo standard FN 940070

Low corrosion stress. Dry internal application or transport and storage protection. Also applies to parts behind covers, in the non-visible interior area, or parts that are covered in the application (e.g. drive trunnions).


²⁾ For information about the area of use, see the EC declaration of conformity at: www.festo.com/catalogue/... → Support/Downloads.

If the devices are subject to usage restrictions in residential, commercial or light-industrial environments, further measures for the reduction of the emitted interference may be necessary.

Datasheet

Circuitry (socket/plug view)						
Electrical connection 1	Pin	Wire colour ¹⁾	Pin	Electrical connection 2		
	1	BN	5			
6	2	WH	4	3		
5 1	3	n.c.	_	+		
0002	4	n.c.	-	(+ +)4		
	5	YE	1	1++5		
	6	GN	3			
	n.c.	GY	2			

1) According to IEC 757



Ordering data				
Electrical connection	Cable length	Weight	Part no.	Туре
	[m]	[g]		
Angled socket M16x0.75 – angled plug M9x0.5	2	160	575898	NEBP-M16W6-K-2-M9W5

Ordering data – Accessories						
			Part no.	Туре		
	Inscription labels for attaching to a cable with diameter 5 8 mm	11x20 mm	33361	KM-BZ		