

Technical data

- Main catalogue
on CD-ROM
or
- www.festo.com

Solenoid valves MZH, Micro pneumatic; MYH, Mini pneumatic

Product range overview



Function	Version	Type	Nominal flow rate [l/min]	Pneumatic connection	Operating voltage [V DC]
3/2-way valves	Solenoid valve – Micro pneumatic				
		MZH-3-0,4...	4.0	0.4 mm	24
		MZH-3-...	80	M3	
				1.5 mm	
	MOZH-3-...	80	M3		
			1.5 mm		
	Solenoid valve – Mini pneumatic				
		MYH-3-0,9...	20	0.9 mm	24
		MYH-3-...	190	M5	
				2.3 mm	
MOYH-3-...		170	M5		
	2.3 mm				

Function	Version	Type	Nominal flow rate [l/min]	Pneumatic connection	Operating voltage [V DC]
5/2-way valves	Solenoid valve – Micro pneumatic				
		MZH-5/2...	80	M3	24
				1.5 mm	
	Solenoid valve – Mini pneumatic				
		MYH-5/2...	190	M5	24
			180	2.3 mm	
	Double solenoid valve – Micro pneumatic				
		JMZH-5/2...	80	M3	24
				1.5 mm	
	Double solenoid valve – Mini pneumatic				
	JMYH-5/2...	190	M5	24	
		180	2.3 mm		

Function	Version	Type	Nominal flow rate [l/min]	Pneumatic connection	Operating voltage [V DC]
5/3-way valves	Solenoid valve – Micro pneumatic				
		MZH-5/3G...	40	M3	24
				1.5 mm	
		MZH-5/E...	40	M3	
				1.5 mm	
	Solenoid valve – Mini pneumatic				
		MYH-5/3G...	130	M5	24
			125	2.3 mm	
MYH-5/E...		130	M5		
		125	2.3 mm		

Solenoid valves MZH, Micro pneumatic; MYH, Mini pneumatic

Product range overview

Type	Semi in-line valve	Sub-base valve	Normal position		Type of pilot control		→ Page
			Closed	Open	Direct	Piloted	
Solenoid valve – Micro pneumatic							
MZH-3-0,4...	-	■	-	-	■	-	2 / 3.5-4
MZH-3-...	■	-	■	-	-	■	2 / 3.5-4
	-	■					
MOZH-3-...	■	-	-	■	-	■	2 / 3.5-4
	-	■					
Solenoid valve – Mini pneumatic							
MZH-3-0,4...	-	■	-	-	■	-	2 / 3.5-5
MZH-3-...	■	-	■	-	-	■	2 / 3.5-5
	-	■					
MOZH-3-...	■	-	-	■	-	■	2 / 3.5-5
	-	■					

Type	Semi in-line valve	Sub-base valve	Type of pilot control		→ Page
			Direct	Piloted	
Solenoid valve – Micro pneumatic					
MZH-5/2...	■	-	-	■	2 / 3.5-4
	-	■			
Solenoid valve – Mini pneumatic					
MYH-5/2...	■	-	-	■	2 / 3.5-5
	-	■			
Double solenoid valve – Micro pneumatic					
JMZH-5/2...	■	-	-	■	2 / 3.5-4
	-	■			
Double solenoid valve – Mini pneumatic					
JMYH-5/2...	■	-	-	■	2 / 3.5-5
	-	■			

Type	Semi in-line valve	Sub-base valve	Type of pilot control		→ Page
			Direct	Piloted	
Solenoid valve – Micro pneumatic					
MZH-5/3G...	■	-	-	■	2 / 3.5-4
	-	■			
MZH-5/E...	■	-	-	■	2 / 3.5-4
	-	■			
Solenoid valve – Mini pneumatic					
MYH-5/3G...	■	-	-	■	2 / 3.5-5
	-	■			
MYH-5/E...	■	-	-	■	2 / 3.5-5
	-	■			

Application-optimised directional control valves
Micro/Mini Pneumatics

Solenoid valves MZH, Micro pneumatic

Ordering data



Micro pneumatic					
Circuit symbol	Description	Semi in-line valve	Sub-base valve	Part No.	Type
3/2-way valves					
	Type of pilot control: direct Moulded-in cable, 0.3 m	-	■	30 210	MZH-3-04-K
	Type of pilot control: direct Switching status display with LED	-	■	30 217	MZH-3-0,4-LED
	Normally closed	■	-	30 192	MZH-M3-L-LED
	Type of pilot control: piloted	-	■	30 218	MZH-3-1,5-L-LED
	Switching status display with LED				
	Normally open	■	-	30 193	MOZH-3-M3-LED
	Type of pilot control: piloted	-	■	30 219	MOZH-3-1,5-L-LED
	Switching status display with LED				
5/2-way valves					
	Type of pilot control: piloted	■	-	30 194	MZH-5/2-M3-L-LED
	Switching status display with LED	-	■	30 195	MZH-5/2-1,5-L-LED
5/2-way valves – Double solenoid valves					
	Type of pilot control: piloted	■	-	30 195	JMZH-5/2-M3-L-LED
	Switching status display with LED	-	■	30 221	JMZH-5/2-1,5-L-LED
5/3-way valves					
	Normally closed	■	-	30 196	MZH-5/2G-M3-L-LED
	Type of pilot control: piloted	-	■	30 222	MZH-5/2G-1,5-L-LED
	Switching status display with LED				
	Normally exhausted	■	-	30 197	MZH-5/2E-M3-L-LED
	Type of pilot control: piloted	-	■	30 223	MZH-5/2E-1,5-L-LED
	Switching status display with LED				

Solenoid valves MYH, Mini pneumatic












Ordering data

Mini pneumatic					
Circuit symbol	Description	Semi in-line valve	Sub-base valve	Part No.	Type
3/2-way valves					
	Type of pilot control: direct Switching status display with LED	–	■	34 300	MYH-3-0,9-LED
	Normally closed Type of pilot control: piloted Switching status display with LED	■	–	34 307	MYH-3-M5-L-LED
		–	■	34 301	MYH-3-2,3-L-LED
	Normally open Type of pilot control: piloted Switching status display with LED	■	–	34 308	MOYH-3-M5-L-LED
		–	■	34 302	MOYH-3-2,3-L-LED
5/2-way valves					
	Type of pilot control: piloted Switching status display with LED	■	–	34 309	MYH-5/2-M5-L-LED
		–	■	34 303	MYH-5/2-2,3-L-LED
5/2-way valves – Double solenoid valves					
	Type of pilot control: piloted Switching status display with LED	■	–	34 310	JMYH-5/2-M5-L-LED
		–	■	34 304	JMYH-5/2-2,3-L-LED
5/3-way valves					
	Normally closed Type of pilot control: piloted Switching status display with LED	■	–	34 311	MYH-5/3G-M5-L-LED
		–	■	34 305	MYH-5/3G-2,3-L-LED
	Normally exhausted Type of pilot control: piloted Switching status display with LED	■	–	34 312	MYH-5/3E-M5-L-LED
		–	■	34 306	MYH-5/3E-2,3-L-LED

Solenoid valves MZH, Micro pneumatic

Accessories












Ordering data				
Designation	Brief description	Part No.	Type	
Sub-base, ports on side				
	for 3/2-way valves	Type of pilot control: direct	34 350	AS-MZ-3-M3
		Type of pilot control: piloted	34 351	AS-MZ-3-M5
	for 5/2- and 5/3-way valves		34 352	AS-MZ-5-M5
Manifold for 3/2-way sub-base valves; type of pilot control: direct				
	for 2 valves		30 224	PRMZ-3-M3-2
	for 4 valves		30 226	PRMZ-3-M3-4
	for 6 valves		30 228	PRMZ-3-M3-6
	for 8 valves		30 230	PRMZ-3-M3-8
	for 10 valves		30 232	PRMZ-3-M3-10
Blanking plate for unused positions, 3/2-way				
			32 607	PRMZB-3
Manifold for 3/2-, 5/2- and 5/3-way semi in-line valves; type of pilot control: piloted				
	for 2 valves		30 233	PRMZ-5-M3-2
	for 4 valves		30 235	PRMZ-5-M3-4
	for 6 valves		30 237	PRMZ-5-M3-6
	for 8 valves		30 239	PRMZ-5-M3-8
	for 10 valves		30 241	PRMZ-5-M3-10
Manifold for 3/2-, 5/2- and 5/3-way sub-base valves; type of pilot control: piloted				
	for 2 valves		30 242	PRMZ-5-M5-2
	for 4 valves		30 244	PRMZ-5-M5-4
	for 6 valves		30 246	PRMZ-5-M5-6
	for 8 valves		30 248	PRMZ-5-M5-8
	for 10 valves		30 250	PRMZ-5-M5-10
Blanking plate for unused positions, 5/2- and 5/3-way				
			33 008	PRMZB-5
Plug socket with cable				
	24 V DC, cable length 0.5 m		34 347	KMY-1-24-0,5
	24 V DC, cable length 2.5 m		30 446	KMYZ-1-24-2,5
	24 V DC, cable length 5 m		30 447	KMYZ-1-24-5
	24 V DC, cable length 15 m		193 454	KMYZ-1-24-15
Plug socket				
	for MY and MZ valves		34 345	MSSD-MY
	Crimp connectors (10 pcs.)		34 346	MSSD-MY-C
				

Solenoid valves MYH, Mini pneumatic

Accessories

FESTO

Ordering data			
Designation	Brief description	Part No.	Type
Sub-base, ports on side			
	for 3/2-way valves	Type of pilot control: direct	34 313 AS-MY-3-M3
		Type of pilot control: piloted	34 314 AS-MY-3-1/8
	for 5/2- and 5/3-way valves		34 315 AS-MZ-5-1/8
Manifold for 3/2-way sub-base valves; type of pilot control: direct			
	for 2 valves		30 316 PRMY-3-M5-2
	for 4 valves		30 318 PRMY-3-M5-4
	for 6 valves		30 320 PRMY-3-M5-6
	for 8 valves		30 322 PRMY-3-M5-8
	for 10 valves		30 324 PRMY-3-M5-10
Blanking plate for unused positions, 3/2-way			
		34 343	PRMYB-3
Manifold for 3/2-, 5/2- and 5/3-way semi in-line valves; type of pilot control: piloted			
	for 2 valves		34 325 PRS-M5-2
	for 4 valves		34 327 PRS-M5-4
	for 6 valves		34 329 PRS-M5-6
	for 8 valves		34 331 PRS-M5-8
	for 10 valves		34 333 PRS-M5-10
Manifold for 3/2-, 5/2- and 5/3-way sub-base valves; type of pilot control: piloted			
	for 2 valves		34 334 PRMY-5-1/8-2
	for 4 valves		34 336 PRMY-5-1/8-4
	for 6 valves		34 338 PRMY-5-1/8-6
	for 8 valves		34 340 PRMY-5-1/8-8
	for 10 valves		34 342 PRMY-5-1/8-10
Blanking plate for unused positions, 5/2- and 5/3-way			
		34 344	PRMYB-5
Plug socket with cable			
	24 V DC, cable length 0.5 m		34 347 KMY-1-24-0,5
	24 V DC, cable length 2.5 m		30 446 KMYZ-1-24-2,5
	24 V DC, cable length 5 m		30 447 KMYZ-1-24-5
	24 V DC, cable length 15 m		193 454 KMYZ-1-24-15
Plug socket			
 	for MY and MZ valves		34 345 MSSD-MY
	Crimp connectors (10 pcs.)		34 346 MSSD-MY-C

Product Range and Company Overview

A Complete Suite of Automation Services

Our experienced engineers provide complete support at every stage of your development process, including: conceptualization, analysis, engineering, design, assembly, documentation, validation, and production.



Custom Automation Components
Complete custom engineered solutions



Custom Control Cabinets
Comprehensive engineering support and on-site services



Complete Systems
Shipment, stocking and storage services

The Broadest Range of Automation Components

With a comprehensive line of more than 30,000 automation components, Festo is capable of solving the most complex automation requirements.



Electromechanical
Electromechanical actuators, motors, controllers & drives



Pneumatics
Pneumatic linear and rotary actuators, valves, and air supply



PLCs and I/O Devices
PLC's, operator interfaces, sensors and I/O devices

Supporting Advanced Automation... As No One Else Can!

Festo is a leading global manufacturer of pneumatic and electromechanical systems, components and controls for industrial automation, with more than 12,000 employees in 56 national headquarters serving more than 180 countries. For more than 80 years, Festo has continuously elevated the state of manufacturing with innovations and optimized motion control solutions that deliver higher performing, more profitable automated manufacturing and processing equipment. Our dedication to the advancement of automation extends beyond technology to the education and development of current and future automation and robotics designers with simulation tools, teaching programs, and on-site services.

Quality Assurance, ISO 9001 and ISO 14001 Certifications

Festo Corporation is committed to supply all Festo products and services that will meet or exceed our customers' requirements in product quality, delivery, customer service and satisfaction.

To meet this commitment, we strive to ensure a consistent, integrated, and systematic approach to management that will meet or exceed the requirements of the ISO 9001 standard for Quality Management and the ISO 14001 standard for Environmental Management.



© Copyright 2008, Festo Corporation. While every effort is made to ensure that all dimensions and specifications are correct, Festo cannot guarantee that publications are completely free of any error, in particular typing or printing errors. Accordingly, Festo cannot be held responsible for the same. For Liability and Warranty conditions, refer to our "Terms and Conditions of Sale", available from your local Festo office. All rights reserved. No part of this publication may be reproduced, distributed, or transmitted in any form or by any means, electronic, mechanical, photocopying or otherwise, without the prior written permission of Festo. All technical data subject to change according to technical update.



Printed on recycled paper at New Horizon Graphic, Inc., FSC certified as an environmentally friendly printing plant.

Festo North America

United States

Customer Resource Center
502 Earth City Expy., Suite 125
Earth City, MO 63045

For ordering assistance, or to find
your nearest Festo Distributor,

Call: 1.800.99.FESTO

Fax: 1.800.96.FESTO

Email: customer.service@us.festo.com

For technical support,

Call: 1.866.GO.FESTO

Fax: 1.800.96.FESTO

Email: product.support@us.festo.com

Headquarters

Festo Corporation
395 Moreland Road
P.O. Box 18023
Hauppauge, NY 11788
www.festo.com/us

Sales Offices

Appleton

N. 922 Tower View Drive, Suite N
Greenville, WI 54942

Boston

120 Presidential Way, Suite 330
Woburn, MA 01801

Chicago

1441 East Business Center Drive
Mt. Prospect, IL 60056

Dallas

1825 Lakeway Drive, Suite 600
Lewisville, TX 75057

Detroit - Automotive Engineering Center

2601 Cambridge Court, Suite 320
Auburn Hills, MI 48326

New York

395 Moreland Road
Hauppauge, NY 11788

Silicon Valley

4935 Southfront Road, Suite F
Livermore, CA 94550

Design and Manufacturing Operations



East: 395 Moreland Road, Hauppauge, NY 11788



Central: 1441 East Business Center Drive, Mt. Prospect, IL 60056



West: 4935 Southfront Road, Suite F, Livermore, CA 94550

Mexico

Headquarters

Festo Pneumatic, S.A.
Av. Ceylán 3, Col. Tequesquahuac
54020 Tlalnepantla, Edo. de México
Call: 011 52 [55] 53 21 66 00
Fax: 011 52 [55] 53 21 66 65
Email: festo.mexico@mx.festo.com
www.festo.com/mx



Canada

Headquarters

Festo Inc.
5300 Explorer Drive
Mississauga, Ontario L4W 5G4
Call: 1.905.624.9000
Fax: 1.905.624.9001
Email: info.ca@ca.festo.com
www.festo.com/ca



Festo Worldwide

Argentina Australia Austria Belarus Belgium Brazil Bulgaria Canada Chile China Colombia Croatia Czech Republic Denmark
Estonia Finland France Germany Great Britain Greece Hong Kong Hungary India Indonesia Iran Ireland Israel Italy Japan
Latvia Lithuania Malaysia Mexico Netherlands New Zealand Norway Peru Philippines Poland Romania Russia Serbia Singapore
Slovakia Slovenia South Africa South Korea Spain Sweden Switzerland Taiwan Thailand Turkey Ukraine United States Venezuela

www.festo.com