





Solenoid Coils MSF/MSN1

Solenoid coils MSF/MSN1

Product range overview

Design	Type	For valve series										→ Page/ Internet	
		MFH	MOFH	JMFH	JMFDH	MFXMH	NVF3	MUFH	MN1H	JMN1H	JMN1DH		
F solenoid coil													
	MSF	■	■	■	■	■	■	■	■	-	-	-	4
F solenoid coil for explosive atmospheres (with ATEX certification)													
	MSF...-EX	■	■	■	■	■	■	■	■	-	-	-	6
N1 solenoid coil													
	MSN1 ¹⁾	-	-	-	-	-	-	-	-	■	■	■	9

1) Free of copper, PTFE and silicone

-  - Note
 ATEX certification is only effective in combination with other ATEX-certified components.
 → www.festo.com

Solenoid coils MSF/MSN1

Selection aid



Solenoid valves and corresponding solenoid coils												
Valve family	Valve type	Solenoid coil										
		D	E	EB	F	N1	N2	V	Y	Z	ZB	ZC
ISO 15 407-1	MN2H, JMN2H, JMN2DH	-	-	-	-	-	■	-	-	-	-	-
ISO 5599-1	MN1H, JMN1H, JMN1DH	-	-	-	-	■	-	-	-	-	-	-
	MFH, JMFH, JMFHDH	-	-	-	■	-	-	-	-	-	-	-
	MDH, JMDH	■	-	-	-	-	-	-	-	-	-	-
	MEBH, JMEBH, JMEBDH	-	-	■	-	-	-	-	-	-	-	-
Namur	NVF3, MFXMH	-	-	-	■	-	-	-	-	-	-	-
	MN1H	-	-	-	-	■	-	-	-	-	-	-
Compact Performance	CPE10-M1BH, CPE14-M1BH	-	-	-	-	-	-	-	-	-	-	■
	CPE18, CPE24	-	-	■	-	-	-	-	-	-	-	-
Tiger 2000	MFH, JMFH	-	-	-	■	-	-	-	-	-	-	-
	MVH, JMVH	-	-	-	-	-	-	■	-	-	-	-
Tiger Classic	MFH, MOFH, JMFH, JMFHDH	-	-	-	■	-	-	-	-	-	-	
Midi Pneumatic	MEBH, MOEBH, JMEBH	-	-	■	-	-	-	-	-	-	-	-
	MEH, MOEH, JMEH	-	■	-	-	-	-	-	-	-	-	-
Directly actuated solenoid valves	MZBH, MOZBH	-	-	-	-	-	-	-	-	-	■	-
	MEBH, MOEBH	-	-	■	-	-	-	-	-	-	-	-
	MVH, MOVH	-	-	-	-	-	-	■	-	-	-	-
	MDH, MODH	■	-	-	-	-	-	-	-	-	-	-
Fast-switching valves	MH2, MH3	-	-	-	-	-	-	-	-	-	-	■
Micro/Mini Pneumatic	MZH, MOZH, JMZH	-	-	-	-	-	-	-	-	■	-	-
	MYH, MOYH, JMYH	-	-	-	-	-	-	-	■	-	-	-
M5 Compact	MUFH	-	-	-	■	-	-	-	-	-	-	

Solenoid coils MSF/MSN1

Type codes

Solenoid coils



		MSFG	–	24DC	–	OD
Type						
MSFG	F solenoid coil, for D.C. voltage					
MSFW	F solenoid coil, for A.C. voltage					
MSN1G	N1 solenoid coil, for D.C. voltage					
MSN1W	N1 solenoid coil, for A.C. voltage					
Operating voltage						
12DC	12 V DC					
24DC	24 V DC					
24AC/12DC	12 V DC/24 V AC					
24DC/42AC	24 V DC/42 V AC					
42DC	42 V DC					
24AC	24 V AC					
48AC	48 V AC					
110AC	110 V AC					
230AC	230 V AC					
240AC	240 V AC					
Scope of delivery						
OD	Without plug socket					

Solenoid coils, explosion-proof


		MSFG	–	24DC	–	K5	–	M	–	EX
Type										
MSFG	F solenoid coil, for D.C. voltage									
MSFW	F solenoid coil, for A.C. voltage									
Operating voltage										
24	24 V DC									
24DC	24 V DC									
24AC	24 V AC									
24-50/60	24 V AC, 50/60 Hz									
110AC	110 V AC									
110-50/60	110 V AC, 50/60 Hz									
230AC	230 V AC									
230-50/60	230 V AC, 50/60 Hz									
Cable length										
	1 m									
K5	5 m									
KX	Upon request									
ATEX symbol										
	II 3 GD EEx nA II T1 30°C X									
M	II 2 GD EExm II T5									
Explosion protection										
EX	Explosion-proof to EN 50 028									

Solenoid coils MSF

Technical data

-  Voltage
12 ... 42 V DC
24 ... 240 V AC
-  Temperature range
-5 ... +40 °C

- In compliance with VDE regulation 0580, insulation class F
- Can be replaced without interrupting the pneumatic circuit
- Low power consumption and temperature rise



General technical data		
	D.C. voltage	A.C. voltage
Min. pick-up time	[ms]	10
Type of mounting	Via knurled nut	
Mounting position	Any (can be rotated 360° on the armature tube)	
Product weight	[g]	65
Materials	Steel, copper, duroplastic	

Electrical data		
	D.C. voltage	A.C. voltage
Electrical connection	Plug vanes for plug sockets MSSD-F, KMF	
Operating voltage	D.C. voltage [V DC]	12, 24, 42, 48
	A.C. voltage [V AC]	-
		24, 42, 48, 110, 230, 240
Perm. voltage fluctuation	[%]	±10
Coil characteristics	D.C. voltage 12 V [W]	4.1
	24, 42 V [W]	4.5
	A.C. voltage [VA]	-
		Pull: 7.5 Hold: 6
Duty cycle	[%]	100
Power factor cosφ		0.7
Protection class to EN 60529	IP65 with plug socket	
CE symbol		73/23/EEC (low voltage)


Operating and environmental conditions		
Ambient temperature	[°C]	-5 ... +40
Temperature of medium	[°C]	-10 ... +60

Solenoid coils MSF


Technical data


FESTO






Dimensions Download CAD data → www.festo.com



1 Retaining nut (min. tightening torque 100 Ncm, max. 150 Ncm)
2 Solenoid coil (can be rotated 360° on the armature tube)
3 Plug vanes for plug sockets MSSD-F, KMF

 Note
 Can only be operated on aluminium valves with the following valve body dimensions:
 ≥ 26 x 16 x 14 mm



Ordering data					
	Description	Operating voltage		Part No.	Type
		V DC	V AC (50 ... 60 Hz)		
	Solenoid coil, without plug socket, with spring washer and knurled nut	12	–	34 410	MSFG-12DC-OD
		24	42	34 411	MSFG-24DC/42AC-OD
		42	–	34 413	MSFG-42DC-OD
		–	24	34 415	MSFW-24AC-OD
		–	48	34 418	MSFW-48AC-OD
		–	110	34 420	MSFW-110AC-OD
		–	230	34 422	MSFW-230AC-OD
		–	240	34 424	MSFW-240AC-OD

Ordering data – Accessories					
	Description	Cable length [m]	Switching status display with LED	Part No.	Type
Plug socket Technical data → Internet: mssd					
	–	–	–	34 431	MSSD-F
Plug socket with insulation displacement technology Technical data → Internet: mssd					
	–	–	–	192 746	MSSD-F-S-M16
Plug socket with cable Technical data → Internet: kmf-1					
	24 V DC	2.5	■	30 935	KMF-1-24DC-2,5-LED
		5	■	30 937	KMF-1-24DC-5-LED
		10	■	193 458	KMF-1-24DC-10-LED
	Up to 240 V	2.5	–	30 936	KMF-1-230AC-2,5
		5	–	30 938	KMF-1-230AC-5
Illuminating seal Technical data → Internet: mf-ld					
	12 ... 24 V DC	–	■	19 143	MF-LD-12-24DC
	230 V DC/V AC	–	■	19 144	MF-LD-230AC
Inscription label Technical data → Internet: kmc					
	Scope of delivery: 35 pieces in each frame	–	–	33 362	KMC/F/V-BZ-35X



Solenoid coils MSF...-EX

Technical data

FESTO

-  Voltage
24 V DC
24 ... 240 V AC
-  Temperature range
-5 ... +40 °C

- In compliance with ATEX directive
- In compliance with VDE regulation 0580, insulation class F
- With cable or plug
- Can be replaced without interrupting the pneumatic circuit
- Manifold mounting permissible (minimum clearance from coil to coil 5 mm)



General technical data			D.C. voltage	A.C. voltage
Min. pick-up time	[ms]		12	
Type of mounting			Via knurled nut	
Mounting position			Any (can be rotated 360° on the armature tube)	
Product weight	Cable version	[g]	175	170
	Plug version	[g]	65	55
Materials	Cable version		Steel, copper, aluminium, epoxy resin	
	Plug version		Steel, copper, duroplastic	

Operating and environmental conditions		
ATEX ambient temperature	[°C]	-5 ... +40
Ambient temperature	[°C]	-5 ... +40
Temperature of medium	[°C]	-5 ... +40

Electrical data – cable version			D.C. voltage	A.C. voltage	
ATEX symbol			II 2 GD EEx m II T5		
Electrical connection			Moulded-in cable 3x0.75 mm², 1 m or 5 m long (other lengths upon request)		
Operating voltage	D.C. voltage	[V DC]	24	-	
	A.C. voltage	[V AC]	-	24, 110, 120, 220, 230, 240	
Perm. voltage fluctuation	[%]		±10		
Coil characteristics	D.C. voltage	24 V	[W]	4.5	-
		A.C. voltage	24 V	[VA]	-
		110 V	[VA]	-	50 Hz, pull: 4.84 60 Hz, pull: 4.32
		230 V	[VA]	-	50 Hz, pull: 6.2 60 Hz, pull: 5.6
Duty cycle	[%]		100		
Min. pick-up time	[ms]		12		
Power factor cosφ			-	0.7	
Protection class to EN 60 529			IP65		
CE symbol			94/9/EC (ATEX)	94/9/EC (ATEX) 73/23/EEC (low voltage)	


Solenoid coils MSF...EX

Technical data

FESTO

Dimensions – cable version

Download CAD data → www.festo.com



- 1 Solenoid coil
(can be rotated 360° on the armature tube)
- 2 Protective earth connection
- 3 Heat resistant rubber tubing,
∅ 6,1 ... 7,9 mm
- 4 Retaining nut
(min. tightening torque 100 Ncm,
max. 150 Ncm)
- 5 Cable length

-  - Note


Can only be operated on aluminium valves with the following valve body dimensions:
≥ 25 x 25 x 17 mm

Electrical data – plug version

			D.C. voltage	A.C. voltage
ATEX symbol			II 3 GD EEx nA II T1 30°C X	
Electrical connection			Plug vanes for plug sockets MSSD-F, KMF	
Operating voltage	D.C. voltage	[V DC]	24	–
	A.C. voltage	[V AC]	–	24, 110, 120, 220, 230, 240
Perm. voltage fluctuation		[%]	±10	
Coil characteristics	D.C. voltage	24 V [W]	4.5	–
	A.C. voltage	24 V [VA]	–	Pull: 7 Hold: 6
		110 V [VA]	–	Pull: 7 Hold: 6
		230 V [VA]	–	Pull: 7 Hold: 6
Duty cycle		[%]	100	
Min. pick-up time		[ms]	12	
Power factor cosφ			–	0.7
Protection class to EN 60 529			IP65 with plug socket	
CE symbol			94/9/EC (ATEX)	94/9/EC (ATEX) 73/23/EEC (lower voltage)

Dimensions – plug version

Download CAD data → www.festo.com



- 1 Retaining nut
(min. tightening torque 100 Ncm,
max. 150 Ncm)



- 2 Solenoid coil
(can be rotated 360° on the armature tube)
- 3 Plug vanes for plug sockets
MSSD-F, KMF


-  - Note

Can only be operated on aluminium valves with the following valve body dimensions:
≥ 26 x 16 x 14 mm

Solenoid coils MSF...EX



Technical data

Ordering data						
	Description	Operating voltage		Cable length [m]	Part No.	Type
		V DC	V AC			
ATEX symbol: II 2 GD EEx m II T5						
	Solenoid coil with cable, explosion-proof, moulded-in cable, with spring washer and knurled nut	24	–	1	535 619	MSFG-24DC-M-EX
		–	–	5	535 621	MSFG-24DC-K5-M-EX
		–	24	1	535 623	MSFW-24AC-M-EX
		–	110	1	535 622	MSFW-110AC-M-EX
		–	–	5	535 624	MSFW-110AC-K5-M-EX
		–	230	1	535 620	MSFW-230AC-M-EX
		–	–	5	535 625	MSFW-230AC-K5-M-EX
		24	–	Upon request	538 215	MSFG-24DC-KX-M-EX
		–	24	–	538 216	MSFW-24AC-KX-M-EX
		–	110	–	538 218	MSFW-110AC-KX-M-EX
–	230	–	538 217	MSFW-230AC-KX-M-EX		
ATEX symbol: II 3 GD EEx nA II T130°C X						
	Solenoid coil with plug vanes, explosion-proof, without plug socket, with spring washer and knurled nut	24	–	–	536 931	MSFG-24-EX
		–	24	–	536 932	MSFW-24-50/60-EX
		–	110	–	536 933	MSFW-110-50/60-EX
		–	230	–	536 934	MSFW-230-50/60-EX

Ordering data – Accessories					
	Description	Cable length [m]	Switching status display with LED	Part No.	Type
Plug socket Technical data → Internet: mssd					
	–	–	–	34 431	MSSD-F

Solenoid coils MSN1

Technical data

-  Voltage
24 V DC
24 ... 230 V AC
-  Temperature range
-10 ... +50 °C

- In compliance with VDE regulation 0580, insulation class F
- Can be replaced without interrupting the pneumatic circuit
- Connection pattern to DIN EN 175 301-803, type A
- Free of copper, PTFE and silicone



General technical data	
Min. pick-up time	[ms] 10
Type of mounting	Via mounting clip
Mounting position	Any (can be rotated 360° on the armature tube)
Product weight	[g] 80
Materials	Steel, copper, thermoplastic
Note on materials	Free of copper, PTFE and silicone

Electrical data						
		D.C. voltage	D.C. voltage/ A.C. voltage	A.C. voltage		
Operating voltage	D.C. voltage [V DC]	24	12	-	-	
	A.C. voltage [V AC]	-	24 (50 ... 60 Hz)	110 (50 ... 60 Hz), 120 (60 Hz)	230 (50 ... 60 Hz)	
Perm. voltage fluctuation	[%]	-15 ... +10	50 Hz: ±10 60 Hz: -10 ... +20	±10		
Coil characteristics	D.C. voltage [W]	2.5	5	-	-	
	A.C. voltage, 50 Hz [VA]	-	Pull: 7.5 Hold: 5.0	Pull: 7.5 Hold: 5.0	Pull: 7.5 Hold: 5.0	
	A.C. voltage, 60 Hz [VA]	-	Pull: 5.0 Hold: 3.7	Pull: 5.0 Hold: 3.7	Pull: 5.0 Hold: 3.7	
Duty cycle	[%]	100				
Power factor cosφ		-	-	0.7		
Electrical connection		Plug vanes with connection pattern to DIN EN 175 301-803, type A				
Protection class to EN 60 529		IP65 with plug socket				
CE symbol		-	-	73/23/EEC (low voltage)		

Ambient conditions		
Ambient temperature	[°C]	-10 ... +50
Temperature of medium	[°C]	-10 ... +50


Solenoid coils MSN1

Technical data

FESTO

Dimensions

Download CAD data → www.festo.com



- 1 Solenoid coil
(can be rotated 360° on the
armature tube)
- 2 Securing clip

- 3 Plug vanes with connection
pattern to
DIN EN 175 301-803,
type A

Ordering data



	Description	Operating voltage		Part No.	Type
		V DC	V AC		
	Solenoid coil, without plug socket, with mounting clip, connection pattern to DIN EN 175 301-803, type A	24	–	123 060	MSN1G-24DC-OD
		12	24	170 152	MSN1W-24AC/12DC-OD
		–	110/120	123 061	MSN1W-110AC-OD
		–	230	123 062	MSN1W-230AC-OD

Ordering data – Accessories

	Description	Cable length [m]	Switching status display with LED	Part No.	Type
Plug socket Technical data → Internet: mssd					
	–	–	–	34 583	MSSD-C
Plug socket with insulation displacement technology Technical data → Internet: mssd					
	–	–	–	192 748	MSSD-C-S-M16
Plug socket with cable Technical data → Internet: kmc-1					
	24 V DC	2.5	■	30 931	KMC-1-24DC-2,5-LED
		5	■	30 933	KMC-1-24DC-5-LED
		10	■	193 459	KMC-1-24DC-10-LED
	Up to 240 V	2.5	–	30 932	KMC-1-230AC-2,5
		5	–	30 934	KMC-1-230AC-5
Illuminating seal Technical data → Internet: mc-ld					
	12 ... 24 V DC	–	■	19 145	MC-LD-12-24DC
	230 V DC/V AC	–	■	19 146	MC-LD-230AC
Inscription label Technical data → Internet: kmc					
	Scope of delivery: 35 pieces in each frame	–	–	33 362	KMC/F/V-BZ-35X

Solenoid coils MD-2/MH-2

Technical data

-  Voltage
24 V DC
110, 230 V AC
-  Temperature range
-20 ... +50 °C
- Can be replaced without interrupting the pneumatic circuit
- Connection pattern to DIN EN 175301-803, type A



General technical data			
Type	MD-2 (system 8)	MH-2 (system 13)	
Min. starting time	[ms]	-	12
Type of mounting		Via knurled nut	Via lock nut
Max. tightening torque of fitting	[Nm]	0.5	2
Mounting position		Any	Any
Product weight	[g]	110	150
Materials	Solenoid coil	Steel, copper, duroplastic	
	Winding	Copper	
Paint-wetting impairment substances criterion		PWIS-free	Contains paint-wetting impairment substances
Switching position display		No	

Electrical data			
Type	MD-2 (system 8)	MH-2 (system 13)	
Operating voltage	DC voltage [V DC]	24	24
	AC voltage [V AC]	110, 230	110, 230
Perm. voltage fluctuations	[%]	±10	±10
Coil characteristics	24 V DC [W]	6.8	7.6
	110 V AC, 50/60 Hz [VA]	Pull: 14.5 Hold: 10.5	14
	230 V AC, 50/60 Hz [VA]	Pull: 14.5 Hold: 10.5	14
Duty cycle	[%]	100	
Power factor cosφ	110 V AC	0.7	0.7
	230 V AC	0.7	0.7
Electrical connection		Plug vanes with connection pattern to DIN EN 175301-803, type A	
Protection class to EN 60529		IP65 with plug socket	
CE mark	110 V AC, 230 V AC	In accordance with EU Low Voltage Directive	

Ambient conditions		
Ambient temperature	[°C]	-20 ... +50

Solenoid coils MD-2/MH-2

Technical data

FESTO

Download CAD data → www.festo.com

MD-2 (system 8)	MH-2 (system 13)
<p>1 Knurled nut M8x0.75</p> <p>2 Plug pattern to EN 175301-803, type A</p> <p>3 Solenoid coil</p>	<p>1 Hex nut G1/8</p> <p>2 Plug pattern to EN 175301-803, type A</p> <p>3 Solenoid coil</p>

Ordering data					
	Description	Operating voltage		Part No.	Type
		V DC	V AC		
MD					
	Solenoid coil, without plug socket, connection pattern to DIN EN 175301-803, type A	24	–	549 903	MD-2-24VDC-PA
		–	110	549 904	MD-2-110VAC-PA
		–	230	549 905	MD-2-230VAC-PA
MH					
	Solenoid coil, without plug socket, connection pattern to DIN EN 175301-803, type A	24	–	549 906	MH-2-24VDC-PA
		–	110	549 907	MH-2-110VAC-PA
		–	230	549 908	MH-2-230VAC-PA

Ordering data – Accessories			
	Description	Part No.	Type
Plug socket			
	3-pin, square design MSF	550 067	MSSD-N

Product Range and Company Overview

A Complete Suite of Automation Services

Our experienced engineers provide complete support at every stage of your development process, including: conceptualization, analysis, engineering, design, assembly, documentation, validation, and production.



Custom Automation Components
Complete custom engineered solutions



Custom Control Cabinets
Comprehensive engineering support and on-site services



Complete Systems
Shipment, stocking and storage services

The Broadest Range of Automation Components

With a comprehensive line of more than 30,000 automation components, Festo is capable of solving the most complex automation requirements.



Electromechanical
Electromechanical actuators, motors, controllers & drives



Pneumatics
Pneumatic linear and rotary actuators, valves, and air supply



PLCs and I/O Devices
PLC's, operator interfaces, sensors and I/O devices

Supporting Advanced Automation... As No One Else Can!

Festo is a leading global manufacturer of pneumatic and electromechanical systems, components and controls for industrial automation, with more than 12,000 employees in 56 national headquarters serving more than 180 countries. For more than 80 years, Festo has continuously elevated the state of manufacturing with innovations and optimized motion control solutions that deliver higher performing, more profitable automated manufacturing and processing equipment. Our dedication to the advancement of automation extends beyond technology to the education and development of current and future automation and robotics designers with simulation tools, teaching programs, and on-site services.

Quality Assurance, ISO 9001 and ISO 14001 Certifications

Festo Corporation is committed to supply all Festo products and services that will meet or exceed our customers' requirements in product quality, delivery, customer service and satisfaction.

To meet this commitment, we strive to ensure a consistent, integrated, and systematic approach to management that will meet or exceed the requirements of the ISO 9001 standard for Quality Management and the ISO 14001 standard for Environmental Management.



© Copyright 2008, Festo Corporation. While every effort is made to ensure that all dimensions and specifications are correct, Festo cannot guarantee that publications are completely free of any error, in particular typing or printing errors. Accordingly, Festo cannot be held responsible for the same. For Liability and Warranty conditions, refer to our "Terms and Conditions of Sale", available from your local Festo office. All rights reserved. No part of this publication may be reproduced, distributed, or transmitted in any form or by any means, electronic, mechanical, photocopying or otherwise, without the prior written permission of Festo. All technical data subject to change according to technical update.



Printed on recycled paper at New Horizon Graphic, Inc., FSC certified as an environmentally friendly printing plant.

Festo North America

United States

Customer Resource Center
502 Earth City Expy., Suite 125
Earth City, MO 63045

For ordering assistance, or to find
your nearest Festo Distributor,

Call: 1.800.99.FESTO

Fax: 1.800.96.FESTO

Email: customer.service@us.festo.com

For technical support,

Call: 1.866.GO.FESTO

Fax: 1.800.96.FESTO

Email: product.support@us.festo.com

Headquarters

Festo Corporation
395 Moreland Road
P.O. Box 18023
Hauppauge, NY 11788
www.festo.com/us

Sales Offices

Appleton

N. 922 Tower View Drive, Suite N
Greenville, WI 54942

Boston

120 Presidential Way, Suite 330
Woburn, MA 01801

Chicago

1441 East Business Center Drive
Mt. Prospect, IL 60056

Dallas

1825 Lakeway Drive, Suite 600
Lewisville, TX 75057

Detroit - Automotive Engineering Center

2601 Cambridge Court, Suite 320
Auburn Hills, MI 48326

New York

395 Moreland Road
Hauppauge, NY 11788

Silicon Valley

4935 Southfront Road, Suite F
Livermore, CA 94550

Design and Manufacturing Operations



East: 395 Moreland Road, Hauppauge, NY 11788



Central: 1441 East Business Center Drive, Mt. Prospect, IL 60056



West: 4935 Southfront Road, Suite F, Livermore, CA 94550

Mexico

Headquarters

Festo Pneumatic, S.A.
Av. Ceylán 3, Col. Tequesquahuac
54020 Tlalnepantla, Edo. de México
Call: 011 52 [55] 53 21 66 00
Fax: 011 52 [55] 53 21 66 65
Email: festo.mexico@mx.festo.com
www.festo.com/mx



Canada

Headquarters

Festo Inc.
5300 Explorer Drive
Mississauga, Ontario L4W 5G4
Call: 1.905.624.9000
Fax: 1.905.624.9001
Email: info.ca@ca.festo.com
www.festo.com/ca



Festo Worldwide

Argentina Australia Austria Belarus Belgium Brazil Bulgaria Canada Chile China Colombia Croatia Czech Republic Denmark
Estonia Finland France Germany Great Britain Greece Hong Kong Hungary India Indonesia Iran Ireland Israel Italy Japan
Latvia Lithuania Malaysia Mexico Netherlands New Zealand Norway Peru Philippines Poland Romania Russia Serbia Singapore
Slovakia Slovenia South Africa South Korea Spain Sweden Switzerland Taiwan Thailand Turkey Ukraine United States Venezuela

www.festo.com