

Non-Contact Pneumatic Sensors

Gap (Air Barrier) Sensor

Gap Sensor Type SFL-6




The air gap sensor is used for non-contact sensing of objects of a maximum width of 0.19 in / 5 mm. The device may also be used for metering and monitoring as well as detecting objects. To reduce air consumption, install a needle valve in air supply line P if the pressure at P is greater than 45 psi / 3 bar.


The recommended operating pressure is 1.5 to 15 psi / 0.1 to 1 bar at connection P (black).

Signal pressure should not exceed the maximum allowable pressure for the downstream amplifier.

The air gap sensor is supplied with compressed air at connection P (black). If passage through the gap is clear, a signal is present at port A (yellow). If an object disrupts the flow of air in the gap, there will be no signal at port A.



P = Supply
A = Outlet



① Barbed fitting for 3/16 in / 3 mm tubing, connection P black, connection A yellow

SW = wrench size, mm

Mounting Accessories:

Flange Mount



Order Number 5129

FBN-8/10

Foot Mount

Order Number 5123


HBN-8/10




Dimensions:

- a 0.42 in / 10.6 mm
- b 0.24 in / 6.2 mm
- c 0.12 in / 3.1 mm
- d 0.20 in / 5 mm
- e 0.24 in / 6 mm
- f 0.55 in / 14 mm
- g 0.16 in / 4 mm
- h 1.58 in / 40 mm
- i 1.90 in / 48 mm
- j 0.99 in / 25 mm
- k 0.18 in / 4.5 mm
- l 1.18 in / 30 mm
- m 0.12 in / 3 mm
- n 0.48 in / 12.1 mm
- o 0.43 in / 11 mm
- p 0.63 in / 16 mm
- q 0.39 in / 10 mm
- r 1.38 in / 35 mm

Signal Pressure at A versus Supply Pressure at P



Air Consumption versus Supply Pressure at P



Order Number	Part No./Type	4439 SFL-6
Medium		Compressed air (filtered, unlubricated)
Mounting		M12 x 1 threaded with 2 mounting nuts
Mounting Hole Diameter		0.5 in / 12.5 mm
Connection		Barbed fitting for 3/16 in / 3 mm tubing
Orifice Size		0.10 in / 2.5 mm
Supply Pressure Range at P*		0 to 120 psi / 0 to 8 bar
Signal Pressure Range at A		See graph, above
Air Consumption at 1.5 psi / 0.1 bar		0.05 SCFM / 1.5 l/min (see graph, above)
Max. Nozzle Range		0.24 in / 6 mm
Ambient Temperature		-40 to 212°F / -40 to 100°C†
Design		Nozzle, no moving parts
Material		Brass
Weight		0.073 lb / 0.033 kg

* 14 to 140°F / -10 to 60°C

† Depending on tubing used

Festo - Your Partner in Automation



1 Festo Inc.
5300 Explorer Drive
Mississauga, ON L4W 5G4
Canada

Festo Customer Interaction Center
Tel: 1 877 463 3786
Fax: 1 877 393 3786
Email: customer.service.ca@festo.com



2 Festo Pneumatic
Av. Ceylán 3,
Col. Tequesquináhuac
54020 Tlalnepantla,
Estado de México

Multinational Contact Center
01 800 337 8669
ventas.mexico@festo.com




3 Festo Corporation
1377 Motor Parkway
Suite 310
Islandia, NY 11749

Festo Customer Interaction Center
1 800 993 3786
1 800 963 3786
customer.service.us@festo.com



4 Regional Service Center
7777 Columbia Road
Mason, OH 45040

Connect with us

www.festo.com/socialmedia



www.festo.com

Subject to change