
# **Control blocks for two-hand start ZSB**

# **FESTO**



#### Key features

#### **Function**


The pneumatic control block for twohand start ZSB is used where the operator is exposed to a risk of accident during manual operation, e.g. when triggering compressed air cylinders or equipment where both hands must be out of the danger zone during start-up. The ZSB only switches when both inputs  $1_1$  and  $1_2$  of the ZSB are supplied simultaneously, i.e. within max. 0.5 seconds, by two external 3/2-way pushbutton valves. There is an output signal at connection 2. If both pushbutton valves are activat-

ed, outlet 2 is pressurised.

If one or both pushbutton valves are released, the flow is immediately interrupted and outlet 2 is no longer pressurised. The system exhausts from 2 to 3.

The pneumatic control block for twohand start is a safety device as defined in the EU Machinery Directive. It conforms to category 1, PL "c" in accordance with EN ISO 13849-1 and to Type III A in accordance with EN 574.

#### Sample circuit




· 🖥 - Note

When installing the two manual pushbuttons for actuating the control block for two-hand start, make sure that the protective effect cannot easily be overridden, e.g. through actuation with a hand and elbow etc. If necessary, attach an additional guard plate to the manual pushbuttons!

- [1] Front panel valve with pushbutton actuator, e.g. SV-3, T-30
- [2] Control chain
- [3] Pressure sequence valve, e.g. VD-3-PK-3
- [4] Service unit components, e.g. MS or D series


# Peripherals overview



Access	Accessories				
		Brief description	→ Page/Internet		
[1]	Front panel valve SV	Poppet valve with quick snap-in coupling for actuator attachments	6		
[2]	Pushbutton actuator T	Actuator attachment for front panel valve SV	6		
[3]	Mushroom pushbutton P	Actuator attachment for front panel valve SV	6		
[4]	Silencer U	For noise reduction at the exhaust port	6		
[5]	Pressure sequence valve VD	For securing the minimum pressure of 4 bar required for operation	6		
[6]	Service unit combination  • D series	For compressed air preparation	lfr*k*		
	MS series		msb		

## Control blocks for two-hand start ZSB

## Datasheet





Safety data		
Safety function	Two-hand control in accordance with EN ISO 12100	
Performance Level (PL)	Two-hand control: category 1, PL c in accordance with EN ISO 13849-1	
Tried-and-tested component	Yes	
Standard approval	Type III A according to EN574	
Certificate-issuing authority	IFA 1201046	
CE marking (see declaration of conformity)	To EU Machinery Directive	
Shock resistance	Shock test with severity level 2 in accordance with FN 942017-5 and EN 60068-2-27	

General technical data		
Pneumatic connection		G1/8
Nominal width [mm]		4
Actuation type		Pneumatic
Design		Poppet valve with spring return
Type of mounting		Via through-hole
		Via female thread
Mounting position		Any
Standard nominal flow rate [l/min]		50
Product weight [g]		420

Operating and environmental conditions			
Operating pressure [MPa		0.4 0.8	
	[bar]	48	
	[psi]	58 116	
Operating medium		Compressed air to ISO 8573-1:2010 [7:4:4]	
Note on the operating/pilot medium		Lubricated operation possible (in which case lubricated operation will always be required)	
Ambient temperature [°C]		0 +60	
Corrosion resistance class CRC <sup>1)</sup>		1	
CE marking (see declaration of conformity) <sup>2)</sup>		To EU Machinery Directive	
UKCA marking (see declaration of conformity) <sup>2)</sup>		To UK regulations for machines	
Certificate-issuing authority		IFA 1201046	
		Intertek UK-MCR-0080	

- 1) More information www.festo.com/x/topic/crc
- 2) More information: www.festo.com/catalogue/zsb  $\rightarrow$  Support/Downloads.

Materials		
Housing Anodised wrought aluminium alloy		
Cover	Die-cast aluminium	
Seals	NBR	
Note on materials	RoHS-compliant RoHS-compliant	
LABS (PWIS) conformity	VDMA24364-B1/B2-L	

Part no.


576656

Type **ZSB-1/8-B** 

# Datasheet

Ordering data

Control block for two-hand start



# Accessories

Ordering data – Fro	ont panel valve SV				Datasheets → Internet: sv
	Pneumatic connection	Valve function	Operating pressure [bar]	Part no.	Туре
	M5	3/2-way valve, closed, monostable	-0.95 8	6817	SV-3-M5
ordering data – Pu	shbutton actuator T   Colour	Installation diameter [mm]		Part no.	Datasheets → Internet:
		Installation diameter [mm]			Type
	Black	22.5		9289	T-22-SW
		30.5		9291	T-30-SW
ordering data – Mi	ushroom pushbutton P				Datasheets → Internet: p
	Colour	Installation diameter [mm]		Part no.	Туре
	Black	22.5		9293	P-22-SW
$(\bigcirc)$					
		30.5	30.5		
GD.					
					<u> </u>
Ordering data – Pr	essure sequence valve VD	I	1	I	Datasheets → Internet: vo
	Pneumatic connection	Valve function	Operating pressure [bar]	Part no.	Туре
A	PK-3	3/2-way valve, normally closed,	1.8 8	9270	VD-3-PK-3
		adjustable switching pressure			
ordering data – Sil	oncor II				Datasheets → Internet: ı
riuciilig uata – 311	Pneumatic connection	Material		Part no.	Type Type
	G1/8	PE		2307	U-1/8
	01/0	Die-cast aluminium		6841	U-1/8-B
		5.5 cust atammam		0041	5 2/5 5

## **Festo - Your Partner in Automation**





1 Festo Inc.

5300 Explorer Drive Mississauga, ON L4W 5G4 Canada

#### **Festo Customer Interaction Center**

Tel: 1877 463 3786 Fax: 1877 393 3786



2 Festo Pneumatic

Av. Ceylán 3, Col. Tequesquináhuac 54020 Tlalnepantla, Estado de México

#### **Multinational Contact Center**

01 800 337 8669



3 Festo Corporation

1377 Motor Parkway Suite 310 Islandia, NY 11749



**Regional Service Center** 

7777 Columbia Road Mason, OH 45040

#### **Festo Customer Interaction Center**

1 800 993 3786 1 800 963 3786 customer.service.us@festo.com

Connect with us







