

Electrical connection technology, for fieldbus connection

Technical data – FBS-SUB-9-BU-...-B

- Fieldbus socket with 9-pin Sub-D connection
- Variants for different fieldbus systems
- Position of DIL switches can be read externally
- Easy to assemble



General technical data		
Type of mounting	2 M3x20 screws	
Cable connector	Pg9	
Electrical connection	9-pin socket, Sub-D	
Permissible cable diameter [mm]	5 ... 10	
Protection class to EN 60529	IP65/67 (assembled)	
Material	Housing	Reinforced polyamide
	Seal	Nitrile rubber
	Union nut	Nickel-plated brass
	Screws	Steel
Material note	RoHS-compliant	
Height/length/width [mm]	62/61/20	

Operating and environmental conditions	
Ambient temperature [°C]	0 ... +50
Storage temperature [°C]	-20 ... +70
Relative air humidity	95%, non-condensing


Ordering data					
	Additional functions	Fieldbus interface	Product weight [g]	Type	Part No.
	Integrated RBST bridge	INTERBUS nodes CPX and CPV 1x 5 spring-loaded terminals	60	FBS-SUB-9-BU-IB-B	532218
	–	DeviceNet/Can CPX and CPV 2x 5 spring-loaded terminals BUS In - BUS Out looped through	60	FBS-SUB-9-BU-2x5POL-B	532219

Electrical connection technology, for fieldbus connection

Technical data – FBS-SUB-9-BU-...-B

Dimensions

Download CAD Data → www.festo.com/us/cad



- 1 Sub-D socket, 9-pin
- 2 Cable connector, polymer, Pg9
- 3 Cable connector, metal, Pg9

Festo - Your Partner in Automation



1 Festo Inc.
5300 Explorer Drive
Mississauga, ON L4W 5G4
Canada

Festo Customer Interaction Center
Tel: 1 877 463 3786
Fax: 1 877 393 3786
Email: customer.service.ca@festo.com



2 Festo Pneumatic
Av. Ceylán 3,
Col. Tequesquináhuac
54020 Tlalnepantla,
Estado de México

Multinational Contact Center
01 800 337 8669
ventas.mexico@festo.com



3 Festo Corporation
1377 Motor Parkway
Suite 310
Islandia, NY 11749

Festo Customer Interaction Center
1 800 993 3786
1 800 963 3786
customer.service.us@festo.com



4 Regional Service Center
7777 Columbia Road
Mason, OH 45040

Connect with us



www.festo.com/socialmedia



www.festo.com

Subject to change