

# Three-point gripper HGDD-40-A-G1

Part number: 1163041

FESTO



## Data sheet

Feature	Value
Size	40
Stroke per gripper jaws	6 mm
Max. replacement accuracy	0.2 mm
Max. angular gripper jaw backlash ax, ay	0.1 deg
Max. gripper jaw backlash Sz	0.05 mm
Rotationally symmetrical	0.2 mm
Repetition accuracy, gripper	0.03 mm
Number of gripper jaws	3
Mounting position	optional
Mode of operation	Double-acting
Gripper function	3-point
Gripper force back-up	During opening
Design	Wedge-shaped drive Force pilot operated motion sequence
Position detection	Via proximity switch
Operating pressure	4 bar...8 bar
Operating pressure of blocked air	0 bar...0.5 bar
Max. operating frequency of gripper	4 Hz
Min. opening time at 0.6 MPa (6 bar, 87 psi)	70 ms
Min. closing time at 0.6 MPa (6 bar, 87 psi)	211 ms
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Degree of protection	IP65
Ambient temperature	5 °C...60 °C
Mass moment of inertia	5.01 kgcm <sup>2</sup>
Max. force on gripper jaw Fz static	700 N
Max. torque at gripper Mx static	25 Nm
Max. torque at gripper My static	18 Nm
Max. torque at gripper Mz static	20 Nm

Feature	Value
Lubrication interval for guide components	5 MioCyc
Max. mass per external gripper finger	130 g
Product weight	775 g
Type of mounting	Via through-hole and dowel pin Via female thread and dowel pin Either:
Pneumatic connection, blocked air	M3
Pneumatic connection	M5
Note on materials	RoHS-compliant
Material cover cap	High-alloy stainless steel
Material housing	Smooth-anodised wrought aluminium alloy
Material gripper jaws	Hardened steel