

Angle gripper DHWS-10-A

Part number: 1310177

FESTO



Data sheet

Feature	Value
Size	10
Max. replacement accuracy	0.2 mm
Max. opening angle	40 deg
Rotationally symmetrical	0.2 mm
Repetition accuracy, gripper	0.04 mm
Number of gripper jaws	2
Mounting position	optional
Mode of operation	Double-acting
Gripper function	Angle
Design	Lever
Position detection	Via Hall sensor
Operating pressure	2 bar...8 bar
Max. operating frequency of gripper	4 Hz
Min. opening time at 0.6 MPa (6 bar, 87 psi)	10 ms
Min. closing time at 0.6 MPa (6 bar, 87 psi)	22 ms
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Suitability for the production of Li-ion batteries	Metals with more than 5% by mass of copper are excluded from use. Exceptions are printed circuit boards, cables, electrical plug connectors and coils
Ambient temperature	5 °C...60 °C
Total gripping torque at 0.6 MPa (6 bar, 87 psi), opening	43 Ncm
Total gripper torque, closing, 0.6 MPa (6 bar, 87 psi)	30 Ncm
Mass moment of inertia	0.03 kgcm ²
Max. force on gripper jaw Fz static	25 N
Max. torque at gripper Mx static	0.6 Nm
Max. torque at gripper My static	0.6 Nm
Max. torque at gripper Mz static	0.6 Nm
Product weight	40 g

Feature	Value
Type of mounting	Via female thread and centring sleeve Via through-hole and centring sleeve Either:
Pneumatic connection	M3
Note on materials	RoHS-compliant
Material cover cap	PA
Material housing	Wrought aluminium alloy Hard anodised
Material gripper jaws	High-alloy steel