


Rotary lifting module EHMB-25-200

Part number: 1095934

FESTO



Data sheet

Feature	Value
Drive pinion diameter	8 mm
Working stroke	0 mm...200 mm
Size	25
Rotation angle	Infinite
Toothed-belt pitch	3 mm
Mounting position	optional
Type of gear unit	Toothed belt gear unit
Design	Electromechanical rotary/lifting module With toothed belt
Gear unit ratio	4:1
Position detection	Via inductive sensors
Max. drive output speed	300 rpm
Max. drive input speed	1200 rpm
Max. speed	1.5 m/s
Repetition accuracy	±0.03°
Sound pressure level	51 dB(A)
Information on the sound pressure level	With covering: 56 [dB (A)]
LABS (PWIS) conformity	VDMA24364 zone III
Ambient temperature	-10 °C...60 °C
Mass moment of inertia	5000 kgcm²
Max. output torque	8.8 Nm
Max. drive torque	2.2 Nm
Max. feed force Fx	480 N
Frictional torque independent of load	0.18 Nm
Reference value effective load, horizontal	5000 g
Reference value effective load, vertical	5000 g
Product weight	3620 g
Moving mass	1942 g
Material drive shaft	Steel High-alloy stainless steel
Note on materials	RoHS-compliant
Material flange	Anodised wrought aluminium alloy

Feature	Value
Material cover	Wrought aluminium alloy Anodised
Material housing	Wrought aluminium alloy Anodised
Material retaining	Wrought aluminium alloy, anodised
Material retaining bracket	Anodised wrought aluminium alloy
Material toothed belt	Polychloroprene with glass fibre