

Fitting NPCK-C-D-G14-K10

Part number: 1489336

FESTO



Data sheet

Feature	Value
Nominal size	6.1 mm
Type of seal on screwed plug	Sealing ring
Mounting position	optional
Design	Straight design
Operating pressure complete temperature range	-0.095 MPa...1.2 MPa -0.95 bar...12 bar -13.775 psi...174 psi
Note on operating pressure	Water: max. 0.6 MPa at 0 - 85 °C Water vapour: 0 – 0.15 MPa, 0 – 1.5 bar, 0 – 22 psi
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-] Water (liquid, ice-free) Water vapour
Note on operating and pilot medium	Lubricated operation possible
Corrosion resistance class CRC	4 - Very high corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Suitability for the production of Li-ion batteries	Product corresponds to the internal product definition from Festo for use in battery production:Metals with more than 1% by mass of copper, zinc or nickel are excluded from use.The exceptions are nickel in steel, chemically nickel-plated surfaces, printed circuit boards, cables, electrical plug connectors and coils
Suitable for use with food	See supplementary material information
Note on temperature of medium	Water vapour: max. 120 °C
Degree of protection	IP69K
Ambient temperature	-20 °C...120 °C
Note on ambient temperature	The NPCK can be used from -40 to 60 °C when using suitable tubing and observing the maximum operating pressure of the tube.
Nominal torque	20 Nm
Note on the nominal tightening torque	7 Nm +/- 10% for NPCK on MPA-C
Tolerance for nominal tightening torque	± 10%
Product weight	32.9 g
Pneumatic connection, port 1	Male thread G1/4
Pneumatic connection, port 2	For tubing outside diameter of 10 mm
Material union nut	High-alloy stainless steel
Material screwed plug	High-alloy stainless steel

Feature	Value
Note on materials	RoHS-compliant
Material sealing ring	PEEK