


Intermediate-position module DADM-EP-G6-16

Part number: 1478121

FESTO



Data sheet

Feature	Value
Size	16
Mounting position	optional
Design	Force pilot operated motion sequence
Position detection	Via proximity switch
Operating pressure	3 bar...6 bar
Max. impact speed	0.8 m/s
Max. swivel time	150 ms
Repetition accuracy	±0.02 mm
Operating medium	Compressed air to ISO 8573-1:2010 [7:~:]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	0 °C...60 °C
Max. stop force	1100 N
Product weight	340 g
Type of mounting	Via through-hole and centring sleeve
Pneumatic connection	M5
Note on materials	RoHS-compliant
Material seals	PU
Material housing	Wrought aluminium alloy
Material lever	High-alloy stainless steel