


Compact cylinder ADVUL-100- -P-A-S6

Part number: 156219

FESTO



Data sheet

| Feature | Value |
|--|--|
| Stroke | 1 mm...400 mm |
| Piston diameter | 100 mm |
| Cushioning | Elastic cushioning rings/plates at both ends |
| Mounting position | optional |
| Design | Piston Piston rod |
| Position detection | Via proximity switch |
| Variants | Heat-resistant seals max. 120°C |
| Protection against torque/guide | Guide rod with yoke |
| Operating pressure | 0.1 MPa...1 MPa 1 bar...10 bar |
| Mode of operation | Double-acting |
| Operating medium | Compressed air to ISO 8573-1:2010 [7:4:4] |
| Note on operating and pilot medium | Lubricated operation possible (in which case lubricated operation will always be required) |
| Corrosion resistance class CRC | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Ambient temperature | 0 °C...120 °C |
| Impact energy in end positions | 1 J |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), return stroke | 4418 N |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke | 4712 N |
| Type of mounting | Either: With through-hole With accessories |
| Pneumatic connection | G1/4 |
| Material collar screws | Galvanised steel |
| Material cover | Wrought aluminium alloy |
| Material dynamic seals | FPM |
| Material piston rod | High-alloy steel |
| Material cylinder barrel | Wrought aluminium alloy |