


# Compact cylinder AEVU-63-15-A-P-A

Part number: 157011

**FESTO**



## Data sheet

| Feature                                                      | Value                                                                                      |
|--------------------------------------------------------------|--------------------------------------------------------------------------------------------|
| Stroke                                                       | 15 mm                                                                                      |
| Piston diameter                                              | 63 mm                                                                                      |
| Piston rod thread                                            | M12x1.25                                                                                   |
| Cushioning                                                   | Elastic cushioning rings/plates at both ends                                               |
| Mounting position                                            | optional                                                                                   |
| Mode of operation                                            | Pushing<br>Single-acting                                                                   |
| Piston-rod end                                               | Male thread                                                                                |
| Design                                                       | Piston<br>Piston rod                                                                       |
| Position detection                                           | Via proximity switch                                                                       |
| Variants                                                     | Piston rod at one end                                                                      |
| Operating pressure                                           | 0.06 MPa...1 MPa<br>0.6 bar...10 bar<br>8.7 psi...145 psi                                  |
| Operating medium                                             | Compressed air to ISO 8573-1:2010 [7:4:4]                                                  |
| Note on operating and pilot medium                           | Lubricated operation possible (in which case lubricated operation will always be required) |
| Corrosion resistance class CRC                               | 2 - Moderate corrosion stress                                                              |
| LABS (PWIS) conformity                                       | VDMA24364-B1/B2-L                                                                          |
| Ambient temperature                                          | -20 °C...80 °C                                                                             |
| Impact energy in end positions                               | 0.7 J                                                                                      |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke | 1799 N                                                                                     |
| Moving mass for 0 mm stroke                                  | 134 g                                                                                      |
| Additional moving mass per 10 mm stroke                      | 16 g                                                                                       |
| Basic weight for 0 mm stroke                                 | 1059 g                                                                                     |
| Additional weight per 10 mm stroke                           | 107 g                                                                                      |
| Type of mounting                                             | Either:<br>With through-hole<br>With accessories                                           |
| Pneumatic connection                                         | G1/8                                                                                       |
| Material collar screws                                       | Galvanised steel                                                                           |
| Material cover                                               | Wrought aluminium alloy                                                                    |

| Feature                  | Value                   |
|--------------------------|-------------------------|
| Material dynamic seals   | NBR<br>TPE-U(PU)        |
| Material piston rod      | High-alloy steel        |
| Material cylinder barrel | Wrought aluminium alloy |