



Flat cylinder DZH-5/8"- -PPV-A-S6

Part number: 157615

FESTO



Data sheet

Feature	Value
Stroke	0.04 in...8 in
Piston diameter	5/8"
Torsional backlash at piston rod +/-	3.1 deg
Cushioning	Pneumatic cushioning, adjustable at both ends
Mounting position	optional
Mode of operation	Double-acting
Design	Piston Piston rod
Position detection	Via proximity switch
Variants	Heat-resistant seals max. 120°C
Protection against torque/guide	Oval piston
Operating pressure	0.1 MPa...1 MPa 1 bar...10 bar
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-20 °C...120 °C
Cushioning length	14 mm
Max. torque for protection against torsion	0.5 Nm
Theoretical force at 0.6 MPa (6 bar, 87 psi), return stroke	104 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke	121 N
Additional moving mass per 10 mm stroke	23 g
Additional weight per 10 mm stroke	11 g
Basic weight for 0 mm stroke	140 g
Type of mounting	Either: Via female thread With accessories
Pneumatic connection	10-32 UNF-2B
Note on materials	RoHS-compliant
Material cover	Aluminium
Material seals	TPE-U(PU)

Feature	Value
Material housing	Aluminium
Material piston rod	High-alloy steel