

Compact cylinder AEVU-1"- -A-P-A

Part number: 160613



FESTO

For proximity sensing, piston-rod end with male thread.

Nut for piston rod thread is included.

This product is only available if ordered from the Festo Corporation, USA.

Products to be discontinued. Available until 2011.



Data sheet

Feature	Value
Stroke	0.2 ... 1 "
Cushioning	P: Flexible cushioning rings/plates at both ends
Mode of operation	single-acting pushing action
Piston-rod end	Male thread
Operating pressure	14.5 ... 145 Psi
Operating medium	Filtered compressed air
Corrosion resistance classification CRC	2
Ambient temperature	-4 ... 176 °F
Theoretical force at 6 bar, advance stroke	269 N
Moving mass with 0 mm stroke	26 g
Additional weight per 10 mm stroke	6 g
Basic weight for 0 mm stroke	180 g
Additional mass factor per 10 mm of stroke	15 g
Pneumatic connection	UNF10-32
Operating pressure [psi]	14.5 ... 145 psi
Materials information for cover	Wrought Aluminium alloy
Materials information for dynamic seals	TPE-U(PU) NBR
Materials information for piston rod	High alloy steel, non-corrosive
Materials information for cylinder barrel	Wrought Aluminium alloy