

# Compact cylinder AEVU-16-20-A-P-A

Part number: 156984

**FESTO**



## Data sheet

| Feature                                                      | Value                                                                                      |
|--------------------------------------------------------------|--------------------------------------------------------------------------------------------|
| Stroke                                                       | 20 mm                                                                                      |
| Piston diameter                                              | 16 mm                                                                                      |
| Piston rod thread                                            | M8                                                                                         |
| Cushioning                                                   | Elastic cushioning rings/plates at both ends                                               |
| Mounting position                                            | optional                                                                                   |
| Mode of operation                                            | Pushing<br>Single-acting                                                                   |
| Piston-rod end                                               | Male thread                                                                                |
| Design                                                       | Piston<br>Piston rod                                                                       |
| Position detection                                           | Via proximity switch                                                                       |
| Variants                                                     | Piston rod at one end                                                                      |
| Operating pressure                                           | 0.13 MPa...1 MPa<br>1.3 bar...10 bar<br>18.85 psi...145 psi                                |
| Operating medium                                             | Compressed air to ISO 8573-1:2010 [7:4:4]                                                  |
| Note on operating and pilot medium                           | Lubricated operation possible (in which case lubricated operation will always be required) |
| Corrosion resistance class CRC                               | 2 - Moderate corrosion stress                                                              |
| LABS (PWIS) conformity                                       | VDMA24364-B1/B2-L                                                                          |
| Ambient temperature                                          | -20 °C...80 °C                                                                             |
| Impact energy in end positions                               | 0.1 J                                                                                      |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke | 111 N                                                                                      |
| Moving mass for 0 mm stroke                                  | 12 g                                                                                       |
| Additional moving mass per 10 mm stroke                      | 4 g                                                                                        |
| Basic weight for 0 mm stroke                                 | 89 g                                                                                       |
| Additional weight per 10 mm stroke                           | 15 g                                                                                       |
| Type of mounting                                             | Either:<br>With through-hole<br>With accessories                                           |
| Pneumatic connection                                         | M5                                                                                         |
| Material collar screws                                       | High-alloy stainless steel                                                                 |
| Material cover                                               | Wrought aluminium alloy                                                                    |

| Feature                  | Value                      |
|--------------------------|----------------------------|
| Material dynamic seals   | NBR<br>TPE-U(PU)           |
| Material piston rod      | High-alloy stainless steel |
| Material cylinder barrel | Wrought aluminium alloy    |