

Compact cylinder AEVU-50-15-A-P-A

Part number: 157007

FESTO



Data sheet

Feature	Value
Stroke	15 mm
Piston diameter	50 mm
Cushioning	Elastic cushioning rings/plates at both ends
Mounting position	optional
Mode of operation	Pushing Single-acting
Piston-rod end	Male thread
Design	Piston Piston rod
Position detection	Via proximity switch
Variants	Piston rod at one end
Operating pressure	0.08 MPa...1 MPa 0.8 bar...10 bar 11.6 psi...145 psi
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-20 °C...80 °C
Impact energy in end positions	0.64 J
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke	1121 N
Moving mass for 0 mm stroke	112 g
Additional moving mass per 10 mm stroke	16 g
Basic weight for 0 mm stroke	560 g
Additional weight per 10 mm stroke	72 g
Type of mounting	With through-hole With accessories Either:
Pneumatic connection	G1/8
Material collar screws	Galvanised steel
Material cover	Wrought aluminium alloy
Material dynamic seals	NBR TPE-U(PU)

Feature	Value
Material piston rod	High-alloy steel
Material cylinder barrel	Wrought aluminium alloy