


Filter combination LFMBA-1-D-MAXI-A

Part number: 162673

FESTO



Data sheet

Feature	Value
Size	Maxi
Series	D
Mounting position	Vertical +/-5°
Grade of filtration	0.01 µm
Filter efficiency	99.9999 %
Condensate drain	Fully automatic
Design	Fibre filter
Max. condensate volume	80 ml
Bowl guard	Metal bowl guard
Operating pressure	1.5 bar...12 bar
Operating medium	Compressed air to ISO 8573-1:2010 [6:8:4] Inert gases
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Air purity class at output	Compressed air to ISO 8573-1:2010 [1:7:2] Inert gases
Media temperature	1.5 °C...60 °C
Residual oil content	0.01 mg/m³
Ambient temperature	-10 °C...60 °C
Product weight	2400 g
Type of mounting	In-line installation With accessories
Pneumatic connection, port 1	G1
Pneumatic connection, port 2	G1
Note on materials	RoHS-compliant
Material filter	Borosilicate fibre
Material housing	Die-cast zinc
Material bowl	PC