


Flat cylinder DZH-2"- -PPV-A

Part number: 16259

FESTO



Data sheet

Feature	Value
Stroke	0.04 in...40 in
Piston diameter	2"
Torsional backlash at piston rod +/-	0.45 deg
Cushioning	Pneumatic cushioning, adjustable at both ends
Mounting position	optional
Mode of operation	Double-acting
Design	Piston Piston rod
Position detection	Via proximity switch
Protection against torque/guide	Oval piston
Operating pressure	0.05 MPa...1 MPa 0.5 bar...10 bar
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-20 °C...80 °C
Cushioning length	23 mm
Max. torque for protection against torsion	1.7 Nm
Theoretical force at 0.6 MPa (6 bar, 87 psi), return stroke	989 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke	1178 N
Additional weight per 10 mm stroke	60 g
Basic weight for 0 mm stroke	1200 g
Type of mounting	Either: Via female thread With accessories
Pneumatic connection	1/4 NPT
Note on materials	RoHS-compliant
Material cover	Aluminium
Material seals	TPE-U(PU)
Material housing	Aluminium
Material piston rod	High-alloy steel

